


SIGN	DATE	DESCRIPTION	APPROVER
△	04/07'10	Add the 2P mark	RUNNER
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!			




Dimension

DIM A	N×5.0+0.10
DIM B	(N-1)×5.0

N=Number of poles

POLES	TOL
2p-6p	±0.15
7p-12p	±0.25
13p-16p	±0.35
17p-24p	±0.40



Material



- Item a Terminal body:Thermoplastic (UL94V-0)
- Item b Terminal body:Thermoplastic (UL94V-0)
- Item c Terminal lever:Thermoplastic (UL94V-0)
- Item d Wire guard:Stainless Steel
- Item e Female contact:PhBz (CuSn) Tin plated
- Item f With flange screw:Steel Zinc plating M2.5 solt "+/-" type

Electrical cULus



- Voltage rating:300V
- Current rating:10A
- Solid wire(AWG):12-26
- Stranded wire(AWG):12-26
- Wire strip length:9-10mm
- Withstanding Voltage:1.6KV
- Operating temperature:-40°C to +115°C
- Safety Approval: cULus

H4 xx 70 x D xxxx G

02 2 CONTACTS	0 Black	0000 Standard @ Logo	RoHS
03 3 CONTACTS	5 Green	000A Standard ANY Logo	Pb<40,000ppm
... ..	6 Blue	Any special item by customer request, please contact sales department.	
24 24 CONTACTS	8 Grey		



SECTION A-A



ANYTEK				CUSTOMER COPY			
ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATSOEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD							
TITLE		H4 5.0 Series hook on back side (With flange)					
PART NO.		H4xx70xDxxxxG		DWG NO.		8H40104	
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.		Tolerance	
		Runner 2010.04.07	Tony 2009.03.12			UNIT: mm	X. ±0.50
						SCALE: NONE	X.X ±0.30
						REVISION: C	X.XX ±0.10
				SHEET: 01/01		X* ±1*	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Amphenol:

<u>H402705D0000G</u>	<u>H403705D0000G</u>	<u>H404705D0000G</u>	<u>H405705D0000G</u>	<u>H406705D0000G</u>	<u>H407705D0000G</u>
<u>H408705D0000G</u>	<u>H409705D0000G</u>	<u>H410705D0000G</u>	<u>H411705D0000G</u>	<u>H412705D0000G</u>	<u>H413705D0000G</u>
<u>H414705D0000G</u>	<u>H415705D0000G</u>	<u>H416705D0000G</u>	<u>H417705D0000G</u>	<u>H418705D0000G</u>	<u>H419705D0000G</u>
<u>H420705D0000G</u>	<u>H421705D0000G</u>	<u>H422705D0000G</u>	<u>H423705D0000G</u>	<u>H424705D0000G</u>	