




CATALOGUE

Amphenol Group | Global Presence



**Sales, R&D, and
Manufacturing on
6 continents**

79% of workforce in
low-cost countries

- = MANUFACTURING OPERATIONS
- ▲ = SALES OFFICES
- ★ = HEADQUARTERS

AMERICAS

UNITED STATES
CANADA
MEXICO
BRAZIL
ARGENTINA

EUROPE

FRANCE
GERMANY
UNITED KINGDOM
IRELAND
THE NETHERLANDS
CZECH REPUBLIC
ESTONIA
SLOVAKIA
ITALY

SPAIN
SWEDEN
NORWAY
RUSSIA
TURKEY
SAUDI ARABIA
FINLAND
AUSTRIA

MIDDLE EAST & AFRICA

TUNISIA
SOUTH AFRICA
UNITED ARAB EMIRATES
ISRAEL

ASIA & PACIFIC

TAIWAN
CHINA
HONG KONG
JAPAN
KOREA
PHILIPPINES
MALAYSIA
SINGAPORE
INDIA
AUSTRALIA
VIETNAM

Amphenol LTW | Global Service



We listen to your needs.

Amphenol LTW Technology Co., Ltd. (Headquarter)

9F., No.657-12, Zhongzheng Rd., Xinzhuang Dist., New Taipei City 242, Taiwan
Telephone: +886-2-29085626 Fax: +886-2-29029787
www.amphenolltw.com

Shulin plant, Taiwan

No.10, Shutan St., Shulin Dist., New Taipei City 238, Taiwan

Kunshan plant, China

No. 62 Da Tung Road, Peng Lang Street, Kunshan City , Jiangsu Province, China
Telephone: +86-512-5761-0501
Fax: : +86-512-5761-0515

For further information, please contact :

Sales & Marketing Department | Email : sales@ltw-tech.com

Our Mission


Amphenol LTW is fully committed to contributing to a safer and greener environment toward an open and friendlier world. ALTW actively and proactively become the interconnects of choice for technologically advanced products with purposes such as:

- Generating power and energies from renewable sources
- Protecting, conserving, saving and better managing resources
- Warning and preventing natural disasters such earthquakes, tsunamis, landslides, flooding...
- Lighting up buildings, residences, streets and factories at lowest possible costs in the most efficiently and environmental friendly ways
- Detecting, monitoring and managing goods and people for seamless flow and exchanges around the world
- Enabling higher speed and broadband communications and telecommunications
- Producing higher yield of crops and maximizing the use of scarce "agricultural" lands
- Accelerating the proliferation of organic crops
- Delivering safe and quality food
- Preventing shortage of food and enabling the production of sufficient food
- Enabling higher productivities in farms while enhancing qualities of produces
- Allowing higher productivities and efficiencies in factories and industries
- Facilitating automation and reducing labor costs and risks
- Making biotechnologies a reality and common place in tomorrow's world
- Ensuring life-saving products available whenever and wherever they are much needed
- Facilitating the "rugged revolution" in mobile world

Amphenol LTW is the innovator and solution provider for products to be used harsh and rugged environments.

Create Company's Profile and
New Industry Orientation by
Innovation & Differentiation

Research Innovation
R&D Management
Technology Foundation



Our History

LTW Technology Co., Ltd, established in March 1993, is the innovator and solution provider for all products that are to be used in harsh and rugged environments indoor or outdoor.

In April 2010, Amphenol Corp (NYSE: APH) acquired LTW Technology ("ALTW") which become Amphenol LTW Technology Co., Ltd.

Amphenol LTW Technology is the leader in rugged and harsh environment interconnects with largest array of I/O and products ranging from IP65 to IP69K. ALTW continuously provides innovative products and solutions for an ever demanding environment with patents covering China, Taiwan, Japan, South Korea, Europe and North America, etc...

Together with our customers, ALTW participate and contribute to a better world, greener and safer environment.

LTW®



1993

Established

2000

Opened Kun Shan
Zhrengri
(KSZ)Electronics
in Kunshan, China



2002

LTW moved to
Shinjuang
City,Taipei.

2004

KSZ expanded plant
to 17,000 sqm.



2006

Established 2nd
Factory in Taipei
with CNC
Automatic Lathe &
Automation Center

Amphenol LTW



2008

Taiwan Small &
Medium Enterprise
Innovation Award

Innovation Research
Award

2010

LTW was acquired by
Amphenol Group in
April of 2010

Shortcut by Product Series

Circular Connector	Power Connector	M Series Sensor Connector	USB Connector
 - Screw Thread Type, Lock Bayonet Type or Push Lock Type - Receptacle, Receptacle with cable, Overmolded With Cable & Field Installable available - Options from 2 to 31 contacts, 2A to 20A - Various sizes, over 1000 items, plastic and metal - UV Resistant - IP65/66/67/68 waterproof mated or unmated - Operating temperature - Field installable: -20°C ~ 105°C - Receptacle: -40°C ~ 105°C - Receptacle with cable: -20°C ~ 80°C - Overmolded with Cable: -20°C ~ 80°C - Customizations are possible - Hybrid available  P 1-1	 - Screw Thread or Lock Bayonet Type (2 points & 3 points) - Receptacle, Overmolded With Cable & Field Installable available - Options from 2 to 7 contacts, 8A to 30A - Over 110 plastic items - UV Resistant - Operating temperature - Overmolded with Cable: -20°C ~ 80°C - Receptacle: -40°C ~ 105°C - Field installable: -40°C ~ 105°C - IP67/68 waterproof mated or unmated - Customizations are possible - Hybrid available - Safety locking available (25A & 30A) - Touch Safe (IP2X) available (25A & 30A)  P 2-1	 - Available in M8 (3P~5P & 8P); M12 (3P ~ 12 in A, B, D & X Codes); Mini 7/8" 5P - Compact and rugged design available in IP67/IP68 waterproof - Available in Stamped, Screw-In, PCB and Solder Contacts - Receptacle (M12 90° PCB), Field Installables & Molded With Cable available - Meets industry standards (IEC, NMEA2000, DeviceNet, EtherNet I/P, Profibus & ProfiNet) - Operating temperature - Field installable: -40°C ~ 105°C - Receptacle: -40°C ~ 105°C - Overmolded with Cable - PVC Cable: -20°C~80°C - PU Cable: -20°C~85°C - Hexagonal-Shaped Diecasted Screw Nuts for Cable Assy for easier Tool access - PVC, PUR Jackets available for cables (Sun, Oil Resistant & Flame rated) - UL/CSA Approval - Hybrid Available Upon Request  P 3-1	 - Screw Threaded or Lock Bayonet Type - USB A, USB B and Mini USB - IP67/IP68 mated and unmated waterproof - Receptacle, Overmolded With Cable available - UV Resistant - Operating temperature - Field installable: -20°C ~ 80°C - Overmolded with Cable: -20°C ~ 80°C - Receptacle - Nylon+GF: -40°C ~ 105°C - M-PPE: -40°C ~ 105°C - ABS: -20°C ~ 80°C - Receptacle with cable - Nylon+GF: -20°C ~ 105°C - ABS: -20°C ~ 80°C - Easy & simple connection structure - PnP – plug and play - Master/Slave framework  P 4-1
* Mini (A) - Size * Standard (B) - Size * Middle (C) - Size * Large (D) - Size * Macro (E) - Size * Others - Size	* 8A * 12A * 16A * 20A * 25A * 30A * 20A+2A	* M8 * M10.5 * M12 * Heavy Duty Shielded * M23	* USB 3.0 A Type * USB 2.0 A Type * USB 2.0 B Type * Mini USB 2.0 B Type

IEEE 1394 Connector	D-SUB Connector	DVI Connector	RJ Connector
			
• Receptacle, Overmolded With Cable & Field Installable available • Screw Thread Type • 0.5A • UV Resistant • Operating temperature ◉ Field installable: -20°C ~ 80°C ◉ Receptacle: -20°C ~ 80°C ◉ Overmolded with Cable: -20°C~80°C • IP67/68 Unmated	• Standard D-Sub (9/15/25/37 /50 contacts), High Density D-Sub (15/26/44/62/78 contacts) and Mixed Options Available • Receptacle, Overmolded With Cable & Field Installable available • Various Connection types, such as hand solder, wire wrap, straight and angled PCB, with and without boardlock, and flat cables • High Reliability for Harsh Environment • IP67/IP68 waterproof • Special Latches instead of thumb screws available • Operating temperature ◉ Field installable: -20°C ~ 105°C ◉ Overmolded with Cable: -20°C ~ 80°C ◉ Receptacle: -20°C~105°C	• DVI-D Single Link (DDS), DVI-I Single Link (DIS), DVI-D Dual Link (DDD) and DVI-I Dual Link (DID) available • Receptacle and Overmolded With Cable available • Screw Threaded Type • 0.5A • 19/23/25/29 contacts available • UV Resistant • Operating temperature ◉ Overmolded with Cable: -20°C ~ 80°C ◉ Receptacle: -20°C~105°C • IP67/68 waterproof	• Screw Thread or lock Bayonet Type • Receptacle, Overmolded With Cable & Field Installable available • Shielded & Unshielded versions • Fast connectivity Networking in Harsh environments • IDC, RJ Jack in 180 & 90 deg., Terminal Block and Cable terminated • Meets industry standards (ODVA, ProfiNet) • UV Resistant • Operating temperature ◉ Overmolded with Cable: -20°C ~ 80°C ◉ Receptacle: -40°C~105°C • IP67/IP68 mated and unmated
 P 5-1	 P 6-1	 P 7-1	 P 8-1
* IEEE 1394B	* Standard * High Density	* DVI-Single Link * DVI-Dual Link * DVI-D Single Link * DVI-D Dual Link	* Cat. 5e

SSL Solution Connector	LED Indicator	HDMI Connector	Sata Connector
 • For B-to-B, W-to-B, W-to-W • Available in 1P, 2P, 4P and 6P • Standard or IP67 • SMT Board Connector for PCB: FR4, MC, or Ceramic • With and without Mounting boardlock • With or Without Lock or Latch • Board Connectors in Right Angle, Straight, or Inverted • Horizontal or Vertical Connection or Disconnection • Overmolded Cable Straight or Right Angle • Operating temperature ◉ Receptacle: -40°C ~ 100°C • Natural white color for all connector housings and over-molding • UL recognized (UL approved upon request) • Lead Free and RoHS Compliant  P 9-1	 • LED lights for your device (Receptacle only) • Light color: red, blue, green, white, yellow and red/green • Plastic LED (Ø3mm) or metal LED (Ø3mm and Ø5mm) • Operating temperature ◉ Metal: -20°C ~ 105°C ◉ Plastic: -20°C ~ 85°C • IP67 Unmated  P 10-1	 • Receptacle (Jack) and Overmolded With Cable (Plug) available • Latch type for 90° PCB • 0.2A • Maximum cable length 5M • UV Resistant • Operating temperature ◉ Receptacle: -20°C ~ 80°C ◉ Overmolded with Cable: -20°C ~ 80°C • IP67 Unmated  P 11-1	 • Snap in with latch: insertion and extraction are easy and quick • Overmolded With Cable and PCB type (Socket) for SMD or DIP • Harpoon board lock or flat board lock • 1.6, 2.6, 3.2mm mounting board-lock available • SATA 2.6 • Available contacts : 7P • Current Capacity : 1.5A • Over-molded Wires Size : #26 • 15V DC • Black color for all connector housings and over-molding • UL recognized materials • Lead Free and RoHS Compliant • PCB thickness 1.6 mm • IEC 60529 / IP67 mated • Sata III available (upon request) • Operating temperature ◉ Receptacle: -20°C ~ 80°C ◉ Overmolded with Cable: -20°C ~ 80°C  P 12-1
* SSL-1	* M8	* Plug * Jack	* PCB Type * Overmolded Plug

Fiber Optic Connector	NMEA 2000 Connector	PV AC Connectors / T-Junction	
		VTC 	SMC  BMC 
• Receptacle (Jack) & Field Installable (Plug) available • For SC & LC types • Lock Bayonet Type (2 points & 3 points) • UV Resistant • Operating temperature ◦ Field installable: -40°C ~ 105°C ◦ Receptacle: -40°C ~ 105°C • IP67 mated P 13-1	• Available in Micro Style "M12" 5P Conn & Mini Style "7/8" 5P Conn for drop and trunk lines respectively • Compatible with Industrial Bus Systems (Devicenet & Profibus) • Compact and rugged design available in IP67/IP68 unmated waterproof to withstand harsh marine environments • Available in Stamped, screw-in, PCB and solder contacts • Panel mounts (M12 90° PCB), Field Installable, Tee Adapters, Molded With Cable & Junction Boxes available • Operating temperature ◦ Receptacle: -40°C ~ 85°C ◦ Overmolded with Cable: -20°C ~ 80°C ◦ Field installable Nylon+GF: -40°C~105°C PU: -20°C~85°C • Corrosion & Vibration Resistant • Thin & Thick PVC Cables available (Sun, Oil Resistant & Flame rated) • Various cable lengths to match installation requirements • NMEA 2000® approved P 14-1	VTC (T-Junction / SMC) • 3 or 4 Contacts • 300 V/AC, 5A Drop, 30A Trunk • IP 67 waterproof • UV Resistant • Operating temperature : - Ambient: -40°C ~ +85°C - Upon Limited Temperature: +105°C • Intertek approved to UL6703A & UL9703 • Uninterrupted cable - Lower power drop than conventional cabling systems • Various configurations of pitch and T Connector Quantity • Cable End-Cap and Cable Joiner available • Ease of installation and service P 15-1	BMC • 3 & 4 Contacts • 300V AC, 17A • Cable TC-ER, UV resistant • Operating temperature : -40°C ~ 105°C • Safety Locking • ETL approved according to UL 6703A • Overmolded with cable, plug-n-play • IP 67 waterproof • Touch Safe (IP2X)
* LC Type * SC Type	* Mini * Micro	* T-Junction (VTC) * SMC * BMC	* T-Junction (VTC) * SMC * BMC

Cable Joiner	Cable Gland - Anti-UV	Vent Connector	RBL Connector
			
- Simple and reliable cable interconnections - For various cable OD and wire sizes - Cable OD range 6mm~16mm - Wire range 10AWG~22AWG - Standard crimping butt terminals or screw terminal blocks - UV Resistant - Operating temperature - Field installable - PPE: -40°C~105°C - Nylon: -40°C~105°C - IP67 waterproof - Safety locking available	- Various options available, from 1"-20UNEF, M8, M12, M16, M20, M25, M32, M40, PG7, PG9, PG11, PG13.5, PG16 to PG29 - Easily find suitable items for different cable OD - Fit into panel thickness from max 3.0 mm to max 9.0 mm - Product length (with strain relief) from 60.0mm to 96.0mm - Product length (without strain relief) from 22.0 mm to 60.0mm - UV Resistant - Operating temperature - Receptacle: -20°C~105°C - IP67 waterproof	- M12 . M8 available upon request - Air permeability: 12 sec/100 cm3 or 10 sec/100 cm3 - Water entry pressure: 100kPa - Panel thickness max 6.5 mm - UV Resistant - Operating temperature - Receptacle: -20°C~105°C - IP67 unmated	- Snap-in with Latch Type - Receptacle, Overmolded With Cable & Field Installable available 6 contacts 5A - UV Resistant - IP67 waterproof mated or unmated - Operating temperature - Overmolded with Cable: -20°C~80°C - Field installable: -40°C~105°C - Receptacle: -40°C~105°C - Customizations are possible
			
P 16-1	P 17-1	P 18-1	P 19-1
* 6~10 mm	* 1"-20 * M40	* M12 Vent Connector	* Middle Size
* 8~10mm	* M8 * PG7		
* 10~12mm	* M12 * PG9		
* 12~16mm	* M16 * PG11		
	* M20 * PG13		
	* M25 * PG16		
	* M32 * PG29		

X-Lok Connector

- Push Lock Type
- Receptacle, Overmolded With Cable & Field Installable available
- 3 contacts
- 20A
- UV Resistant
- IP67 waterproof mated or unmated
- Operating temperature
 - Overmolded with Cable: -20°C~80°C
 - Field installable: -40°C~105°C
 - Receptacle: -40°C~105°C
- Customizations are possible



P 20-1

* Middle Size

Circular Connector






Circular Connector




Range Overview


Receptacle To Overmolded with Cable




Receptacle To Field Installable




Receptacle with Cable to Overmolded with Cable




Receptacle with Cable to Field Installable




In Line




Accessories



I Adaptor
See page 21-7




T Adaptor
See page 21-4




T Cable
See page 21-1



Tool
See page 21-22




Extension
See page 21-19



Dust Cap
See page 21-9



Waterproof Cap
See page 21-11



Dummy
See page 21-18

【Note】 Design and specification are subject to change without notice.

Specification

Identifications	A Size (Mini Size: 7/16"-28 UNS) B Size (Standard Size: 5/8"-27 UNS) C Size (Middle Size: 13/16"-28 UNS) D Size (Large Size: 1"-20 UNEF) E Size (Macro Size: 1 3/16"-20 UNS)
Description	Receptacle Receptacle with cable Overmolded with Cable Field Installable
Current Rating / Data	2A, 5A, 10A, 20A, 5A+2A, 10A+2A, 10A+5A, 20A+2A, 20A+5A
Material	Contacts: Copper Alloy, Gold Plated Connector Body (Housing) : Nylon+GF, UL Recognized
Waterproof Rating	IP66~68
Temperature Range	Receptacle: -40°C~105°C Receptacle with cable: -20°C~80°C Overmolded with Cable: -20°C~80°C Field installable: -40°C~105°C
Contact Resistance	≤ 10mΩ
Insulation Resistance	≥ 100MΩ at DC500V
Durability	1000 cycles
Breakdown Voltage	≥ AC1000V / 1 minute
More to know	Salt Spray Corrosion Test: 48H Standard Cable Length: 01~99M

Ordering Information


1	2	3	4	5	6	7	8	9	10
Specification / Current Rating <u>>Mini Size</u> (AU) 2A (AD) 5A <u>>Mini Size Metal</u> (ASU) 2A (ASD) 5A <u>>Standard Size</u> (BU) 2A (BD) 5A (BB) 10A (BDU) 5A+2A (BBD) 10A+5A <u>>Standard Size Metal</u> (BSU) 2A (BSD) 5A (BSB) 10A <u>>Middle Size</u> (CU) 2A (CD) 5A (CB) 10A (CC) 20A (CDU) 5A+2A (CBU) 10A+2A (CBD) 10A+5A (CGU) 16A+2A* <u>>Large Size</u> (DU) 2A (DD) 5A (DC) 20A (DCU) 20A+2A (DCD) 20A+5A (DCB) 20A+10A* <u>>Large Size Metal</u> (DSD) 5A <u>>Macro Size</u> (ED) 5A <u>>Others</u> (GBD) 10A+5A (Between Standard Size & Middle Size) (MAB) 10A (Equivalent to AMP) (PLD) 5A (Size 12)									
Number of Contacts 02, 03..... EX. (02) = 2 Contacts									
Connector Body (Style) <u>> For Receptacle</u> (P) Front Fastened (R) Rear Fastened <u>> For Overmolded with Cable</u> (A) With Strain Relief (B) Without Strain Relief <u>> For Field installable</u> (B) Without Strain Relief									
Connector (Housing) Gender (M) Male Connector (F) Female Connector									
Contact Gender (M) Male (D) Female (Power) + Male (Signal) (F) Female (E) Male (Power) + Female (Signal)									
Assemble Style <u>> For Receptacle</u> (S) Solder Type (B) Screw in Type (P) 180° PCB Type (R) 90° PCB Type <u>> For Overmolded with Cable</u> (M) Overmolded with Cable <u>> For Field Installable</u> (A) Field installable (Solder) (B) Screw in Type									
Mating Style (L) 2 Points Lock Bayonet (T) 3 Points Lock Bayonet (S) Screw Thread (Q) Push Lock									
Backshell <u>> For Receptacle</u> (C) Circular (S) Square <u>> For Overmolded with Cable</u> (L) Straight (R) Right Angle <u>> For Field Installable</u> (L) Straight									
Waterproof Rating (6) IP 66 (7) IP 67 (8) IP 68									
More Information (C00) Similar Standard with TC-ER Cable <u>> For Overmolded with Cable</u> <u>> For Receptacle</u> (001), (002)..... Without Cable : Different Versions (□) : Cable Type (A) UL2464 Cable (B) UL2586 Cable (C) Power Cable(TC-ER) (■) : Cable Length From 1M to 99M EX. (01) = 1M									

* Coming soon


【Note】 Design and specification are subject to change without notice.

Physical Dimension


Receptacle Panel Cut-Out



Connector Dimension



Overmolded with Cable




with Strain Relief / Straight

Current Rating		Dimension		Type	L / W	OD	ø	L (Connector Body)
Size	Metal	Connector Gender	Male					
Mini Size	-	2A(AU)	A	10.4	10.9	-	40.5	-
	-	2A(ASU)	D	10.4 / 12.7	10.9	3.05	-	-
	Metal	5A(AD)	A	10.4	10.9	-	40.5	-
	Metal	5A(ASD)	D	10.4 / 12.7	10.9	3.05	-	-
Standard Size	-	2A(BU)	A	14.8	15.6	-	42.6	-
	Metal	2A(BSU)	B	-	15.6	-	-	-
			C	14.0	16.0	-	-	-
	-	5A(BD)	A	14.8	15.6	-	42.6	-
	Metal	5A(BSD)	B	-	15.6	-	-	-
			E	16.0	15.6	3.1	-	-
	-	5A+2A(BDU)	A	14.8	15.6	-	42.6	-
	-	10A(BB)	A	14.8	15.6	-	42.6	-
Middle Size	Metal	10A(BSB)	C	14.1	15.6	-	-	-
	-	10A+5A(BBD)	A	14.8	15.6	-	42.6	-
	-	2A(CU)	A	19.4	20.8	-	-	-
	-	5A(CD)	A	19.4	20.8	-	47.0	-
	-	5A+2A(CDU)	A	19.4	20.8	-	-	-
	-	10A(CB)	A	19.4	20.8	-	47.0	-
	-	10A+2A(CBU)	A	19.4	20.8	-	-	-
Large Size	-	10A+5A(CBD)	A	19.4	20.8	-	59.5	-
	-	20A(CC)	A	19.4	20.8	-	47.0	-
	-	2A(DU)	A	23.6	25.6	-	-	-
	-	5A(DD)	A	23.6	25.6	-	-	-
	Metal	5A(DD)	D	23.6/24.4	25.6	3.1	-	-
			E	24.8/24.5	24.8	3.1	-	-
	Metal	5A(DSD)	F	23.2/24.5	25.6	3.1	-	-
Macro Size	-	20A(DC)	A	23.6	25.6	-	-	-
	-	20A(DC)	D	23.6/24.4	25.6	3.1	-	-
	-	20A+2A(DCU)	A	23.6	25.6	-	-	-
	-	20A+5A(DCD)	A	23.6	25.6	-	-	-
	-	5A(ED)	D	29.0/30.1	30.1	3.5	-	-
	-	10+5A(GBD)	-	-	-	-	-	-
	-	10A(MAB)	-	-	-	-	-	-
Others	-	5A(PLD)	C	11.3	12.8	-	-	-

A	B	C	D	Panel Thickness Max	
				Lock Type	Screw Type
P:18.4 R:18.0	P:14.0 R:10.8	15.7	18.1	P:3.5 R:5.0	P:5.0 R:5.0
18.6	14.0	15.7	18.1	P:3.5	-
P:18.4 R:18.0	P:14.0 R:10.8	15.7	18.1	P:3.5 R:5.0	P:5.0 R:5.0
18.6	14.0	15.7	18.1	P:3.5	-
P:18.0 R:18.0	P:14.0 R:10.65	20.6	23.5	P:4.5 R:5.0	P:4.0 R:5.0
P:18.8 R:19.8	P:16.3 R:11.3	22.0	25.4	-	P:5.0 R:7.0
P:18.0 R:18.0	P:14.0 R:10.65	20.6	25.4	P:4.5 R:5.0	P:4.0 R:5.0
P:18.0 R:18.0	P:14.0 R:11.3	P:21.0 R:22.0	P:23.9 R:25.4	-	P:4.4 R:7.0
P:18.0 R:18.0	P:14.0 R:10.65	20.6	23.5	P:4.5 R:5.0	P:4.0 R:5.0
P:18.0 R:18.0	P:14 R:10.65	20.6	23.5	P:4.5 R:5.0	P:4.0 R:5.0
19.8	11.3	22.0	25.4	-	R:7.0
P:18.0 R:18.0	P:14.0 R:10.65	20.6	23.8	P:4.5 R:5.0	P:4.0 R:5.0
17.0	14.0	25.4	29.3	P:4.0	P:3.0
P:17.0 R:18.0	P:14.0 R:10.0	25.4	29.3	P:4.0 R:4.0	P:3.0 R:4.0
18.0	14.0	25.4	29.3	P:4.0	P:3.0
P:17.0 R:18.0	P:14.0 R:10.0	25.4	29.3	P:4.0 R:4.0	P:3.0 R:4.0
18.0	15.0	25.4	29.3	P:4.0	-
19.5	F:15 R:11.5	25.4	29.3	P:4.0	P:3.0
P:17.0 R:18.0	P:14.0 R:10.0	25.4	29.3	P:4.0 R:4.0	P:3.0 R:4.0
18.0	14.8	28.5	33.0	P:4.0	-
P:18.0 R:18.0	P:14.9 R:10.3	28.5	33.0	P:4.0 R:4.0	P:4.0 R:4.0
17.9	14.6	29.0	33.5	-	P:3.5
18.0	14.6	29.0	33.4	-	P:3.5
P:18.0 R:18.0	P:14.9 R:10.3	28.5	33.0	P:4.0 R:4.0	P:4.0 R:4.0
18.8	14.8	28.5	33.0	P:4.0	-
19	P:14.9/R:10.8	28.5	33.0	P:4.0/R:3.5	P:4.0/R:3.5
17.6	14.9	34.9	4.0	P:3.5	-
-	-	-	-	-	-
-	-	-	-	-	-
15.9	13.4	15.8	17.3	P:3.0	-

L		OD	
Female	Male	Female	Male
43.5	44.5	15.2	13.5
-	-	-	-
43.5	44.5	15.2	13.5
-	-	-	-
55.5	59.0	S-20.0 L-18.0	14.6
-	-	-	-
55.5	59.0	S-20.0 L-18.0	14.6
-	-	-	-
55.5	-	S-20.0 L-18.0	-
55.5	59.0	S-20.0 L-18.0	14.6
-	-	-	-
43.0	59.0	S-20.0 L-18.0	14.6
60.0	-	L-22.2 S-25.4	-
60.0	60.0	L-22.2 S-25.4	20.0
60.5	-	L-22.2 S-25.4	-
60.0	-	L-22.2 S-25.4	-
60.0	-	L-22.2 S-25.4	-
60.0	-	L-22.2 S-25.4	-
59.5	-	S-32.0 L-28.5	-
59.5	59.5	S-32.0 L-28.5	22.5
-	-	-	-
-	-	-	-
59.5	-	S:32.0 L:28.5	-
63.5	69.7	28.5	22.5
59.5	59.5	28.5	22.5
70.0	-	33.3	-
68.7	73.5	26.6	25.0
61.5	61.5	23.0	19.4
-	-	-	-

➤ **Field installable**



without Strain Relief / Straight

with Strain Relief / Right Angle

without Strain Relief / Right Angle

without Strain Relief / Straight

L		OD	
Female	Male	Female	Male
34.0	35.3	15.2	13.5
-	-	-	-
34.0	35.3	15.2	13.5
-	-	-	-
43.0	45.0	S-20.0 L-18.0	14.6
37.8	-	19.0	-
43.0	45.0	S-20.0 L-18.0	14.6
37.8	-	19.0	-
43.0	-	S-20.0 L-18.0	-
43.0	45.0	S-20.0 L-18.0	14.6
-	-	-	-
43.0	45.0	S-20.0 L-18.0	14.6
41.8	-	L-22.2 S-25.4	-
41.8	41.8	L-22.2 S-25.4	20.0
41.8	-	L-22.2 S-25.4	-
41.8	-	L-22.2 S-25.4	-
-	-	-	-
41.8	-	L-22.2 S-25.4	-
41.8	-	L-22.2 S-25.4	-
52.0	-	S-32.0 L-28.5	-
52.0	52.0	S-32.0 L-28.5	22.5
49.3	-	30.0	-
49.3	-	30.0	-
52.0	-	S32.0 L-28.5	-
-	-	-	-
-	-	-	-
60.2	65.0	26.6	25.0
53.0	53.0	23.0	19.4
-	-	-	-

L [A]		L [B]		OD	
Female	Male	Female	Male	Female	Male
-	-	-	-	-	-
-	-	-	-	-	-
-	-	-	-	-	-
34.0	-	35.0	-	S-20.0 L-18.0	-
-	-	-	-	-	-
34.0	-	35.0	-	S-20.0 L-18.0	-
-	-	-	-	-	-
34.0	-	35.0	-	S-20.0 L-18.0	-
34.0	-	35.0	-	S-20.0 L-18.0	-
-	-	-	-	-	-
34.0	-	35.0	-	S-20.0 L-18.0	-
-	-	-	-	-	-
42.5	-	39.5	-	22.2	-
-	-	-	-	-	-
-	-	-	-	-	-
-	-	-	-	-	-
-	-	-	-	-	-
-	-	-	-	-	-
-	-	-	-	-	-
-	-	-	-	-	-
44.1	-	49.8	-	S-32.0 L-28.5	-
40.0	-	40.0	-	30.0	-
40.0	-	40.0	-	30.0	-
-	-	-	-	-	-
-	-	-	-	-	-
44.1	-	49.8	-	28.5	-
-	-	-	-	-	-
-	-	-	-	-	-
-	-	-	-	-	-

L [A]		L [B]		OD	
Female	Male	Female	Male	Female	Male
24.0	-	29.4	-	15.2	-
-	-	-	-	-	-
24.0	-	29.4	-	15.2	-
-	-	-	-	-	-
-	-	-	-	-	-
30.0	-	33.6	-	19.0	-
25.5	-	31.0	-	S-20.0 L-18.0	-
30.0	-	33.6	-	19.0	-
-	-	-	-	-	-
25.5	-	31.0	-	S-20.0 L-18.0	-
-	-	-	-	-	-
25.5	-	31.0	-	S-20.0 L-18.0	-
-	-	-	-	-	-
-	-	-	-	-	-
-	-	-	-	-	-
-	-	-	-	-	-
-	-	-	-	-	-
-	-	-	-	-	-
-	-	-	-	-	-
-	-	-	-	-	-
40.0	-	40.0	-	30.0	-
40.0	-	40.0	-	30.0	-
-	-	-	-	-	-
-	-	-	-	-	-
-	-	-	-	-	-
-	-	-	-	-	-
-	-	-	-	-	-
-	-	-	-	-	-

L		OD	
Female	Male	Female	Male
41.5	41.5	15.2	13.5
-	-	-	-
41.5	41.5	15.2	13.5
-	-	-	-
44.0	43.0	S-20.0 L-18.0	14.6
-	-	-	-
43.0	43.0	S-20.0 L-18.0	14.6
-	-	-	-
43.0	-	S-20.0 L-18.0	-
43.0	43.0	S-20.0 L-18.0	14.6
-	-	-	-
43.0	43.0	S-20.0 L-18.0	14.6
48.2	-	L-22.2 S-25.4	-
48.2	48.65	L-22.2 S-25.4	20.0
-	-	-	-
48.2	-	L-22.2 S-25.4	-
49.7	-	23.0	-
-	-	-	-
48.2	-	L-22.2 S-25.4	-
-	-	-	-
54.9	54.9	S-32.0 L-28.5	23.0
-	-	-	-
-	-	-	-
54.9	54.9	S-32.0 L-28.5	23.0
62.8	59.3	L-28.5	23.0
59.9	59.9	L-28.5	23.0
-	-	-	-
-	-	-	-
39.2	35.3	15.0	15.0

Unit: mm

【Note】 Design and specification are subject to change without notice.

Contact Configuration

	Mini Size (A)						Standard Size (B)							
	2A(AU)(ASU)		5A(AD)		5A(ASD)		2A(BU)(BSU)		5A(BD)		5A(BSD)		10A(BB)	
4 5	MM or FF	MF or FM	MM or FF	MF or FM	MM or FF	MF or FM	MM or FF	MF or FM	MM or FF	MF or FM	MM or FF	MF or FM	MM or FF	MF or FM
2 Pin														
			R C F		R				R C F	R C F			R C F	R C F
3 Pin														
			R C F						R C F	R C F			R C F	R C F
4 Pin														
	R C F								R C F	R C F	R C F		R C F	
5 Pin														
	R C F								R C F	R C F	R C F			
6 Pin														
	R C F								R C F	R C F	R C F			
7 Pin														
									R C F		R C F			
8 Pin														
									R C F		R C F			
9 Pin														
10 Pin														
							R C F							
12 Pin														
							R C F							
14 Pin														
18 Pin														
20 Pin														
21 Pin														
22 Pin														
31 Pin														

* Standard Size Metal (BSU): 10 Contact

Standard Size (10A | 5A+2A | 10A+5A)
Middle Size (2A | 5A | 10A | 20A | 5A+2A)

[illegible]

R: Receptacle

C: Overmolded with Cable

F: Field Installable

- 2A (AU/ASU/BSU/BU/CU/DU) **1**
- ▲ 5A (AD/ASD/BD/BSD/CD/DD/
DSD/ED/PLD)
- 10A (BB/BSB/MAB)
- ◇ 20A (CC/DC)
- ▲ ● 5A+2A (BDU/CDU)
- ● 10A+2A (CBU)
- ▲ 10A+5A (BBD/CBD/GBD)
- ◇ ● 20A+2A (DCU)
- ◇ ▲ 20A+5A (DCD)

Number of Contacts:

Ex.2 contacts (02)

Connector (Housing) Gender:

Male (M) or Female (F)

Contact Gender:

Male (M) or Female (F)


Male + Female (D) / (E)*

More to Choose:

- Solder (**S**)
 - Solder Cup
- Screw In (**B**)



- PCB Type
 - 90° PCB **(R)***
 - 180° PCB **(P)***



- Crimp (C)*



More available:

1. The plating to gold or tin
2. Plated thickness

* Refer to page 1-6 for ordering info
** PCB and crimp styles are upon request for certain of items.

Please contact with ALTW in advance.

【Note】 Design and specification are subject to change without notice.

Contact Configuration

	Middle Size (C)						Middle Size (C)				Large Size (D)			
	10A(CB)		20A(CC)		5A+2A(CDU)		10A+5A(CBD)		10A+2A(CBU)		2A(DU)		5A(DD)(DSD)	
4 5	MM or FF	MF or FM	MM or FF	MF or FM	MM or FF	MF or FM	MM or FF	MF or FM	MM or FF	MF or FM	MM or FF	MF or FM	MM or FF	MF or FM
2 Pin														
				R C F										
3 Pin														
			R C F											
4 Pin														
	R C F	R C F												
5 Pin														
	R C F	R C F												
6 Pin														
	R C F													
7 Pin														
8 Pin														
							R C	R C	R C F	R C F				
9 Pin														
10 Pin														
12 Pin														
						R C F								
14 Pin														
						R C F								
18 Pin														
													R C F	R C F
20 Pin														
											R C F			
21 Pin														
											R C F			
22 Pin														
											R C F			
31 Pin														


Other Size (10A+5A | 10A | 5A)

Large Size (D)						Marco Size (E)		Other Size					
20A(DC)		20A+2A(DCU)		20A+5A(DCD)		5A(ED)		10A+5A(GBD)		10A(MAB)		5A(PLD)	
MM or FF	MF or FM	MM or FF	MF or FM	MM or FF	MF or FM	MM or FF	MF or FM	MM or FF	MF or FM	MM or FF	MF or FM	MM or FF	MF or FM
R C F													R C F
R C F													R C F
R C F											R C F		R C F
R C F													
R C F													
R C F													
R C F								C					
		R C F	R C F										
				R C F	R C F								
								R C F					

Innovation in Waterproof Solution 1-12

Product Features

┘ Receptacle



Flange 8



Circular (C)



Square (S)

Mating Style 7



2 Points Lock Bayonet (L)



3 Points Lock Bayonet (T)




Screw Thread (S)




Push Lock (Q)

Connector Body(Style) 3



Rear Fastened (R)




Front Fastened (P)


┘ Overmolded with Cable



Backshell 8



Straight
(L)



Right Angle
(R)

Mating Style 7



2 Points Lock Bayonet (L)



3 Points Lock Bayonet (T)




Screw Thread (S)

Push Lock (Q)

*Upon request

Connector Body(Style) 3




With Strain Relief (A)




Without Strain Relief (B)

┘ Field Installable



Backshell 8



Straight
(L)

Mating Style 7



2 Points Lock Bayonet (L)



3 Points Lock Bayonet (T)



Screw Thread (S)



Push Lock (Q)




Connector Body(Style) 3



Without Strain Relief (B)




Find Our Standard Products

└ Mini Size: 7/16"-28 UNS > In-line

• Male Connector (Housing) • Male Contacts • 2 Points Lock Bayonet		Overmolded with Cable	Overmolded with Cable	Field Installable
				
Current Rating (Code)	Contacts ②	Male Connector (M) Male Contacts (M)	Female Connector (F) Female Contacts (F)	Female Connector (F) Female Contacts (F)
2A (AU)	04,05,06	AU- ② AMMM-LL6A $\underline{XX}$ * AU- ② BMMM-LL7A $\underline{XX}$ *	AU- ② AFFM-LL6A $\underline{XX}$ * AU- ② BFFM-LL7A $\underline{XX}$ * AU- ② BFFM-LR6A $\underline{XX}$ *	AU- ② BFFA-LL7001
5A (AD)	02,03	AD- ② AMMM-LL6A $\underline{XX}$ * AD- ② BMMM-LL7A $\underline{XX}$ *	AD- ② AFFM-LL6A $\underline{XX}$ * AD- ② BFFM-LL7A $\underline{XX}$ * AD- ② BFFM-LR6A $\underline{XX}$ *	AD- ② BFFA-LL7001

* $\underline{XX}$: Choose the cable length from 01~99m

└ Mini Size: 7/16"-28 UNS > In-line

• Female Connector (Housing) • Female Contacts • 2 Points Lock Bayonet		Overmolded with Cable	Overmolded with Cable	Field Installable
				
Current Rating (Code)	Contacts ②	Female Connector (F) Female Contacts (F)	Male Connector (M) Male Contacts (M)	Male Connector (M) Male Contacts (M)
2A (AU)	04,05,06	AU- ② AFFM-LL6A $\underline{XX}$ * AU- ② BFFM-LL7A $\underline{XX}$ * AU- ② BFFM-LR6A $\underline{XX}$ *	AU- ② AMMM-LL6A $\underline{XX}$ * AU- ② BMMM-LL7A $\underline{XX}$ *	AU- ② BMMA-LL7001
5A (AD)	02,03	AD- ② AFFM-LL6A $\underline{XX}$ * AD- ② BFFM-LL7A $\underline{XX}$ * AD- ② BFFM-LR6A $\underline{XX}$ *	AD- ② AMMM-LL6A $\underline{XX}$ * AD- ② BMMM-LL7A $\underline{XX}$ *	AD- ② BMMA-LL7001

* $\underline{XX}$: Choose the cable length from 01~99m




【Note】 Design and specification are subject to change without notice.

Mini Size: 7/16"-28 UNS

Receptacle and Mating Pair | Receptacle with Overmolded Cable and Mating Pair
Screw Thread & 2 Points Lock Bayonet




IP 66 ~ 68 9
Unmated or Mated

Mini Size: 7/16"-28 UNS > Receptacle and Mating Pair

• Male Connector (Housing) • Male Contacts • Screw Thread & 2 Points Lock Bayonet		Receptacle  7 2 Points Lock Bayonet (L) 6 Choose the PCB Type (P/R) or Solder Type (S) 8 Choose the backshell circular (C) or square flange (S). 10 Choose Plastic (001) or Metal Nut (002)	Overmolded with Cable  7 Choose 2 Points Lock Bayonet (L) or Screw Thread (S)	Field Installable  7 Choose 2 Points Lock Bayonet (L) or Screw Thread (S)
Current Rating (Code)	Contacts 2	Male Connector (M) Male Contacts (M)	Female Connector (F) Female Contacts (F)	Female Connector (F) Female Contacts (F)
2A (AU)	04,05,06	AU- 2 PMM 6 - 7 8 7001 AU- 2 RMMS - 7 C7001	AU- 2 AFFM- 7 L6AXX* AU- 2 BFFM- 7 L7AXX* AU- 2 BFFM- 7 R6AXX*	AU- 2 BFFA- 7 L7001
2A (ASU) *Metal	04,05,06	ASU- 2 PMMS- LS70010	AU- 2 AFFM-LL6AXX* AU- 2 BFFM-LL7AXX* AU- 2 BFFM-LR6AXX*	AU- 2 BFFA-LL7001
5A (AD)	02,03	AD- 2 PMM 6 - 7 8 7001 AD- 2 RMMS - 7 C70010	AD- 2 AFFM- 7 L6AXX* AD- 2 BFFM- 7 L7AXX* AD- 2 BFFM- 7 R6AXX*	AD- 2 BFFA- 7 L7001
5A (ASD) *Metal	02,03	ASD- 2 PMM 6 -LS70010	AD- 2 AFFM-LL6AXX* AD- 2 BFFM-LL7AXX* AD- 2 BFFM-LR6AXX*	AD- 2 BFFA-LL7001



* XX: Choose the cable length from 01~99m

Mini Size: 7/16"-28 UNS > Receptacle with Overmolded Cable and Mating Pair

• Male Connector (Housing) • Male Contacts • Screw Thread & 2 Points Lock Bayonet		Receptacle  7 2 Points Lock Bayonet (L) 7 Screw Thread (S)	Overmolded with Cable  7 Choose 2 Points Lock Bayonet (L) or Screw Thread (S)	Field Installable  7 Choose 2 Points Lock Bayonet (L) or Screw Thread (S)
Current Rating (Code)	Contacts 2	Male Connector (M) Male Contacts (M)	Female Connector (F) Female Contacts (F)	Female Connector (F) Female Contacts (F)
2A (AU)	04,05,06	AU- 2 PMMM- 7 L7AXX*	AU- 2 AFFM- 7 L6AXX* AU- 2 BFFM- 7 L7AXX* AU- 2 BFFM- 7 R6AXX*	AU- 2 BFFA- 7 L7001
5A (AD)	02,03	AD- 2 PMMM- 7 L7AXX*	AD- 2 AFFM- 7 L6AXX* AD- 2 BFFM- 7 L7AXX* AD- 2 BFFM- 7 R6AXX*	AD- 2 BFFA- 7 L7001




* XX: Choose the cable length from 01~99m

Standard Size: 5/8"-27 UNS > In-line

- Male Connector (Housing) - Male Contacts 2 Points Lock Bayonet		Overmolded with Cable 	Overmolded with Cable 	Field Installable 
Current Rating (Code)	Contacts ②	Male Connector (M) Male Contacts (M)	Female Connector (F) Female Contacts (F)	Female Connector (F) Female Contacts (F)
2A (BU)	10, 12	BU- ② AMMM-LL6A $\underline{XX}$ * BU- ② BMMM-LL7A $\underline{XX}$ *	BU- ② AFFM-LL6A $\underline{XX}$ * BU- ② AFFM-LR7A $\underline{XX}$ * BU- ② BFFM-LL7A $\underline{XX}$ * BU- ② BFFM-LR6A $\underline{XX}$ *	BU- ② BFFA-LL7001
5A (BD)	02,03,04, 05,06,07,08	BD- ② AMMM-LL6A $\underline{XX}$ * BD- ② BMMM-LL7A $\underline{XX}$ *	BD- ② AFFM-LL6A $\underline{XX}$ * BD- ② AFFM-LR7A $\underline{XX}$ * BD- ② BFFM-LL7A $\underline{XX}$ * BD- ② BFFM-LR6A $\underline{XX}$ *	BD- ② BFFA-LL7001
10A (BB)	02,03,04	BB- ② AMMM-LL6A $\underline{XX}$ * BB- ② BMMM-LL7A $\underline{XX}$ *	BB- ② AFFM-LL6A $\underline{XX}$ * BB- ② AFFM-LR7A $\underline{XX}$ * BB- ② BFFM-LL7A $\underline{XX}$ * BB- ② BFFM-LR6A $\underline{XX}$ *	BB- ② BFFA-LL7001

* $\underline{XX}$: Choose the cable length from 01~99m

Standard Size: 5/8"-27 UNS > In-line

- Male Connector (Housing) - Male Contacts 2 Points Lock Bayonet		Field Installable 	Overmolded with Cable 	Field Installable 
Current Rating (Code)	Contacts ②	Male Connector (M) Male Contacts (M)	Female Connector (F) Female Contacts (F)	Female Connector (F) Female Contacts (F)
2A (BU)	10, 12	BU- ② BMMA-LL7001	BU- ② AFFM-LL6A $\underline{XX}$ * BU- ② AFFM-LR7A $\underline{XX}$ * BU- ② BFFM-LL7A $\underline{XX}$ * BU- ② BFFM-LR6A $\underline{XX}$ *	BU- ② BFFA-LL7001
5A (BD)	02,03,04, 05,06,07,08	BD- ② BMMA-LL7001	BD- ② AFFM-LL6A $\underline{XX}$ * BD- ② AFFM-LR7A $\underline{XX}$ * BD- ② BFFM-LL7A $\underline{XX}$ * BD- ② BFFM-LR6A $\underline{XX}$ *	BD- ② BFFA-LL7001
10A (BB)	02,03,04	BB- ② BMMA-LL7001	BB- ② AFFM-LL6A $\underline{XX}$ * BB- ② AFFM-LR7A $\underline{XX}$ * BB- ② BFFM-LL7A $\underline{XX}$ * BB- ② BFFM-LR6A $\underline{XX}$ *	BB- ② BFFA-LL7001

【Note】 Design and specification are subject to change without notice.

* $\underline{XX}$: Choose the cable length from 01~99m

Standard Size: 5/8"-27 UNS > In-line

- Female Connector (Housing) - Female Contacts 2 Points Lock Bayonet		Overmolded with Cable	Overmolded with Cable	Field Installable
Current Rating (Code)	Contacts 2	Female Connector (F) Female Contacts (F)	Male Connector (M) Male Contacts (M)	Male Connector (M) Male Contacts (M)
2A (BU)	10,12	BU- 2 AFFM-LL6A ^{XX} * BU- 2 AFFM-LR7A ^{XX} * BU- 2 BFFM-LL7A ^{XX} * BU- 2 BFFM-LR6A ^{XX} *	BU- 2 AMMM-LL6A ^{XX} * BU- 2 BMMM-LL7A ^{XX} *	BU- 2 BMMA-LL7001
5A (BD)	02,03,04, 05,06,07,08	BD- 2 AFFM-LL6A ^{XX} * BD- 2 AFFM-LR7A ^{XX} * BD- 2 BFFM-LL7A ^{XX} * BD- 2 BFFM-LR6A ^{XX} *	BD- 2 AMMM-LL6A ^{XX} * BD- 2 BMMM-LL7A ^{XX} *	BD- 2 BMMA-LL7001
10A (BB)	02,03,04	BB- 2 AFFM-LL6A ^{XX} * BB- 2 AFFM-LR7A ^{XX} * BB- 2 BFFM-LL7A ^{XX} * BB- 2 BFFM-LR6A ^{XX} *	BB- 2 AMMM-LL6A ^{XX} * BB- 2 BMMM-LL7A ^{XX} *	BB- 2 BMMA-LL7001



* XX: Choose the cable length from 01~99m

Standard Size: 5/8"-27 UNS > In-line

- Female Connector (Housing) - Female Contacts 2 Points Lock Bayonet		Field Installable	Overmolded with Cable	Field Installable
Current Rating (Code)	Contacts 2	Female Connector (F) Female Contacts (F)	Male Connector (M) Male Contacts (M)	Male Connector (M) Male Contacts (M)
2A (BU)	10,12	BU- 2 BFFA-LL7001	BU- 2 AMMM-LL6A ^{XX} * BU- 2 BMMM-LL7A ^{XX} *	BU- 2 BMMA-LL7001
5A (BD)	02,03,04, 05,06,07,08	BD- 2 BFFA-LL7001	BD- 2 AMMM-LL6A ^{XX} * BD- 2 BMMM-LL7A ^{XX} *	BD- 2 BMMA-LL7001
10A (BB)	02,03,04	BB- 2 BFFA-LL7001	BB- 2 AMMM-LL6A ^{XX} * BB- 2 BMMM-LL7A ^{XX} *	BB- 2 BMMA-LL7001

* XX: Choose the cable length from 01~99m

Standard Size: 5/8"-27 UNS > In-line

• Female Connector (Housing) • Male Contacts • 2 Points Lock Bayonet		Overmolded with Cable -->	Overmolded with Cable -->	Field Installable
				
Current Rating (Code)	Contacts 2	Female Connector (F) Male Contacts (M)	Male Connector (M) Female Contacts (F)	Male Connector (M) Female Contacts (F)
5A (BD)	02,03,04, 05,06	BD- 2 AFMM-LL6A _{XX} * BD- 2 AFMM-LR7A _{XX} * BD- 2 BFMM-LL7A _{XX} * BD- 2 BFMM-LR6A _{XX} *	BD- 2 AMFM-LL6A _{XX} * BD- 2 BMFM-LL7A _{XX} *	BD- 2 BMFA-LL7001
10A (BB)	02,03	BB- 2 AFMM-LL6A _{XX} * BB- 2 AFMM-LR7A _{XX} * BB- 2 BFMM-LL7A _{XX} * BB- 2 BFMM-LR6A _{XX} *	BB-02AMFM-LL6A _{XX} * BB-02BMFM-LL7A _{XX} * BB-03AMFM-LL6A _{XX} * BB-03BMFM-LL7A _{XX} *	BB-02BMFA-LL7001 BB-03BMFA-LL7001
5A+2A (BDU)	08 (2+6)	BDU-08AFMM-LL6A _{XX} * BDU-08AFMM-LR7A _{XX} * BDU-08BFMM-LL7A _{XX} *	BDU-08AMFM-LL6A _{XX} * BDU-08BMFM-LL7A _{XX} *	BDU-08BMFA-LL7001
10A+5A (BBD)	06 (2+4)	BBD- 2 AFMM-LL6A _{XX} * BBD- 2 AFMM-LR7A _{XX} * BBD- 2 BFMM-LL7A _{XX} * BBD- 2 BFMM-LR6A _{XX} *	BBD-06AMFM-LL6A _{XX} * BBD-06BMFM-LL7A _{XX} *	BBD-06BMFA-LL7001

【Note】BDU-08AMFM-LL6A_{XX} and BDU-08BMFM-LL7A_{XX} are coming soon.






* _{XX}: Choose the cable length from 01~99m

Standard Size: 5/8"-27 UNS > Receptacle and Mating Pair

• Male Connector (Housing) • Male Contacts • Screw Thread & 2 Points Lock Bayonet Receptacle 7 Screw Thread (S) 7 2 Points Lock Bayonet (L) 6 Choose the PCB Type (P/R) or Solder Type (S) Overmolded with Cable 7 Screw Thread (S) 7 2 Points Lock Bayonet (L) Field Installable 7 Choose 2 Points Lock Bayonet (L) or Screw Thread (S)				
Current Rating (Code)	Contacts 2	Male Connector (M) Male Contacts (M)	Female Connector (F) Female Contacts (F)	Female Connector (F) Female Contacts (F)
2A (BU)	10, 12	BU- 2 PMM 6 - 7 C7001 BU- 2 RMMS - 7 C7001	BU- 2 AFFM- 7 L6A _{XX} * BU- 2 AFFM- 7 R7A _{XX} * BU- 2 BFFM- 7 L7A _{XX} * BU- 2 BFFM-LR6A _{XX} *	BU- 2 BFFA- 7 L7001
2A (BSU) *Metal	10	BSU- 2 PMM 6 -SC7001 BSU- 2 RMMS-SC7001	BSU-10BFFM-SL7A _{XX} * BSU-10BFFM-SR6A _{XX} *	BSU-10BFFA-SL7001
5A (BD)	02,03,04, 05,06,07,08	BD- 2 PMM 6 - 7 C7001 BD- 2 RMMS - 7 C7001 BD- 2 RMM 6 -LC7001	BD- 2 AFFM- 7 L6A _{XX} * BD- 2 AFFM- 7 R7A _{XX} * BD- 2 BFFM- 7 L7A _{XX} * BD- 2 BFFM- 7 R6A _{XX} *	BD- 2 BFFA- 7 L7001
5A (BSD)	04,05,06, 07.08	BSD- 2 PMM 6 -SC7001 BSD- 06RMMS-SC7001 BSD- 08RMMS-SC7001	BSD- 2 BFFM-SL6A _{XX} * BSD- 2 BFFM-SR6A _{XX} *	-
10A (BB)	02,03,04	BB- 2 PMM 6 - 7 C7001 BB- 2 RMMS- 7 C7001 BB- 2 RMM 6 -LC7001	BB- 2 AFFM- 7 L6A _{XX} * BB- 2 AFFM- 7 R7A _{XX} * BB- 2 BFFM- 7 L7A _{XX} * BB- 2 BFFM- 7 R6A _{XX} *	BB- 2 BFFA- 7 L7001
10A (BSB) *Metal	04	BSB-04RMMS-SC7001	BSB-04BFFM-SL7A _{XX} *	-

* XX: Choose the cable length from 01~99m

Standard Size: 5/8"-27 UNS > Receptacle with Overmolded Cable and Mating Pair

• Male Connector (Housing) • Male Contacts • Screw Thread & 2 Points Lock Bayonet		Receptacle  7 Screw Thread (S)  7 2 Points Lock Bayonet (L)	Overmolded with Cable  7 Screw Thread (S)  7 2 Points Lock Bayonet (L)	Field Installable  7 Choose 2 Points Lock Bayonet (L) or Screw Thread (S)
Current Rating (Code)	Contacts 2	Male Connector (M) Male Contacts (M)	Female Connector (F) Female Contacts (F)	Female Connector (F) Female Contacts (F)
2A (BU)	10, 12	BU- 2 PMMM- 7 L7A _{XX} *	BU- 2 AFFM- 7 L6A _{XX} * BU- 2 AFFM- 7 R7A _{XX} * BU- 2 BFFM- 7 L7A _{XX} *	BU- 2 BFFA- 7 L7001
5A (BD)	02,03,04, 05,06,07,08	BD- 2 PMMM- 7 L7A _{XX} *	BD- 2 AFFM- 7 L6A _{XX} * BD- 2 AFFM- 7 R7A _{XX} * BD- 2 BFFM- 7 L7A _{XX} * BD- 2 BFFM- 7 R6A _{XX} *	BD- 2 BFFA- 7 L7001
10A (BB)	02,03,04	BB- 2 PMMM- 7 L7A _{XX} *	BB- 2 AFFM- 7 L6A _{XX} * BB- 2 AFFM- 7 R7A _{XX} * BB- 2 BFFM- 7 L7A _{XX} * BB- 2 BFFM- 7 R6A _{XX} *	BB- 2 BFFA- 7 L7001

* _{XX}: Choose the cable length from 01~99m




【Note】 Design and specification are subject to change without notice.

Standard Size: 5/8"-27 UNS > Receptacle and Mating Pair

• Male Connector (Housing) • Female Contacts • Screw Thread & 2 Points Lock Bayonet Receptacle Overmolded with Cable Field Installable				
7 Screw Thread (S) 6 Choose the PCB Type (P/R) or Solder Type (S) Front Fastened Rear Fastened 7 2 Points Lock Bayonet (L) 7 Screw Thread (S) 7 2 Points Lock Bayonet (L) 7 Choose 2 Points Lock Bayonet (L) or Screw Thread (S)				
Current Rating (Code)	Contacts 2	Male Connector (M) Female Contacts (F)	Female Connector (F) Male Contacts (M)	Female Connector (F) Male Contacts (M)
5A (BD)	02,03,04,05,06	BD- 2 PMF 6 - 7 C7001 BD- 2 RMFS- 7 C7001	BD- 2 AFMM- 7 L6AXX* BD- 2 AFMM- 7 R7AXX* BD- 2 BFMM- 7 L7AXX* BD- 2 BFMM- 7 R6AXX*	BD- 2 BFMA- 7 L7001
10A (BB)	02,03	BB- 2 PMF 6 - 7 C7001 BB- 2 RMFS- 7 C7001	BB- 2 AFMM- 7 L6AXX* BB- 2 AFMM- 7 R7AXX* BB- 2 BFMM- 7 L7AXX* BB- 2 BFMM- 7 R6AXX*	BB- 2 BFMA- 7 L7001
5A+2A (BDU)	08 (2+6)	BDU-08PMF 6 - 7 C7001 BDU-08RMFS- 7 C7001	BDU-08AFMM- 7 L6AXX* BDU-08AFMM- 7 R7AXX* BDU-08BFMM- 7 L7AXX*	BDU-08BFMA- 7 L7001
10A+5A (BBD)	06 (2+4)	BBD-06PMF 6 - 7 C7001 BBD-06RMFS- 7 C7001	BBD- 06AFMM- 7 L6AXX* BBD- 06AFMM- 7 R7AXX* BBD- 06BFMM- 7 L7AXX* BBD- 06BFMM- 7 R6AXX*	BBD-06BFMA- 7 L7001




* XX: Choose the cable length from 01~99m

Middle Size: 13/16"-28 UNS > In-line

- Male Connector (Housing) - Male Contacts 2 Points Lock Bayonet		Overmolded with Cable -->	Overmolded with Cable	Field Installable
				
Current Rating (Code)	Contacts 2	Male Connector (M) Male Contacts (M)	Female Connector (F) Female Contacts (F)	Female Connector (F) Female Contacts (F)
5A (CD)	07,08,09, 10,12,14	CD- 2 AMMM-LL7AXX* CD- 2 BMMM-LL6AXX*	CD- 2 AFFM-LL7AXX* CD- 2 BFFM-LL6AXX* CD- 2 AFFM-LR7AXX*	CD- 2 BFFA-LL7001




* XX: Choose the cable length from 01~99m

Middle Size: 13/16"-28 UNS > In-line

- Male Connector (Housing) - Male Contacts 2 Points Lock Bayonet		Field Installable	Overmolded with Cable	Field Installable
				
Current Rating (Code)	Contacts 2	Male Connector (M) Male Contacts (M)	Female Connector (F) Female Contacts (F)	Female Connector (F) Female Contacts (F)
5A (CD)	07,08,09, 10,12,14	CD- 2 BMMA-LL7001	CD- 2 AFFM-LL7AXX* CD- 2 AFFM-LR7AXX* CD- 2 BFFM-LL6AXX*	CD- 2 BFFA-LL7001

* XX: Choose the cable length from 01~99m

Middle Size: 13/16"-28 UNS > In-line

- Female Connector (Housing) - Female Contacts 2 Points Lock Bayonet		Overmolded with Cable -->	Overmolded with Cable	Field Installable
				
Current Rating (Code)	Contacts 2	Female Connector (F) Female Contacts (F)	Male Connector (M) Male Contacts (M)	Male Connector (M) Male Contacts (M)
5A (CD)	07,08,09, 10,12,14	CD- 2 AFFM-LL7AXX* CD- 2 AFFM-LR7AXX* CD- 2 BFFM-LL6AXX*	CD- 2 AMMM-LL7AXX* CD- 2 BMMM-LL6AXX*	CD- 2 BMMA-LL7001

* XX: Choose the cable length from 01~99m

[Note] Design and specification are subject to change without notice.

Middle Size: 13/16"-28 UNS > In-line

• Female Connector (Housing) • Female Contacts • 2 Points Lock Bayonet		Field Installable	Overmolded with Cable	Field Installable
Current Rating (Code)	Contacts 2	Female Connector (F) Female Contacts (F)	Male Connector (M) Male Contacts (M)	Male Connector (M) Male Contacts (M)
5A (CD)	07,08,09, 10,12,14	CD- 2 BFFA-LL7001	CD- 2 AMMM-LL7A ^{XX} * CD- 2 BMMM-LL6A ^{XX} *	CD- 2 BMMA-LL7001

* XX: Choose the cable length from 01~99m

Middle Size: 13/16"-28 UNS > In Line

• Male Connector (Housing) • Female Contacts • 2 Points Lock Bayonet		Overmolded with Cable	Overmolded with Cable	Field Installable
Current Rating (Code)	Contacts 2	Male Connector (M) Female Contacts (F)	Female Connector (F) Male Contacts (M)	Female Connector (F) Male Contacts (M)
5A (CD)	07,08,09	CD- 2 AMFM-LL7A ^{XX} * CD- 2 BMFM-LL6A ^{XX} *	CD- 2 AFMM-LL7A ^{XX} * CD- 2 BFMM-LL6A ^{XX} *	CD- 2 BFMA-LL7001








* XX: Choose the cable length from 01~99m

Middle Size: 13/16"-28 UNS > In Line

• Female Connector (Housing) • Male Contacts • 2 Points Lock Bayonet		Overmolded with Cable	Overmolded with Cable	Field Installable
Current Rating (Code)	Contacts 2	Female Connector (F) Male Contacts (M)	Male Connector (M) Female Contacts (F)	Male Connector (M) Female Contacts (F)
5A (CD)	07,08,09	CD- 2 AFMM-LL7A ^{XX} * CD- 2 BFMM-LL6A ^{XX} *	CD- 2 AMFM-LL7A ^{XX} * CD- 2 BMFM-LL6A ^{XX} *	CD- 2 BMFA-LL7001

* XX: Choose the cable length from 01~99m

Middle Size: 13/16"-28 UNS > Receptacle and Mating Pair

• Male Connector (Housing) • Male Contacts • Screw Thread & 2 Points Lock Bayonet Receptacle     Overmolded with Cable   Field Installable  6 Choose PCB (P/R) or Solder Type (S) 7 Screw Thread (S) 7 2 Points Lock Bayonet (L) 7 Choose 2 Points Lock Bayonet (L) or Screw Thread (S) ** Select cable length from 01~99m				
Current Rating (Code)	Contacts ②	Male Connector (M) Male Contacts (M)	Female Connector (F) Female Contacts (F)	Female Connector (F) Female Contacts (F)
2A (CU)	18	CU-18PMMP-⑦C7001 CU-18PMMP-SC7002	CU-18AFFM-⑦L7A XX * CU-18BFFM-⑦L6A XX *	CU-18BFFA-⑦L7001
5A (CD)	07,08,09, 10,12,14	CD-②PMM⑥-⑦C7001 CD-②RMMS-⑦C7001	CD-②AFFM-⑦L7A XX * CD-②BFFM-⑦L6A XX * CD-②AFFM-LR7A XX *	CD-②BFFA-⑦L7001
10A (CB)	04,05,06	CB-②PMM⑥-⑦C7001 CB-②RMMS-⑦C7001	CB-②AFFM-⑦L7A XX * CB-②BFFM-⑦L6A XX *	CB-②BFFA-⑦L7001
10A+5A (CBD)	08 (2+6)	CBD-08PMM⑥-⑦C7001	CBD-08AFFM-⑦L7A XX * CBD-08BFFM-⑦L6A XX *	CBD-08BFFA-⑦L7001
20A (CC)	03	CC-03PMM⑥-⑦C7001 CC-03RMMS-⑦C7001	CC-03AFFM-⑦L7A XX * CC-03BFFM-⑦L6A XX *	CC-03BFFA-⑦L7001

* XX: Choose the cable length from 01~99m

【Note】 Design and specification are subject to change without notice.

Middle Size: 13/16"-28 UNS

Receptacle with Overmolded Cable and Mating Pair
Screw Thread & 2 Points Lock Bayonet






IP 66 ~ 68 9
Unmated or Mated

Middle Size: 13/16"-28 UNS > Receptacle with Overmolded Cable and Mating Pair

• Male Connector (Housing) • Male Contacts • Screw Thread & 2 Points Lock Bayonet		Receptacle Overmolded with Cable Field Installable		
Current Rating (Code)	Contacts 2	Male Connector (M) Male Contacts (M)	Female Connector (F) Female Contacts (F)	Female Connector (F) Female Contacts (F)
5A (CD)	07,08,09,10,12,14	CD- 2 PMMM- 7 L7A XX *	CD- 2 AFFM- 7 L7A XX * CD- 2 BFFM- 7 L6A XX * CD- 2 AFFM-LR7A XX *	CD- 2 BFFA- 7 L7001
10A (CB)	04,05,06	CB- 2 PMMM- 7 L7A XX *	CB- 2 AFFM- 7 L7A XX * CB- 2 BFFM- 7 L6A XX *	CB- 2 BFFA- 7 L7001
20A (CC)	03	CC-03PMMM-SL7A XX *	CC-03AFFM-SL7A XX * CC-03BFFM-SL6A XX *	CC-03BFFA-SL7001

* ~~XX~~: Choose the cable length from 01~99m

Middle Size: 13/16"-28 UNS > Receptacle and Mating Pair

• Male Connector (Housing) • Female Contacts • Screw Thread & 2 Points Lock Bayonet		Receptacle  7 Screw Thread (S)  7 2 Points Lock Bayonet (L) 6 Choose PCB (P/R) or Solder Type (S)	Overmolded with Cable  7 Screw Thread (S)  7 2 Points Lock Bayonet (L)	Field Installable  7 Choose 2 Points Lock Bayonet (L) or Screw Thread (S)
Current Rating (Code)	Contacts 2	Male Connector (M) Female Contacts (F)	Female Connector (F) Male Contacts (M)	Female Connector (F) Male Contacts (M)
5A (CD)	07,08,09	CD- 2 PMF 6 - 7 C7001 CD- 2 RMFS- 7 C7001	CD- 2 AFMM- 7 L7A XX * CD- 2 BFMM- 7 L6A XX *	CD- 2 BFMA- 7 L7001
5A+2A (CDU)	12 (2+10) 14 (2+12)	CDU- 2 PMF 6 - 7 C7001	CDU- 2 AFMM- 7 L7A XX * CDU- 2 BFMM- 7 L6A XX * CDU- 2 BFMM- 7 L7A XX *	CDU- 2 BFMA- 7 L7001
10A (CB)	04,05	CB- 2 PMF 6 - 7 C7001 CB- 2 RMFS- 7 C7001	CB- 2 AFMM- 7 L7A XX * CB- 2 BFMM- 7 L6A XX *	CB- 2 BFMA- 7 L7001
10A+5A (CBD)	08 (2+6)	CBD-08PMF 6 - 7 C7001	CBD-08AFMM- 7 L7A XX * CBD-08BFMM- 7 L6A XX *	CBD-08BFMA- 7 L7001
20A (CC)	02	CC-02PMFS- LC7001	CC-02AFMM- LL7A XX *	CC-02BFMA-LL7001

* XX: Choose the cable length from 01~99m






【Note】 Design and specification are subject to change without notice.

Middle Size: 13/16"-28 UNS

Receptacle with Overmolded Cable and Mating Pair
Screw Thread & 2 Points Lock Bayonet




IP 66 ~ 68 9
Unmated or Mated

➤ Middle Size: 13/16"-28 UNS > Receptacle with Overmolded Cable and Mating Pair

• Male Connector (Housing) • Female Contacts • Screw Thread & 2 Points Lock Bayonet		Receptacle	Overmolded with Cable	Field Installable
		 7 Screw Thread (S)  7 2 Points Lock Bayonet (L)	 7 Screw Thread (S)  7 2 Points Lock Bayonet (L)	 7 Choose 2 Points Lock Bayonet (L) or Screw Thread (S)
Current Rating (Code)	Contacts 2	Male Connector (M) Female Contacts (F)	Female Connector (F) Male Contacts (M)	Female Connector (F) Male Contacts (M)
5A (CD)	07,08,09	CD- 2 PMFM- 7 L7A XX *	CD- 2 AFMM- 7 L7A XX * CD- 2 BFMM- 7 L6A XX *	CD- 2 BFMA- 7 L7001
10A (CB)	04,05	CB- 2 PMFM- 7 L7A XX *	CB- 2 AFMM- 7 L7A XX * CB- 2 BFMM- 7 L6A XX *	CB- 2 BFMA- 7 L7001




* XX: Choose the cable length from 01~99m

Middle Size: 13/16"-28 UNS > Receptacle and Mating Pair

• Male Connector (Housing) • Female Power+Male Signal • 3 Points Lock Bayonet		Receptacle 	Overmolded with Cable 	Field Installable 
Current Rating (Code)	Contacts	Male Connector (M) Female Power+Male Signal (D)	Female Connector (F) Male Power+Female Signal (E)	Female Connector (F) Male Power+Female Signal (E)
10A+2A (CBU)	(3+5)	CBU-08PMDS-TC7001	CBU-08AFEM-TL7A XX *	CBU-08BFEA-TL7001

* XX: Choose the cable length from 01~99m




Middle Size: 13/16"-28 UNS > Receptacle and Mating Pair

• Male Connector (Housing) • Male Power+Female Signal • 3 Points Lock Bayonet		Receptacle 	Overmolded with Cable 	Field Installable 
Current Rating (Code)	Contacts	Male Connector (M) Male Power+Female Signal (E)	Female Connector (F) Female Power+Male Signal (D)	Female Connector (F) Female Power+Male Signal (D)
10A+2A (CBU)	(3+5)	CBU-08PMES-TC7001	CBU-08AFDM-TL7A XX *	CBU-08BFDA-TL7001

* XX: Choose the cable length from 01~99m


【Note】 Design and specification are subject to change without notice.

Large Size: 1"-20 UNEF > In-line

• Male Connector (Housing) • Male Contacts • 2 Points Lock Bayonet		Overmolded with Cable	Overmolded with Cable	Field Installable
				
Current Rating (Code)	Contacts	Male Connector (M) Male Contacts (M)	Female Connector (F) Female Contacts (F)	Female Connector (F) Female Contacts (F)
5A (DD)	18	DD-18AMMM-LL7A ^{XX} * DD-18BMMM-LL6A ^{XX} *	DD-18AFFM-LL7A ^{XX} * DD-18AFFM-LR7A ^{XX} * DD-18BFFM-LL6A ^{XX} *	DD-18BFFA-LL7001




* XX: Choose the cable length from 01~99m

Large Size: 1"-20 UNEF > In-line

• Female Connector (Housing) • Female Contacts • 2 Points Lock Bayonet		Overmolded with Cable	Overmolded with Cable	Field Installable
				
Current Rating (Code)	Contacts	Female Connector (F) Female Contacts (F)	Male Connector (M) Male Contacts (M)	Male Connector (M) Male Contacts (M)
5A (DD)	18	DD-18AFFM-LL7A ^{XX} * DD-18AFFM-LR7A ^{XX} * DD-18BFFM-LL6A ^{XX} *	DD-18AMMM-LL7A ^{XX} * DD-18BMMM-LL6A ^{XX} *	DD-18BMMA-LL7001




* XX: Choose the cable length from 01~99m

Large Size: 1"-20 UNEF > In-line

• Male Connector (Housing) • Female Contacts • 2 Points Lock Bayonet		Overmolded with Cable	Overmolded with Cable	Field Installable
				
Current Rating (Code)	Contacts	Male Connector (M) Female Contacts (F)	Female Connector (F) Male Contacts (M)	Female Connector (F) Male Contacts (M)
5A (DD)	18	DD-18AMFM-LL7A ^{XX} * DD-18BMFM-LL6A ^{XX} *	DD-18AFMM-LL7A ^{XX} * DD-18BFMM-LL6A ^{XX} *	DD-18BFMA-LL7001




* XX: Choose the cable length from 01~99m

Large Size: 1"-20 UNEF > In-line

- Female Connector (Housing) - Male Contacts 2 Points Lock Bayonet		Overmolded with Cable	Overmolded with Cable	Field Installable
				
Current Rating (Code)	Contacts	Female Connector (F) Male Contacts (M)	Male Connector (M) Female Contacts (F)	Male Connector (M) Female Contacts (F)
5A (DD)	18	DD-18AFMM-LL7A _{XX} * DD-18BFMM-LL6A _{XX} *	DD-18AMFM-LL7A _{XX} * DD-18BMFM-LL6A _{XX} *	DD-18BMFA-LL7001



* XX: Choose the cable length from 01~99m

Large Size: 1"-20 UNEF > In-line

- Male Connector (Housing) - Female Power+Male Signal 2 Points Lock Bayonet		Overmolded with Cable	Overmolded with Cable	Field Installable
				
Current Rating (Code)	Contacts	Male Connector (M) Female Power+Male Signal (D)	Female Connector (F) Male Power+Female Signal (E)	Female Connector (F) Male Power+Female Signal (E)
20A+2A (DCU)	(3+5)	DCU-08AMDMD-LL7B _{XX} *	DCU-08AFEM-LL7B _{XX} *	DCU-08BFEM-LL7001
20A+5A (DCD)	(3+9)	DCD-12AMDMD-LL7A _{XX} *	DCD-12AFEM-LL7A _{XX} * DCD-12AFEM-LR7A _{XX} *	DCD-12BFEM-LL7001

* XX: Choose the cable length from 01~99m




Large Size: 1"-20 UNEF > In-line

- Male Connector (Housing) - Female Power+Male Signal 2 Points Lock Bayonet		Field Installable	Overmolded with Cable	Field Installable
				
Current Rating (Code)	Contacts	Male Connector (M) Female Power+Male Signal (D)	Female Connector (F) Male Power+Female Signal (E)	Female Connector (F) Male Power+Female Signal (E)
20A+2A (DCU)	(3+5)	DCU-08BMDA-LL7001	DCU-08AFEM-LL7B _{XX} *	DCU-08BFEM-LL7001
20A+5A (DCD)	(3+9)	DCD-12BMDA-LL7001	DCD-12AFEM-LL7A _{XX} * DCD-12AFEM-LR7A _{XX} *	DCD-12BFEM-LL7001

* XX: Choose the cable length from 01~99m



【Note】 Design and specification are subject to change without notice.

Large Size: 1"-20 UNEF > In-line

		Overmolded with Cable	Overmolded with Cable	Field Installable
- Male Connector (Housing) - Male Power+Female Signal 2 Points Lock Bayonet				
Current Rating (Code)	Contacts	Male Connector (M) Male Power+Female Signal(E)	Female Connector (F) Female Power+Male Signal(D)	Female Connector (F) Female Power+Male Signal(D)
20A+2A (DCU)	(3+5)	DCU-08AMEM-LL7BXX*	DCU-08AFDM-LL7BXX*	DCU-08BFDA-LL7001
20A+5A (DCD)	(3+9)	DCD-12AMEM-LL7AXX*	DCD-12AFDM-LL7AXX* DCD-12AFDM-LR7AXX*	DCD-12BFDA-LL7001

* XX: Choose the cable length from 01~99m

Large Size: 1"-20 UNEF > In-line




		Field Installable	Overmolded with Cable	Field Installable
- Male Connector (Housing) - Male Power+Female Signal 2 Points Lock Bayonet				
Current Rating (Code)	Contacts	Male Connector (M) Male Power+Female Signal (E)	Female Connector (F) Female Power+Male Signal (D)	Female Connector (F) Female Power+Male Signal (D)
20A+2A (DCU)	(3+5)	DCU-08BMEA-LL7001	DCU-08AFDM-LL7BXX*	DCU-08BFDA-LL7001
20A+5A (DCD)	(3+9)	DCD-12BMEA-LL7001	DCD-12AFDM-LL7AXX* DCD-12AFDM-LR7AXX*	DCD-12BFDA-LL7001

* XX: Choose the cable length from 01~99m

		Receptacle	Overmolded with Cable	Field Installable
• Male Connector (Housing) • Male Contacts • Screw Thread & 2 Points Lock Bayonet		7 Screw Thread (S) 7 2 Points Lock Bayonet (L) 6 Choose PCB (P/R) or Solder Type (S)	7 Screw Thread (S) 7 2 Points Lock Bayonet (L)	7 Screw Thread (S) 7 2 Points Lock Bayonet (L)
Current Rating (Code)	Contacts	Male Connector (M) Male Contacts (M)	Female Connector (F) Female Contacts (F)	Female Connector (F) Female Contacts (F)
2A (DU)	20,21,22**	DU- 2 PMM 6 - 7 C7001	DU- 2 AFFM- 7 L7A XX * DU- 2 BFFM- 7 L6A XX *	DU- 2 BFFA-SL7001
5A (DD)	18	DD-18PMM 6 - 7 C7001 DD-18RMMS- 7 C7001	DD-18AFFM- 7 L7A XX * DD-18AFFM- 7 R7A XX * DD-18BFFM- 7 L6A XX *	DD-18BFFA- 7 L7001
20A (DC)	02,03,04, 05,06,07	DC- 2 PMM 6 - 7 C7001 DC- 2 PMM 6 - 7 S7001 DC- 2 RMMS- 7 C7001	DC- 2 AFFM- 7 L7A XX * DC- 2 BFFM- 7 L6A XX *	DC- 2 BFFA- 7 L7001 DC-02BFFB- 7 L7001




* XX: Choose the cable length from 01~99m
 ** The specification of 22 contacts is upon request.

Large Size: 1"-20UNEF > Receptacle and Mating Pair

- Male Connector (Housing) - Female Power+Male Signal 2 Points Lock Bayonet		Receptacle 	Overmolded with Cable 	Field Installable 
		PCB (P/R) Type Solder Type (S) 6 Choose PCB (P/R) or Solder Type (S)		
Current Rating (Code)	Contacts	Male Connector (M) Female Power+Male Signal (D)	Female Connector (F) Male Power+Female Signal (E)	Female Connector (F) Male Power+Female Signal (E)
20A+2A (DCU)	(3+5)	DCU-08PMDS-LC7001	DCU-08AFEM-LL7BXX*	DCU-08BFEM-LL7001
20A+5A (DCD)	(3+9)	DCD-12PMD 6 -LC7001	DCD-12AFEM-LL7AXX* DCD-12AFEM-LR7AXX*	DCD-12BFEM-LL7001




* XX: Choose the cable length from 01~99m

Large Size: 1"-20 UNEF > Receptacle and Mating Pair

- Male Connector (Housing) - Male Power+Female Signal 2 Points Lock Bayonet		Receptacle 	Overmolded with Cable 	Field Installable 
Current Rating (Code)	Contacts	Male Connector (M) Male Power+Female Signal (E)	Female Connector (F) Female Power+Male Signal (D)	Female Connector (F) Female Power+Male Signal (D)
20A+2A (DCU)	(3+5)	DCU-08PMES-LC7001	DCU-08AFDM-LL7BXX*	DCU-08BFDA-LL7001
20A+5A (DCD)	(3+9)	DCD-12PMES-LC7001	DCD-12AFDM-LL7AXX* DCD-12AFDM-LR7AXX*	DCD-12BFDA-LL7001

* XX: Choose the cable length from 01~99m

Macro Size: 1 3/16"-20 UNS > Receptacle and Mating pair

- Male Connector (Housing) - Female Contacts 2 Points Lock Bayonet		Receptacle 	Overmolded with Cable 	Field Installable 
		6 Choose PCB (P) or Solder Type (S)		
Current Rating (Code)	Contacts	Male Connector (M) Female Contacts (F)	Female Connector (F) Male Contacts (M)	Female Connector (F) Male Contacts (M)
5A (ED)	31	ED-31PMF 6 -LS7001	ED-31AFMM-LL7AXX*	-

* XX: Choose the cable length from 01~99m



【Note】 Design and specification are subject to change without notice.

Other Size

In-line
2 & 3 Points Lock Bayonet

IP 66 ~ 68 9
Unmated or Mated

Other Size > In-line

•Male Connector (Housing) •Female Power+Male Signal •3 Points Lock Bayonet		Receptacle 	Overmolded with Cable 	Field Installable
Current Rating (Code)	Contacts	Male Connector (M) Male Contacts (M)	Female Connector (F) Female Contacts (F)	Female Connector (F) Female Contacts (F)
5A (GBD)	08	GBD-08AMMM-TL8AXX* GBD-08BMMM-TL7AXX*	GBD-08AFFM-TL8AXX* GBD-08BFFM-TL7AXX*	-



* XX: Choose the cable length from 01~99m

Other Size > In-line



•Male Connector (Housing) •Female Power+Male Signal •2 Points Lock Bayonet		Receptacle 	Overmolded with Cable 	Field Installable
Current Rating (Code)	Contacts	Male Connector (M) Female Contacts (F)	Female Connector (F) Male Contacts (M)	Female Connector (F) Male Contacts (M)
10A (MAB)	04	MAB-04AMFM-LL7AXX* MAB-04BMFM-LL6AXX*	MAB-04AFMM-LL7AXX* MAB-04BFMM-LL6AXX*	-

* XX: Choose the cable length from 01~99m

Other Size > Receptacle and Mating Pair

• Male Connector (Housing) • Female Contacts • Push Lock		Receptacle 	Field Installable 	Field Installable
Current Rating (Code)	Contacts ②	Male Connector (M) Female Contacts (F)	Female Connector (F) Male Contacts (M)	Female Connector (F) Male Contacts (M)
5A (PLD)	02,03,04	PLD-② PMFS-QC7001	PLD-② BFMA-QL7001	-

Other Size > In-line

• Male Connector (Housing) • Female Contacts • Push Lock		Field Installable 	Field Installable 	Field Installable
Current Rating (Code)	Contacts ②	Male Connector (M) Female Contacts (F)	Female Connector (F) Male Contacts (M)	Female Connector (F) Male Contacts (M)
5A (PLD)	02,03,04	PLD-② BMFA-QL7001	PLD-② BFMA-QL7001	-

【Note】 Design and specification are subject to change without notice.

Power Connector

PWE, PWF, PWG



PWC, PWCU



PWL



Power II Series: PWJ, PWH




PWCU




Range Overview


Receptacle to Overmolded with Cable



Receptacle to Field Installable




In Line




Accessories



Waterproof Cap
See page 21-13



Waterproof Cap
See page 21-13



Waterproof Cap
See page 21-13

[Note] Design and specification are subject to change without notice.

Specification

Identifications	Power Connector
Description	Receptacle Overmolded with Cable Field Installable
Current Rating / Data	8A, 12A, 16A, 20A, 25A, 30A, 10A+2A, 20A+2A
Material	Contacts: Copper Alloy, Gold Plated Connector Body (Housing) : Nylon+GF, UL Recognized, PPE
Waterproof Rating	IP66~68
Temperature Range	Receptacle : -40°C ~ +105°C Overmolded with Cable : -20°C ~ +80°C Field Installable : -40°C ~ +105°C
Contact Resistance	≤ 5mΩ
Insulation Resistance	≥ 100MΩ at DC500V
Durability	500 cycles
Breakdown Voltage	≥ AC1000V / 1 minute
More to know	Standard Cable Length: 01~99M

Ordering Information

1	2	3	4	5	6	7	8	9	10
Specification / Current Rating (PWE) 8A (PWCU) 20A+2A (PWF) 12A (PWG) 16A (PWC) 20A (PWJ) 30A* (PWH) 25A* (PWL) 30A**									
Number of Contacts 02, 03, 04, 05, 06, 07.... EX. (02) = 2 Contacts									
Connector Body (Style) <u>> For Receptacle</u> (P) Front Fastened (R) Rear Fastened <u>> For Overmolded with Cable</u> (A) With Strain Relief (B) Without Strain Relief <u>> For Field installable</u> (B) Without Strain Relief									
Connector (Housing) Gender (M) Male Connector (F) Female Connector									
Contact Gender (M) Male (C) Combo (F) Female									
Assemble Style <u>> For Receptacle</u> (S) Solder Type (B) Screw in Type (C) Crimp Type <u>> For Overmolded with Cable</u> (M) Overmolded with Cable <u>> For Field Installable</u> (A) Field installable (Solder) (B) Screw in Type (C) Crimp Type									
Mating Style (S) Screw Thread (L) 2 or 3 Points Lock Bayonet (T) 3 Points Lock Bayonet									
Backshell <u>> For Receptacle</u> (C) Circular (S) Square <u>> For Overmolded with Cable</u> (L) Straight (R) Right Angle <u>> For Field Installable</u> (L) Straight (R) Right Angle									
Waterproof Rating (6) IP 66 (7) IP 67 (8) IP 68									
More Information <u>> For Receptacle</u> 001, 002, 003..... Without Cable : Different Versions <u>> For Overmolded with Cable</u> (□)+(■) : Cable Type + Cable Length EX. (A01) = UL2464 Cable + 1M (■) : Cable Length (A) UL2464 Cable (D) SJTW Cable From 1M to 99M (B) Power Cable(TC-ER) (E) H05 Cable EX. (01) = 1M (C) SJTOW Cable (F) H07 Cable <u>> For Field Installable</u> (001) Cable OD range 12-16mm (002) Cable OD range 09-12mm									

* Recommended For Inverter Application


** Recommended For LED Application

[Note] Design and specification are subject to change without notice.

Physical Dimension

Receptacle Cut-Out


Panel Cut-Out



Connector(Housing) Gender Current Rating*	Type	L / W		OD	L / W		OD
Connector Gender		Male			Female		
8A (PWE)	C	31.1	21.55	31.1	21.55		
12A (PWF)	C	31.1	21.55	31.1	21.55		
16A (PWG)	C	31.1	21.60	31.1	21.60		
20A (PWC)	B	19.4	20.80	-	-		
25A (PWH)	B	30.2	32.00	-	-		
	A	23.2	25.20	-	-		
20A+2A (PWCU)	B	19.4	20.80	-	-		
30A (PWL)	D	23.0	23.00	-	-		
30A (PWJ)	A	23.2	25.20	-	-		

Unit: mm

Connector Dimension




Connector(Housing) Gender Current Rating*	Type	L		OD / W		Recommend Panel Thickness
Connector Gender		Female	Male	Female	Male	Female & Male
8A (PWE)	II	27.50	26.50	38.00	38.00	-
12A (PWF)	II	27.50	26.50	38.00	38.00	-
16A (PWG)	II	32.40	31.00	38.00	38.00	-
20A (PWC)	I	-	18.00	-	25.00	4.5 mm Max.
25A (PWH)	I	-	55.00	-	40.00	5.0 mm Max.
		-	47.00	-	35.00	0.5~8 mm
20A+2A (PWCU)	I	-	18.00	-	25.00	4.5 mm Max.
30A (PWL)	III	-	34.60	-	31.80	-
30A (PWJ)	I	-	47.00	-	35.00	0.5~8 mm

Unit: mm

*Current rating represents a maximum value for a largest wire size recommended for use.


Overmolded with Cable




Connector(Housing) Gender Current Rating*	L		OD	
	Female	Male	Female	Male
8A (PWE)	70.3	72.0	30.2	30.2
12A (PWF)	70.3	72.0	30.2	30.2
20A (PWC)	60.0	65.5	22.2 (L)** 23.0 (T)**	18.0
25A (PWH)	91.55	100.4	40.0	31.75
20A+2A (PWCU)	60.0	65.5	22.2	18.0

** (L) 2 Points Lock Bayonet | (T) 3 Points Lock Bayonet

Field Installable



(See 3rd top-right hand chart)



(See bottom right hand chart)

Connector(Housing) Gender Current Rating*	L		OD	
	Female	Male	Female	Male
8A (PWE)	60.7	60.4	30.2	30.2
12A (PWF)	60.7	60.4	30.2	30.2
16A (PWG)	67.0	67.0	30.2	30.2
20A (PWC)	48.15	-	22.2	-
20A+2A (PWCU)	88.4	91.0	33.0	26.9
	48.15	-	22.2	-
25A (PWH)	87.4	84.1	38.0	38.0
30A (PWL)	92.14	-	35.2	-
30A (PWJ)	87.4	84.1	38.0	38.0

Connector(Housing) Gender Current Rating	L [A]	L [B]	OD
	Female / Male	Female / Male	Female / Male
16A (PWG)	62.0	54.0	30.2

Unit: mm

*Current rating represents a maximum value for a largest wire size recommended for use.

[Note] Design and specification are subject to change without notice.

Contact Configuration

	8A (PWE)		12A (PWF)		16A (PWG)		20A (PWC)	
4 5	MM or FF	MF or FM	MM or FF	MF or FM	MM or FF	MF or FM	MM or FF	MF or FM
2Contacts (02)			 R C F					
3Contacts (03)			 R C F				 R C	 R C
4Contacts (04)			 R C F		 F			
5Contacts (05)	 R C F							
6Contacts (06)	 R C F							
7Contacts (07)	 R C F							
12Contacts (12)								

25A (PWH)			20A+2A (PWCU)			30A (PWL)/(PWJ)		
MM or FF	MF or FM		MM or FF	MF or FM		MM or FF	MF or FM	
								
R	C					R		F
								
			R	C	F	R	C	F
								
R		F	R		F			
								
					F			

R: receptacle

C: overmolded with cable

F: field installable

-  8A (PWE) 1
 12A (PWF)
 16A (PWG)
 20A (PWC)
 25A (PWH)
 20A+2A (PWCU)
 30A (PWL)

Number of Contacts: 2

Ex.2 contacts (02)

Connector (Housing) Gender: 4

Male(M) or Female(F)

Contact Gender: 5

Male(M) or Female(F)

More to Choose: 6


• Solder (S)

- Solder Cup

- Solder Contact



• Screw In (B)




• Crimped (C)



Product Features

┘ Receptacle



Backshell 8



Circular (C)



Square (S)


Mating Style 7



2 Points Lock Bayonet (L)




3 Points Lock Bayonet (T)
 (With or without Unlocking
 Tool)




Screw Thread (S)

Connector Body(Style) 3




Rear Fastened (R)



Front Fastened (P)

┘ Overmolded with Cable



Backshell 8



Straight
 (L)

Mating Style 7



2 Points Lock Bayonet (L)




Screw Thread (S)

Connector Body(Style) 3




With Strain Relief (A)



Without Strain Relief (B)


┘ Field Installable



Backshell 8



Straight
 (L)



Right Angle
 (R)

Mating Style 7



2 Points Lock Bayonet (L)




3 Points Lock Bayonet (T)
 (With or without Unlocking
 Tool)



Screw Thread (S)



Connector Body(Style) 3



Without Strain Relief (B)




Find Our Standard Products

└ In-line

• Male Connector (Housing) • Male Contacts • Screw Thread		Overmolded with Cable	Overmolded with Cable	Field Installable
				
Current Rating (Code)	Contacts ②	Male Connector (M) Male Contacts (M)	Female Connector (F) Female Contacts (F)	Female Connector (F) Female Contacts (F)
8A (PWE)	05,06,07	PWE- ② AMMM-SL7A $\underline{\text{XX}}$ *	PWE- ② AFFM-SL7A $\underline{\text{XX}}$ *	PWE- ② BFFA-SL7001
12A (PWF)	02,03,04	PWF- ② AMMM-SL7A $\underline{\text{XX}}$ *	PWF- ② AFFM-SL7A $\underline{\text{XX}}$ *	PWF- ② BFFA-SL7001
25A (PWH)	03	PWH-03AMMM-SL7A $\underline{\text{XX}}$ *	PWH-03AFFM-SL7A $\underline{\text{XX}}$ *	—



* $\underline{\text{XX}}$: Choose the cable length from 01~99m

└ In-line

• Female Connector (Housing) • Female Contacts • Screw Thread		Overmolded with Cable	Overmolded with Cable	Field Installable
				
Current Rating (Code)	Contacts ②	Female Connector (F) Female Contacts (F)	Male Connector (M) Male Contacts (M)	Male Connector (M) Male Contacts (M)
8A (PWE)	05,06,07	PWE- ② AFFM-SL7A $\underline{\text{XX}}$ *	PWE- ② AMMM-SL7A $\underline{\text{XX}}$ *	PWE- ② BMMA-SL7001
12A (PWF)	02,03,04	PWF- ② AFFM-SL7A $\underline{\text{XX}}$ *	PWF- ② AMMM-SL7A $\underline{\text{XX}}$ *	PWF- ② BMMA-SL7001
25A (PWH)	03	PWH-03AFFM-SL7A $\underline{\text{XX}}$ *	PWH-03AMMM-SL7A $\underline{\text{XX}}$ *	—

* $\underline{\text{XX}}$: Choose the cable length from 01~99m




└ In-line

• Female Connector (Housing) • Female Contacts • Screw Thread		Field Installable	Overmolded with Cable	Field Installable
				
		⑧ Choose straight (L) or right angle (R)		⑧ Choose straight (L) or right angle (R)
Current Rating (Code)	Contacts ②	Female Connector (F) Female Contacts (F)	Male Connector (M) Male Contacts (M)	Male Connector (M) Male Contacts (M)
8A (PWE)	05~07	PWE- ② BFFA-SL7001	—	PWE- ② BMMA-SL7001
12A (PWF)	02~04	PWF- ② BFFA-SL7001	—	PWF- ② BMMA-SL7001
16A (PWG)	04	PWG-04BFFB-S ⑧ 7 $\underline{\text{XXX}}$ *	—	PWG-04BMMS-S ⑧ 7 $\underline{\text{XXX}}$ *

* $\underline{\text{XXX}}$: Choose Pin Plated: Gold Plated (001), Silver Plated (002) to Tin Plated (003)

[Note] Design and specification are subject to change without notice.


In-line

• Male Connector (Housing) • Male Contacts • 2 Points Lock Bayonet & 3 Points Lock Bayonet		Overmolded with Cable 	Overmolded with Cable 	Field Installable 
Current Rating (Code)	Contacts	Male Connector (M) Male Contacts (M)	Female Connector (F) Female Contacts (F)	Female Connector (F) Female Contacts (F)
20A (PWC)	03	PWC-03AMMM-LL7AXX* PWC-03AMMM-LL7BXX* PWC-03AMMM-LL7DXX* PWC-03AMMM-LL7EXX* PWC-03BMMM-LL7DXX* PWC-03BMMM-LL7EXX* PWC-03AMMM-TL7AXX* PWC-03AMMM-TL7BXX*	PWC-03AFFM-LL7AXX* PWC-03AFFM-LL7BXX* PWC-03AFFM-LL7DXX* PWC-03AFFM-LL7EXX* PWC-03BFFM-LL7DXX* PWC-03BFFM-LL7EXX* PWC-03AFFM-TL7AXX* PWC-03AFFM-TL7BXX*	PWC-03BFFA-LL7XXX** PWC-03BFFA-TL7001
20A+2A (PWCU)	04	PWCU-04AMMM-LL7AXX* PWCU-04AMMM-LL7BXX* PWCU-04AMMM-TL7AXX* PWCU-04AMMM-TL7BXX*	PWCU-04AFFM-LL7AXX* PWCU-04AFFM-LL7BXX* PWCU-04AFFM-TL7AXX* PWCU-04AFFM-TL7BXX*	PWCU-04BFFA-LL7XXX** PWCU-04BFFA-TL7001

* XX: Choose the cable length from 01~99m



** XXX: Select UL (002) or Non-UL (001)

In-line




• Female Connector (Housing) • Female Contacts • 2 Points Lock Bayonet		Overmolded with Cable 	Overmolded with Cable 	Field Installable
Current Rating (Code)	Contacts	Female Connector (F) Female Contacts (F)	Male Connector (M) Male Contacts (M)	-
20A (PWC)	03	PWC-03AFFM-LL7AXX* PWC-03AFFM-LL7BXX* PWC-03AFFM-LL7DXX* PWC-03AFFM-LL7EXX*	PWC-03AMMM-LL7AXX* PWC-03AMMM-LL7BXX* PWC-03AMMM-LL7DXX* PWC-03AMMM-LL7EXX*	-
20A+2A (PWCU)	(1+3)	PWCU-04AFFM-LL7AXX* PWCU-04AFFM-LL7BXX*	PWCU-04AMMM-LL7AXX* PWCU-04AMMM-LL7BXX*	-

* XX: Choose the cable length from 01~99m

In-line

• Female Connector (Housing) • Female Contacts • 3 Points Lock Bayonet		Field Installable 	Overmolded with Cable 	Field Installable
Current Rating (Code)	Contacts	Female Connector (F) Female Contacts (F)	Male Connector (M) Male Contacts (M)	Male Connector (M) Male Contacts (M)
20A+2A (PWCU)	(6+6)	PWCU-12BFFA-TL7001	-	PWCU-12BMMA-TL7001


In-line

• Male Connector (Housing) • Male Contacts • 3 Points Lock Bayonet • Unlock Tool Needed (Part Number: ANB00010649) 		Field Installable 	Overmolded with Cable 	Field Installable
Current Rating (Code)	Contacts	Male Connector (M) Male Contacts (M)	Female Connector (F) Female Contacts (F)	Female Connector (F)** Female Contacts (F)
25A (PWH)	05	PWH-05BMMC-LL8XXX*	-	PWH-05BFFC-LL8XXX*
30A (PWJ)	03	PWJ-03BMMB-LL8XXX*	-	PWJ-03BFFB-LL8XXX*

* XXX: Choose the cable OD range 12~16mm (001) or OD 09~12mm (002)

** The unlock tool is packed with the female connector to sell.



In-line

• Male Connector (Housing) • Female Contacts • 3 Points Lock Bayonet • Unlock Tool Needed (Part Number: ANB00010649) 		Field Installable	Overmolded with Cable	Field Installable
				
Current Rating (Code)	Contacts	Male Connector (M) Female Contacts (F)	Female Connector (F) Male Contacts (M)	Female Connector (F)** Male Contacts (M)
25A (PWH)	05	PWH-05BMFC-LL8XXX*	-	PWH-05BFMC-LL8XXX*
30A (PWJ)	03	PWJ-03BMFB-LL8XXX*	-	PWJ-03BFMB-LL8XXX*

* XXX: Choose the cable OD range 12~16mm (001) or OD 09~12mm (002)

** The unlock tool is packed with the female connector to sell.



In-line

• Male Connector (Housing) • Male Contacts • 2 Points Lock Bayonet & 3 Points Lock Bayonet		Overmolded with Cable	Overmolded with Cable	Field Installable
				
Current Rating (Code)	Contacts	Male Connector (M) Female Contacts (F)	Female Connector (F) Male Contacts (M)	Female Connector (F) Male Contacts (M)
20A (PWC)	03	PWC-03AMFM-LL7AXX* PWC-03AMFM-LL7BXX* PWC-03AMFM-LL7DXX* PWC-03AMFM-LL7EXX* PWC-03BMFM-LL7DXX* PWC-03BMFM-LL7EXX* PWC-03AMFM-TL7AXX* PWC-03AMFM-TL7BXX*	PWC-03AFMM-LL7AXX* PWC-03AFMM-LL7BXX* PWC-03AFMM-LL7DXX* PWC-03AFMM-LL7EXX* PWC-03BFMM-LL7DXX* PWC-03BFMM-LL7EXX* PWC-03AFMM-TL7AXX* PWC-03AFMM-TL7BXX*	PWC-03BFMA-LL7XXX**
20A+2A (PWCU)	04	PWCU-04AMFM-LL7AXX* PWCU-04AMFM-LL7BXX*	PWCU-04AFMM-LL7AXX* PWCU-04AFMM-LL7BXX*	-

* XX: Choose the cable cable length from 1~99m

** XXX: Select UL (002) or Non-UL (001)



Receptacle and Mating Pair

• Female Connector (Housing) • Female Contacts • Screw Thread		Receptacle	Overmolded with Cable	Field Installable
				
		8 Choose straight (L) or right angle (R)		
Current Rating (Code)	Contacts 2	Female Connector (F) Female Contacts (F)	Male Connector (M) Male Contacts (M)	Male Connector (M) Male Contacts (M)
8A (PWE)	05~07	PWE-2 PFFS-SC7001	PWE-2 AMMM-SL7A _{XX} **	PWE-2 BMMA-SL7001
12A (PWF)	02~04	PWF-2 PFFS-SC7001	PWF-2 AMMM-SL7A _{XX} **	PWF-2 BMMA-SL7001
16A (PWG)	04	PWG-04PFFB-SC7 _{XX} *	—	PWG-04BMMB-S 8 7 _{XX} *

* Choose Pin Plated: Gold Plated (001) / Silver Plated (002) / Tin Plated (003)

** Choose the cable length from 01~99m




Receptacle and Mating Pair

• Male Connector (Housing) • Male Contacts • Screw Thread		Receptacle	Overmolded with Cable	Field Installable
				
		8 Choose straight (L) or right angle (R)		
Current Rating (Code)	Contacts 2	Male Connector (M) Male Contacts (M)	Female Connector (F) Female Contacts (F)	Female Connector (F) Female Contacts (F)
8A (PWE)	05~07	PWE-2 PMMS-SC7001	PWE-2 AFFM-SL7A _{XX} **	PWE-2 BFFA-SL7001
12A (PWF)	02~04	PWF-2 PMMS-SC7001	PWF-2 AFFM-SL7A _{XX} **	PWF-2 BFFA-SL7001
16A (PWG)	04	PWG-2 PMMB-SC7 _{XX} *	—	PWG-04BFFB-S 8 7 _{XX} *
25A (PWH)	03	PWH-03PMMB-SC7001	PWH-03AFFM-SL7A _{XX} **	—

* Choose Pin Plated: Gold Plated (001) / Silver Plated (002) / Tin Plated (003)




** Choose the cable length from 01~99m

Receptacle and Mating Pair

• Male Connector (Housing) • Male Contacts • 2 Points Lock Bayonet		Receptacle 	Overmolded with Cable 	Field Installable 
Current Rating (Code)	Contacts	Male Connector (M) Male Contacts (M)	Female Connector (F) Female Contacts (F)	Female Connector (F) Female Contacts (F)
20A (PWC)	03	PWC-03PMMS-LC7001 (UL) PWC-03RMMS-LC7001 (Non UL) PWC-03RMMS-LC7002 (UL)	PWC-03AFFM-LL7A XX * PWC-03AFFM-LL7B XX * PWC-03AFFM-LL7D XX * PWC-03AFFM-LL7E XX * PWC-03BFFM-LL7D XX * PWC-03BFFM-LL7E XX *	PWC-03BFFA-LL7 XXX **
20A+2A (PWCU)	(3+1)	PWCU-04RMMS-LC7001 (Non UL) PWCU-04RMMS-LC7002 (UL)	PWCU-04AFFM-LL7A XX * PWCU-04AFFM-LL7B XX *	-


* ~~XX~~: Choose the proper cable length from 01~99m** ~~XXX~~: Select UL (002) or Non-UL (001)

Receptacle and Mating Pair

• Male Connector (Housing) • Male Contacts • 3 Points Lock Bayonet		Receptacle 	Overmolded with Cable  ** Cable length from 1~99m for your connector	Field Installable  ***Selecting UL(002) or Non-UL (001)
Current Rating (Code)	Contacts	Male Connector (M) Male Contacts (M)	Female Connector (F) Female Contacts (F)	Female Connector (F) Female Contacts (F)
20A (PWC)	03	PWC-03RMMS-TC7001	PWC-03AFFM-TL7A <u>XX</u> * PWC-03AFFM-TL7B <u>XX</u> *	-
30A (PWL)	03	PWL-03PMMB-TS7001	-	PWL-03BFFA-TL7 <u>XXX</u> **

* XX: Choose the proper cable length from 01~99m** XXX: Select UL (002) or Non-UL (001)




Receptacle and Mating Pair

• Male Connector (Housing) • Male Contacts • 3 Points Lock Bayonet • PWH For Inverter Application • Unlock Tool Needed  (Part Number: ANB00010649)		Receptacle 	Overmolded with Cable	Field Installable  UL 6703A Certification (E-Number 346280)
Current Rating (Code)	Contacts	Male Connector (M) Male Contacts (M)	Female Connector (F) Female Contacts (F)	Female Connector (F)* Female Contacts (F)
25A (PWH)	05	PWH-05PMMC-LC8001	-	PWH-05BFFC-LL8 <u>XXX</u> **
30A (PWJ)	03	PWJ-03PMMB-LC8001	-	PWJ-03BFFB-LL8 <u>XXX</u> **

* The unlock tool is packed with the female connector to sell.

** XXX: Select the cable OD range 12~16mm (001) or OD 09~12mm (002)




Receptacle and Mating Pair

• Male Connector (Housing) • Female Contacts • 2 Points Lock Bayonet & 3 Points Lock Bayonet		Receptacle	Overmolded with Cable	Field Installable
				
Current Rating (Code)	Contacts	Male Connector (M) Female Contacts (F)	Female Connector (M) Male Contacts (F)	Female Connector (M) Male Contacts (F)
20A (PWC)	03	PWC-03PMFS-LC7001 PWC-03RMFS-LC7XXX* PWC-03RMFS-TC7001	PWC-03AFMM-LL7AXX** PWC-03AFMM-LL7BXX** PWC-03AFMM-LL7DXX** PWC-03AFMM-LL7EXX** PWC-03AFMM-TL7AXX** PWC-03AFMM-TL7BXX**	PWC-03BFMA-LL7XXX* PWC-03BFMA-TL7001
20A+2A (PWCU)	(3+1)	PWCU-04RMFS-LC7XXX*	PWCU-04AFMM-LL7AXX** PWCU-04AFMM-LL7BXX**	PWCU-04BFMA-LL7002



* XXX: Select UL (002) or Non-UL (001)

** XX: Choose the proper cable length from 01~99m

Receptacle and Mating Pair


• Male Connector (Housing) • Female Contacts • 3 Points Lock Bayonet		Receptacle	Overmolded with Cable	Field Installable
				 Non-UL (001)  UL(002)
Current Rating (Code)	Contacts	Male Connector (M) Female Contacts (F)	Female Connector (F) Male Contacts (M)	Female Connector (F) Male Contacts (M)
30A (PWL)	03	PWL-03PMFB-TS7001	-	PWL-03BFMA-TL7XXX*

* XXX: Select UL (002) or Non-UL (001)

• Male Connector (Housing) • Female Contacts • 3 Points Lock Bayonet • PWJ & PWH For Inverter Application • Unlock Tool Needed  (Part Number: ANB00010649)		Receptacle	Overmolded with Cable	Field Installable
				 UL 6703A Certification (E-Number 346280)
Current Rating (Code)	Contacts	Male Connector (M) Female Contacts (F)	Female Connector (F) Male Contacts (M)	Female Connector (F)* Male Contacts (M)
25A (PWH)	05	PWH-05PMFC-LC8001	-	PWH-05BFMC-LL8XXX**
30A (PWJ)	03	PWJ-03PMFB-LC8001	-	PWJ-03BFMB-LL8XXX**

* The unlock tool is packed with the female connector to sell. ** XXX: Select the cable OD range 12~16mm (001) or OD 09~12mm (002)

Blank lined paper for writing.




M Series Sensor Connector




Range Overview


Receptacle to Overmolded with Cable




Receptacle to Field Installable




In Line



Others




Accessories




T Cable
See page 21-2




Y Cable
See page 21-3



T Adaptor
See page 21-5



Y Adaptor
See page 21-6



I Adaptor
See page 21-8



Waterproof Cap
See page 21-14

Specification

Identifications	M8, M10.5, M12 (A, B, D code), Heavy Duty Shielded Connector, M23
Description	Receptacle Overmolded with Cable Field Installable
Current Rating / Data	1.5A~28A
Material	Contacts: Copper Alloy, Gold Plated Connector Body (Housing) : Nylon+GF or PU, UL Recognized Metal Screw Nut: Zinc Alloy or Copper Alloy, Nickel Plated
Waterproof Rating	IP65, IP67~68
Temperature Range	Receptacle: -40°C~105°C Overmolded with Cable: PVC Cable: -20°C~80°C PU Cable: -20°C~85°C Field Installable: -40°C~105°C * Higher working temperature upon request.
Contact Resistance	≤ 10mΩ
Standard Cable Length	01~99M
Mating Cycle	100*Minimum
Vibration	10 ~ 500 Hz and 0.35 mm
Standards	IEC 61076-2-101 IEC 61076-2-104

* Design and specification are subject to change without notice.

Ordering Information

Specification / Size

>M8 Size

- (8) M8
(8P) M8 (Plastic)
(8A) M8 W/ KEY
(8AP) M8 W/ KEY (Plastic)

>M10.5 Size

- (10S) M10.5

>M12 Size:

- (12) M12 A-Coded
(12L) M12 A-Coded inserted with LED
(12P) M12 A-Coded (Plastic)
(12S) M12 A-Coded (Shielded)
(12B) M12 B-Coded
(SBP) M12 B-Coded (Plastic)
(SBS) M12 B-Coded (Shielded)
(12D) M12 D-Coded
(SDP) M12 D-Coded (Plastic)
(SDS) M12 D-Coded (Shielded)

>Heavy Duty Shielded Connector,

- (HB20) Metal, Salt Spray Test 500H, 10A
(LB20) Metal, Salt Spray Test 48H, 10A
(HC20) Metal, Salt Spray Test 500H, 20A
(LC20) Metal, Salt Spray Test 48H, 20A
(HD20) Metal, Salt Spray Test 500H, 5A
(LD20) Metal, Salt Spray Test 48H, 5A
>M23 Size
(LJ23) Metal, Salt Spray Test 48H, 28A

Number of Contacts

02, 03..., 14...Contacts

EX. (02) = 2 Contacts

Connector Body (Style)

> For Receptacle

- (P) Panel

> For Overmolded with Cable

- (A) With Strain Relief
(B) Without Strain Relief

> For Field installable

- (B) Without Strain Relief
(D) With Ground Pin

Connector (Housing) Gender

- (M) Male Connector

- (F) Female Connector

Contact Gender

- (M) Male
(F) Female

- (I) I style (Male+Female)

Assemble Style

> For Receptacle

- (S) Solder Type
(P) 180° PCB Type
(R) 90° PCB Type
(C) Crimp Type

> For Field Installable

- (A) Field installable(Solder)
(B) Field installable(Screw)
(C) Field installable(Crimp)
(D) Field Installable (IDC)

> For Overmolded with Cable

- (M) Overmolded with Cable

Mating Style

- (S) Screw Thread

- (Q) Quick

Backshell

> For Receptacle

- (C) Circular (Rear Fastened)
(F) Hexagonal Front Fastened
(H) Rear Hexagonal (Rear Fastened)

> For Receptacle

- (W) Square Front Fastened with Screw
(N) Square Rear Fastened with Nut

> For Overmolded with Cable

- (L) Straight
(R) Right Angle

> For Field Installable

- (L) Straight
(R) Right Angle

Waterproof Rating

- (5) IP65 (Quick Type)
(7) IP 67

- (8) IP 68

Cable information

> For Receptacle

- (001) / (002) : PG9
(003) / (004) / (005) : M16
(006) : M12

> For Overmolded with Cable

- (□)+(■) : Cable Type + Cable Length
EX. (A01) = UL2464 Cable + 1M
(□) : Cable Type (■) : Cable Length
(A) PVC UL2464 Cable From 1M to 99M
(B) PU VW-1 Cable EX.(01)= 1M

> For Receptacle with wire harness


- (□)+(■) : Cable Type + Wire Length
EX. (A15) = UL 1007 (For M8) + 150mm
(□) Cable Type
(A) UL 1007 (For M8)
(B) UL1061 (For M12-PG9 W/ O Logo)
(C) UL1061 (For M12-M16 W / O Logo)
(■) Wire length
(15) 150mm
(30) 300mm
(50) 500mm

* UL2517 / UL20549 available by 2014

Physical Dimension

Receptacle


Panel Cut-Out



Size		Dimension		Type	L / W	OD	Type	L / W	OD
Size	Thread Description	Female			Male				
M105	M10.5 X 0.75	-	-	-	A	-	-	-	10.9
M8	M8 X 1.0	B	7.1	8.1	B	7.1	8.1	-	-
		-	-	-	A	-	-	-	8.1
M12	M12 X 1.0 - PG9	B	13.6	15.4	B	13.6	15.4	-	-
	M12 X 1.0 - M16.0 X 1.5	B	13.6	16.1	B	13.6	16.1	-	-
	M12.0 X 1.0	B	10.5	12.2	B	10.5	12.2	-	-
HDSC*	M22 X 1.0	-	-	-	C	19.2	20.2	-	-
		-	-	-	D	19.2 / 23.0	20.2	-	-
M23	M23 X 1.0	-	-	-	C	24.4	25.1	-	-

*HDSC: Heavy Duty Shielded Connector



Connector Dimension



Series		Receptacle				Panel Thickness		
Conn. Gender	Type	Female		Male				
		L (A)	L (B)	L (A)	L (B)	Front Fastened	Rear Fastened	
M8		Straight	18.0	13.8	16.4	11.5	3.0 mm Max.	3.5 mm Max.
M105		Straight	-	-	18.0	15.0	-	6.0 mm Max.
M12	PG9/ M16	Straight	20.0	20.8	20.5	20.8	4.5mm Max. 4.0mm Max.(Plastic)	4.5mm Max.
		Right Angle	20.0	20.8	20.5	20.8		
	M12* 1.0	Right Angle	16.9	15.0	16.2	15.0	3.0mm Max.	
HDSC*		Straight	-	-	23.5	29.0	9.0mm Min.	5.0 mm Max.
M23		Straight	-	-	36.0	29.0	6.0 mm Max.	-

*HDSC: Heavy Duty Shielded Connector

Overmolded with Cable




Size		Dimension		L	OD
Size	Thread Description	Female			
M105	M10.5 X 0.75	36.5	8.4	-	-

Size		Dimension		L		OD	
Size	Thread Description	Female	Male	Female	Male	Female	Male
M105	M10.5 X 0.75	41.5	-	12.0	-	-	-
M8	M8 X 1.0	38.1	42.7	10.1	10.5	-	-
M12	M12.0 X 1.0	43.3	44.4	14.5	14.4	-	-


Dimensions are shown in millimeters

M Series Sensor Connector I Physical Dimension


Receptacle I Overmolded with Cable I Field Installable



* Screw thread type





* Snap-In type



Size \ Dimension		L		OD	
Size	Type	Female	Male	Female	Male
M8	Screw Thread M8 X 1.0	36.0	40.5	10.1	10.5
M8	Snap-In M8 X 1.0	36.5	-	8.4	-
M105	Screw Thread M10.5 X 0.75	37.2	-	12.0	-
M12	Screw Thread M12.0 X 1.0	43.3	44.4	14.5	14.4



Size \ Dimension		L		OD	
Size	Thread Description	Female	Male	Female	Male
M12	M12.0 X 1.0	39.2	40.1	14.5	14.5



Size \ Dimension		L [A]		L [B]		OD	
Size	Thread Description	Female	Male	Female	Male	Female	Male
M105	M10.5 X 0.75	24.0	-	24.0	-	12.0	-
M8	M8 X 1.0	20.7	20.7	20.0	25.5	10.1	10.5
M12	M12.0 X 1.0	28.0	28.0	27.9	28.9	14.5	14.4

Size \ Dimension		L [A]		L [B]		OD	
Size	Thread Description	Female	Male	Female	Male	Female	Male
M105	M10.5 X 0.75	19.0	-	24.0	-	12.0	-
M8	M8 X 1.0	25.0	25.0	21.0	25.6	10.1	10.5
M12	M12.0 X 1.0	35.0	35.0	26.9	27.9	14.5	14.4

Field Installable



Size \ Dimension		Pin Type	L		OD	
Size	Type		Female	Male	Female	Male
M8	M8 X 1.0	Screw In	55.4	59.1	16.7	16.7
M12	M12.0 X 1.0	Solder	40.5	41.8	14.5	14.4
		Screw In	61.3	61.3	20.8	20.8
M12 Plastic	M12.0 X 1.0	Solder	40.5	41.8	14.8	13.8
		Screw In	61.3	61.3	20.8	20.4
HDSC*	M22 X 1.0	-	72.5	-	27.7	-
M23	M23 X 1.0	-	73.0	-	28.5	-

Size \ Dimension		Pin Type	L [A]		L [B]		OD	
Size	Thread Description		Female	Male	Female	Male	Female	Male
M12	M12.0 X 1.0	Screw In	38.9	38.9	52.3	52.3	20.8	20.8
M12 Plastic			38.9	38.9	52.3	52.3	20.8	20.8

Dimensions are shown in millimeters

*HDSC: Heavy Duty Shielded Connector


* Design and specification are subject to change without notice.

Contact Configuration

	M8			M105	M12 A Code	M12 B Code	M12 D Code	M12 I Style				
	(1.5A)	(3A)		(2A)	(3~5P: 4A 8P: 2A)	(4A)	(4A)	(4A)				
④ ⑤	MM or FF	MM or FF	MM or FF	MF or FM	MM or FF	MF or FM	MM or FF	MF or FM	MM or FF	MF or FM	MMF or FFM	MF or FM
2Pin (02)												
		R C F		R C								
3Pin (03)												
		R C F	R C F	R C	R C F		R F		R F			
4Pin (04)												
		R C F	R C F	R C	R C F		R C F		R C F			
5Pin (05)												
	R C F			R C	R C F		R C F		R C F		R C F	
6Pin (06)												
	R C F											
7Pin (07)												
8Pin (08)												
					R C F							
10Pin (10)												
12Pin (12)												
14Pin (14)												

More to know:

No. of Poles & Contact Configuration (Connection side view)



Color Identification:

1 = Brown, 2 = White, 3 = Blue, 4 = Black, 5 = Green

Color Identification:

1 = White, 2 = Brown, 3 = Green, 4 = Yellow,

5 = Gray, 6 = Pink, 7 = Blue, 8 = Red

HDSC* (5A)		HDSC* (10A)		HDSC* (20A)		M23 (28A)	
MM or FF	MF or FM	MM or FF	MF or FM	MM or FF	MF or FM	MM or FF	MF or FM
							
					R F		
							
					R F		
							
			R F				
							
			R F				
							
						R F	R F
							
			R F				
							
	R F						
							
	R F						
							
	R F						

*HDSC: Heavy Duty Shielded Connector

M12 Panel Version	Screw Thread Size	Logo
001	M12XPG9	With Logo
002	M12XPG9	Without Logo
003	M12XM16.0X1.5	With Logo
004	M12XM16.0X1.5	Without Logo
005	M12XM16.0X1.5	Without Logo
006	M12X1.0	With Logo
007	M12X1.0	Without Logo

* Design and specification are subject to change without notice.

R: receptacle

C: overmolded with cable

F: field installable

-  1.5A (M8)
  2A (M105/M12 A)
  3A (M8)
  4A (M12 A/M12 B/M12 D/M12 I Style)
  5A (HDSC*)
  10A (HDSC*)
  20A (HDSC*)
  28A (M23)

Contact Number:

Ex.2 contacts (02)

Connector (Housing) Gender:

Male(M) or Female(F)

Contact Gender:


Male(M) or Female(F)

Male + Female (I)

More to Choose:

• Solder (S)


- Solder Cup



• PCB Type

- 90° PCB (R)

- 180° PCB (P)



More to know:

A-Code

B-Code


D-Code

I-Style



Product Features

Receptacle



Mating Style ⑦



Screw Thread (S)

Backshell ⑧




Circular (C)




Hexagonal (H)(F)



Square (N)(W)



Rear Fastened



Front Fastened (P)

Overmolded with Cable



Mating Style ⑦



Screw Thread (S)
(For M12)




Quick (Q)
(For M8)

Backshell ⑧



Straight
(L)



Right Angle
(R)

Connector Body(Style) ③




With Strain Relief (A)



Without Strain Relief (B)

Field Installable




Mating Style ⑦




Screw Thread (S)

Backshell ⑧




Straight (L)



Right Angle (R)

Connector Body(Style) ③




Without Strain Relief (B)


Find Our Standard Products

≧ M8 (Metal) > Receptacle > Male Connector > Front Fastened

> IEC 61076-2-104


					
Backshell: Hexagonal					
Type	2 Contacts	3 Contacts	4 Contacts	5 Contacts	6 Contacts
PCB Pin	-	8-03PMMP-SF7001	8-04PMMP-SF7001	-	-
Solder Pin	-	8-03PMMS-SF7001	8-04PMMS-SF7001	-	-
Wire Leads (150mm)	-	8-03PMMS-SF7A15	8-04PMMS-SF7A15	-	-
Wire Leads (300mm)	-	8-03PMMS-SF7A30	8-04PMMS-SF7A30	-	-
Wire Leads (500mm)	-	8-03PMMS-SF7A50	8-04PMMS-SF7A50	-	-

> with alignment Key


					
Backshell: Hexagonal					
Type	2 Contacts	3 Contacts	4 Contacts	5 Contacts	6 Contacts
PCB Pin	8A-02PMMP-SF7001	8A-03PMMP-SF7001	8A-04PMMP-SF7001	8A-05PMMP-SF7001	8A-06PMMP-SF7001
Solder Pin	8A-02PMMS-SF7001	8A-03PMMS-SF7001	8A-04PMMS-SF7001	8A-05PMMS-SF7001	8A-06PMMS-SF7001

≧ M8 (Metal) > Receptacle > Male Connector > Rear Fastened

> IEC 61076-2-104

					
Backshell: Hexagonal					
Type	2 Contacts	3 Contacts	4 Contacts	5 Contacts	6 Contacts
Solder Pin	-	8-03PMMS-SH7001	8-04PMMS-SH7001		
Wire Leads (150mm)	-	8-03PMMS-SH7A15	8-04PMMS-SH7A15	-	-
Wire Leads (300mm)	-	8-03PMMS-SH7A30	8-04PMMS-SH7A30	-	-
Wire Leads (500mm)	-	8-03PMMS-SH7A50	8-04PMMS-SH7A50	-	-

> with alignment Key

					
Backshell: Hexagonal					
Type	2 Contacts	3 Contacts	4 Contacts	5 Contacts	6 Contacts
Solder Pin	8A-02PMMS-SH7001	8A-03PMMS-SH7001	8A-04PMMS-SH7001	8A-05PMMS-SH7002	8A-06PMMS-SH7002

* Design and specification are subject to change without notice.

M8 (Metal)

Receptacle > Female Connector




Overmolded with Cable > Male Connector

IP 65 . 67 9


Receptacle | Unmated
Overmolded with Cable | Mated
Field Installable | Mated

└ M8 (Metal) Receptacle > Female Connector > Rear Fastened

> IEC 61076-2-104




					
Backshell: Hexagonal					
Type	2 Contacts	3 Contacts	4 Contacts	5 Contacts	6 Contacts
Solder Pin	-	8-03PFFS-SH7001	8-04PFFS-SH7001	-	-
Wire Leads (150mm)	-	8-03PFFS-SH715	8-04PFFS-SH715	-	-
Wire Leads (300mm)	-	8-03PFFS-SH730	8-04PFFS-SH730	-	-
Wire Leads (500mm)	-	8-03PFFS-SH750	8-04PFFS-SH750	-	-

> with alignment Key


					
Backshell: Hexagonal					
Type	2 Contacts	3 Contacts	4 Contacts	5 Contacts	6 Contacts
Solder Pin	8A-02PFFS-SH7001	8A-03PFFS-SH7001	8A-04PFFS-SH7001	8A-05PFFS-SH7002	8A-06PFFS-SH7002

└ M8 (Metal) > Overmolded with cable > Male Connector > Right Angle

> IEC 61076-2-104

					
Type	2 Contacts	3 Contacts	4 Contacts	5 Contacts	6 Contacts
With Strain Relief	-	8-03AMMM-SR7	8-04AMMM-SR7	-	-
Without Strain Relief	-	8-03BMMM-SR7	8-04BMMM-SR7	-	-


> with alignment Key

					
Type	2 Contacts	3 Contacts	4 Contacts	5 Contacts	6 Contacts
With Strain Relief	8A-02AMMM-SR7	8A-03AMMM-SR7	8A-04AMMM-SR7	8A-05AMMM-SR7	8A-06AMMM-SR7

Cable Type	1M	2M	5M	10M
PVC	A01	A02	A05	A10
PU	B01	B02	B05	B10





M8 (Metal) > Overmolded with cable > Male Connector > Straight

> IEC 61076-2-104

					
Type	2 Contacts	3 Contacts	4 Contacts	5 Contacts	6 Contacts
With Strain Relief	-	8-03AMMM-SL7	8-04AMMM-SL7	-	-
Without Strain Relief	-	8-03BMMM-SL7	8-04BMMM-SL7	-	-
> with alignment Key					
					
Type	2 Contacts	3 Contacts	4 Contacts	5 Contacts	6 Contacts
With Strain Relief	8A-02AMMM-SL7	8A-03AMMM-SL7	8A-04AMMM-SL7	8A-05AMMM-SL7	8A-06AMMM-SL7

M8 (Metal) > Overmolded with cable > Female Connector > Right Angle

> IEC 61076-2-104

					
Type	2 Contacts	3 Contacts	4 Contacts	5 Contacts	6 Contacts
With Strain Relief	-	8-03AFFM-SR7	8-04AFFM-SR7	-	-
Without Strain Relief	-	8-03BFFM-SR7	8-04BFFM-SR7	-	-
> with alignment Key					
					
Type	2 Contacts	3 Contacts	4 Contacts	5 Contacts	6 Contacts
With Strain Relief	8A-02AFFM-SR7	8A-03AFFM-SR7	8A-04AFFM-SR7	8A-05AFFM-SR7	8A-06AFFM-SR7




Cable Type	1M	2M	5M	10M
PVC	A01	A02	A05	A10
PU	B01	B02	B05	B10

* Design and specification are subject to change without notice.

M8 (Metal)





Overmolded with Cable > Female Connector

IP 67 . 68 **9**Receptacle | Unmated
Overmolded with Cable | Mated
Field Installable | Mated≧ **M8 (Metal) > Overmolded with cable > Female Connector > Straight****> IEC 61076-2-104**





					
Type	2 Contacts	3 Contacts	4 Contacts	5 Contacts	6 Contacts
With Strain Relief	-	8-03AFFM-SL7	8-04AFFM-SL7	-	-
Without Strain Relief	-	8-03BFFM-SL7	8-04BFFM-SL7	-	-
> with alignment Key					
					
Type	2 Contacts	3 Contacts	4 Contacts	5 Contacts	6 Contacts
With Strain Relief	8A-02AFFM-SL7	8A-03AFFM-SL7	8A-04AFFM-SL7	8A-05AFFM-SL7	8A-06AFFM-SL7

Cable Type	1M	2M	5M	10M
PVC	A01	A02	A05	A10
PU	B01	B02	B05	B10

M8 (Plastic) > Receptacle > Male Connector > Front Fastened

> IEC 61076-2-104					
					
	Backshell: Hexagonal				
Type	2 Contacts	3 Contacts	4 Contacts	5 Contacts	6 Contacts
PCB Pin	-	8P-03PMMP-SF7001	8P-04PMMP-SF7001	-	-
Solder Pin	-	8P-03PMMS-SF7001	8P-04PMMS-SF7001	-	-
> with alignment Key					
					
	Backshell: Hexagonal				
Type	2 Contacts	3 Contacts	4 Contacts	5 Contacts	6 Contacts
PCB Pin	8AP-02PMMP-SF7001	8AP-03PMMP-SF7001	8AP-04PMMP-SF7001	8AP-05PMMP-SF7001	8AP-06PMMP-SF7001
Solder Pin	8AP-02PMMS-SF7001	8AP-03PMMS-SF7001	8AP-04PMMS-SF7001	8AP-05PMMS-SF7001	8AP-06PMMS-SF7001

M8 (Plastic) > Overmolded with cable > Male Connector > Right Angle

> IEC 61076-2-104					
					
Type	2 Contacts	3 Contacts	4 Contacts	5 Contacts	6 Contacts
With Strain Relief	-	8P-03AMMM-SR7	8P-04AMMM-SR7	-	-
Without Strain Relief	-	8P-03BMMM-SR7	8P-04BMMM-SR7	-	-
> with alignment Key					
					
Type	2 Contacts	3 Contacts	4 Contacts	5 Contacts	6 Contacts
With Strain Relief	8AP-02AMMM-SR7	8AP-03AMMM-SR7	8AP-04AMMM-SR7	8AP-05AMMM-SR7	8AP-06AMMM-SR7



Cable Type	1M	2M	5M	10M
PVC	A01	A02	A05	A10
PU	B01	B02	B05	B10

* Design and specification are subject to change without notice.






M8 (Plastic)

Overmolded with Cable > Male / Female Connector

IP 67 . 68 **9**Receptacle | Unmated
Overmolded with Cable | Mated
Field Installable | Mated**≧ M8 (Plastic) > Overmolded with cable > Male Connector > Straight**



> IEC 61076-2-104					
					
Type	2 Contacts	3 Contacts	4 Contacts	5 Contacts	6 Contacts
With Strain Relief	-	8P-03AMMM-SL7	8P-04AMMM-SL7	-	-
Without Strain Relief	-	8P-03BMMM-SL7	8P-04BMMM-SL7	-	-
> with alignment Key					
					
Type	2 Contacts	3 Contacts	4 Contacts	5 Contacts	6 Contacts
With Strain Relief	8AP-02AMMM-SL7	8AP-03AMMM-SL7	8AP-04AMMM-SL7	8AP-05AMMM-SL7	8AP-06AMMM-SL7

≧ M8 (Plastic) > Overmolded with cable > Female Connector > Right Angle



> IEC 61076-2-104					
					
Type	2 Contacts	3 Contacts	4 Contacts	5 Contacts	6 Contacts
With Strain Relief	-	8P-03AFFM-SR7	8P-04AFFM-SR7	-	-
Without Strain Relief	-	8P-03BFFM-SR7	8P-04BFFM-SR7	-	-
> with alignment Key					
					
Type	2 Contacts	3 Contacts	4 Contacts	5 Contacts	6 Contacts
With Strain Relief	8AP-02AFFM-SR7	8AP-03AFFM-SR7	8AP-04AFFM-SR7	8AP-05AFFM-SR7	8AP-06AFFM-SR7

Cable Type	1M	2M	5M	10M
PVC	A01	A02	A05	A10
PU	B01	B02	B05	B10



M8 (Plastic) > Overmolded with cable > Female Connector > Straight

> IEC 61076-2-104					
					
Type	2 Contacts	3 Contacts	4 Contacts	5 Contacts	6 Contacts
With Strain Relief	-	8P-03AFFM-SL7	8P-04AFFM-SL7	-	-
Without Strain Relief	-	8P-03BFFM-SL7	8P-04BFFM-SL7	-	-
* Mating style (Quick) also available for 3 & 4 contacts					
> with alignment Key					
					
Type	2 Contacts	3 Contacts	4 Contacts	5 Contacts	6 Contacts
With Strain Relief	8AP-02AFFM-SL7	8AP-03AFFM-SL7	8AP-04AFFM-SL7	8AP-05AFFM-SL7	8AP-06AFFM-SL7
* Mating style (Quick) also available for 3 & 4 contacts					
Cable Type	1M	2M	5M	10M	
PVC	A01	A02	A05	A10	
PU	B01	B02	B05	B10	

M8 (Plastic) > Field Installable > Male Connector > Straight

					
Type	Contact Type	3 Contacts	4 Contacts	5 Contacts	6 Contacts
Without Strain Relief	Solder	-	-	-	-
	Screw-in	8P-03BMMB-SL7001	8P-04BMMB-SL7001		

M8 (Plastic) > Field Installable > Female Connector > Straight

					
Type	Contact Type	3 Contacts	4 Contacts	5 Contacts	6 Contacts
Without Strain Relief	Solder	-	-	-	-
	Screw-in	-	8P-04BFFB-SL7001	-	-






* Design and specification are subject to change without notice.

M10.5 (Metal)




Receptacle > Male Connector

Overmolded with Cable > Male Connector






IP 67 . 68 **9**Receptacle | Unmated
Overmolded with Cable | Mated
Field Installable | Mated**≧ M10.5 (Metal) > Receptacle > Male Connector > Rear Fastened**

				
Backshell: Hexagonal Backshell: Circular				
Type	2 Contacts	3 Contacts	4 Contacts	5 Contacts
Backshell: Hexagonal Solder Pin (180°)	105-02PMFS-SH7001	105-03PMFS-SH7001	105-04PMFS-SH7001	105-05PMFS-SH7001
Backshell: Circular Solder Pin (180°)	105-02PMFS-SC7001	105-03PMFS-SC7001	105-04PMFS-SC7001	105-05PMFS-SC7001

≧ M10.5 (Metal) > Overmolded with cable > Male Connector > Right Angle






				
Type	2 Contacts	3 Contacts	4 Contacts	5 Contacts
With Strain Relief	105-02AMMM-SR7A	105-03AMMM-SR7A	105-04AMMM-SR7A	105-05AMMM-SR7A
Without Strain Relief	105-02BFMM-SR7A	105-03BFMM-SR7A	105-04BFMM-SR7A	105-05BFMM-SR7A

≧ M10.5 (Metal) > Overmolded with cable > Male Connector > Straight






				
Type	2 Contacts	3 Contacts	4 Contacts	5 Contacts
With Strain Relief	105-02AFMM-SL7A	105-03AFMM-SL7A	105-04AFMM-SL7A	105-05AFMM-SL7A
Without Strain Relief	105-02BFMM-SL7A	105-03BFMM-SL7A	105-04BFMM-SL7A	105-05BFMM-SL7A

Cable Type	1M	2M	5M	10M
PVC	A01	A02	A05	A10
PU	B01	B02	B05	B10

M12 A (Metal) > Receptacle > Male Connector > Front Fastened






					
Backshell: Hexagonal					
Type	Mounting Thread	3 Contacts	4 Contacts	5 Contacts	8 Contacts
PCB Pin (180°)	PG9	12-03PMMP-SF8001	12-04PMMP-SF8001	12-05PMMP-SF8001	12-08PMMP-SF8001
	M16.0	12-03PMMP-SF8003 12-03PMMP-SF8004	12-04PMMP-SF8003 12-04PMMP-SF8004	12-05PMMP-SF8003 12-05PMMP-SF8004	12-08PMMP-SF8003 12-08PMMP-SF8004
PCB Pin (90°)	M12	12-03PMMR-SF7001	12-04PMMR-SF7001	12-05PMMR-SF7001	12-08PMMR-SF7001
	M12 (Shielded)	12S-03PMMR-SF7001	12S-04PMMR-SF7001	12S-05PMMR-SF7001	12S-08PMMR-SF7001
	PG9	12-03PMMR-SF8001	12-04PMMR-SF8001	12-05PMMR-SF8001	-
	M16.0	12-03PMMR-SF8003	12-04PMMR-SF8003	12-05PMMR-SF8003	-
Solder Pin (180°)	PG9	12-03PMMS-SF8001	12-04PMMS-SF8001	12-05PMMS-SF8001	12-08PMMS-SF8001
	M16.0	12-03PMMS-SF8003 12-03PMMS-SF8004	12-04PMMS-SF8003 12-04PMMS-SF8004	12-05PMMS-SF8003 12-05PMMS-SF8004	12-08PMMS-SF8003 12-08PMMS-SF8004
Wire Leads (150mm)	PG9	12-03PMMS-SF8B15	12-04PMMS-SF8B15	12-05PMMS-SF8B15	12-08PMMS-SF8B15
	M16.0	12-03PMMS-SF8C15	12-04PMMS-SF8C15	12-05PMMS-SF8C15	12-08PMMS-SF8C15
Wire Leads (300mm)	PG9	12-03PMMS-SF8B30	12-04PMMS-SF8B30	12-05PMMS-SF8B30	12-08PMMS-SF8B30
	M16.0	12-03PMMS-SF8C30	12-04PMMS-SF8C30	12-05PMMS-SF8C30	12-08PMMS-SF8C30
Wire Leads (500mm)	PG9	12-03PMMS-SF8B50	12-04PMMS-SF8B50	12-05PMMS-SF8B50	12-08PMMS-SF8B50
	M16.0	12-03PMMS-SF8C50	12-04PMMS-SF8C50	12-05PMMS-SF8C50	12-08PMMS-SF8C50

M12 A (Metal) > Receptacle > Male Connector > Rear Fastened





					
Type	Mounting Thread	3 Contacts	4 Contacts	5 Contacts	8 Contacts
Solder Pin (180°)	PG9	12-03PMMS-SH8001	12-04PMMS-SH8001	12-05PMMS-SH8001	12-08PMMS-SH8001
	M16.0	12-03PMMS-SH8003 12-03PMMS-SH8004	12-04PMMS-SH8003 12-04PMMS-SH8004	12-05PMMS-SH8003 12-05PMMS-SH8004	12-08PMMS-SH8003 12-08PMMS-SH8004
Wire Leads (150mm)	PG9	12-03PMMS-SH8B15	12-04PMMS-SH8B15	12-05PMMS-SH8B15	12-08PMMS-SH8B15
	M16.0	12-03PMMS-SH8C15	12-04PMMS-SH8C15	12-05PMMS-SH8C15	12-08PMMS-SH8C15
Wire Leads (300mm)	PG9	12-03PMMS-SH8B30	12-04PMMS-SH8B30	12-05PMMS-SH8B30	12-08PMMS-SH8B30
	M16.0	12-03PMMS-SH8C30	12-04PMMS-SH8C30	12-05PMMS-SH8C30	12-08PMMS-SH8C30
Wire Leads (500mm)	PG9	12-03PMMS-SH8B50	12-04PMMS-SH8B50	12-05PMMS-SH8B50	12-08PMMS-SH8B50
	M16.0	12-03PMMS-SH8C50	12-04PMMS-SH8C50	12-05PMMS-SH8C50	12-08PMMS-SH8C50

* Design and specification are subject to change without notice.






M12 A (Metal) > Receptacle > Female Connector > Front Fastened

					
Backshell: Hexagonal					
Type	Mounting Thread	3 Contacts	4 Contacts	5 Contacts	8 Contacts
PCB Pin (180°)	PG9	12-03PFFP-SF8001	12-04PFFP-SF8001	12-05PFFP-SF8001	12-08PFFP-SF8001
	M16.0	12-03PFFP-SF8003 12-03PFFP-SF8004 12-03PFFP-SF8005	12-04PFFP-SF8003 12-04PFFP-SF8004 12-04PFFP-SF8005	12-05PFFP-SF8003 12-05PFFP-SF8004 12-05PFFP-SF8005	12-08PFFP-SF8003 12-08PFFP-SF8004 12-08PFFP-SF8005
PCB Pin (90°)	M12	12-03PFFR-SF7001	12-04PFFR-SF7001	12-05PFFR-SF7001	12-08PFFR-SF7001
	M12 (Shielded)	12S-03PFFR-SF7001	12S-04PFFR-SF7001	12S-05PFFR-SF7001	12S-08PFFR-SF7001
	PG9	12-03PFFR-SF8001	12-04PFFR-SF8001	12-05PFFR-SF8001	-
	M16.0	12-03PFFR-SF8003	12-04PFFR-SF8003	12-05PFFR-SF8003	-
Solder Pin (180°)	PG9	12-03PFFS-SF8001	12-04PFFS-SF8001	12-05PFFS-SF8001	12-08PFFS-SF8001
	M16.0	12-03PFFS-SF8003 12-03PFFS-SF8004	12-04PFFS-SF8003 12-04PFFS-SF8004	12-05PFFS-SF8003 12-05PFFS-SF8004	12-08PFFS-SF8003 12-08PFFS-SF8004
Wire Leads (150mm)	PG9	12-03PFFS-SF8B15	12-04PFFS-SF8B15	12-05PFFS-SF8B15	12-08PFFS-SF8B15
	M16.0	12-03PFFS-SF8C15	12-04PFFS-SF8C15	12-05PFFS-SF8C15	12-08PFFS-SF8C15
Wire Leads (300mm)	PG9	12-03PFFS-SF8B30	12-04PFFS-SF8B30	12-05PFFS-SF8B30	12-08PFFS-SF8B30
	M16.0	12-03PFFS-SF8C30	12-04PFFS-SF8C30	12-05PFFS-SF8C30	12-08PFFS-SF8C30
Wire Leads (500mm)	PG9	12-03PFFS-SF8B50	12-04PFFS-SF8B50	12-05PFFS-SF8B50	12-08PFFS-SF8B50
	M16.0	12-03PFFS-SF8C50	12-04PFFS-SF8C50	12-05PFFS-SF8C50	12-08PFFS-SF8C50






M12 A (Metal) > Receptacle > Female Connector > Rear Fastened

					
Type	Mounting Thread	3 Contacts	4 Contacts	5 Contacts	8 Contacts
Solder Pin (180°)	PG9	12-03PFFS-SH8001	12-04PFFS-SH8001	12-05PFFS-SH8001	12-08PFFS-SH8001
	M16.0	12-03PFFS-SH8003 12-03PFFS-SH8004	12-04PFFS-SH8003 12-04PFFS-SH8004	12-05PFFS-SH8003 12-05PFFS-SH8004	12-08PFFS-SH8003 12-08PFFS-SH8004
Wire Leads (150mm)	PG9	12-03PFFS-SH8B15	12-04PFFS-SH8B15	12-05PFFS-SH8B15	12-08PFFS-SH8B15
Wire Leads (150mm)	M16	12-03PFFS-SC8B15	12-04PFFS-SH8C15	12-05PFFS-SH8C15	12-08PFFS-SH8C15
Wire Leads (300mm)	PG9	12-03PFFS-SH8B30	12-04PFFS-SH8B30	12-05PFFS-SH8B30	12-08PFFS-SH8B30
Wire Leads (300mm)	M16	12-03PFFS-SC8B30	12-04PFFS-SC8B30	12-05PFFS-SC8B30	12-08PFFS-SC8B30
Wire Leads (500mm)	PG9	12-03PFFS-SH8B50	12-04PFFS-SH8B50	12-05PFFS-SH8B50	12-08PFFS-SH8B50
Wire Leads (500mm)	M16	12-03PFFS-SC8B50	12-04PFFS-SC8B50	12-05PFFS-SC8B50	12-08PFFS-SC8B50

M12 A (Metal) > Overmolded with cable > Male Connector > Right Angle

				
Type	3 Contacts	4 Contacts	5 Contacts	8 Contacts
With Strain Relief	12-03AMMM-SR7	12-04AMMM-SR7	12-05AMMM-SR7	12-08AMMM-SR7
Without Strain Relief	12-03BMMM-SR7 12-03BMMM-SR8	12-04BMMM-SR7 12-04BMMM-SR8	12-05BMMM-SR7 12-05BMMM-SR8	12-08BMMM-SR7 12-08BMMM-SR8

M12 A (Metal) > Overmolded with cable > Male Connector > Straight

				
Type	3 Contacts	4 Contacts	5 Contacts	8 Contacts
With Strain Relief	12-03AMMM-SL7	12-04AMMM-SL7	12-05AMMM-SL7	12-08AMMM-SL7
Without Strain Relief	12-03BMMM-SL7 12-03BMMM-SL8	12-04BMMM-SL7 12-04BMMM-SL8	12-05BMMM-SL7 12-05BMMM-SL8	12-08BMMM-SL7 12-08BMMM-SL8
	12S-03BMMM-SL7 (Shielded)	12S-04BMMM-SL7 (Shielded)	12S-05BMMM-SL7 (Shielded)	12S-08BMMM-SL7 (Shielded)






Cable Type	1M	2M	5M	10M
PVC	A01	A02	A05	A10
PU	B01	B02	B05	B10

* Design and specification are subject to change without notice.






M12 A Code (Metal)

Overmolded with cable > Female Connector

IP 67 . 68 **9**Receptacle | Unmated
Overmolded with Cable | Mated
Field Installable | Mated**➤ M12 A (Metal) > Overmolded with cable > Female Connector > Right Angle**






				
Type	3 Contacts	4 Contacts	5 Contacts	8 Contacts
With Strain Relief	12-03AFFM-SR7	12-04AFFM-SR7	12-05AFFM-SR7	12-08AFFM-SR7
Without Strain Relief	12L-03BFFM-SR7 (With LED)	12-04BFFM-SR8	12-05BFFM-SR8	12-08BFFM-SR8
	12-03BFFM-SR8			

➤ M12 A (Metal) > Overmolded with cable > Female Connector > Straight







				
Type	3 Contacts	4 Contacts	5 Contacts	8 Contacts
With Strain Relief	12-03AFFM-SL7	12-04AFFM-SL7	12-05AFFM-SL7	12-08AFFM-SL7
Without Strain Relief	12S-03BFFM-SL7 (Shielded)	12S-04BFFM-SL7 (Shielded)	12S-05BFFM-SL7 (Shielded)	12S-08BFFM-SL7 (Shielded)
	12-03BFFM-SL8	12-04BFFM-SL8	12-05BFFM-SL8	12-08BFFM-SL8

Cable Type	1M	2M	5M	10M
PVC	A01	A02	A05	A10
PU	B01	B02	B05	B10






M12 A (Metal) > Field Installable > Male Connector > Right Angle

					
Type	Contact Type	3 Contacts	4 Contacts	5 Contacts	8 Contacts
Without Strain Relief	Screw Type	12-03BMMB-SR7001	12-04BMMB-SR7001	12-05BMMB-SR7001	-





M12 A (Metal) > Field Installable > Male Connector > Straight

					
Solder Type 					
Screw Type					
Type	Contact Type	3 Contacts	4 Contacts	5 Contacts	8 Contacts
Without Strain Relief	Solder Type	12-03BMMA-SL8001	12-04BMMA-SL8001	12-05BMMA-SL8001	12-08BMMA-SL8001
	Screw Type	12-03BMMB-SL7001	12-04BMMB-SL7001	12-05BMMB-SL7001	-

M12 A (Metal) > Field Installable > Female Connector > Right Angle

					
Type	Contact Type	3 Contacts	4 Contacts	5 Contacts	8 Contacts
Without Strain Relief	Screw Type	12-03BFFB-SR7001	12-04BFFB-SR7001	12-05BFFB-SR7001	-






M12 A (Metal) > Field Installable > Female Connector > Straight

					
Solder Type 					
Screw Type					
Type	Contact Type	3 Contacts	4 Contacts	5 Contacts	8 Contacts
Without Strain Relief	Solder Type	12-03BFFA-SL8001	12-04BFFA-SL8001	12-05BFFA-SL8001	12-08BFFA-SL8001
	Screw Type	12-03BFFB-SL7001	12-04BFFB-SL7001	12-05BFFB-SL7001	-






M12 A Code (Plastic)

Receptacle > Male / Female Connector






IP 67 . 68 9Receptacle | Unmated
Overmolded with Cable | Mated
Field Installable | Mated**└ M12 A (Plastic) > Receptacle > Male Connector > Front Fastened**

					
Backshell: Hexagonal					
Type	Mounting Thread	3 Contacts	4 Contacts	5 Contacts	8 Contacts
PCB Pin (90°)	M12	12P-03PMMR-SF8001	12P-04PMMR-SF8001	12P-05PMMR-SF8001	-
PCB Pin (180°)	M12	12P-03PMMR-SC8001	12P-04PMMR-SC8001	12P-05PMMR-SC8001	-






└ M12 A (Plastic) > Receptacle > Female Connector > Front Fastened

					
Backshell: Hexagonal					
Type	Mounting Thread	3 Contacts	4 Contacts	5 Contacts	8 Contacts
PCB Pin (180°)	M16.0	12P-03PFFP-SF8001	12P-04PFFP-SF8001	12P-05PFFP-SF8001	12P-08PFFP-SF8001
PCB Pin (90°)	M16.0	12P-03PFFR-SF8001	12P-04PFFR-SF8001	12P-05PFFR-SF8001	-
Solder Pin (180°)	M16.0	12P-03PFFS-SF8001	12P-04PFFS-SF8001	12P-05PFFS-SF8001	12P-08PFFS-SF8001





┘ M12 A (Plastic) > Overmolded with cable > Male Connector > Right Angle

				
Type	3 Contacts	4 Contacts	5 Contacts	8 Contacts
Without Strain Relief	12P-03BMMM-SR8	12P-04BMMM-SR8	12P-05BMMM-SR8	12P-08BMMM-SR8






┘ M12 A (Plastic) > Overmolded with cable > Male Connector > Straight

				
Type	3 Contacts	4 Contacts	5 Contacts	8 Contacts
Without Strain Relief	12P-03BMMM-SL8	12P-04BMMM-SL8	12P-05BMMM-SL8	12P-08BMMM-SL8

┘ M12 A (Plastic) > Overmolded with cable > Female Connector > Right Angle

				
Type	3 Contacts	4 Contacts	5 Contacts	8 Contacts
Without Strain Relief	12P-03BFFM-SR8	12P-04BFFM-SR8	12P-05BFFM-SR8	12P-08BFFM-SR8

┘ M12 A (Plastic) > Overmolded with cable > Female Connector > Straight

				
Type	3 Contacts	4 Contacts	5 Contacts	8 Contacts
Without Strain Relief	12P-03BFFM-SL8	12P-04BFFM-SL8	12P-05BFFM-SL8	12P-08BFFM-SL8






Cable Type	1M	2M	5M	10M
PVC	A01	A02	A05	A10
PU	B01	B02	B05	B10

* Design and specification are subject to change without notice.






M12 A Code (Plastic)

Field Installable > Male / Female Connector






IP 67 . 68 Receptacle | Unmated
Overmolded with Cable | Mated
Field Installable | Mated**└ M12 A (Plastic) > Field Installable > Male Connector > Right Angle**

					
Type	Contact Type	3 Contacts	4 Contacts	5 Contacts	8 Contacts
Without Strain Relief	Solder Type	-	-	-	-
	Screw Type	12P-03BMMB-SR7001	12P-04BMMB-SR7001	12P-05BMMB-SR7001	-






└ M12 A (Plastic) > Field Installable > Male Connector > Straight





 Solder Type Screw Type					
Type	Contact Type	3 Contacts	4 Contacts	5 Contacts	8 Contacts
Without Strain Relief	Solder Type	12P-03BMMA-SL7001 12P-03BMMA-SL8001	12P-04BMMA-SL7001 12P-04BMMA-SL8001	12P-05BMMA-SL7001 12P-05BMMA-SL8001	12P-08BMMA-SL8001
	Screw Type	12P-03BMMB-SL7001	12P-04BMMB-SL7001	12P-05BMMB-SL7001	





└ M12 A (Plastic) > Field Installable > Female Connector > Right Angle

					
Type	Contact Type	3 Contacts	4 Contacts	5 Contacts	8 Contacts
Without Strain Relief	Solder Type	-	-	-	-
	Screw Type	12P-03BFFB-SR7001	12P-04BFFB-SR7001	12P-05BFFB-SR7001	-

└ M12 A (Plastic) > Field Installable > Female Connector > Straight




 Solder Type Screw Type					
Type	Contact Type	3 Contacts	4 Contacts	5 Contacts	8 Contacts
Without Strain Relief	Solder Type	12P-03BFFA-SL8001	12P-04BFFA-SL8001	12P-05BFFA-SL8001	12P-08BFFA-SL8001
	Screw Type	12P-03BFFB-SL7001	12P-04BFFB-SL7001	12P-05BFFB-SL7001	

				
Type	Mounting Thread	3 Contacts	4 Contacts	5 Contacts
PCB Pin (180°)	PG9	12B-03PMMP-SF8001	12B-04PMMP-SF8001	12B-05PMMP-SF8001
	M16	12B-03PMMP-SF8003	12B-04PMMP-SF8003 12B-04PMMP-SF8004	12B-05PMMP-SF8003 12B-05PMMP-SF8004
PCB Pin (90°)	M12	-	-	SBS-05PMMR-SF7001
	PG9	12B-03PMMR-SF8001	12B-04PMMR-SF8001	12B-05PMMR-SF8001 12B-05PMMR-SF7001
	M16	12B-03PMMR-SF8003	12B-04PMMR-SF8003	12B-05PMMR-SF8003
Solder Pin (180°)	PG9	12B-03PMMS-SF8001	12B-04PMMS-SF8001	12B-05PMMS-SF8001
	M16	12B-03PMMS-SF8003	12B-04PMMS-SF8003 12B-04PMMS-SF8004	12B-05PMMS-SF8003 12B-05PMMS-SF8004
Wire Leads (150mm)	PG9	-	-	12B-05PMMS-SF8B15
	M16	-	-	12B-05PMMS-SF8C15
Wire Leads (300mm)	PG9	-	-	12B-05PMMS-SF8B30
	M16	-	-	12B-05PMMS-SF8C30
Wire Leads (500mm)	PG9	-	-	12B-05PMMS-SF8B50
	M16	-	-	12B-05PMMS-SF8C50





				
Type	Mounting Thread	3 Contacts	4 Contacts	5 Contacts
PCB Pin (180°)	PG9	12B-03PMMS-SH8001	12B-04PMMS-SH8001	12B-05PMMS-SH8001
	M16	12B-03PMMS-SH8003	12B-04PMMS-SH8003 12B-04PMMS-SH8004	12B-05PMMS-SH8003 12B-05PMMS-SH8004
Wire Leads (150mm)	PG9	-	-	12B-05PMMS-SH8B15
	M16	-	-	12B-05PMMS-SH8C15
Wire Leads (300mm)	PG9	-	-	12B-05PMMS-SH8B30
	M16	-	-	12B-05PMMS-SH8C30
Wire Leads (500mm)	PG9	-	-	12B-05PMMS-SH8B50
	M16	-	-	12B-05PMMS-SH8C50

* Design and specification are subject to change without notice.





M12 B (Metal) Receptacle > Female Connector > Front Fastened

				
Backshell: Hexagonal				
Type	Mounting Thread	3 Contacts	4 Contacts	5 Contacts
PCB Pin (180°)	PG9	12B-03PFFP-SF8001	12B-04PFFP-SF8001	12B-05PFFP-SF8001
	M16	12B-03PFFP-SF8003	12B-04PFFP-SF8003 12B-04PFFP-SF8004 12B-04PFFP-SF8005	12B-05PFFP-SF8003 12B-05PFFP-SF8004 12B-05PFFP-SF8005
PCB Pin (90°)	M12	-	-	SBS-05PFFR-SF7001
	PG9	12B-03PFFR-SF8001	12B-04PFFR-SF8001	12B-05PFFR-SF8001 12B-05PFFR-SF7001
	M16	12B-03PFFR-SF8003	12B-04PFFR-SF8003	12B-05PFFR-SF8003
Solder Pin (180°)	PG9	12B-03PFFS-SF8001	12B-04PFFS-SF8001	12B-05PFFS-SF8001
	M16	12B-03PFFS-SF8003	12B-04PFFS-SF8003 12B-04PFFS-SF8004	12B-05PFFS-SF8003 12B-05PFFS-SF8004
Wire Leads (150mm)	PG9	-	-	12B-05PFFS-SF8B15
	M16	-	-	12B-05PFFS-SF8C15
Wire Leads (300mm)	PG9	-	-	12B-05PFFS-SF8B30
	M16	-	-	12B-05PFFS-SF8C30
Wire Leads (500mm)	PG9	-	-	12B-05PFFS-SF8B50
	M16	-	-	12B-05PFFS-SF8C50





M12 B (Metal) > Receptacle > Female Connector > Rear Fastened

				
Type	Mounting Thread	3 Contacts	4 Contacts	5 Contacts
PCB Pin (180°)	PG9	12B-03PFFS-SH8001	12B-04PFFS-SH8001	12B-05PFFS-SH8001
	M16	12B-03PFFS-SH8003	12B-04PFFS-SH8003 12B-04PFFS-SH8004	12B-05PFFS-SH8003 12B-05PFFS-SH8004
Wire Leads (150mm)	PG9	-	-	12B-05PFFS-SH8B15
Wire Leads (300mm)	PG9	-	-	12B-05PFFS-SH8B30
Wire Leads (500mm)	PG9	-	-	12B-05PFFS-SH8B50




M12 B (Metal) > Overmolded with cable > Male Connector > Right Angle

			
Type	3 Contacts	4 Contacts	5 Contacts
Without Strain Relief	12B-03BMMM-SR8	12B-04BMMM-SR8	12B-05BMMM-SR8




M12 B (Metal) > Overmolded with cable > Male Connector > Straight

			
Type	3 Contacts	4 Contacts	5 Contacts
Without Strain Relief	12B-03BMMM-SL8	12B-04BMMM-SL8	12B-05BMMM-SL8

M12 B (Metal) > Overmolded with cable > Female Connector > Right Angle

			
Type	3 Contacts	4 Contacts	5 Contacts
Without Strain Relief	12B-03BFFM-SR8	12B-04BFFM-SR8	12B-05BFFM-SR8





MM12 B (Metal) > Overmolded with cable > Female Connector > Straight

			
Type	3 Contacts	4 Contacts	5 Contacts
Without Strain Relief	12B-03BFFM-SL8	12B-04BFFM-SL8	12B-05BFFM-SL8






Cable Type	1M	2M	5M	10M
PVC	A01	A02	A05	A10
PU	B01	B02	B05	B10

* Design and specification are subject to change without notice.




└ M12 B (Metal) > Field Installable > Male Connector > Right Angle

				
Type	Contact Type	3 Contacts	4 Contacts	5 Contacts
Without Strain Relief	Screw Type	12B-03BMMB-SR7001	12B-04BMMB-SR7001	12B-05BMMB-SR7001






└ M12 B (Metal) > Field Installable > Male Connector > Straight

 Solder Type  Screw Type				
Type	Contact Type	3 Contacts	4 Contacts	5 Contacts
Without Strain Relief	Solder Type	12B-03BMMA-SL8001	12B-04BMMA-SL8001	12B-05BMMA-SL8001
	Screw Type	12B-03BMMB-SL7001	12B-04BMMB-SL7001	12B-05BMMB-SL7001





└ M12 B (Metal) > Field Installable > Female Connector > Right Angle

				
Type	Contact Type	3 Contacts	4 Contacts	5 Contacts
Without Strain Relief	Screw Type	12B-03BFFB-SR7001	12B-04BFFB-SR7001	12B-05BFFB-SR7001





└ M12 B (Metal) > Field Installable > Female Connector > Straight

 Solder Type  Screw Type				
Type	Contact Type	3 Contacts	4 Contacts	5 Contacts
Without Strain Relief	Solder Type	12B-03BFFA-SL8001	12B-04BFFA-SL8001	12B-05BFFA-SL8001
	Screw Type	12B-03BFFB-SL7001	12B-04BFFB-SL7001	12B-05BFFB-SL7001




M12 B (Plastic) > Receptacle > Male Connector > Front Fastened

				
Backshell: Hexagonal				
Type	Mounting Thread	3 Contacts	4 Contacts	5 Contacts
PCB Pin (90°)	M12	-	-	SBP-05PMMR-SF8001





M12 B (Plastic) > Receptacle > Female Connector > Front Fastened

				
Backshell: Hexagonal				
Type	Mounting Thread	3 Contacts	4 Contacts	5 Contacts
PCB Pin (90°)	M12	-	-	SBP-05PFFR-SF8001

M12 B (Plastic) > Overmolded with cable > Male Connector > Right Angle

				
Type	3 Contacts	4 Contacts	5 Contacts	
Without Strain Relief	SBP-03BMMM-SR8	SBP-04BMMM-SR8	SBP-05BMMM-SR8	

M12 B (Plastic) > Overmolded with cable > Male Connector > Straight

				
Type	3 Contacts	4 Contacts	5 Contacts	
Without Strain Relief	SBP-03BMMM-SL8	SBP-04BMMM-SL8	SBP-05BMMM-SL8	

Cable Type	1M	2M	5M	10M
PVC	A01	A02	A05	A10
PU	B01	B02	B05	B10

* Design and specification are subject to change without notice.




M12 B Code (Plastic)

Overmolded with cable > Female Connector
Field Installable > Male Connector





IP 67 . 68 

Receptacle | Unmated
Overmolded with Cable | Mated
Field Installable | Mated

└ M12 B (Plastic) > Overmolded with cable > Female Connector > Right Angle





			
Type	3 Contacts	4 Contacts	5 Contacts
Without Strain Relief	SBP-03BFFM-SR8	SBP-04BFFM-SR8	SBP-05BFFM-SR8

└ M12 B (Plastic) > Overmolded with cable > Female Connector > Straight





			
Type	3 Contacts	4 Contacts	5 Contacts
Without Strain Relief	SBP-03BFFM-SL8	SBP-04BFFM-SL8	SBP-05BFFM-SL8

Cable Type	1M	3M	5M	10M
PVC	A01	A02	A05	A10
PU	B01	B02	B05	B10





└ M12 B (Plastic) > Field Installable > Male Connector > Right Angle

				
Type	Contact Type	3 Contacts	4 Contacts	5 Contacts
Without Strain Relief	Screw Type	SBP-03BMMB-SR7001	SBP-04BMMB-SR7001	SBP-05BMMB-SR7001






M12 B (Plastic) > Field Installable > Male Connector > Straight

 Solder Type  Screw Type				
Type	Contact Type	3 Contacts	4 Contacts	5 Contacts
Without Strain Relief	Solder Type	SBP-03BMMA-SL800 1	SBP-04BMMA-SL800 1	SBP-05BMMA-SL800 1
	Screw Type	SBP-03BMMB-SL700 1	SBP-04BMMB-SL700 1	SBP-05BMMB-SL700 1





M12 B (Plastic) > Field Installable > Female Connector > Right Angle

				
Type	Contact Type	3 Contacts	4 Contacts	5 Contacts
Without Strain Relief	Screw Type	SBP-03BFFB-SR700 1	SBP-04BFFB-SR700 1	SBP-05BFFB-SR700 1





M12 B (Plastic) > Field Installable > Female Connector > Straight





 Solder Type  Screw Type				
Type	Contact Type	3 Contacts	4 Contacts	5 Contacts
Without Strain Relief	Solder Type	SBP-03BFFA-SL800 1	SBP-04BFFA-SL800 1	SBP-05BFFA-SL800 1
	Screw Type	SBP-03BFFB-SL700 1	SBP-04BFFB-SL700 1	SBP-05BFFB-SL700 1





M12 D (Metal) > Receptacle > Male Connector > Front Fastened

				
Backshell: Hexagonal				
Type	Mounting Thread	3 Contacts	4 Contacts	5 Contacts
PCB Pin (180°)	PG9	-	12D-04PMMP-SF8001	12D-05PMMP-SF8001
	M16.0	-	12D-04PMMP-SF8003 12D-04PMMP-SF8004	12D-05PMMP-SF8003 12D-05PMMP-SF8004
PCB Pin (90°)	PG9	-	12D-04PMMR-SF7001 12D-04PMMR-SF8001	-
	M12	-	12D-04PMMR-SF7007	-
	M12 (Shielded)	-	SDS-04PMMR-SF7007	-
Solder Pin (180°)	PG9	12D-03PMMS-SF8001	12D-04PMMS-SF8001	12D-05PMMS-SF8001
	M16.0	-	12D-04PMMS-SF8003 12D-04PMMS-SF8004	12D-05PMMS-SF8003 12D-05PMMS-SF8004
Wire Leads (150mm)	PG9	-	12D-04PMMS-SF8B15	-
	M16.0	-	12D-04PMMS-SF8C15	-
Wire Leads (300mm)	PG9	-	12D-04PMMS-SF8B30	-
	M16.0	-	12D-04PMMS-SF8C30	-
Wire Leads (500mm)	PG9	-	12D-04PMMS-SF8B50	-
	M16.0	-	12D-04PMMS-SF8C50	-

M12 D (Metal) > Receptacle > Male Connector > Rear Fastened

				
Type	Mounting Thread	3 Contacts	4 Contacts	5 Contacts
Solder Pin (180°)	PG9	12D-03PMMS-SH8001	12D-04PMMS-SH8001	12D-05PMMS-SH8001
	M16.0	-	12D-04PMMS-SH8003 12D-04PMMS-SH8004	12D-05PMMS-SH8003 12D-04PMMS-SH8004
Wire Leads (150mm)	PG9	-	12D-04PMMS-SH8B15	-
	M16.0	-	12D-04PMMS-SH8C15	-
Wire Leads (300mm)	PG9	-	12D-04PMMS-SH8B30	-
	M16.0	-	12D-04PMMS-SH8C30	-
Wire Leads (500mm)	PG9	-	12D-04PMMS-SH8B50	-
	M16.0	-	12D-04PMMS-SH8C50	-





				
Backshell: Hexagonal				
Type	Mounting Thread	3 Contacts	4 Contacts	5 Contacts
PCB Pin (180°)	PG9	12D-03PFFP-SF8001	12D-04PFFP-SF8001	12D-05PFFP-SF8001
	M16.0	-	12D-04PFFP-SF8003 12D-04PFFP-SF8004 12D-04PFFP-SF8005	12D-05PFFP-SF8003 12D-05PFFP-SF8004 12D-05PFFP-SF8005
PCB Pin (90°)	PG9	12D-03PFFR-SF8001	12D-04PFFR-SF8001	12D-05PFFR-SF8001
	M16.0	12D-03PFFR-SF8003	12D-04PFFR-SF8003	12D-05PFFR-SF8003
	M12	-	12D-04PFFR-SF7001	-
	M12 (Shielded)		SDS-04PFFR-SF7001	
Solder Pin (180°)	PG9	12D-03PFFS-SF8001	12D-04PFFS-SF8001	12D-05PFFS-SF8001
	M16.0	12D-03PFFS-SF8003	12D-04PFFS-SF8003 12D-04PFFS-SF8004	12D-05PFFS-SF8003 12D-05PFFS-SF8004
Wire Leads (150mm)	PG9	-	12D-04PFFS-SF8B15	-
	M16.0	-	12D-04PFFS-SF8C15	-
Wire Leads (300mm)	PG9	-	12D-04PFFS-SF8B30	-
	M16.0	-	12D-04PFFS-SF8C30	-
Wire Leads (500mm)	PG9	-	12D-04PFFS-SF8B50	-
	M16.0	-	12D-04PFFS-SF8C50	-

				
Type	Mounting Thread	3 Contacts	4 Contacts	5 Contacts
Solder Pin (180°)	PG9	12D-03PFFS-SH8001	12D-04PFFS-SH8001	12D-05PFFS-SH8001
	M16.0	12D-03PFFS-SH8003	12D-04PFFS-SH8003 12D-04PFFS-SH8004	12D-05PFFS-SH8003 12D-05PFFS-SH8004
Wire Leads (150mm)	PG9	-	12D-04PFFS-SH8B15	-
Wire Leads (300mm)	PG9	-	12D-04PFFS-SH8B30	-
Wire Leads (500mm)	PG9	-	12D-04PFFS-SH8B50	-





M12 D Code (Metal)

Overmolded with cable > Male / Female Connector





IP 67 . 68 **9**Receptacle | Unmated
Overmolded with Cable | Mated
Field Installable | Mated**└ M12 D (Metal) > Overmolded with cable > Male Connector > Right Angle**

			
Type	3 Contacts	4 Contacts	5 Contacts
Without Strain Relief	12D-03BMMM-SR8	12D-04BMMM-SR8	12D-05BMMM-SR8




└ M12 D (Metal) > Overmolded with cable > Male Connector > Straight

			
Type	3 Contacts	4 Contacts	5 Contacts
Without Strain Relief	12D-03BMMM-SL8	12D-04BMMM-SL8	12D-05BMMM-SL8

└ M12 D (Metal) > Overmolded with cable > Female Connector > Right Angle





			
Type	3 Contacts	4 Contacts	5 Contacts
Without Strain Relief	12D-03BFFM-SR8	12D-04BFFM-SR8	12D-05BFFM-SR8

└ M12 D (Metal) > Overmolded with cable > Female Connector > Straight





			
Type	3 Contacts	4 Contacts	5 Contacts
Without Strain Relief	12D-03BFFM-SL8	12D-04BFFM-SL8	12D-05BFFM-SL8

Cable Type	1M	2M	5M	10M
PVC	A01	A02	A05	A10
PU	B01	B02	B05	B10





└ M12 D (Metal) > Field Installable > Male Connector > Right Angle

				
Type	Contact Type	3 Contacts	4 Contacts	5 Contacts
Without Strain Relief	Screw Type	12D-03BMMB-SR700 1	12D-04BMMB-SR700 1	12D-05BMMB-SR700 1





└ M12 D (Metal) > Field Installable > Male Connector > Straight

				
Solder Type				
Screw Type				
Type	Contact Type	3 Contacts	4 Contacts	5 Contacts
Without Strain Relief	Solder Type	12D-03BMMA-SL800 1	12D-04BMMA-SL800 1	12D-05BMMA-SL800 1
	Screw Type	12D-03BMMB-SL700 1	12D-04BMMB-SL700 1	12D-05BMMB-SL700 1

└ M12 D (Metal) > Field Installable > Female Connector > Right Angle

				
Type	Contact Type	3 Contacts	4 Contacts	5 Contacts
Without Strain Relief	Screw Type	12D-03BFFB-SR700 1	12D-04BFFB-SR700 1	12D-05BFFB-SR700 1

└ M12 D (Metal) > Field Installable > Female Connector > Straight

				
Solder Type				
Screw Type				
Type	Contact Type	3 Contacts	4 Contacts	5 Contacts
Without Strain Relief	Solder Type	12D-03BFFA-SL800 1	12D-04BFFA-SL800 1	12D-05BFFA-SL800 1
	Screw Type	12D-03BFFB-SL700 1	12D-04BFFB-SL700 1	12D-05BFFB-SL700 1





M12 D Code (Plastic)

Receptacle > Male / Female Connector
Overmolded with cable > Male Connector





IP 67 . 68 **9**

Receptacle | Unmated
Overmolded with Cable | Mated
Field Installable | Mated





➤ **M12 D (Plastic) > Receptacle > Male Connector > Front Fastened**

				
Backshell: Hexagonal				
Type	Mounting Thread	3 Contacts	4 Contacts	5 Contacts
PCB Pin (90°)	M12	-	SDP-04PMMR-SF8001	-





➤ **M12 D (Plastic) > Receptacle > Female Connector > Front Fastened**

				
Backshell: Hexagonal				
Type	Mounting Thread	3 Contacts	4 Contacts	5 Contacts
PCB Pin (90°)	M16	-	SDP-04PFFR-SF8001	-

➤ **M12 D (Plastic) > Overmolded with cable > Male Connector > Right Angle**





				
Type		3 Contacts	4 Contacts	5 Contacts
Without Strain Relief	SDP-03BMMM-SR8	SDP-04BMMM-SR8	SDP-05BMMM-SR8	

➤ **M12 D (Plastic) > Overmolded with cable > Male Connector > Straight**




				
Type		3 Contacts	4 Contacts	5 Contacts
Without Strain Relief	SDP-03BMMM-SL8	SDP-04BMMM-SL8	SDP-05BMMM-SL8	

Cable Type	1M	2M	5M	10M
PVC	A01	A02	A05	A10
PU	B01	B02	B05	B10





M12 D (Plastic) > Overmolded with cable > Female Connector > Right Angle

			
Type	3 Contacts	4 Contacts	5 Contacts
Without Strain Relief	SDP-03BFFM-SR8	SDP-04BFFM-SR8	SDP-05BFFM-SR8






M12 D (Plastic) > Overmolded with cable > Female Connector > Straight

			
Type	3 Contacts	4 Contacts	5 Contacts
Without Strain Relief	SDP-03BFFM-SL8	SDP-04BFFM-SL8	SDP-05BFFM-SL8

M12 D (Plastic) > Field Installable > Male Connector > Right Angle

				
Type	Contact Type	3 Contacts	4 Contacts	5 Contacts
Without Strain Relief	Screw Type	SDP-03BMMB-SR700 1	SDP-04BMMB-SR700 1	SDP-05BMMB-SR700 1

M12 D (Plastic) > Field Installable > Male Connector > Straight

	Solder Type			
	Screw Type			
Type	Contact Type	3 Contacts	4 Contacts	5 Contacts
Without Strain Relief	Solder Type	SDP-03BMMA-SL800 1	SDP-04BMMA-SL800 1	SDP-05BMMA-SL800 1
	Screw Type	SDP-03BMMB-SL700 1	SDP-04BMMB-SL700 1	SDP-05BMMB-SL700 1




M12 D Code (Plastic)

Field Installable > Female Connector





IP 67 . 68 9


Receptacle | Unmated
Overmolded with Cable | Mated
Field Installable | Mated


└ M12 D (Plastic) > Field Installable > Female Connector > Right Angle


				
Type	Contact Type	3 Contacts	4 Contacts	5 Contacts
Without Strain Relief	Screw Type	SDP-03BFFB-SR700 1	SDP-04BFFB-SR700 1	SDP-05BFFB-SR700 1

└ M12 D (Plastic) > Field Installable > Female Connector > Straight

 Solder Type Screw Type				
Type	Contact Type	3 Contacts	4 Contacts	5 Contacts
Without Strain Relief	Solder Type	SDP-03BFFA-SL800 1	SDP-04BFFA-SL800 1	SDP-05BFFA-SL800 1
	Screw Type	SDP-03BFFB-SL700 1	SDP-04BFFB-SL700 1	SDP-05BFFB-SL700 1

					
Backshell: Hexagonal					
Type	Mounting Thread		5 Contacts		
PCB Pin (180°)	PG9		12-05PMIP-SF800 1		
	M16.0		12-05PMIP-SF8003 12-05PMIP-SF8004		
PCB Pin (90°)	PG9		12-05PMIR-SF800 1		
	M16.0		12-05PMIR-SF8003		
Solder Pin (180°)	PG9		12-05PMIS-SF800 1		
	M16.0		12-05PMIS-SF8003 12-05PMIS-SF8004		

					
Type	Mounting Thread		5 Contacts		
Solder Pin (180°)	PG9		12-05PMIS-SH800 1		
	M16.0		12-05PMIS-SH8003 12-05PMIS-SH8004		

					
Backshell: Hexagonal					
Type	Mounting Thread		5 Contacts		
PCB Pin (180°)	PG9		12-05PFIP-SF800 1		
	M16.0		12-05PFIP-SF8003 12-05PFIP-SF8004		
PCB Pin (90°)	PG9		12-05PFIR-SF800 1		
	M16.0		12-05PFIR-SF8003		
Solder Pin (180°)	PG9		12-05PFIS-SF800 1		
	M16.0		12-05PFIS-SF8003 12-05PFIS-SF8004		

* Design and specification are subject to change without notice.


M12 I Style (Metal)

Receptacle > Female / Male Connector (Housing)
Overmolded with cable > Male Connector (Housing)


IP 67 . 68 **9**

Receptacle | Unmated
Overmolded with Cable | Mated
Field Installable | Mated


➤ **M12 I (Metal) > Receptacle > Female Connector (Housing) > Rear Fastened (Male+Female Contact)**

		
Type	Mounting Thread	5 Contacts
Solder Pin (180°)	PG9	12-05PFIS-SH8001
	M16.0	12-05PFIS-SH8003 12-05PFIS-SH8004

➤ **M12 I (Metal) > Overmolded with cable > Male Connector (Housing) > Right Angle (Male+Female Contact)**



		
Type	5 Contacts	
With Strain Relief	12-05AMIM-SR7	
Without Strain Relief	12-05BMIM-SR8	

➤ **M12 I (Metal) > Overmolded with cable > Male Connector (Housing) > Straight (Male+Female Contact)**

		
Type	5 Contacts	
With Strain Relief	12-05AMIM-SL7	
Without Strain Relief	12-05BMIM-SL8	

Cable Type	1M	2M	5M	10M
PVC	A01	A02	A05	A10
PU	B01	B02	B05	B10

M12 I (Metal) > Overmolded with cable > Female Connector (Housing) > Right Angle (Male+Female Contact)

 	
Type	5 Contacts
With Strain Relief	12-05AFIM-SR7
Without Strain Relief	12-05BFIM-SR8

M12 I (Metal) > Overmolded with cable > Female Connector (Housing) > Straight

 	
Type	5 Contacts
With Strain Relief	12-05AFIM-SL7
Without Strain Relief	12-05BFIM-SL8

Cable Type	1M	2M	5M	10M
PVC	A01	A02	A05	A10
PU	B01	B02	B05	B10

* Design and specification are subject to change without notice.


M12 I Style (Metal)

Field Installable > Female / Male Connector (Housing)



IP 67 . 68 9

Receptacle | Unmated
Overmolded with Cable | Mated
Field Installable | Mated



➤ M12 I (Metal) > Field Installable>Male Connector (Housing) > Straight (Male+Female Contact)

		
Type	Contact Type	5 Contacts
Without Strain Relief	Solder Type	12P-05BMIA-SL8001



➤ M12 I (Plastic) > Field Installable > Female Connector (Housing) > Straight (Male+Female Contact)

		
Type	Contact Type	5 Contacts
Without Strain Relief	Solder Type	12P-05BFIA-SL8001



M12 I (Plastic) > Overmolded with cable > Female Connector (Housing) > Right Angle (Male+Female Contact)

	
Type	5 Contacts
Without Strain Relief	12P-05BFIM-SR8



M12 I (Plastic) > Overmolded with cable > Female Connector (Housing) > Straight (Male+Female Contact)

	
Type	5 Contacts
Without Strain Relief	12P-05BFIM-SL8

M12 I (Plastic) > Overmolded with cable > Male Connector (Housing) > Straight (Male+Female Contact)

	
Type	5 Contacts
Without Strain Relief	12P-05BMIM-SL8

M12 I (Plastic) > Overmolded with cable > Male Connector (Housing) > Right Angle (Male+Female Contact)

	
Type	5 Contacts
Without Strain Relief	12P-05BMIM-SR8

Cable Type	1M	2M	5M	10M
PVC	A01	A02	A05	A10
PU	B01	B02	B05	B10

* Design and specification are subject to change without notice.

M23 Style (Metal)



Receptacle (Field Installable Type) > Male Connector (Housing)

Field Installable > Female Connector (Housing)



IP 67 . 68 **9**

Receptacle | Unmated
Overmolded with Cable | Mated
Field Installable | Mated



➤ **M23 (Metal) > Receptacle (Field Installable Type) > Male Connector (Housing)**
> Front Fastened

		
Backshell: Hexagonal		
Type	Contact Gender	6 Contacts
Crimp Pin	Male	LJ23-06PMMC-SF7001


➤ **M23 (Metal) > Receptacle (Field Installable Type) > Male Connector (Housing)**
> Front Fastened

		
Backshell: Hexagonal		
Type	Contact Gender	6 Contacts
Crimp Pin	Female	LJ23-06PMFC-SF7001





➤ **M23 (Metal) > Field Installable > Female Connector (Housing) > Straight**






			
Type	Contact Type	Contact Gender	6 Contacts
Without Strain Relief	Crimp Pin	Male	LJ23-06DFMC-SL7001

➤ **M23 (Metal) > Field Installable > Female Connector (Housing) > Straight**

			
Type	Contact Type	Contact Gender	6 Contacts
Without Strain Relief	Crimp Pin	Female	LJ23-06DFFC-SL7001 LJ23-06DFFC-SL7002

➤ Heavy Duty Shielded Connector (Metal) > Field Installable > Female Connector (Housing) > Straight

						
Without Strain Relief			2 Contacts	3 Contacts	4 Contacts	5 Contacts
10A	Solder Type / Male	48H	-	-	LB20-04BFMA-SL8001	LB20-05BFMA-SL8001
		500H	-	-	HB20-04BFMA-SL8001	HB20-05BFMA-SL8001
20A	Solder Type / Male	48H	LC20-02BFMA-SL8001	LC20-03BFMA-SL8001	-	-
		500H	HC20-02BFMA-SL8001	HC20-03BFMA-SL8001	-	-

						
Without Strain Relief			7 Contacts	10 Contacts	12 Contacts	14 Contacts
5A	Solder Type / Male	48H	-	LD20-10BFMA-SL8001	LD20-12BFMA-SL8001	LD20-14BFMA-SL8001
		500H	-	HD20-10BFMA-SL8001	HD20-12BFMA-SL8001	HD20-14BFMA-SL8001
10A	Solder Type / Male	48H	LB20-07BFMA-SL8001	-	-	-
		500H	HB20-07BFMA-SL8001	-	-	-

Blank lined paper for writing.




Scan to visit our website

USB Connector




Range Overview


Receptacle to Overmolded with Cable



Receptacle with Cable to Overmolded with Cable



In Line



Micro USB




Accessories



Waterproof Cap
See page 21-16



Waterproof Cap
See page 21-16



Box
See page 21-21

Specification

Identifications	USB 3.0 A Type USB 2.0 A Type, USB 2.0 B Type Mini USB 2.0 B Type Micro USB: Available soon
Description	Receptacle Receptacle With Cable Overmolded with Cable Field Installable
Current Rating / Data	1.5A
Material	Contacts: Copper Alloy, Gold Plated Connector Body (Housing) : PBT UL94V-0
Waterproof Rating	IP67~68
Temperature Range	Receptacle: Nylon+GF: -40°C~105°C M-PPE: -40°C~105°C ABS: -20°C~80°C Receptacle with cable: Nylon+GF: -20°C~105°C ABS: -20°C~80°C Overmolded with Cable: -20°C~80°C Field Installable: -20°C~80°C
Contact Resistance	≤ 30mΩ
Insulation Resistance	≥ 1000mΩ at DC500V
Breakdown Voltage	≥ AC500V / 1 minute
More to know	USB 2.0: Standard Cable Length: 01-05M USB 3.0: Standard Cable Length: 01-03M Mini USB: Standard Cable Length: 01-04M

* Design and specification are subject to change without notice.

Ordering Information

Specification		1	2	3	4	5	6	7	8	9	10
(UA) USB A Type	(NUB) Mini USB B										
(UB) USB B Type											
Data Transfer Rate											
(20) 2.0	(30) 3.0										
Connector Body (Style)											
> For Receptacle	> For Overmolded with Cable										
(P) Front Fastened	(A) With Strain Relief										
> For Field installable	(B) Without Strain Relief										
(B) Without Strain Relief											
Connector (Housing) Gender											
(M) Male	(F) Female										
Contact Gender											
(M) Male (Plug)	(F) Female (Jack)										
Assemble Style											
> For Receptacle	> For Overmolded with Cable										
(P) 180° PCB Type	(M) Overmolded with Cable										
(R) 90° PCB Type	> For Field Installable										
(J) Jack	(A) Field installable (Solder)										
Mating Style											
(S) Screw Thread	(L) 2 Points Lock Bayonet (Nut OD: 28.5mm)										
(N) 2 Points Lock Bayonet (Nut OD: 25.4mm)											
Backshell											
> For Receptacle	> For Overmolded with Cable										
(C) Circular	(L) Straight										
(S) Square	(R) Right Angle										
Waterproof Rating											
(7) IP 67											
(8) IP 68											
More Information											
> For Receptacle	> For Overmolded with Cable										
(001) Without Cable	(□)+(■) : Cable Type + Cable Length										
(002) With Cable (Harness (50mm))	EX. (A01) = USB 2.0 Cable + 1M										
	(□) : Cable Type										
	(A) USB 2.0 Cable										
	(B) USB 3.0 Cable										
	(■) : Cable Length										
	USB2.0 :From 1M to 5M										
	USB3.0 :From 1M to 3M										
	Mini USB2.0: From 1M to 4M										
	EX. (01) = 1M										

Ordering Information I Double-ended

ALTW waterproof connector to ALTW waterproof connector

ALTW waterproof connector to Standard USB connector (None Waterproof)


	1	2	3	4	5	6	7	8	9
Specification									
(UA) USB A Type									
(UB) USB B Type									
Data Transfer Rate									
(20) 2.0			(30) 3.0						
Connector Body (Style)									
> For Receptacle			> For Overmolded with Cable						
(P) Front Fastened			(A) With Strain Relief						
			(B) Without Strain Relief						
Connector (Housing) Gender									
(M) Male			(F) Female						
Contact Gender									
(M) Male (Plug)			(F) Female (Jack)						
Mating Style									
(S) Screw Thread			(L) 2 Points Lock Bayonet (Nut OD: 28.5mm)						
Non-Waterproof (2ne End)									
(A) USB2.0 A Type (Plug)			(D) USB3.0 A Type (Plug)						
(B) USB2.0 B Type (Plug)									
Waterproof Rating									
(6) IP 66									
(7) IP 67									
(8) IP 68									
More Information									
> For Receptacle with Cable			> For Overmolded with Cable						
(□)+(■) : Cable Type + Cable Length			(□)+(■) : Cable Type + Cable Length						
EX. (BX10) = USB 3.0 Cable + 100mm			EX. (A01) = USB 2.0 Cable + 1M						
(□) : Cable Type			(□) : Cable Type						
(B) USB 3.0 Cable			(A) USB 2.0 Cable						
(■) : Cable Length			(■) : Cable Length						
USB3.0 :From 100mm to 300mm			USB2.0 :From 1M to 5M						
EX. (10) = 100mm			USB3.0 :From 1M to 3M						
			Mini USB2.0: From 1M to 4M						
			EX. (01) = 1M						

* Design and specification are subject to change without notice.

Physical Dimension

Receptacle

Panel Cut-Out




Type		Connector Gender (Housing)	L	OD
			Male	
USB2.0	Type A	Screw Thread	19.4	20.8
		2 Points Lock Bayonet	23.6	25.6
	Type B	Screw Thread	19.4	20.8
		2 Points Lock Bayonet	23.6	25.6
USB3.0	Type A	Screw Thread	19.4	20.8
		2 Points Lock Bayonet	23.6	25.6
Mini USB	-	Screw Thread	14.8	15.6

* Maximum Panel Thickness: USB: 4mm I Mini USB: 2.5mm Dimensions are shown in millimeters

* USB: Screw I Middle Size (13/16"-28 UNS)
2 Points Lock Bayonet I Large Size (1"20 UNEF)

* Mini USB: Screw I Standard Size (5/8"-27 UNS)

Connector Dimension



Receptacle with Cable

Type		Connector Gender (Housing)	W(A)	W(B)	W(C)	L1	L2
			Male				
USB2.0	Type A	Screw Thread	19.0	25.4	29.3	22.0	-
		2 Points Lock Bayonet	23.2	28.5	32.9	20.3	-
	Type B	Screw Thread	19.0	25.4	29.3	22.0	-
		2 Points Lock Bayonet	23.2	28.5	32.9	20.3	-
USB3.0	Type A	Screw Thread	19.0	25.4	29.3	-	37.2
		2 Points Lock Bayonet	23.2	28.5	32.9	-	37.5
Mini USB	-	Screw Thread	14.5	20.6	23.5	15.0	-


* USB: Screw I Middle Size (13/16"-28 UNS)

Dimensions are shown in millimeters

2 Points Lock Bayonet I Large Size (1"20 UNEF)

*Mini USB: Screw I Standard Size (5/8"-27 UNS)

Overmolded with Cable



Type		Connector Gender (Housing)	L		OD	
			Female	Male	Female	Male
USB2.0	Type A	Screw Thread	42.6	45.0	25.4	20.6
		2 Points Lock Bayonet	73.3	-	28.5	-
	Type B	Screw Thread	42.6	45.0	25.4	20.6
		2 Points Lock Bayonet	73.3	-	28.5	-
USB3.0	Type A	Screw Thread	42.6	45.0	42.6	20.6
		2 Points Lock Bayonet	75.0	-	28.5	-
Mini USB	-	Screw Thread	42.6	45.0	20.0	15.45


* USB: Screw I Middle Size (13/16"-28 UNS)

Dimensions are shown in millimeters

2 Points Lock Bayonet I Large Size (1"20 UNEF)

*Mini USB: Screw I Standard Size (5/8"-27 UNS)

Overmolded with Cable




Type		Connector Gender (Housing)	L(A)		L(B)		OD	
			Female	Male	Female	Male	Female	Male
USB2.0	Type A	Screw Thread	-	-	-	-	-	-
		2 Points Lock Bayonet	46.8	-	44.1	-	28.5	-
	Type B	Screw Thread	-	-	-	-	-	-
		2 Points Lock Bayonet	46.8	-	44.1	-	28.5	-

* USB: Screw I Middle Size (13/16"-28 UNS)

Dimensions are shown in millimeters

2 Points Lock Bayonet I Large Size (1"20 UNEF)

Field Installable



Type		Connector Gender (Housing)	L		OD	
			Female	Male	Female	Male
USB2.0	Type A	Screw Thread	-	56.0	-	20.6
		2 Points Lock Bayonet	-	-	-	-
	Type B	Screw Thread	-	56.0	-	20.6
		2 Points Lock Bayonet	-	-	-	-
Mini USB	-	Screw Thread	-	45.0	-	15.45

* USB: Screw I Middle Size (13/16"-28 UNS)


Dimensions are shown in millimeters

2 Points Lock Bayonet I Large Size (1"20 UNEF)

*Mini USB: Screw I Standard Size (5/8"-27 UNS)

Product Features

Receptacle



Backshell 8



Circular (C)

Mating Style 7




Screw Thread (S)



2 Points Lock Bayonet (L)
(Nut OD: 28.5mm)


2 Points Lock Bayonet (N)
(Nut OD: 25.4mm)

Connector Body (Style) 3



Front Fastened (P)


Overmolded with Cable



Backshell 8



Straight (L)



Right Angle (R)

Mating Style 7




Screw Thread (S)




2 Points Lock Bayonet (L)
(Nut OD: 28.5mm)

2 Points Lock Bayonet (N)
(Nut OD: 25.4mm)

Connector Body (Style) 3




With Strain Relief (A)



Without Strain Relief (B)

Field Installable



Backshell 8




Straight
(L)

Mating Style 7



Screw Thread (S)



Connector Body (Style) 3



Without Strain Relief (B)



Find Our Standard Products

USB > In-line

•Male Connector (Housing) •Female Contacts •Screw Thread •Middle Size (13/16"-28 UNS)	Overmolded with Cable-----> Overmolded with Cable-----> Overmolded with Cable (Double-Ended)		
	 ** USB 2.0: Choose the cable length from 01~05m ** USB 3.0: Choose the cable length from 01~03m  ** USB 2.0: Choose the cable length from 01~05m ** USB 3.0: Choose the cable length from 01~03m  Non-Waterproof ** USB 2.0: Choose the cable length from 01~05m ** USB 3.0: Choose the cable length from 01~03m		
Speed (Code)	Male Connector (M) Female Contacts (F)	Female Connector (F) Male Contacts (M)	Female Connector (F) Male Contacts (M)
USB 2.0 Type A	UA-20AMFM-SL7A**	UA-20BFMM-SL7A**	UA-20BFM-SA7A** UA-20BFM-SB7A**
USB 2.0 Type B	UB-20AMFM-SL7A**	UB-20BFMM-SL7A**	UB-20BFM-SA7A** UB-20BFM-SB7A**
USB 3.0 Type A	UA-30AMFM-SL7B**	UA-30BFMM-SL7B**	UA-30BFM-SD7B**



* Refer to P4-4 for ordering information.

USB > In-line

• Male Connector (Housing) • Female Contacts • Screw Thread • Middle Size (13/16"-28 UNS)	Field Installable 	Overmolded with Cable 	Overmolded with Cable (Double-Ended)  Non-Waterproof
	** USB 2.0: Choose the cable length from 01~05m	** USB 2.0: Choose the cable length from 01~05m	
Speed (Code)	Male Connector (M) Female Contacts (F)	Female Connector (F) Male Contacts (M)	Female Connector (F) Male Contacts (M)
USB 2.0 Type A	UA-20BMFA-SL8001	UA-20BFMM-SL7A**	UA-20BFM-SA7A** UA-20BFM-SB7A**
USB 2.0 Type B	UB-20BMFA-SL8001	UB-20BFMM-SL7A**	UB-20BFM-SA7A** UB-20BFM-SB7A**

* Refer to P4-4 for ordering information.




USB > In-line

• Male Connector (Housing) • Female Contacts • Screw Thread • Middle Size (13/16"-28 UNS)	Overmolded with Cable----->	Overmolded with Cable (Double-Ended)	Field Installable
	 USB2.0 and USB3.0 ** USB 2.0: Choose the cable length from 01~05m ** USB 3.0: Choose the cable length from 01~03m	 USB2.0 and USB3.0 ** USB 2.0: Choose the cable length from 01~05m ** USB 3.0: Choose the cable length from 01~03m	
Speed (Code)	Male Connector (M) Female Contacts (F)	Female Connector (F) Male Contacts (M)	Female Connector (F) Male Contacts (M)
USB 2.0 Type A	UA-20AMF-SA7A**	UA-20BFM-SA7A**	-
USB 3.0 Type A	UA-30AMF-SD7B**	UA-30BFM-SD7B**	-
USB 2.0 Type B	UB-20AMFM-SL7A**	-	-

* Refer to P4-4 for ordering information.



* Refer to P4-4 for ordering information.

USB > Receptacle and Mating Pair



• Male Connector (Housing) • Female Contacts • Screw Thread • Middle Size (13/16"-28 UNS)	Receptacle	Overmolded with Cable	Overmolded with Cable (Double-Ended)
	 Type 1 Type 2	 ** Choose the cable length from 01~05m	 Non-Waterproof ** Choose the cable length from 01~05m
Speed (Code)	Male Connector (M) Female Contacts (F)	Female Connector (F) Male Contacts (M)	Female Connector (F) Male Contacts (M)
USB 2.0 Type A	UA-20PMFP-SC8001 UA-20PMFP-SC8002 Type1 UA-20PMFP-SC8003 Type2	UA-20BFMM-SL7A**	UA-20BFM-SA7A** UA-20BFM-SB7A**
USB 2.0 Type B	UB-20PMFP-SC8001 UB-20PMFP-SC8002 UB-20PMFP-SC8003	UB-20BFMM-SL7A**	UB-20BFM-SA7A** UB-20BFM-SB7A**

* Refer to P4-4 for ordering information.

USB > Receptacle and Mating Pair

	Receptacle	Overmolded with Cable	Field Installable
• Male Connector (Housing) • Female Contacts • 2 Points Lock Bayonet (Nut OD: 28.5mm) • Large Size (1" 20 UNEF)	 Type 1 Type 2	 ** Choose the cable length from 01~05m	
Speed (Code)	Male Connector (M) Female Contacts (F)	Female Connector (F) Male Contacts (M)	Female Connector (F) Male Contacts (M)
USB 2.0 Type A	UA-20PMFP-LC7001 UA-20PMFP-LC7002 Type1 UA-20PMFP-LC7003 Type2	UA-20AFMM-LL7A** UA-20AFMM-LR7A**	-
USB 2.0 Type B	UB-20PMFP-LC7001 UB-20PMFP-LC7002 UB-20PMFP-LC7003	UB-20AFMM-LL7A** UB-20AFMM-LR7A**	-

USB > Receptacle and Mating Pair






	Receptacle	Overmolded with Cable	Field Installable
• Male Connector (Housing) • Female Contacts • 2 Points Lock Bayonet (Nut OD: 25.4mm) • Large Size (13/16-28 UN)		 ** Choose the cable length from 01~05m	
Speed (Code)	Male Connector (M) Female Contacts (F)	Female Connector (F) Male Contacts (M)	Female Connector (F) Male Contacts (M)
USB 2.0 Type A	UA-20PMFJ-NC7001	UA-20BFMM-NL7A**	-

USB

Receptacle with Overmolded Cable and Mating Pair
2 Points Lock Bayonet
Large Size

IP 67 . 68 9
Unmated or Mated



USB > Receptacle with Overmolded Cable and Mating Pair

• Male Connector (Housing) • Female Contacts • Screw Thread • 2 Points Lock Bayonet (Nut OD: 28.5mm) • Large Size (1"20 UNEF)	Receptacle with Cable (Double-Ended)	Overmolded with Cable (Double-Ended)	
	  Non-Waterproof ** USB 3.0: Choose the cable length from 100~300mm	 	  ** USB 3.0: Choose the cable length from 01~03m
Speed (Code)	Male Connector (M) Female Contacts (F)	Female Connector (F) Male Contacts (M)	Female Connector (F) Male Contacts (M)
USB 3.0 Type A	UA-30PMF-LD7B** UA-30PMF-SD7B**	UA-30AFMM-LL7BXX UA-30BFMM-SL7BXX	UA-30BFM-SD7B** UA-30AFM-LD7B**



* Refer to P4-4 for ordering information.

* Refer to P4-4 for ordering information.



Mini USB > In-line

• Male Connector (Housing) • Female Contacts • Screw Thread • Standard Size (5/8"-27 UNS)	Overmolded with Cable ----->		Field Installable
			
	** Choose the cable length from 01~04m	** Choose the cable length from 01~04m	
Speed (Code)	Male Connector (M) Female Contacts (F)	Female Connector (F) Male Contacts (M)	Female Connector (F) Male Contacts (M)
Mini USB 2.0 Type B	NUB-20AMFM-SL7A**	NUB-20AFMM-SL7A**	-

Mini USB > In-line

• Male Connector (Housing) • Female Contacts • Screw Thread • Standard Size (5/8"-27 UNS)	Field Installable ----->		Field Installable
			
	** Choose the cable length from 01~04m	** Choose the cable length from 01~04m	
Speed (Code)	Male Connector (M) Female Contacts (F)	Female Connector (F) Male Contacts (M)	Female Connector (F) Male Contacts (M)
Mini USB 2.0 Type B	NUB-20AMFM-SL7A**	NUB-20AFMM-SL7A**	-

Mini USB > Receptacle and Mating Pair


• Male Connector (Housing) • Female Contacts • Screw Thread • Standard Size (5/8"-27 UNS)	Receptacle ----->		Field Installable
			
		** Choose the cable length from 01~04m	
Speed (Code)	Male Connector (M) Female Contacts (F)	Female Connector (F) Male Contacts (M)	Female Connector (F) Male Contacts (M)
Mini USB 2.0 Type B	NUB-20PMFP-SC7001 NUB-20PMFR-SC7001	NUB-20AFMM-SL7A**	-

IEEE 1394 Connector




Range Overview


Receptacle to Overmolded with Cable



In Line



Accessories



Waterproof Cap
See page 21-16

Specification

Identifications	IEEE 1394
Description	Receptacle Overmolded with Cable Field Installable
Current Rating / Data	Receptacle: 1A Overmolded with Cable: 0.5A
Material	Contacts: Copper Alloy, Gold Plated Connector Body (Housing) : PBT UL94V-0
Waterproof Rating	IP67~68
Temperature Range	Receptacle: -20 °C~80 °C Overmolded with Cable: -20 °C~80 °C Field Installable: -20 °C~80 °C
Contact Resistance	≤ 50mΩ Max
Insulation Resistance	Receptacle: ≥ 100MΩ at DC 100V Overmolded with Cable: ≥ 1000MΩ at DC 100V
Durability	500 cycles
Breakdown Voltage	Receptacle: ≥ AC 500V / 1 minute Overmolded with Cable: ≥ AC 100V / 1 minute
More to know	Standard Cable Length: 01~04M

【Note】 Design and specification are subject to change without notice.

Ordering Information

1 — 2 3 4 5 6 — 7 8 9 10

Specification

(13) 1394 Connector

Type

(AA) 1394A

Connector Body (Style)
> For Receptacle

(P) Front Fastened

> For Field installable

(B) Without Strain Relief

> For Overmolded with Cable

(A) With Strain Relief

(B) Without Strain Relief

Connector (Housing) Gender

(M) Male Connector

(F) Female Connector

Contact Gender

(M) Male (Plug)

(F) Female (Jack)

Assemble Style
> For Receptacle

(P) 180° PCB Type

> For Overmolded with Cable

(M) Overmolded with Cable

> For Field Installable

(A) Field installable (Solder)

Mating Style

(S) Screw Thread

Backshell
> For Receptacle

(C) Circular

> For Field Installable

(L) Straight

> For Overmolded with Cable

(L) Straight

Waterproof Rating

(7) IP 67

(8) IP 68

More Information
> For Receptacle

(001) Without Cable

 (002) With Cable (Harness
(50mm))

> For Overmolded with Cable

(□)+(■) : Cable Type + Cable Length

EX. (A01) = 1394A Cable + 1M

(□) : Cable Type

(A) 1394A Cable

(■) : Cable Length


From 1M to 4M

EX. (01) = 1M


Physical Dimension

Receptacle

Panel Cut-Out



Connector Dimension




Type	Dimension	L	OD
Connector Gender		Male	
IEEE 1394		19.4	20.8

* Maximum Panel Thickness: 4mm

Unit: mm


Overmolded with Cable

Female Connector



Without Strain Relief

Male Connector




With Strain Relief

Type	Dimension	L		OD	
Connector Gender		Female	Male	Female	Male
IEEE 1394		39.0	55.0	25.4	20.6

Unit: mm

Field Installable




without Strain Relief / Straight

Type	Dimension	L		OD	
Connector Gender		Female	Male	Female	Male
IEEE 1394		-	56.5	-	20.6

Unit: mm


Contact Configuration



【Note】 Design and specification are subject to change without notice.

Product Features

Receptacle



* PCB Pin 180°

Backshell 8




Circular (C)

Mating Style 7




Screw Thread (S)

Connector Body(Style) 3




Front Fastened (P)

Overmolded with Cable



Backshell 8




Straight
(L)

Mating Style 7




Screw Thread (S)

Connector Body(Style) 3




With Strain Relief (A)




Without Strain Relief (B)

Field Installable



Backshell 8



Straight
(L)

Mating Style 7



Screw Thread (S)



Connector Body(Style) 3



Without Strain Relief (B)




Find Our Standard Products

└ In-line

• Male Connector (Housing) • Female Contacts • Screw Thread	Overmolded with Cable 	Overmolded with Cable 	Field Installable
Code	Male Connector (M) Female Contacts (F)	Female Connector (F) Male Contacts (M)	Female Connector (F) Male Contacts (M)
IEEE 1394 A Type (13)	13-AAAMFM-SL7A <u>XX</u> *	13-AABFMM-SL7A <u>XX</u> *	-



* XX: Choose the cable length from 01~04m

└ In-line

• Female Connector (Housing) • Male Contacts • Screw Thread	Overmolded with Cable 	Overmolded with Cable 	Field Installable 
Code	Female Connector (F) Male Contacts (M)	Male Connector (M) Female Contacts (F)	Male Connector (M) Female Contacts (F)
IEEE 1394 A Type (13)	13-AABFMM-SL7A <u>XX</u> *	13-AAAMFM-SL7A <u>XX</u> *	13-AABMFA-SL8001

* XX: Choose the cable length from 01~04m

└ Receptacle and Mating Pair

• Male Connector (Housing) • Female Contacts • Screw Thread	Receptacle 	Overmolded with Cable 	Field Installable
Code	Male Connector (M) Female Contacts (F)	Female Connector (F) Male Contacts (M)	Female Connector (F) Male Contacts (M)
IEEE 1394 A Type (13)	13-AAPMFP-SC8001	13-AABFMM-SL7A <u>XX</u> *	-

* XX: Choose the cable length from 01~04m


【Note】 Design and specification are subject to change without notice.

D-Sub Connector




Range Overview


Receptacle to Overmolded with Cable




Receptacle to Field Installable




Accessories




Dust Cap
See page 21-10



Waterproof Cap
See page 21-16



Joint
See page 21-23



Specification

Identifications	Standard D-Sub Connector High Density D-Sub Connector
Description	Receptacle Overmolded with Cable Field Installable
Current Rating / Data	Standard D-Sub : 5A High Density D-Sub : 2A
Material	Contacts: Copper Alloy, Gold Plated Connector Body (Housing) : Nylon 9T or PBT, UL Recognized Shell: Steel, Nickel Plated
Waterproof Rating	Receptacle: IP68 Overmolded with Cable: IP67 Field Installable: IP67
Temperature Range	Receptacle: -40°C~105°C Overmolded with Cable: -20°C~80°C Field Installable: -40°C~105°C
Contact Resistance	≤ 20mΩ
Insulation Resistance	≥ 500mΩ at DC500V
Durability	500 cycles
Breakdown Voltage	≥ AC500V / 1 minute
More to know	Standard Cable Length: 01~99M


【Note】 Design and specification are subject to change without notice.

Ordering Information

	1	2	3	4	5	6	7	8	9	10
Specification > <u>Standard</u> (SDB) D-SUB > <u>High Density</u> (HDB) High Density D-SUB										
Number of Contacts 09, 15,, 25, 26...78 Contacts Ex. 09 Pin = (09)										
Connector Body (Style) > <u>For Receptacle</u> (P) Front Fastened > <u>For Overmolded with Cable</u> (A) With Strain Relief > <u>For Field installable</u> (B) Without Strain Relief										
Connector (Housing) Gender (M) Male (F) Female										
Contact Gender (M) Male (Plug) (F) Female (Jack)										
Assemble Style > <u>For Receptacle</u> (S) Solder Type (P) PCB Type (90° / 180°) > <u>For Overmolded with Cable</u> (M) Overmolded with Cable > <u>For Field Installable</u> (A) Field Installable (Solder) (C) Field Installable (Crimped)										
Mating Style (S) Screw Thread (Q) Automated Latch										
Backshell > <u>For Receptacle</u> (With Board Lock) (A) Straight (B) Right Angle (Without Board Lock) (L) Straight (R) Right Angle > <u>For Overmolded with Cable</u> (Without Board Lock) (L) Straight > <u>For Field Installable</u> (Without Board Lock) (L) Straight										
Waterproof Rating (7) IP 67 (8) IP 68										
More Information > <u>For Receptacle</u> (001), (002)..... Without Cable : Different Versions > <u>For Overmolded with Cable</u> (□)+(■) : Cable Type + Cable Length EX. (A01) = UL2464 Cable + 1M (□) : Cable Type (A) UL2464 Cable (■) : Cable Length From 1M to 99M EX. (01) = 1M										

Physical Dimension

Receptacle




Dimension			Type	L (A)	L (B)	L (C)	I	II	III	IV
Connector	Current Rating	Number of Contacts	Female / Male				Female	Male	Female	Male
Standard D-SUB	5A	9Pins	B	20.0	28.2	-	39.4	25.0	16.33	16.92
		15Pins	A	28.0	36.5	58.4	-	-	24.66	25.25
		25Pins	B	28.0	36.5	-	47.8	33.3	24.66	25.25
		37Pins	B	41.5	51.0	-	64.5	47.04	38.4	38.96
		50Pins	B	57.9	67.8	-	78.4	63.5	54.8	55.4
		62Pins	B	55.5	65.0	-	75.9	61.0	52.20	52.80
High Density D-SUB	2A	15Pins	B	20.0	28.2	-	39.4	25.0	16.33	16.92
		26Pins	A	28.0	36.5	58.4	-	-	24.66	25.25
		44Pins	B	28.0	36.5	-	47.8	33.3	24.66	25.25
		62Pins	B	41.5	51.0	-	64.5	47.04	38.40	38.96
		78Pins	B	57.9	67.8	-	78.4	63.5	54.8	55.4
		78Pins	B	55.5	65.0	-	75.9	61.1	52.20	52.80

* Maximum Panel Thickness: 2mm

Unit: mm

Overmolded with Cable




With Strain Relief / Straight

Dimension			L	W
Connector	Current Rating	Number of Contacts	Female / Male	Female / Male
Standard D-SUB	5A	9	55.9	42.4
		15	53.5	50.6
		25	60.0	64.5
		37	69.3	81.1
		50	71.8	79.3
High Density D-SUB	2A	15	55.9	42.4
		26	53.5	50.6
		44	60.0	64.5
		62	69.3	81.1
		78	71.8	79.3

Unit: mm

Field Installable



Without Strain Relief / Straight

Dimension			L	W
Connector	Current Rating	Number of Contacts	Female / Male	Female / Male
Standard D-SUB	5A	9	66.8	42.8
		15	63.0	50.7
		25	81.6	50.6
		25	91.9	64.4
High Density D-SUB	2A	15	66.8	42.8
		26	63.0	50.7
		44	81.6	50.6
			91.9	64.4

Unit: mm

[Note] Design and specification are subject to change without notice.

Contact Configuration

	Standard D-SUB (5A)	High Density D-SUB (2A)
9Pin (09)	 R C F	
15Pin (15)	 R C F	 R C F
25Pin (25)	 R C F	
26Pin (26)		 R C F
37Pin (37)	 R C	
44Pin (44)		 R C F
50Pin (50)	 R C	
62Pin (62)		 R C
78Pin (78)		 R C

R: Receptacle

C: Overmolded with Cable

F: Field Installable

▲ 2A (HDB)

● 5A (SDB)

1

Number of Contacts :

2

Ex.2 contacts (02)

Connector (Housing) Gender:

4

Male(M) or Female(F)

Contact Gender:


5

Male(M) or Female(F)


More to Choose:

6


- Solder (S)
- Solder Contact



- PCB Type (P)
- 90° PCB - 180° PCB




- Crimp type (C)




Product Features

≧ Receptacle




Connector Body(Style) ③



Front
Fastened (P)

Mating Style ⑦




Automated Latch (Q)




Screw Thread (S)


Backshell ⑧



(With Board Lock)
Straight (A)



Right Angle (B)




(Without Board Lock)
Straight (L)




Right Angle (R)

≧ Overmolded with Cable



Backshell ⑧




Straight (L)

Mating Style ⑦




Screw Thread (S)

Connector Body(Style) ③



With Strain Relief (A)


≧ Field Installable



(Metal Item)

Mating Style ⑦

(Metal Item)



Automated Latch (Q)


Mating Style ⑦

(Plastic Item)




Screw Thread (S)

Connector Body(Style) ③



Without Strain Relief (B)

Backshell ⑧



Straight (L)

【Note】 Design and specification are subject to change without notice.




Find Our Standard Products

Receptacle and Mating Pair

• Male Connector (Housing) • Male Contacts • Screw Thread • Plastic Connectors		Receptacle	Overmolded with Cable	Field Installable
Current Rating (Code)	Contacts ②	Male Connector (M) Male Contacts (M)	Female Connector (F) Female Contacts (F)	Female Connector (F) Female Contacts (F)
Standard D-SUB 5A (SDB)	09, 15, 25, 37, 50	SDB-② PMMP-SA8001 SDB-② PMMP-SB8001 SDB-② PMMP-SL8001 SDB-② PMMP-SR8001 SDB-② PMMS-SL8001	SDB-② AFFM-SL7AXX*	SDB-② BFFA-SL7001 SDB-② BFFC-SL7001
High Density D-SUB 2A (HDB)	15, 26, 44, 62, 78	HDB-② PMMP-SA8001 HDB-② PMMP-SB8001 HDB-② PMMP-SL8001 HDB-② PMMP-SR8001 HDB-② PMMS-SL8001	HDB-② AFFM-SL7AXX*	HDB-② BFFA-SL7001
		- PCB 180° with Board Lock : 5A (SDB) 09 / 15 / 25 / 37 pins. 2A (HDB) 15 / 26 / 44 / 62 pins. - PCB 90° with Board Lock: 5A (SDB) 09 / 15 pins. 2A (HDB) 15 / 26 pins. - Solder Type: 5A (SDB) 09 / 15 / 25 / 37 / 50 pins. 2A (HDB) 15 / 26 / 44 / 62 / 78 pins.		- Crimp Pin: 5A (SDB) 09 / 15 / 25 pins. - Solder Pin: 5A (SDB) 09 / 15 / 25 pins. 2A (HDB) 15 / 26 / 44 pins.

* XX: Choose the cable length from 01~99



Receptacle and Mating Pair

• Female Connector (Housing) • Female Contacts • Screw Thread • Plastic Connectors		Receptacle 	Overmolded with Cable 	Field Installable 
Current Rating (Code)	Contacts ②	Female Connector (F) Female Contacts (F)	Male Connector (M) Male Contacts (M)	Male Connector (M) Male Contacts (M)
Standard D-SUB 5A (SDB)	09, 15, 25, 37, 50	SDB-② PFFP-SA8001 SDB-② PFFP-SB8001 SDB-② PFFP-SL8001 SDB-② PFFP-SR8001 SDB-② PFFS-SL8001	SDB-② AMMM-SL7XX*	SDB-② BMMA-SL7001 SDB-② BMMC-SL7001
High Density D-SUB 2A (HDB)	15, 26, 44, 62, 78	HDB-② PFFP-SA8001 HDB-② PFFP-SB8001 HDB-② PFFP-SL8001 HDB-② PFFP-SR8001 HDB-② PFFS-SL8001	HDB-② AMMM-SL7AXX*	HDB-② BMMA-SL7001
		- PCB 180° with Board Lock : 5A (SDB) 09 / 15 / 25 / 37 pins. 2A (HDB) 15 / 26 / 44 / 62 pins. - PCB 90° with Board Lock: 5A (SDB) 09 / 15 pins. 2A (HDB) 15 / 26 pins. - Solder Type: 5A (SDB) 09 / 15 / 25 / 37 / 50 pins. 2A (HDB) 15 / 26 / 44 / 62 / 78 pins.	-	- Crimp Pin: 5A (SDB) 09 / 15 / 25 pins. - Solder Pin: 5A (SDB) 09 / 15 / 25 pins. 2A (HDB) 15 / 26 / 44 pins.



* XX: Choose the cable length from 01~99

【Note】 Design and specification are subject to change without notice.


Receptacle and Mating Pair

• Male Connector (Housing) • Male Contacts • Automated Latch • Metal Connectors		Receptacle 	Overmolded with Cable 	Field Installable 
Current Rating (Code)	Contacts	Male Connector (M) Male Contacts (M)	Female Connector (F) Female Contacts (F)	Female Connector (F) Female Contacts (F)
Standard D-SUB 5A (SDB)	15	SDB-15PMMP-QA8001 SDB-15PMMP-QB8001 SDB-15PMMP-QL8001 SDB-15PMMS-QL8001	-	SDB-15BFFA-QL7001
High Density D-SUB 2A (HDB)	26	HDB-26PMMP-QA8001 HDB-26PMMP-QB8001 HDB-26PMMP-QL8001 HDB-26PMMS-QL8001	-	HDB-26BFFA-QL7001

Receptacle and Mating Pair

• Female Connector (Housing) • Female Contacts • Automated Latch • Metal Connectors		Receptacle 	Overmolded with Cable 	Field Installable 
Current Rating (Code)	Contacts	Female Connector (F) Female Contacts (F)	Male Connector (M) Male Contacts (M)	Male Connector (M) Male Contacts (M)
Standard D-SUB 5A (SDB)	15	SDB-15PFFP-QA8001 SDB-15PFFP-QB8001 SDB-15PFFP-QL8001 SDB-15PFFS-QL8001	-	SDB-15BMMA-QL7001
High Density D-SUB 2A (HDB)	26	HDB-26PFFP-QA8001 HDB-26PFFP-QB8001 HDB-26PFFP-QL8001 HDB-26PFFS-QL8001	-	HDB-26BMMA-QL7001

Blank lined paper for writing.




DVI Connector




Range Overview

Receptacle to Overmolded with Cable



Accessories



Waterproof Cap
See page 21-16

Specification

Identifications	DVI-D Single Link (DDS): Digital DVI-D Dual Link (DDD): Digital DVI-I Single Link (DIS): Digital and Analog DVI-I Dual Link (DID): Digital and Analog
Description	Receptacle Overmolded with Cable
Current Rating / Data	1.5A
Material	Contacts: Cooper Alloy, Gold Plated Connector Body (Housing): Nylon + GF, UL Recognized Shell: Steel, Nickel Plated
Waterproof Rating	Receptacle: IP68 Overmolded with Cable: IP67
Temperature Range	Receptacle: -20°C~80°C Overmolded with Cable: -20°C~80°C
Contact Resistance	$\leq 20\text{m}\Omega$
Insulation Resistance	$\geq 1000\text{m}\Omega$ at DC500V
Durability	100 cycles
Breakdown Voltage	$\geq$ AC 500V / 1 minute
More to know	Standard Cable Length: 01~05M

【Note】 Design and specification are subject to change without notice.

1-2 3 4 5 6-7 8 9 10

(DIS) DVI-I Single Link **(DDS)** DVI-D Single Link
(DID) DVI-I Dual Link **(DDD)** DVI-D Dual Link

Number of Contacts

19, 23, 25, 29... Contacts

Ex. 19 Pin = (19)

> For Receptacle

(P) Front Fastened

> For Overmolded with Cable

(A) With Strain Relief

(M) Male

(F) Female

(M) Male

(F) Female

> For Receptacle

> For Overmolded with Cable

(S) Solder Type

(M) Overmolded with Cable

(S) Screw Thread

> For Receptacle

> For Overmolded with Cable

(L) Straight / Without Board Lock

(L) Straight

(7) IP 67

(8) IP 68

More Info

> For Receptacle

> For Overmolded with Cable

(001), (002).....

() + (): Cable Type + Cable Length

Without Cable : Different Versions

EX. (A01) = UL20276 Cable + 1M

(□) : Cable Type

(L) : Cable Length

(A) UL20276

From 1M to 5M



28AWG/PVC

EX. (01) = 1M

Physical Dimension


Receptacle

Panel Cut-Out



* Maximum Panel Thickness: 2mm


Connector Dimension



* Unit: mm

* The dimension is feasible for DVI-D Single Link(DDS), DVI-D Dual Link(DDD), DVI-D Single Link(DIS), and DVI-D Dual Link(DID)

Overmolded with Cable



* Unit: mm

* The dimension is feasible for DVI-D Single Link(DDS), DVI-D Dual Link(DDD), DVI-D Single Link(DIS), and DVI-D Dual Link(DID)

Contact Configuration


DVI-D Dual Link (DDD)
25 Contacts
DVI-I Dual Link (DID)
29 Contacts

DVI-D Single Link (DDS)
19 Contacts
DVI-I Single Link (DIS)
23 Contacts


【Note】 Design and specification are subject to change without notice.

Product Features

Receptacle



Backshell 8




Straight (L)

Mating Style 7




Screw Thread (S)

Connector Body(Style) 3




Front Fastened (P)

Overmolded with Cable



Backshell 8




Straight
(L)

Mating Style 7



Screw Thread (S)



Connector Body(Style) 3



With Strain Relief (A)

Find Our Standard Products

▾ Receptacle and Mating Pair

• Female Connector (Housing) • Female Contacts • Screw Thread	Receptacle	Overmolded with Cable	Field Installable
			
Code	Female Connector (F) Female Contacts (F)	Male Connector (M) Male Contacts (M)	Male Connector (M) Male Contacts (M)
DVI-D Single Link (DDS)	DDS-19PFFS-SL8001	DDS-19AMMM-SL7A <u>XX</u> *	-
DVI-D Dual Link (DDD)	DDD-25PFFS-SL8001	DDD-25AMMM-SL7A <u>XX</u> *	-
DVI-I Single Link (DIS)	DIS-23PFFS-SL8001	DIS-23AMMM-SL7A <u>XX</u> *	-
DVI-I Dual Link (DID)	DID-29PFFS-SL8001	DID-29AMMM-SL7A <u>XX</u> *	-

【Note】 For digital and analog, please choose DVI-I
For digital only, please choose DVI-D


* XX: Choose UL20276 cable and select the cable length from 01~05m

RJ Connector




Range Overview


Receptacle and Mating Pair (Middle Size 13/16"-28UNS)




Receptacle and Mating Pair (ODVA)




Receptacle and Mating Pair (Large Size 1"20-UNEF)




I Adaptor



Accessories



Waterproof Cap
See page 21-17



Patch Cable (Double-ended)
See page 21-24

* Design and specification are subject to change without notice.

Specification

Identifications	Middle Size: 13/16"-28 UNS (Cat. 5e) Large Size: 1"-20 UNS (Cat. 5e) ODVA (Cat. 5e)
Description	Receptacle Receptacle With Cable Overmolded with Cable Field Installable
Current Rating / Data	100 Base, 100 Base T and 1000 Base T Networks Cat 5E per TIA or EIA 568B Class D per ISO / IEC 11801
Material	Connector Body: -Housing: Polyester, UL94V-0, UV Resistant -Fastening Nut (Panel Side): Polyester UL94V-0,UV Resistant -Mating Lock Nut: Polyester , UL94V-0,UV Resistant RJ45 Jack and Plug Contacts: Phosphor Bronze, Gold Plated Cable Termination: Flame Protection per UL94V-0,UV Resistant
Waterproof Rating	IP67
Temperature Range	Receptacle: -40 °C~105 °C Overmolded with Cable: -20 °C~80 °C
Contact Resistance	≤ 20mΩ
Insulation Resistance	≥ 500mΩ at DC500V
Durability	750 cycles
Breakdown Voltage	≥ AC1000V / 1 minute
More to know	Thermal shock: -20°C~80°C 5cycls Salt Spray Corrosion: 48H POE: 60W /2A Standard Cable Length: 01-99M

Ordering Information

	1	2	3	4	5	6	7	8	9	10
Specification										
(RCP) RJ45 C Size (Plastic)										
(RCM) RJ45 C Size (Metal)										
(RDP) RJ45 D Size (Plastic)										
(RDM) RJ45 D Size (Metal)										
(ROP) RJ45 ODVA (Plastic)										
Cat Type & Shielded										
(00) None										
(5S) Cat.5e shielded										
(5U) Cat.5e Unshielded										
Connector Body (Style)										
> For Receptacle										
(P) Front Fastened										
(R) Rear Fastened										
(D) Dual Fastened										
> For Overmolded with Cable										
(A) With Strain Relief										
(B) Without Strain Relief										
> For Field Installable										
(A) With Strain Relief										
(B) Without Strain Relief										
Connector (Housing) Gender										
(MM) Plug										
(FF) Jack										
Assemble Style										
> For Receptacle										
(H) Jack 180 (Horizontal)										
(V) Jack 90 (Vertical)										
> For Overmolded with Cable										
(M) Overmolded with Cable										
> For Field Installable										
(A) Field installable (Compled)										
(S) Field installable (Feed-Thru)										
Mating Style										
(T) 3 Points Lock Bayonet										
(S) Screw Thread										
Backshell										
> For Receptacle										
(C) Circular										
(S) Square										
> For Overmolded with Cable										
(L) Straight										
(R) Right Angle										
> For Field Installable										
(L) Straight										
Waterproof Types										
(U) Unmated Waterproof										
(M) Mated Waterproof										
Waterproof Rating										
(7) IP 67										
*IP 68 upon request.										
More information										
> For Receptacle										
(001), (002).....										
> For Overmolded with Cable										
(□)+(■) : Cable Type + Cable Length										
(□) : Cable Type										
(A) C5e UTP Solid Cable										
(B) C5e FTP Solid Cable										
(■) : Cable Length										
From 1M to 99M										
EX. (01) = 1M										

* Design and specification are subject to change without notice.

Ordering Information | Double-ended

ALTW waterproof connector to ALTW waterproof connector

ALTW waterproof connector to Standard RJ connector (None Waterproof)

f to Waterproof / Non-Waterproof

1 2 3 4 5 6 7 8 9

Specification (1st End)

(RCP) RJ45 C Size (Plastic)

(RCM) RJ45 C Size (Metal)

(RDP) RJ45 D Size (Plastic)

(RDM) RJ45 D Size (Metal)

(ROP) RJ45 ODVA (Plastic)

Cat Type & Shielded (1st End)

(5U) Cat.5e Unshielded

(5S) Cat.5e Shielded

Connector (Housing) Gender (1st End)

(M) Plug

(F) Jack

Specification (2nd End)

> For Waterproof Connectors

(RCP) RJ45 C Size (Plastic)

(RCM) RJ45 C Size (Metal)

(RDP) RJ45 D Size (Plastic)

(RDM) RJ45 D Size (Metal)

(ROP) RJ45 ODVA (Plastic)

> For Non-Waterproof Plug

(UPG) Unshielded Plug

(SPG) Shielded Plug

Cat Type & Shielded (2nd End)

> For Waterproof Connectors

(5U) Cat.5e Unshielded

(5S) Cat.5e Unshielded

> For Non-Waterproof Plug

(06) Gold Plating 6u"

Connector (Housing) Gender (2nd End)

(M) Plug

Mating Style

(T) 3 Points Lock Bayonet

(S) Screw Thread

Backshell

> For Overmolded with Cable

(L) Straight

(R) Right Angle

More information

> For Overmolded with Cable

(□)+(■) : Cable Type + Cable Length

(□) : Cable Type

(■) : Cable Length

(A) C5e UTP Solid Cable

From 1M to 99M


(B) C5e FTP Solid Cable

EX. (01) = 1M

Physical Dimension

Receptacle


Panel Cut-Out



Type \ Dimension	Type	L / W	OD	Ø
Connector Gender (Housing)	Female			
Middle Size (13/16"-28 UNS)	A	19.4	20.8	-
	B	19.4/24.4	20.8	3.1
Large Size (1"20 UNEF)	A	23.6	25.6	-
	B	23.6/24.4	25.6	3.1
ODVA	C	12.4	27.1	-
	D	12.4/25.9	27.1	M3.0*0.5

Dimensions are shown in millimeters


Connector Dimension



Type \ Dimension	Type	Shape	L	W
Connector Gender (Housing)	Female			
Middle Size (13/16"-28 UNS)	A1	Circle	44.0	26.0
		Square	44.0	32.0
	A2	Circle	39.9	26.0
		Square	39.9	32.0
Large Size (1"20 UNEF)	A1	Circle	44.0	32.0
		Square	44.0	32.0
	A2	Circle	39.9	32.0
		Square	39.9	32.0
ODVA	B	Circle	33.2	34.0
		Square	33.2	36.0

* Choose backshell: Circular (C) or Square Flange (S) | Dimensions are shown in millimeters


Overmolded with Cable



Type \ Dimension	Type	L		OD	
Connector Gender (Housing)		Female	Male	Female	Male
Middle Size (13/16"-28 UNS)	A	-	58.0	-	25.4
	B	-	45.0	-	25.4
Large Size (1"20 UNEF)	A	-	73.6	-	28.8
	B	-	53.4	-	28.8
ODVA	A	-	79.3	-	31.5

Dimensions are shown in millimeters

Field Installable




Type \ Dimension	Type	L		OD	
Connector Gender (Housing)		Female	Male	Female	Male
Middle Size (13/16"-28 UNS)	A	-	72.0	-	25.4
	B	-	40.7	-	25.4
Large Size (1"20 UNEF)	A	-	76.7	-	25.4
	B	-	59.7	-	32.0
ODVA	A	-	77.6	-	31.5

Dimensions are shown in millimeters

* Design and specification are subject to change without notice.

Product Features


Receptacle



Backshell ⁷





Circular (C)



Square (S)

Assembly Style ⁵

Jack 180
(Horizontal) (H)

Jack 90 (Vertical) (V)

Mating Style ⁶




Screw Thread (S)





3 Points Lock (T)


Connector Body(Style) ³





Front Fastened (P)

Rear Fastened(R)
(For ODVA only)Double Fastened (D)
(For ODVA only)

Overmolded with Cable



Backshell ⁷

Straight
(L)Right Angle
(R)

Mating Style ⁶




Screw Thread (S)




3 Points Lock (T)

Connector Body(Style) ³




With Strain Relief (A)

Field Installable



Backshell ⁷

Straight
(L)

Mating Style ⁶




Screw Thread (S)



3 Points Lock (T)

Connector Body(Style) ³






With Strain Relief (A)

* Refer to P8-4 for Ordering Information

Find Our Standard Products

▮ Middle Size 13/16"-28 UNS > Receptacle and Mating Pair

• Female Connector (Housing) • Female Contacts • Screw Thread		Receptacle ----->	-----> Overmolded with Cable		Field Installable
					
		8 Choose unmated (U) or mated (M) waterproof	2 Choose shielded (5S) or unshielded (5U) *** Choose the cable length:01-99m	*** Choose the cable length:01-99m	
Cat. 5e		Female Connector (F) Female Contacts (F)	Male Connector (M) Male Contacts (M)	Male Connector (M) Male Contacts (M)	Male Connector (M) Male Contacts (M)
Plastic	Jack 180	RCP-5SPFFH-SC 8 7001 RCP-5SPFFH-SS 8 7001	RCP-5 2 AMMM-SLM7*** RCP-5 2 AMMM-SRM7***	RCP5UM-RCP5UM-SL*** RCP5UM-RCP5UM-SR***	RCP-00AMMA-SLM7001 RCP-00BMMS-SLM7001
	Jack 90	RCP-5SPFFV-SC 8 7001 RCP-5SPFFV-SS 8 7001		RCP5UM-UPG06M-SL*** RCP5UM-UPG06M-SR***	
Metal	Jack 180	RCM-5SPFFH-SC 8 7001 RCM-5SPFFH-SS 8 7001	RCM-5 2 AMMM-SLM7*** RCM-5 2 AMMM-SRM7***	-	-
	Jack 90	RCM-5SPFFV-SC 8 7001 RCM-5SPFFV-SS 8 7001			

* Refer to P8-5 for ordering.




Middle Size 13-16"-28UNS

Receptacle and Mating Pair
3 Points Lock Bayonet

IP 67 9





Receptacle | Unmated & Mated
Overmolded with Cable | Mated
Field Installable | Mated

Middle Size 13/16"-28 UNS > Receptacle and Mating Pair

		Receptacle	Overmolded with Cable		Field Installable
• Female Connector (Housing) • Female Contacts • 3 Points Lock Bayonet					
		8 Choose unmated (U) or mated (M) waterproof	2 Choose shielded (5S) or unshielded (5U) *** Choose the cable length: 01-99m		*** Choose the cable length: 01-99m
Cat. 5e		Female Connector (F) Female Contacts (F)	Male Connector (M) Male Contacts (M)	Male Connector (M) Male Contacts (M)	Male Connector (M) Male Contacts (M)
Plastic	Jack 180	RCP-5SPFFH-TC 8 7001 RCP-5SPFFH-TS 8 7001	RCP-5 2 AMMM-TLM7*** RCP-5 2 AMMM-TRM7***	RCP5UM-RCP5UM-TL*** RCP5UM-RCP5UM-TR***	RCP-00AMMA-TLM7001 RCP-00BMMS-TLM7001
	Jack 90	RCP-5SPFFV-TC 8 7001 RCP-5SPFFV-TS 8 7001		RCP5UM-UPG06M-TL*** RCP5UM-UPG06M-TR***	

*Refer to P8-5 for ordering information.

Large Size 1"-20 UNEF > Receptacle and Mating Pair

• Female Connector (Housing) • Female Contacts • Screw Thread		Receptacle	Overmolded with Cable		Field Installable
					
		8 Choose unmated (U) or mated (M) waterproof	2 Choose shielded (5S) or unshielded (5U) *** Choose the cable length:0.1-99m	*** Choose the cable length:0.1-99m	Completed Feed-Thru
Cat. 5e		Female Connector (F) Female Contacts (F)	Male Connector (M) Male Contacts (M)	Male Connector (M) Male Contacts (M)	Male Connector (M) Male Contacts (M)
Plastic	Jack 180	RDP-5SPFFH-SC 8 7001 RDP-5SPFFH-SS 8 7001	RDP-5 2 AMMM-SLM7*** RDP-5 2 AMMM-SRM7***	RDP5UM-RDP5UM-SL*** RDP5UM-RDP5UM-SR***	RDP-00AMMA-SLM7001 RDP-00BMMS-SLM7001
	Jack 90	RDP-5SPFFV-SC 8 7001 RDP-5SPFFV-SS 8 7001		RDP5UM-UPG06M-SL *** RDP5UM-UPG06M-SR***	
Metal	Jack 180	RDM-5SPFFH-SC 8 7001 RDM-5SPFFH-SS 8 7001	RDM-5 2 AMMM-SLM7*** RDM-5 2 AMMM-SRM7***	-	-
	Jack 90	RDM-5SPFFV-SC 8 7001 RDM-5SPFFV-SS 8 7001			

*Refer to P8-5 for ordering information.

Large Size 1"-20 UNEF




Receptacle and Mating Pair

3 Points Lock Bayonet

IP 67 ⁹




Receptacle | Unmated & Mated
Overmolded with Cable | Mated
Field Installable | Mated

Large Size 1"-20 UNEF > Receptacle and Mating Pair




		Receptacle	Overmolded with Cable		Field Installable
		- Female Connector (Housing) - Female Contacts 3 Points Lock Bayonet 			
		8 Choose unmated (U) or mated (M) waterproof	2 Choose shielded (5S) or unshielded (5U) *** Choose the cable length: 01-99m		5 Choose Compled (A) or Feed-Thru (S)
Cat. 5e		Female Connector (F) Female Contacts (F)	Male Connector (M) Male Contacts (M)	Male Connector (M) Male Contacts (M)	Male Connector (M) Male Contacts (M)
Plastic	Jack 180	RDP-5SPFFH-TC 8 7001 RDP-5SPFFH-TS 8 7001	RDP-5 2 AMMM-TLM7*** RDP-5 2 AMMM-TRM7***	RDP5UM-RDP5UM-TL*** RDP5UM-RDP5UM-TR***	RDP-00AMM 5 -TLM7001 RDP-00BMMS-TLM7001
	Jack 90	RDP-5SPFFV-TC 8 7001 RDP-5SPFFV-TS 8 7001		RDP5UM-UPG06M-TL*** RDP5UM-UPG06M-TR***	

*Refer to P8-5 for ordering information.


ODVA > Receptacle and Mating Pair

- Female Connector - Female Contacts 3 Points Lock Bayonet - ODVA	Receptacle	Overmolded with Cable	Field Installable
	 3 Choose the Back shell position: Front (P) or Rear (R) or Double (D) Mounting 8 Choose unmated (U) or mated (M) waterproof	 *** Choose the cable length:0.1-99m	 Compled
ODVA (ROP)	Female Connector (F) Female Contacts (F)	Male Connector (M) Male Contacts (M)	Male Connector (M) Male Contacts (M)
Jack 180°	ROP-5S 3 FFH-TC 8 7001 ROP-5S 3 FFH-TS 8 7001	ROP-5SAMMM-TLM7***	ROP-00AMMA-TLM7001

I Adaptor

- Shielded RJ45 - Front Fastened - Screw Thread - Backshell: Circular - Panel Thickness Max: 3.5mm - IP 67   Upon request			
			
	Type 1 Receptacle	Type 2 Field Installable	Type 3 Field Installable (In-line)
	RDP-00PFFH-SCU7001	RDP-00DFFA-SLM7001	RDP-00BFFA-SLM7001


SSL Connector




Range Overview

▮ PCB Mount to PCB Mount


Right Angle




Straight




Right Angle & Straight



▮ PCB Mount to Wire





▮ Wire to Wire



Specification


Identifications	SSL 1.1 DC Connector (PCB Connector & Cable)
Description	PCB to PCB PCB to Wire Wire to Wire
Current Rating / Data	3A per Pin 2, 4 & 6P
Voltage Rating	Max100 VAC / VDC
Material	Contact: Copper Alloy, Tin over Nickel Housing: LCP, UL 94V-0 Rated Hood: Nylon (PA66), UL 94V-0 Rated Lock: Nylon (PA66), UL 94V-0 Rated SR: PP, UL 94V-0 Rated. UL recognized wire & flat cable available
Temperature Range	-40°C ~ +100°C
Contact Resistance	$\leq 20\text{m}\Omega$
Insulation Resistance	$\geq 1000\text{m}\Omega$ at 250VDC
Durability	100 cycles
Breakdown Voltage	1200 V AC
More to know	Standard cable length: every 10cm

Ordering Information

1	2	3	4	5	6	7	8
Connector Series (11) SSL 1.1 None Waterproof Series							
Connector (Housing) Gender (J) Jack (P) Plug							
Number of Contacts 2,4, 6 contacts EX. (2) = 2 Contacts							
Connector Type <u>> For PCB Mount Type</u> (A) SMT Board Straight with Post (C) SMT Board Right Angle with Post (D) SMT Board Right Angle without Post <u>> For Wire Assembly</u> (L) Wire Assembly, Straight, With SR							
Wires Assembly Options <u>> For PCB Mount Type</u> (00) For PCB Mount Type <u>> For Wire Assembly</u> (2J) 2-End Jack Connector (2P) 2-End Plug Connector (JP) End 1: Jack, End 2: Plug, (JO) End 1: Jack, End 2: Open (PO) End 1: Plug, End 2: Open							
Lock Option (0) None (Without Lock) (B) W2B Lock in End 1 (W) W2W Lock in End 1 (D) With Two W2B Lock (T) With Two W2W Lock (S) W2B Lock in End 1, W2W Lock in End 2		 Wire to Board Lock (W2B Lock)		 Wire to Wire Lock (W2W Lock)			
Wire Size <u>> For PCB Mount Type</u> (00) Not Applicable for SMT Board <u>> For Wire Assembly</u> (22) 22 AWG							
Wire Assembly / Wires Type <u>> For PCB Mount Type</u> (001), (002)..... Without Wire : Different Versions <u>> For Wire Assembly</u> (□)+(■) : Wire Type + Length EX. (A01) = Wire + 10cm (□) : Wire Type (A) UL recognized wire (D) UL recognized flat cable (■) : Length From 10cm~990cm EX. (01) = 10cm							

Physical Dimension

└ PCB Mount to PCB Mount > Right Angle






	P1 Pitch	P2 TTL Pitch	D Depth	W Width	H Height
2P	2.0	-	6.5	4.0	3.0
4P	1.5	4.5	6.5	6.9	3.0
6P	1.5	7.5	6.5	9.9	3.0

Dimensions are shown in millimeters

* Design and specification are subject to change without notice.


▮ PCB Mount to PCB Mount > Straight



	P1 Pitch	P2 TTL Pitch	D Depth	W Width	H Height
2P	-	-	Jack: 3.3 Plug: 2.9	Jack: 4.3 Plug: 4.3	Jack: 6.0 Plug: 7.0
4P	3.0	-	Jack: 3.3 Plug: 2.9	Jack: 7.2 Plug: 6.9	Jack: 6.0 Plug: 7.0
6P	3.0	6.0	Jack: 3.3 Plug: 2.9	Jack: 10.2 Plug: 9.9	Jack: 6.0 Plug: 7.0

Dimensions are shown in millimeters

Wire Assembly



	L0	H	W	Cable Length (L)
2P	16.2	4.8	7.8	**Wire & flat cable length available from 10cm to 990cm in multiples of 10cm.
4P	16.2	4.8	11.2	
6P	16.2	4.8	14.2	

* Design and specification are subject to change without notice.

Find Our Standard Products


▾ PCB Mount to PCB Mount > Right Angle

			
		④ PCB Mount (Right Angle) ; With post (C) or without post (D)	
		Plug	Jack
2P		SSL11-P 2 ④ 00-000001	SSL11-J 2 ④ 00-000001
4P		SSL11-P 4 ④ 00-000001	SSL11-J 4 ④ 00-000001
6P		SSL11-P 6 ④ 00-000001	SSL11-J 6 ④ 00-000001


▾ PCB Mount to PCB Mount > Straight

			
		④ PCB Mount (Straight) ; With post (A) or without post (B)	
		Plug	Jack
2P		SSL11-P2 ④ 00-000001	SSL11-J 2 ④ 00-000001
4P		SSL11-P4 ④ 00-000001	SSL11-J 4 ④ 00-000001
6P		SSL11-P6 ④ 00-000001	SSL11-J 6 ④ 00-000001

PCB Mount to PCB Mount > Right Angle & Straight


 * Plug (Right Angle) * Plug (Straight) 4 PCB Mount (Right Angle) ; With post (C) or without post (D) PCB Mount (Straight) ; With post (A) or without post (B) * Jack (Straight) * Plug (Right Angle)		
	Plug	Jack
2P	SSL11-P 2 4 00-000001	SSL11-J 2 4 00-000001
4P	SSL11-P 4 4 00-000001	SSL11-J 4 4 00-000001
6P	SSL11-P 6 4 00-000001	SSL11-J 6 4 00-000001

PCB Mount (Plug) to Wire



PCB

4 PCB Mount (Right Angle) ; With post (C) or without post (D)





**Wire & flat cable length available from 10cm to 990cm in multiples of 10cm. EX. (01) = 10cm

	Mount Type		End 1 + End 2	Cable Type	Part Number	
2P	Right Angle Plug	SSL11-P2 4 00-000001	Jack + Jack	Flat Cable	SSL11-J2L2J-D22D**	
			Jack + Plug	Flat Cable	SSL11-P2LJP-D22D**	
			Jack + Open End	Wire	SSL11-J2LJ0-B22A**	
Flat Cable		SSL11-J2LJ0-B22D**				
4P		SSL11-P4 4 00-000001	Jack + Jack	Flat Cable	SSL11-J4L2J-D22D**	
			Jack + Plug	Flat Cable	SSL11-P4LJP-D22D**	
			Jack + Open End	Wire	SSL11-J4LJ0-B22A**	
Flat Cable				SSL11-J4LJ0-B22D**		
6P			SSL11-P6 4 00-000001	Jack + Jack	Flat Cable	SSL11-J6L2J-D22D**
				Jack + Plug	Flat Cable	SSL11-P6LJP-D22D**
		Jack + Open End		Wire	SSL11-J6LJ0-B22A**	
Flat Cable				SSL11-J6LJ0-B22D**		

* Design and specification are subject to change without notice.

▾ PCB Mount (Jack) to Wire

 PCB 4 PCB Mount (Right Angle) ; With post (C) or without post (D)			 **Wire & flat cable length available from 10cm to 990cm in multiples of 10cm. EX. (01) = 10cm		
	Mount Type	Jack	End 1 + End 2	Cable Type	Part Number
2P	Right Angle Jack	SSL11-J2 4 00-000001	Plug + Plug	Flat Cable	SSL11-P2L2P-D22D**
			Plug + Jack	Flat Cable	SSL11-P2LJP-D22D**
			Plug + Open End	Wire	SSL11-P2LP0-B22A**
Flat Cable		SSL11-P2LP0-B22D**			
4P		SSL11-J4 4 00-000001	Plug + Plug	Flat Cable	SSL11-P4L2P-D22D**
			Plug + Jack	Flat Cable	SSL11-P4LJP-D22D**
			Plug + Open End	Wire	SSL11-P4LP0-B22A**
				Flat Cable	SSL11-P4LP0-B22D**
			6P	SSL11-J6 4 00-000001	Plug + Plug
Plug + Jack	Flat Cable	SSL11-P6LJP-D22D**			
Plug + Open End	Wire	SSL11-P6LP0-B22A**			
	Flat Cable	SSL11-P6LP0-B22D**			

▾ Wire to Wire

			
		**Wire & flat cable length available from 10cm to 990cm in multiples of 10cm. EX. (01) = 10cm	**Wire & flat cable length available from 10cm to 990cm in multiples of 10cm. EX. (01) = 10cm
	Cable Type	Plug	Jack
2P	Wire	SSL11-P2LP0-W22A**	SSL11-J2LJ0-022A**
	Flat Cable	SSL11-P2LP0-W22D**	SSL11-J2LJ0-022D**
4P	Wire	SSL11-P4LP0-W22A**	SSL11-J4LJ0-022A**
	Flat Cable	SSL11-P4LP0-W22D**	SSL11-J4LJ0-022D**
6P	Wire	SSL11-P6LP0-W22A**	SSL11-J6LJ0-022A**
	Flat Cable	SSL11-P6LP0-W22D**	SSL11-J6LJ0-022D**

Blank lined paper for writing.




Scan to visit our website

LED Indicator

Range Overview

⌵ Receptacle



Specification

Identifications	M8 LED (Plastic or Metal)
Description	Receptacle with LED light
LED Size	Metal LED: $\varnothing$ 3mm, $\varnothing$ 5mm Plastic LED: $\varnothing$ 3mm
Material	Connector Body: Metal: Copper Alloy, Nickel Plated Plastic: PC+ABS
Waterproof Rating	IP67
Temperature Range	Metal: -20°C ~ +105°C Plastic: -20°C ~ +85°C
Operating Voltage	4V
Light Color	Red, Blue, Green, White, Yellow, Red / Green
More to know	Absolute Maximum Ratings at Ta=25°C - Power Dissipation: 80~120mW Max - Peak Forward Current: 100mA Max - Continuous Forward Current: 20~35mA Max - Lead Soldering Temperature: 260°C for 5 Seconds


Ordering Information

	1	2	3	4	5	6	7	8	9	10
Specification (L08) M8										
Number of LED (01) 1 LED										
Light Color Style (R) Red (B) Blue (G) Green (W) White (A) Red/Green (Y) Yellow										
LED Size (A) Ø3mm (B) Ø5mm										
Electrical Type (A) DC 4V										
Assemble Style > For Receptacle (S) Solder Type (P) 180° PCB Type										
Housing Material (M) Metal (P) Plastic										
Backshell > For Receptacle (R) Circular / Rear Fastened										
Waterproof Rating (7) IP 67										
More Information > For Receptacle (001) Without Cable										

Physical Dimension

Receptacle

Panel Cut-Out




Size \ Dimension	L (A)	OD	L (B)	W
L08 - ϕ 3.0 (Plastic)	7.1	8.2	21.0	10.5
L08 - ϕ 3.0 (Metal)	7.1	8.2	20.0	10.5
L08 - ϕ 5.0 (Metal)	7.1	8.2	20.0	10.5

* Maximum Panel Thickness: 6.5mm


Dimensions are shown in millimeters

Connector Dimension




Find Our Standard Products

Receptacle

• Plastic connectors	Receptacle  3 Choose the color of LED: - Mono-color: Red (R) / Blue (B) / Green (G) / White (W) / Yellow (Y) The size of plastic LED: ϕ3mm	
	LED M8 Plastic	L08-01 3 AAS-PR700 1

Receptacle

• Metal connectors	Receptacle  3 Choose the color of LED: - Mono-color: Red (R) / Blue (B) / Green (G) / White (W) / Yellow (Y) - Multi-color: Red & Green (A) 4 Choose the size of LED (ϕ3mm (A) or ϕ5mm (B))	
	LED M8 Metal	L08-01 3 4 AS-MR700 1

Blank lined paper for writing.



Scan to visit our website


HDMI Connector




Range Overview

Receptacle to Overmolded with Cable

Rectangle Type




Receptacle




Overmolded with Cable

Circular Type




Receptacle



Overmolded with Cable

Accessories

Waterproof Cap
See page 21-17Waterproof Cap
See page 21-17

Specification

Identifications	HDMI connector
Description	Receptacle Overmolded with Cable
Current Rating / Data	0.5A
Material	Contacts: Phospor Bronze Connector Body (Housing): PBT Shell: Brass
Waterproof Rating	IP67 (Mated Waterproof)
Temperature Range	Receptacle: -20°C~80°C Overmolded with Cable: -20°C~80°C
Contact Resistance	≤ 20mΩ
Insulation Resistance	≥ 100mΩ at DC500V
More to know	Standard Cable Length: 01~05 M

[illegible]


Innovation in Waterproof Solution 11-2

Physical Dimension


Receptacle

Panel Cut-Out


Rectangle Type






Connector Dimension



Connector Dimension




Circular Type



* Unit: mm

Overmolded with Cable




Rectangle Type




Circular Type

* Unit: mm

Contact Configuration



PCB Layoyt




19Pin HDMI PCB Layout
 Scale 2/1

* Unit: mm

【Note】 This only show contact configuration of Jack as your reference.

Product Features

Receptacle





Mating Style 7



Connector Body(Style) 3



Backshell 8




Mating Style 7




Connector Body(Style) 3



Backshell 8



Overmolded with Cable




Mating Style 7



Connector Body(Style) 3



Backshell 8




Mating Style 7



Connector Body(Style) 3



Backshell 8



Find Our Standard Products


Receptacle and Mating Pair

	Receptacle	Overmolded with Cable	Field Installable
- Female Connector (Housing) - Female Contacts - Latch - Screw Thread	Rectangle Type Circular Type	Rectangle Type Circular Type	
Connector Style	Female Connector (F) Female Contacts (F)	Male Connector (M) Male Contacts (M)	Male Connector (M) Male Contacts (M)
Rectangle Type	HJ-19PFFR-QS7001	HP-19AMMM-QL7A ^{XX} *	-
Circular Type	HJ-19PMFP-SC7001	HP-19AFMM-SL7A ^{XX} *	-

* XX: Choose UL20276 cable and select the cable length from 01~05m


【Note】 Design and specification are subject to change without notice.

Sata Connector



Range Overview

Receptacle to Overmolded with Cable



Specification

Identifications	SATA II connector
Description	PCB to Wire
Current Rating	1.5 A
Material	Contacts: Copper Alloy, Gold Plated Connector Body (Housing): LCP / PBT
Waterproof Rating	IP67
Temperature Range	Receptacle: -20°C~80°C Overmolded with Cable: -20°C~80°C
Contact Resistance	≤ 30mΩ
Insulation Resistance	≥ 1000mΩ at DC500V
Durability	500 cycles
More to know	SATA III (upon request)

Ordering Information


1	2	3	4	5	6	7
Specification						
(SA7) SATA 7 Pin Type						
Type						
(2) SATA II * SATA III upon request						
Connector (Housing) Gender						
> For Receptacle / PCB > For Overmolded with Cable						
(P) Female (Socket) (A) Male (Plug)						
Connector Body						
> For Receptacle / PCB > For Overmolded with Cable						
(S) SMD (L) Cable Latch (Double)						
(D) DIP (P) Cable Latch (Single)						
Board Lock / Cable Type						
> For Receptacle / PCB > For Overmolded with Cable						
(TA) Flat Board Lock 2.6mm (DU) 2 End Cable Type						
(TB) Flat Board Lock 1.6mm (SN) 1 End Cable Type						
(FA) Harpoon Board Lock 2.6mm						
(FB) Harpoon Board Lock 3.2mm						
Waterproof Rating						
(7) IP 67						
More Information						
> For Receptacle > For Overmolded with Cable						
(001) Without Cable (A01) 100MM						
(A05) 500MM						

* Design and specification are subject to change without notice.

Physical Dimension


Receptacle

DIP Layout





Board Lock Type

Harpoon




Flate



A	B	C	D	E	F
14.0	21.0	20.0	11.5	16.9	2.6
					3.2
14.0	21.0	20.0	11.5	16.9	2.6
					1.6


Receptacle

SMT Layout





Board Lock Type

Harpoon




Flate




A	B	C	D	E	F
14.0	21.0	20.0	11.5	16.9	2.6
					3.2
14.0	21.0	20.0	11.5	16.9	2.6
					1.6

Overmolded with Cable


Cable Latch (Double)



Cable Latch (Single)





Contact Configuration



Find Our Standard Products

Receptacle and Mating Pair

SATA II	Receptacle 	Overmolded with Cable 
	Jack	Plug
	SA7-2PDFA-7001 SA7-2PDFB-7001 SA7-2PDTA-7001 SA7-2PDTB-7001 SA7-2PSFA-7001 SA7-2PSFB-7001 SA7-2PSTA-7001 SA7-2PSTB-7001	SA7-2ALDU-7AXX SA7-2APDU-7AXX *Upon request


* Design and specification are subject to change without notice.

Fiber Optic Connector




Range Overview

⌵ Receptacle to Field Installable




Receptacle



Field Installable

⌵ Accessories



Waterproof Cap
See page 21-18

Specification

Identifications	LC Type SC Type
Description	Receptacle Field Installable
Material	Receptacle: Mousing: PPO Screw Nut: Nylon Field Installable: Clamp Ring: PPO Lock Nut: PPO Sealing Nut: Nylon
Waterproof Rating	IP67
Temperature Range	Receptacle: -40 °C ~ 105 °C Field Installable: -40 °C ~ 105 °C


Ordering Information

1	2	3	4	5	6	7	8	9
Specification								
(FB) Fiber Optic								
Mode								
(SM) Single - Mode		(00) None						
Connector Body (Style)								
> For Receptacle		> For Field installable						
(R) Rear Fastened		(B) Without Strain Relief						
Connector (Housing) Gender								
(LM) LC Type / Plug		(SM) SC Type / Plug						
(LF) LC Type / Jack		(SF) SC Type / Jack						
Assemble Style								
> For Receptacle		> For Field Installable						
(J) Put Through		(A) Field Installable						
Mating Style								
(T) 3 Points Lock Bayonet								
Backshell								
> For Receptacle		> For Field Installable						
(C) Circular		(L) Straight						
Waterproof Rating								
(7) IP 67								
More Information								
(001), (002).....								
Without Cable : Different Versions								



Physical Dimension

Receptacle

Panel Cut-Out




Connector Dimension



Unit: mm


Field Installable



Unit: mm

Product Features

Receptacle



Mating Style 6




3 Points Lock Bayonet
(T)

Backshell 7




Circle (C)

Connector Body(Style) 3



Rear Fastened (R)

Field Installable




Mating Style 6




3 Points Lock
Bayonet (T)

Backshell 7



Straight
(L)



Connector Body(Style) 3



Without Strain Relief
(B)

Find Our Standard Products


⌵ Receptacle and Mating Pair

• Female Connector (Housing) • 3 Point Lock Bayonet	Receptacle 	Field Installable 
Type	Female Connector (F)	Male Connector (M)
LC Type (L)	FB-00RLFJ-TC7001	FB-00BLMA-TL7001 FB-00BLMA-TL7002
SC Type (S)	FB-SMRSFJ-TC7001	FB-00BSMA-TL7001

FB-00BLMA-TL7001 (Cable OD: 2.5~2.8)
 FB-00BLMA-TL7002 (Cable OD: 4.5~6.8)
 FB-00BSMA-TL7001 (Cable OD: 2.4 max)

NMEA 2000 Connector

Range Overview




About NMEA 2000

Amphenol LTW Technology expands its coverage targeting the marine industry that features the NMEA 2000 standard.

The NMEA 2000 standard contains the requirements of a serial data communications network to inter-connect marine electronic equipment on

vessels. It is multi-master and self-configuring, and there is no central network controller. Equipment designed to this standard will have the ability to

share data, including commands and status with other compatible equipment over a status with other compatible equipment over a single channel.



Specification

Identifications	Micro(AWG: 22 AWG, 24 AWG) Mini(AWG: 18 AWG, 15 AWG)
Description	Micro: Bulkhead (With Wire / Double-ended / Right Angle) Cable (Drop Line / Double-ended Cordset / Field Installable / T-Cable) Network Terminator (Single-ended / In-line) Adaptor (T-Adaptor / Elbow) Multi-port Waterproof Cap Mini: Bulkhead (Double-ended) Cable (Drop Line / Double-ended Cordset / Field Installable / T-Cable) Network Terminator (Single-ended) Adaptor (T-Adaptor / Elbow) Power Tap Tee Waterproof Cap Mini to Micro: Adaptor (T-Adaptor / I-Adaptor)
Current Rating / Data	4A, 8A
Material	Contacts: Copper Alloy, Gold Plated Contacts Holder: PA
Waterproof Rating	IP67~68
Temperature Range	Receptacle: -40℃~85℃ Overmolded with Cable: -20℃~80℃ Field Installable: Nylon+GF: -40℃~105℃ PU: -20℃~85℃ * Higer working temperature upon request.

Contact Configuration

	Micro-C	Mini-C
	4A	8A
	FF or MM	FF or MM
4Pin		
5Pin		



Number of Contacts:

Ex.2 contacts **(02)**

Connector (Housing) Gender:

Male**(M)** or Female**(F)**

Contact Gender:

Male**(M)** or Female**(F)**

More to Choose:

- Solder **(S)**
- Solder Cup



- Screw In **(B)**



Cabling Information

Micro


NMEA Approved

(A): (24#* 1P+AL) + (22#* 1P+AL) + Drain + Mylar + Braid

Conforming

(A): (24#* 1P+AL) + (22#* 1P+AL) + Drain + AL + Braid

(B): (22#* 1P+AL) + (18#* 1P+AL) + Drain + AL + Braid




Mini

NMEA Approved

(C): (18#* 1P+AL) + (15#* 1P+AL) + Drain + Braid

Conforming


(C): (18#* 1P+AL) + (16#* 1P+AL) + Drain + AL+Braid




* Design and specification are subject to change without notice.

Find Our Standard Products


Micro > Bulkhead (Double-ended)

• 5 Contacts • Screw Thread • Unmated IP68		 18 (Hexagon) For Panel thickness Max 8.5mm	
Type	Connector	Connector 1 (Female Connector / Female Contacts)	
		Connector 2 (Male Connector / Male Contacts)	
None- Certified NMEA 2000 (4A, 60V)		MC-000505-0FM-BS001	
Certified NMEA 2000 (4A, 60V)		UMC-000505-0FM-BS001	


Micro > Bulkhead

• 5 Contacts • Screw Thread • For device side • Unmated IP68		 * Front Fastened Male: 25.9 Female: 22.9 Male: 20.5 Female: 20.0 18 (Hexagon) OD: 15.4 13.6 * Rear Fastened Male: 24.5 Female: 28.0 Male: 22.0 Female: 22.6 18 (Hexagon) OD: 15.4 13.6	
Type	Connector	Connector (Male Connector / Male Contacts)	Connector (Female Connector / Female Contacts)
		MC-05PMMS-SF8001 MC-05PMMS-SH8001	MC-05PFFS-SF8001 MC-05PFFS-SH8001


Micro > Cable > Double-ended Cordset

• 5 Contacts • Screw Thread • Mated IP68		 *Available in 1, 2, 5, 10 M *Cable 22+24+B PVC		
Type	Connector	Connector 1 (Male Connector Male Contacts)	Connector 1 (Female Connector Female Contacts)	Connector 1 (Male Connector Male Contacts)
	Connector 2 (Male Connector Male Contacts)	Connector 2 (Female Connector Female Contacts)	Connector 2 (Female Connector Female Contacts)	Connector 2 (Female Connector Female Contacts)
None- Certified NMEA 2000 (4A, 60V)		MC-000505-0MM-CS*	MC-000505-0FF-CS*	MC-000505-0MF-CS*
None- Certified NMEA 2000 (Plastic / (4A, 60V)		PC-000505-0MM-CS*	PC-000505-0FF-CS*	PC-000505-0MF-CS*
Certified NMEA 2000 (4A, 60V)		-	-	UMC-000505-0MF-CSA*


Micro > Cable > Field Installable

• 5 Contacts • Screw Thread • Screw-in Contacts • Mated IP68		 * Conforming to NMEA * NMEA approved	
Type	Connector	Connector (Male Connector / Male Contacts)	Connector (Female Connector / Female Contacts)
None- Certified NMEA 2000 (4A, 60V)		12-05BMMB-SL7001 12-05BMMB-SR7001 (Ø4.5 ~ Ø6.0mm; 18AWG Max.)	12-05BFFB-SL7001 12-05BFFB-SR7001 (Ø4.5 ~ Ø6.0mm; 18AWG Max.)
None- Certified NMEA 2000 (Plastic / 4A, 60V)		12P-05BMMB-SL7001 12P-05BMMB-SR7001 (Ø4.5 ~ Ø6.0mm; 18AWG Max.)	12P-05BFFB-SL7001 12P-05BFFB-SR7001 (Ø4.5 ~ Ø6.0mm; 18AWG Max.)
Certified NMEA 2000 (4A, 60V)		UMC-05BMMB-SL7001 (Ø4.5 ~ Ø7.5mm; 18AWG Max.)	UMC-05BFFB-SL7001 (Ø4.5 ~ Ø7.5mm; 18AWG Max.)

Micro > Cable > T-Cable

• 5 Contacts • Screw Thread • For Power Tap Connection • Mated IP68		 * Cable 22+18+8 PVC * Available in 1, 2, 5, 10 M.		
Type	Connector	Connector 1 (Male Connector Male Contacts)	Connector 1 (Female Connector Female Contacts)	Connector 1 (Female Connector Female Contacts)
		Connector 2 (Male Connector Male Contacts)	Connector 2 (Female Connector Female Contacts)	Connector 2 (Male Connector Male Contacts)
None- Certified NMEA 2000 (4A, 60V)		MC-050500-MM0-TSB*	MC-050500-FF0-TSB*	MC-050500-FM0-TSB*
None- Certified NMEA 2000 (Plastic) (4A, 60V)		PC-050500-MM0-TSB*	PC-050500-FF0-TSB*	PC-050500-FM0-TSB*
Certified NMEA 2000 (4A, 60V)		-	-	UMC-050500-FM0-TSA*

Micro > Network terminator > Terminator

• 5 Contacts • Screw Thread • With 120Ω Resistor • Mated IP68			
Type	Connector	Connector (Male Connector / Male Contacts)	Connector (Female Connector / Female Contacts)
None- Certified NMEA 2000 (4A, 60V)		MC-05BMMT-SL8001	MC-05BFFT-SL8001
None- Certified NMEA 2000 (Plastic / 4A, 60V)		MCP-05BMMT-SL8001	MCP-05BFFT-SL8001
Certified NMEA 2000 (4A, 60V)		UMC-05BMMT-SL8001	UMC-05BFFT-SL8001

* Design and specification are subject to change without notice.


Micro > Network Terminator > Terminator (In-Line)

• 5 Contacts • Screw Thread • With 120Ω Resistor • Mated IP68		50.0 1 2 49.2 1 2	
Type	Connector	Connector 1 (Male Connector / Male Contacts)	Connector 1 (Female Connector / Female Contacts)
		Connector 2 (Female Connector / Female Contacts)	Connector 2 (Female Connector / Female Contacts)
None- Certified NMEA 2000 (4A, 60V)		MC-000505-0MF-IS001	* Please contact our sales team for more information

Micro > Adaptor > T-Adaptor


• 5 Contacts • Screw Thread • Mated IP68		55.9 1 2 43.8 3 ALTW	
Type	Connector	Connector 1 (Female Connector / Female Contacts)	
		Connector 2 (Male Connector / Male Contacts)	
		Connector 3 (Female Connector / Female Contacts)	
None- Certified NMEA 2000 (4A, 60V)		UMC-050505-FMF-TS001	

Micro > Adaptor > Elbow

• 5 Contacts • Screw Thread • Mated IP68	
Type Connector	Connector 1 (Female Connector / Female Contacts)
	Connector 2 (Male Connector / Male Contacts)
None- Certified NMEA 2000 (4A, 60V)	MC-000505-0FM-ES001


Micro > Adaptor > T-Adaptor

- 5 Contacts
- Screw Thread
- Mated IP68





Type	Connector	Connector 1 (Female Connector / Female Contacts)	Connector 1 (Female Connector / Female Contacts)
		Connector 2 (Female Connector / Female Contacts)	Connector 2 (Female Connector / Female Contacts)
		Connector 3 (Female Connector / Female Contacts)	Connector 3 (Female Connector / Female Contacts)
		Connector 4 (Male Connector / Male Contacts)	Connector 4 (Female Connector / Female Contacts)
		-	Connector 5 (Female Connector / Female Contacts)
		-	Connector 6 (Male Connector / Male Contacts)
None- Certified NMEA 2000 (4A, 60V)		S-555500-FFFM00-S001	S-555555-FFFFFM-S001
Certified NMEA 2000 (4A, 60V)		E-555500-FFFM00-S001	E-555555-FFFFFM-S001

Micro > Multi-port > Box


• 5 Contacts • Screw Thread • Mated IP68	 * Cable 22+18+B PVC ** Cable 22+24+B PVC
Connector Type	Connector 1 (Female Connector / Female Contacts)
	Connector 2 (Female Connector / Female Contacts)
	Connector 3 (Female Connector / Female Contacts)
	Connector 4 (Female Connector / Female Contacts)
None- Certified NMEA 2000 (4A, 30V)	S-555500-FFFF00-SB*
Certified NMEA 2000 (4A, 30V)	E-555500-FFFF00-SA**

* Design and specification are subject to change without notice.


Micro > Cap > Waterproof Cap

• Screw Thread • Mated IP68		 Male (12.0) Female (10.5) Male (14.0) Female (16.5) * Plastic	 Male (15.5) Female (12.0) 14.5 * Metal
		4 Choose gender of mating pair : Male(M) / Female(F) 7 Choose plastic(1) or metal(2) items	
Size	Mating Pair	Mating Style	Part Number
Micro	Receptacle	Screw Thread	CAP-WBDMSPB2
	Receptacle and Overmolded with Cable	Screw Thread	CAP-WBD 4 SMA 7


Mini > Bulkhead (Double-ended)

• 5 Contacts • Screw Thread • Unmated IP68		 Mini 48.5 28.4 ALTW OD: 22.2 For Panel thickness Max 9.0mm
Type	Connector	Connector 1 (Female Connector / Female Contacts)
		Connector 2 (Male Connector / Male Contacts)
None- Certified NMEA 2000 (8A, 600V)		MN-000505-0FM-BS001
Certified NMEA 2000 (8A, 600V)		UMN-000505-0FM-BS001

Mini > Cable > Drop Line



• 5 Contacts • Screw Thread • Mated IP68		
 Male (57.8) Female (58.0) 25.5 10 Cabling Information NMEA Approved (C): (18#*1P+AL) + (15#*1P+AL) + Drain + Braid Conforming (C): (18#*1P+AL) + (16#*1P+AL) + Drain + AL+Braid **Available in 1, 2, 5, 10 M.		
Connector Type	Connector (Male Connector / Male Contacts)	Connector (Female Connector / Female Contacts)
None- Certified NMEA 2000 (8A, 30V)	MN-05AMMM-SL8 10 **	MN-05AFFM-SL8 10 **
NMEA Approved (8A, 600V)	UMN-05AMMM-SL8 10 **	-

Mini > Cable > Double-ended Cordset


• 5 Contacts • Screw Thread • Mated IP68		
 *Available in 1, 2, 5, 10 M		
Connector Type	Connector 1 (Male Connector / Male Contacts)	
	Connector 2 (Female Connector / Female Contacts)	
None- Certified NMEA 2000 (8A, 30V)	MN-000505-0MF-CSC*	
Certified NMEA 2000 (8A, 600V)	UMN-000505-0MF-CSC*	

* Design and specification are subject to change without notice.


Mini > Cable > Field Installable

• 5 Contacts • Screw Thread • Screw-in Contacts • Mated IP68   * Conforming to NMEA * NMEA approved		
Type	Connector (Male Connector / Male Contacts)	Connector (Female Connector / Female Contacts)
	None- Certified NMEA 2000 (8A, 600V)	MN-05BMMB-SL7001 (Ø8 ~Ø11mm; 15AWG Max.)
	Certified NMEA 2000 (8A, 600V)	UMN-05BMMB-SL7001 (Ø8 ~Ø12.2mm; 15AWG Max.)


Mini > Cable > T-Cable

• 5 Contacts • Screw Thread • Mated IP68  * Cable: Refer to P14-4 * Available in 1, 2, 5, 10 M.		
Type	Connector (Female Connector / Female Contacts)	Connector 1
	Connector 2 (Male Connector / Male Contacts)	Connector 2
None- Certified NMEA 2000 (8A, 30V)	MN-050500-FM0-TSC *	

▾ Mini > Network Terminator > Terminator


• 5 Contacts • Screw Thread • With 120Ω Resistor • Mated IP68			 * Conforming to NMEA * Signal function LED * NMEA approved	
Connector Type			Connector 1 (Male Connector / Male Contacts)	Connector 1 (Female Connector / Female Contacts)
None- Certified NMEA 2000 (8A, 250V)			MNL-05BMMT-SL8001	MNL-05BFFT-SL8001
Certified NMEA 2000 (8A, 250V)			UMN-05AMMT-SL8001	UMN-05AFFT-SL8001

▾ Mini > Adaptor > T-Adaptor



• 5 Contacts • Screw Thread • Mated IP68				
Connector Type			Connector 1 (Female Connector / Female Contacts)	
			Connector 2 (Male Connector / Male Contacts)	
			Connector 3 (Female Connector / Female Contacts)	
None- Certified NMEA 2000 (8A, 300V)			MN-050505-FMF-TS001	
Certified NMEA 2000 (8A, 300V)			UMN-050505-FMF-TS001	

* Design and specification are subject to change without notice.


Mini > Adaptor > Elbow

• 5 Contacts • Screw Thread • Mated IP68			
Type	Connector	Connector 1 (Female Connector / Female Contacts)	
		Connector 2 (Male Connector / Male Contacts)	
None- Certified NMEA 2000 (8A, 300V)		MN-000505-0FM-ES001	

Mini > Power Tap Tee


• 5 Contacts • Screw Thread • With replaceable fuse • Mated IP68 		* Recommended Mating Pair for 3 MN-04AFFM-SL8D** Male (57.8) Female (58.0)  Cabling Information Conforming (C): (18#*1P+AL) + (16#*1P+AL) + Drain + AL+Braid ** Available in 1, 2, 5, 10 M
Type Connector	Connector 1 (Male Connector / Male Contacts)	
	Connector 2 (Female Connector / Female Contacts)	
	Connector 3 (Female Connector / Female Contacts)	
None- Certified NMEA 2000 (8A, 250V)		N-455000-MFF000-S001
Certified NMEA 2000 (8A, 250V)		U-455000-MFF000-S001

Mini > Cap > Waterproof Cap


• 5 Contacts • Screw Thread • Mated IP68		Male (25.2) Female (25.4) 	
		4 Choose gender of mating pair : Male(M) / Female(F)	
Size	Mating Pair	Mating Style	P/N
Mini	Receptacle and Overmolded with Cable	Screw Thread	CAP-WMN 4 SMA1

* Design and specification are subject to change without notice.

Mini to Micro > Adaptor > T-Adaptor

• 5 Contacts • Screw Thread • Mated IP68			
Type	Connector	Connector 1 (Female Connector / Female Contacts)	
		Connector 2 (Male Connector / Male Contacts)	
		Connector 3 (Female Connector / Female Contacts)	
None- Certified NMEA 2000 (4A, 60V)		NC-050505-FMF-TS001	
Certified NMEA 2000 (4A, 60V)		UNC-050505-FMF-TS001	

Mini to Micro > I-Adaptor

• 5 Contacts • Screw Thread • Mated IP68			
Type	Connector	Connector 1 (Male Connector / Male Contacts)	
		Connector 2 (Female Connector / Female Contacts)	
None- Certified NMEA 2000 (4A, 60V)		NC-000505-0MF-IS001	


Blank lined paper for writing.




Scan to visit our website

PV AC Connectors / T-Junction Connector


Range Overview



> VTC | PT (Trunk Cable with Receptacle) & SMC



> VTC | PA (Trunk Cable Overmolded with Cable) & SMC



VTC | SMC

(Overmolded with Cable)

- Certificate:
ETL: UL6703A
TUV: 2 pfg 1915
- Refer to page 15-9



Tool

- Refer to page 15-10



Tool

- Refer to page 15-13

VTC | T-Junction PT

(Trunk Cable with Receptacle)

- Certificate:
ETL: UL6703A
TUV: 2 pfg 1915
- Refer to page 15-8

BMC

- Certificate:
ETL: UL6703A
TUV: 2 pfg 1915
- Refer to page 15-13

End Cap

- Certificate:
ETL: UL6703A
TUV: 2 pfg 1915
- Refer to page 15-10

> SMC | In Line




> SMC | Receptacle to Overmolded with Cable



> SMC | Receptacle to Receptacle



> BMC | In Line



【Note】 Design and specification are subject to change without notice.

Specification

Identifications	VTC I T Junction: PT & PA (For Trunk Cable) VTC I SMC (For Drop or Receptacle) BMC
Description	Cabling System for Micro-inverter
Current Rating / Data	VTC I T Junction: Trunk Range: UL15A~30A / TUV17-25A / 3~4Pin VTC I SMC: 5A / 3~4Pin BMC: UL17A / TUV19A / 3~4Pin
Material	Contacts: Copper Alloy Connector Body: m-PPE
Waterproof Rating	IP67
Temperature Range	Ambient: -40°C ~ +85°C Upper Limited Temperature: +105°C
Contact Resistance	≤ 10mΩ
Insulation Resistance	≥ 100mΩ at DC500V
Durability	500 cycles
Breakdown Voltage	≥ DC6000V / 1 minute
Certificate	VTC I T-Junction: ETL: UL9703, TUV: 2 pfg 1915 VTC I SMC: ETL: UL6703A, TUV: 2 pfg 1915 BMC: ETL: UL6703A, TUV: 2 pfg 1915
Voltage Rating	AC 300V
More to know	Salt Spray Corrosion test: 48H Cable for Trunk: 14~10AWG or 2.5mm ² ~4mm ² Cable for Drop: 18AWG or 0.75mm ² Trunk Cable Pitch: Upon request

Ordering Information | VTC | T-Junction

1

2

3

4

5

6

Specification

>PT Type
(PT) Trunk Cable with Receptacle

>PA Type
(PA) Trunk Cable Overmolded with Cable

Number of Contacts
(3) 3 Contacts (4) 4 Contacts

Cable Style
>UL : TCER Cable Style >TUV : EU Cable Style
(10) 10# (4A) 4mm² 1940 Cable
(12) 12# (4B) 4mm² HAR Cable
(14) 14# (2A) 2.5mm² 1940Cable

Cable pitch
(105) 1.05m pitch
(170) 1.7m pitch
(205) 2.05m pitch * More options available



> For Trunk Cable with Receptacle (PT)
(00) SMC connector
* More options available (Upon request)

> For Trunk Cable Overmolded with Cable (PA)
(□)+(■): (Drop Cable Length) + (Cable type with or without connector)
EX. (07B) = 0.7m length + 18# without Connector

(□) : Drop Cable Length
(07) 0.7m length
(10) 1.0m length
(15) 1.5m length * More options available

(■) : Cable type with or without connector

>UL : TCER Cable Style >TUV : EU Cable Style
(A) 18# With SMC connector (E) 0.75mm² HAR Cable With SMC
(B) 18# Without Connector (Open ended) (F) 0.75mm² HAR Cable Without SMC
(C) 16# Without Connector (Open ended) (G) 1.0mm² HAR CableWithout SMC
(D) 14# Without Connector (Open ended) (H) 0.75mm² 1940 Cable With SMC
(I) 0.75mm² 1940 Cable Without SMC
(J) 1.0mm² 1940 Cable Without SMC



Number of T-Junctions
008, 011, 017, ..., 999 EX. (008) = 8 T-Junctions

【Note】 Design and specification are subject to change without notice.

Ordering Information | VTC | SMC

1 — 2 3 4 5 6 — 7 8 9 10

Specification

(SPS) Solar Power AC (Small size)

Number of Contacts

(03) 3 Contacts (04) 4 Contacts

Connector Body (Style)

> Receptacle > Overmolded with Cable
(R) ALTW Rear Fastened (A) With Strain Relief

Connector Housing Gender

(M) Male (Plug) (F) Female (Socket)

Contact Gender

(M) Male (F) Female

Assemble Style

> Receptacle > Overmolded with Cable
(C) Crimp Type (With Wire) (M) Overmolded with Cable

Mating Style

(L) 2 Points Lock (Push & Pull)
(With Unlocking Tool)

Backshell

> Receptacle > Overmolded with Cable
(C) Circular (L) Straight

Waterproof Rating

(7) IP 67

More Information

> For Receptacle

001, 002, 003.....

001 is US Spec, 002 is EU Spec

> For Overmolded with Cable

(□)+(■) : Cable Type + Cable Length

EX. (T01) = US Cable For TCER 18# Cable + 1M

(□) : Cable Type

(T) US Cable For TCER 18# Cable

(D) EU Cable For HAR 0.75mm² Cable

(E) EU Cable For 1940 0.75mm² Cable


(■) : Cable Length

From 1M to 99M


EX. (01) = 1M

Physical Dimension

└ VTC | PT




└ VTC | PA



Unit: mm


└ SMC | Receptacle

Panel Cut-Out




Connector Dimension

(A) Male



(B) Female




* Maximum Panel Thickness: 4.0mm


Unit: mm

└ SMC | Overmolded with Cable

(A) Male



(B) Female



Unit: mm

【Note】 Design and specification are subject to change without notice.

Contact Configuration

└ VTC I T-Junction

	VTC (Output)			
	3Pin		4Pin	
	US	EU	US	EU
10#	●		●	
12#	●		●	
14#	●		●	
4.0mm		●		
2.5mm		●		

└ VTC I SMC

	SPS (Input)	
	5A	
	MM or FF	MF or FM
3 Contacts		
		R C
4 Contacts		
		R C

R: receptacle

C: overmolded with cable

● 5A

Number of Contacts :

2

Ex.3 contacts (03)

Connector (Housing) Gender:

4

Male(M) or Female(F)

Contact Gender:


5

Male(M) or Female(F)

More to Choose:

6

● Crimped (C)



Find Our Standard Products

⌵ VTC (PT) and SMC (Overmolded with Cable)

SMC : Overmolded with cable

	Cable type 10	AMP (Code)	Contacts 2	Female Connector (F) Male Contacts (M)
US (UL TC-ER cable)	TCER 18# cable (T)	5A(SPS)	03,04	SPS- 2 AFMM-LL7T*
EU (TUV 2pfg1940 cable)	HAR 0.75 mm ² cable (D)		03	SPS-03AFMM-LL7 10 *
	1940 0.75 mm ² cable (E)			

(PT) Trunk Cable with Receptacle

	Wire Size 3	Contacts 2	T-Junction Pitch 4	Number of T-Junction 6	P/N
US (UL TCER cable)	10# (30A) (10) 12# (20A) (12) 14# (15A) (14)	03,04	1.05M (105) 1.7M (170) 2.05M (205)	001 . 075	PT- 2 3 4 -00- 6
EU (TUV 2pfg1940 cable)	4mm ² (4A/4B) (25A) 2.5mm ² (2A) (17A)	03			PT-3- 3 4 -00- 6

*Refer to page 15-5 for ordering

⌵ VTC (PA) and SMC (Receptacle)

SMC : Receptacle


	AMP (Code)	Contacts 2	Female Connector (F) Male Contacts (M)
US (UL TC-ER Cable)	5A (SPS)	03,04	SPS- 2 RFMC-LC7001
EU (TUV 2pfg1940 Cable)		03	SPS- 2 RFMC-LC7002

(PA) Trunk Cable Overmolded With Cable

	Wire Size 3	Contacts 2	T-Junction Pitch 4	Number of T-Junction 6	Drop Cable Length + Cable type 5	P/N
US (UL TCER cable)	10# (30A) (10) 12# (20A) (12) 14# (15A) (14)	03,04	1.05M (105) 1.7M (170) 2.05M (205)	001 . 075	0.7M (07) 1.0M (10) 1.5M (15)	18#with SMC Conn. 18#without Conn. 16#without Conn. 14#without Conn. PA- 2 3 4 5 6
EU (TUV 2pfg1940 Cable)	4mm ² (4A/4B) (25A) 2.5mm ² (2A) (17A)	03				0.75mm ² with SMC Conn. 0.75mm ² without Cor 1.0mm ² without Cor PA-3 3 4 5 6

【Note】 Design and specification are subject to change without notice.

$\searrow$ SMC > In-line

• Male Connector (Housing) • Female Contacts • Safety Lock (Unlock tool needed)  Unlock tool ULT-SSMC-01			Overmolded with Cable $\longrightarrow$  	Overmolded with Cable  
	Contacts 2	Cable type 10	Male Connector (M) Female Contacts (F)	Female Connector (F) Male Contacts (M)
5A(SPS)	03,04	(T) TCEK 18# Cable (US)	SPS- 2 AMFM-LL7TXX*	SPS- 2 AFMM-LL7TXX*
	03	(D) HAR 0.75mm ² Cable (EU)	SPS-03AMFM-LL7 10 XX*	SPS-03AFMM-LL7 10 XX*
		(E) 1940 0.75mm ² Cable (EU)		



*XX: Choose the cable length from 01~99m

$\searrow$ SMC > Receptacle and Mating Pair

• Male Connector (Housing) • Female Contacts • Safety Lock (Unlock tool needed)  Unlock tool ULT-SSMC-01			Receptacle $\longrightarrow$  	Overmolded with Cable  
AMP (Code)	Contacts 2	Cable type 10	Male Connector (M) Female Contacts (F)	Female Connector (F) Male Contacts (M)
5A(SPS)	03,04	(T) TCER 18# Wire (US)	SPS- 2 RMFC-LC7001	SPS- 2 AFMM-LL7TXX*
	03	(D) HAR 0.75mm ² Wire (EU)	SPS-03RMFC-LC7002	SPS-03AFMM-LL7 10 XX*
		(E) 940 0.75mm ² Wire (EU)		



*XX: Choose the cable length from 01~99m

SMC > Receptacle and Mating Pair


- Female Connector (Housing) - Male Contacts - Safety Lock (Unlock tool needed)  Unlock tool ULT-SSMC-01			Receptacle  	Overmolded with Cable  
AMP (Code)	Contacts 2	Cable type 10	Female Connector (F) Male Contacts (M)	Male Connector (M) Female Contacts (F)
5A(SPS)	03,04	(T) TCER 18# Wire (US)	SPS- 2 RFMC-LC7001	SPS- 2 AMFM-LL7TXX*
	03	(D) HAR 0.75mm ² Wire (EU)	SPS-03RFMC-LC7002	SPS-03AMFM-LL7 10 XX*
		(E) 1940 0.75mm ² Wire (EU)		

*XX: Choose the cable length from 01~99m


Accessories > Waterproof Cap

 Mating Pair (Gender): Male Connector  Mating Pair (Gender): Female Connector				
Size	Mating Pair	Mating Pair (Gender)	Mating Style	Part Number
SMC	Receptacle and Overmolded with Cable	Male Connector	2 point lock bayonet	CAP-WSMMFLA 1
	Receptacle and Overmolded with Cable	Female Connector	2 point lock bayonet	CAP-WSMMLA 1

Accessories > End-Cap

	
Cable OD.	Part Number
16~12mm / 0.62~0.47 inch	CAP-WTCASMA 1
12~10mm / 0.47~0.39 inch	CAP-WTCASMA 2
10~08mm 039~0.31 inch	CAP-WTCASMA 3

Accessories > Tool

	
Size	Part Number
SMC	ULT-SSMC-01

【Note】 Design and specification are subject to change without notice.

Ordering Information | BMC

1 — 2 3 4 5 6 — 7 8 9 10

Specification

(SPB) Solar Power For Big MC
 (17A: UL US Market ; 19A: TUV EU Market ; 20A: Upon request)

Number of Contacts

(3) 3 Contacts **(4)** 4 Contacts

Connector Body (Style)

> Overmolded with Cable

(A) With Strain Relief

Connector Housing Gender

(M) Male (Plug) **(F)** Female (Socket)

Contact Gender

(M) Male **(F)** Female

Assemble Style

> Overmolded with Cable

(M) Overmolded with Cable

Mating Style

(L) 2 Points Lock (Push & Pull)
 (With Unlocking Tool)

Backshell

> Overmolded with Cable

(L) Straight

Waterproof Rating

(7) IP 67

More Information

> For Overmolded with Cable

☐ + ☒ : Cable Type + Cable Length

EX. (C01) = EU Cable For HAR 4mm² Cable + 1M

☐ : Cable Type

☒ : Cable Length


(R) UL Cable For TCER 12# Cable From 1M to 99M

(C) EU Cable For HAR 4mm² Cable EX. (01) = 1M

(L) EU Cable For 1940 4mm² Cable

Physical Dimension

└ BMC | Overmolded with Cable



Connector Gender	L		W		H	
	(B)	(A)	(B)	(A)	(B)	(A)
17A (SPB)	94.95	98.5	58.0	58.0	25.0	25.0
19A (SPB)	94.95	98.5	58.0	58.0	25.0	25.0

【Note】 17A: Comply to UL standard for USA
19A: Comply to TUV standard for Europe
20A: Upon request

Unit: mm

Contact Configuration

└ BMC

	SPB (Output)			
	17A		19A	
	MM or FF	MM or FF	MM or FF	MM or FF
3 Contacts				
	C			C
4 Contacts				
	C			


【Note】 17A: Comply to UL standard for USA
19A: Comply to TUV standard for Europe
20A: Upon request

Number of Contacts : 2
Ex.3 contacts (03)

Connector (Housing) Gender: 4
Male(M) or Female(F)
• For BMC & SMC

Contact Gender: 5
Male(M) or Female(F)
• For BMC & SMC



More to Choose: 6
• Crimped (C)



【Note】 Design and specification are subject to change without notice.



Find Our Standard Products

➤ BMC > Receptacle and Mating Pair


• Male Connector (Housing) • Female Contacts • Safety Lock (Unlock tool needed)  Unlock tool ULT-SBMC01			Receptacle  Overmolded with Cable   	
AMP (Code)	Contacts 2	Cable type 10	Male Connector (M) Female Contacts (F)	Female Connector (F) Male Contacts (M)
17A(SPB)	03,04	R-TCER 12# cable (US)	SPB- 2 AMFM-LL7R XX *	SPB- 2 AFMM-LL7R XX *
19A(SPB)	03	C-HAR 4.0 mm ² cable (EU)	SPB-03AMFM-LL7 10 XX *	SPB-03AFMM-LL7 10 XX *
		L-1940 4.0 mm ² cable (EU)		

*XX: Choose the cable length from 01~99m

➤ Accessories > Waterproof Cap

 Mating Pair (Gender): Male Connector  Mating Pair (Gender): Female Connector				
Size	Mating Pair	Mating Pair (Gender)	Mating Style	Part Number
BMC	Receptacle and Overmolded with Cable	Male Connector	2 point lock bayonet	CAP-WBMCFLD1
	Receptacle and Overmolded with Cable	Female Connector	2 point lock bayonet	CAP-WBMCMLD1

➤ Accessories > Tool

	
Size	Part Number
BMC	ULT-SBMC01

【Note】 Design and specification are subject to change without notice.

Blank lined paper for writing.




Scan to visit our website

Cable Joiner Connector



Range Overview

└ Field Installable



Specification

Identifications (Cable OD)	6~10 mm, 8~10mm, 10~12mm, 12~16mm
Material	M20: Nylon M32: PPE
Waterproof Rating	IP67
Temperature Range	Field Installable: PPE: -40°C~105°C Nylon: -40°C~105°C


Ordering Information

1	2	3	4	5	6	7
Specification						
(CX) Cable Joiner						
No. of Conductor						
(00) None		(04) 4 Conductors				
Connector Body (Style)						
(B) For Cable without Strain Relief						
AWG (Terminal)						
(B) 14~16AWG		(C) 10~12AWG				
(0) No Terminal						
Size						
(M20) M20						
(M32) M32						
Waterproof Rating						
(7) IP 67						
Jacket OD						
(001) 12mm~16mm						
(002) 10mm~12mm						
(003) 8mm~16mm						

Physical Dimension

Cable Joiner

Connector Dimension



Size \ Dimension	L	W	Cable OD	AWG (Terminal)
M20	56.0	25.4	6~10	-
M32	130.2	50.0	12~16	-
	130.2	50.0	10~12	-
	130.2	50.0	8~10	-
	130.2	50.0	8~10	14~16
	130.2	50.0	12~16	10~12
	130.2	50.0	10~12	10~12


Unit: 00

【Note】 Design and specification are subject to change without notice.


Find Our Standard Products

Cable Joiner

M20



M32



- UV Resistant
- Unlock with tool
- Butt splice terminals optional
- ETL: UL6703A
- TUV: 2 pfg 1915

Size	AWG (Terminal)	Part Number
M20	Without Terminal (0)	CX-00B0M20-700 1
M32	14~16 (B)	CX-04BBM32-700 1
	10~12 (C)	CX-04BCM32-700XX*
	Without Terminal (0)	CX-00B0M32-700XX**


* M32 with terminal 10~12 AWG - Choose Cable OD: 10mm ~ 12mm / 12mm ~ 16mm
** M32 without terminal - Choose Cable OD: 8mm ~ 10mm / 10mm ~ 12mm / 12mm ~ 16mm

Accessories > Unlock Tool

Customized - Upon Request

M32- Size	ULT-JOIN01
-----------	------------

Blank lined paper for writing.





Cable Gland




Range Overview

└ Plastic Cable Gland



└ Metal Cable Gland



Specification


Identifications	1"-20 UNF Metal, M8, M12, M16, M20, M25, M32, M40 PG7, PG9, PG11, PG13, PG16, PG29
Material	Connector Body (Plastic): Nylon 66, UL Recognized UV Resistant Connector Body (Metal): Zinc Alloy, Nickel plated (1"-20 Only)
Waterproof Rating	IP67~68
Temperature Range	Receptacle: -20°C ~ +105°C
More to know	Without Strain Relief / With Strain Relief Mating Style: Screw Thread

Ordering Information


	1	2	3
Specification			
(CSG) Cable Gland			
Screw Thread Type			
(20E) 1"-20 UNF Metal	(07G) PG7		
(08M) M8	(09G) PG9		
(12M) M12	(11G) PG11		
(16M) M16	(13G) PG13.5		
(20M) M20	(16G) PG16		
(25M) M25	(29G) PG29		
(32M) M32			
(40M) M40			
More information			
(001), (002), (003)...			

Physical Dimension

Without Strain Relief




With Strain Relief




Size	Dimension (Without Strain Relief)		Dimension (With Strain Relief)		Maximum Panel Thickness
	Short	Long	Short	Long	
PG7	-	30.0mm	-	60.0mm	3.0mm
PG9	-	45.0mm	-	78mm	7.5mm
PG11	-	48.3mm	-	79.1mm	6.0mm
PG13	-	49.6mm	-	86.6mm	6.2mm
PG16	45.0mm	49.6mm	81.6mm	86.6mm	4.5mm (Short) 6.0mm (Long)
PG29	-	52.5mm	-	-	6.0mm
M8	22.0 mm	-	-	-	-
M12	30.0 mm	42.2mm	-	60.0mm	3.0mm
M16	40.0mm	45.0mm	75.3mm	78.0mm	3.0mm (Short) 7.5mm (Long)
M20	36.7mm	43.7mm	79.6 mm	86.6mm	6.2mm
M25	45.0mm	52.1mm	89.0 mm	96.0mm	6.2mm
M32	47.5 mm	52.5mm	-	-	6.0mm
M40	-	60.0mm	-	-	9.0mm
1"-20 UNF Metal	35.0mm		-	-	5.0mm

Find Our Standard Products


Plastic Cable Gland




With Strain Relief / Without Screw Nut



With Strain Relief / With Screw Nut




Without Strain Relief / Without Screw Nut




Without Strain Relief / With Screw Nut

PG Thread	Thread Style	Cable OD	Part Number	Cable Information ³
	PG7	4.5~6.5	CSG-07G00 ³	001-Without strain relief ,Black 002-Without strain relief ,Gray 003-With strain relief ,Black 004-With strain relief ,Gray 005-Without strain relief ,Gray For Knock Hole
	PG9	6.0~10.0	CSG-09G00 ³	001-Without strain relief ,Black 002-Without strain relief ,Gray 003-With strain relief ,Black 004-With strain relief ,Gray 005-Without strain relief ,Gray For Knock Hole
	PG11	6.0~10.0	CSG-11G00 ³	001-Without strain relief ,Black 002-Without strain relief ,Gray 003-With strain relief ,Black 004-With strain relief ,Gray
	PG13	10.0~14.0	CSG-13G00 ³	001-Without strain relief ,Black 002-Without strain relief ,Gray 003-With strain relief ,Black 004-With strain relief ,Gray
	PG16	10.0~14.0	CSG-16G00 ³	001-Without strain relief ,Black (Long Body) 002-Without strain relief ,Gray (Long Body) 003-With strain relief ,Black (Long Body) 004-With strain relief ,Gray (Long Body) 006-Without strain relief ,Gray (Short Body),without Screw Nut 007-Without strain relief ,Black (Short Body),without Screw Nut 008-With strain relief ,Black (Short Body),without Screw Nut 009-With strain relief ,Gray (Short Body)
		5.5~7.6	CSG-16G005	Without strain relief, without screw nut Black (Short Body) For RJ Cable Use
		Max 6.5	CSG-16G010	Without strain relief ,Black (Long Body) For RJ Cable Use
	PG29	16~22	CSG-29G00 ³	001-Without strain relief ,Black 002-Without strain relief ,Gray
		18~25	CSG-29G00 ³	003-Without strain relief ,Black 004-Without strain relief ,Gray


* Design and specification are subject to change without notice.




With Strain Relief / Without Screw Nut



With Strain Relief / With Screw Nut




Without Strain Relief / Without Screw Nut



Without Strain Relief / With Screw Nut

	Thread Style	Cable OD	Part Number	Cable Information 3
	M8	2.5~3.0	CSG-08M00 3	001-Without strain relief,Black 002-Without strain relief ,Gray
Metric Thread	M12	4.5~6.5	CSG-12M00 3	001-Without strain relief,Black 002-Without strain relief ,Gray 003-With strain relief ,Black 004-With strain relief ,Gray 005-Without strain relief ,Black (Short Body),V0 F1 006-Without strain relief ,Black (Long Body),V0 F1
	M16	6.0~10.0	CSG-16M00 3	001-Without strain relief ,Black (Long Body) 002-Without strain relief ,Black (Long Body), UV Resistant 003-Without strain relief ,Gray (Long Body) 004-Without strain relief ,Black (Short Body) 005-Without strain relief ,Gray (Short Body) 006-With strain relief ,Black (Long Body) 007-With strain relief ,Gray (Long Body) 008-With strain relief ,Black (Short Body),without Screw Nut 009-With strain relief ,Gray (Short Body),without Screw Nut
	M20	10.0~14.0	CSG-20M00 3	001-Without strain relief ,Black (Long Body) 002-Without strain relief ,Black (Short Body),without Screw Nut 003-Without strain relief ,Gray (Long Body) 004-Without strain relief ,Gray (Short Body),without Screw Nut 005-With strain relief ,Black (Long Body) 006-With strain relief ,Gray (Long Body) 007-With strain relief ,Black (Short Body),without Screw Nut 008-With strain relief ,Gray (Short Body),without Screw Nut
	M25	13.0~18.0	CSG-25M00 3	001-Without strain relief ,Gray (Long Body) 002-Without strain relief ,Black (Short Body),without Screw Nut 003-Without strain relief ,Black (Long Body) 004-Without strain relief ,Gray (Short Body),without Screw Nut 005-With strain relief ,Black (Long Body) 006-With strain relief ,Gray (Long Body) 007-With strain relief ,Black (Short Body),without Screw Nut 008-With strain relief ,Gray (Short Body),without Screw Nut
	M32	16.0~22	CSG-32M00 3	001-Without strain relief ,Black (Long Body) 002-Without strain relief ,Gray (Long Body) 003-Without strain relief ,Black (Short Body),without Screw Nut 004-Without strain relief ,Gray (Short Body),without Screw Nut
		18.0~25.0	CSG-32M00 3	005-Without strain relief ,Black (Long Body) 006-Without strain relief ,Gray (Long Body) 007-Without strain relief ,Black (Short Body),without Screw Nut 008-Without strain relief ,Gray (Short Body),without Screw Nut
	M40	20~25	CSG-40M00 3	001-Without strain relief ,Black (Long Body) 002-Without strain relief ,Gray (Long Body)
		24~32	CSG-40M00 3	003-Without strain relief ,Black (Long Body) 004-Without strain relief ,Gray (Long Body)

➤ Metal Cable Gland



	Thread Style	Cable OD	Part Number	Cable Information
	1"-20 UNF Metal	5.5~7.0	CSG-20E001	Without strain relief, Silver
		7.8~9.3	CSG-20E002	Without strain relief, Silver


* Design and specification are subject to change without notice.

Vent Connector




Range Overview

Receptacle



M12*1.25



M12*1.5

Ordering Information

1

2

3

Specification
(VENT) Vent

Type
(BD) M12 x 1.25 (BJ) M12 x 1.5

More Information
(001), (002)


Specification

Identifications	M12 Vent Connector
Material	PBT+PC (M12 x 1.25) / M-PPE (M12 x 1.5)
Waterproof Rating	IP67 (M12 x 1.25) / IP69K (M12 x 1.5)
Temperature Range	Receptacle: -20°C ~ +105°C (M12 x 1.25) -40°C ~ +105°C (M12 x 1.5)
More to know	Thermal Shock: EIA 364-32 or IEC 60512-11d UV Resistant: F1


Physical Dimension

Receptacle


M12*1.25
Panel Cut-Out




Connector Dimension



M12*1.5
Panel Section




Connector Dimension




Find Our Standard Products

Receptacle



M12*1.25


* Rear Fastened



VENT-BD001
VENT-BD002


Different air permeability: 1.VENT-BD001:Air permeability: 12sec/100cm³
2.VENT-BD002:Air permeability: 10sec/100cm³

Receptacle



M12*1.5

* Front Fastened



VENT-BJ001

Note: VENT-BJ001:Air permeability: 10sec/cm³

* Design and specification are subject to change without notice.


RBL Connector




- Haptic
- Blind Mating
- Push-to-Connector
- Easy and Fast Disconnect

Range Overview


└ In-line




└ Receptacle and Mating Pair



└ Receptacle to Field Installable



└ Accessories



Waterproof Cap
See page 20-6

Specification

Identifications	C Size (Middle Size: 13/16"-28 UNS)
Description	Receptacle Overmolded with Cable Field Installable
Current Rating / Data	5A, 10A
Material	Contacts: Copper Alloy, Tin Plated & Gold Plated (Selective) Connector Body (Housing) : m-PPE,540Z,BK
Waterproof Rating	IP67(Mate Waterproof)
Temperature Range	Receptacle: -40°C ~ +105°C Overmolded with Cable: -20°C~80°C Field Installable: -40°C~ +105°C
Contact Resistance	≤ 10mΩ
Insulation Resistance	≥ 100mΩ at DC500V
Durability	1000 cycles
Breakdown Voltage	≥ AC1000V / 1 minute
More to know	Salt Spray Corrosion Test: 4H Standard cable length: 01~99M

Ordering Information


1	2	3	4	5	6	7	8	9	10
Specification / Current Rating <u>>Middle size:13 / 16"-28 UNS</u> (SCD) 5A (SCB) 10A									
Number of Contacts 04, 06 EX. (04) = 4 Contacts									
Connector Body (Style) <u>> For Receptacle</u> (R) Rear Fastened		<u>> For Ovremolded with Cable</u> (M) With Strain Relief	<u>> For Field installable</u> (F) Without Strain Relief						
Connector (Housing) Gender (M) Male (F) Female									
Contact Gender (S) Male (P) Female		* Choose the Plating to Tin or Gold.							
Assemble Style <u>> For Receptacle</u> (S) Solder Type		<u>> For Overmolded with Cable</u> (C) Crimp Type <u>> For Field Installable</u> (C) Crimp Type							
Mating Style (R) Snap-in with									
Backshell <u>> For Receptacle</u> (C) Circular (S) Square Flange		<u>> For Overmolded with Cable</u> (L) Straight	<u>> For Field Installable</u> (L) Straight						
Waterproof Rating (7) IP 67									
More information <u>> For Receptacle with Wirehamess</u> (□)+(■) : Wire Type + Wire Length EX. (A10) = UL1015 Wire + 10 CM		<u>> For Overmolded with Cable</u> (□)+(■) : Cable Type + Cable Length (□) : Cable Type (■) : Cable Length (A) UL2464 Cable From 1M to 99M (B) UL2586 Cable EX.(01) = 1M (C) Power Cable(TC-ER)							

Physical Dimension



Receptacle

A Backshell: Circular **B** Backshell: Square Flange


Panel Cut-Out





Connector Dimension




Panel Cut-Out




Connector Dimension



Overmolded with Cable



Field Installable



Contact Configuration

	Middle Size (C)			
	5A		10A	
④ ⑤	MM or FF	MF or FM	MM or FF	MF or FM
2Pin				
3Pin				
4Pin				
			R C F	
5Pin				
6Pin				
	R C F			

R: receptacle

C: overmolded with cable

F: Field Installable

● 5A (SCD)

● 10A (SCB)

Contact Number:

Contacts (06) , (04)

Connector (Housing) Gender:

Male(M) or Female(F)

Contact Gender:

Male(M) or Female(F)

More to Choose:

● Solder (S)

● Crimp (C)






* More available: 1. The plating to gold or tin
2. Plated thickness

① — ② ③ ④ ⑤ ⑥ — ⑦ ⑧ ⑨ ⑩




* Design and specification are subject to change without notice.

Find Our Standard Products




▮ Middle Size: 13/16"-28 UNS > Receptacle and Mating Pair

- Female Connector - Snap-in with Latch		Receptacle  * Receptacle With Wireharness: A10 - 10cm; A30 - 30cm ** Choose the cable length:01-99	Overmolded with Cable  ** Select cable length from 01~99m	Field Installable 
Current Rating (Code)	Contacts	Female Connector (F)	Male Connector (M)	Male Connector (M)
5A (SCD)	06	SCD-06RFPS-RC** SCD-06RFPS-RS**	SCD-06MMSC-RL7A**	SCD-06FMSC-RL7001
10A (SCB)	04	SCB-04RFPS-RC** SCB-04RFPS-RS**	SCB-04MMSC-RL7A**	SCB-04FMSC-RL7001



▮ Middle Size: 13/16"-28 UNS > In-line

- Female Connector - Snap-in with Latch		Overmolded with Cable  ** Select cable length from 01~99m	Overmolded with Cable  ** Select cable length from 01~99m	Field Installable 
Current Rating (Code)	Contacts	Female Connector (F)	Male Connector (M)	Male Connector (M)
5A (SCD)	06	SCD-06MFPC-RL7A**	SCD-06MMSC-RL7A**	SCD-06FMSC-RL7001
10A (SCB)	04	SCB-04MFPS-RS**	SCB-04MMSC-RL7A**	SCB-04FMSC-RL7001

Middle Size: 13/16"-28 UNS >In-line

- Female Connector - Snap-in with Latch		Field Installable 	Overmolded with Cable 	Field Installable 
		** Select cable length from 01~99m		
Current Rating (Code)	Contacts	Female Connector (F)	Male Connector (M)	Male Connector (M)
5A (SCD)	06	SCD-06FFPC-RL7001	SCD-06MMSC-RL7A**	SCD-06FMSC-RL7001
10A (SCB)	04	SCB-04FFPC-RL7001	SCB-04MMSC-RL7A**	SCB-04FMSC-RL7001

Accessories > Waterproof Cap

  Mating Pair (Gender): Female Mating Pair (Gender): Male			
5 Choose Connector Gender Male (M) or Female (F)			
Size	Mating Pair	Mating Style	Part Number
13/16"-28 UNS	Receptacle	Snap In With Latch	CAP-WAC 5 RMA1
	Overmolded with Cable	Snap In With Latch	
	Receptacle and Overmolded with Cable	Snap In With Latch	


X-Lok Connector



- Haptic
- Blind Mating
- Push-to-Connector
- Easy and Fast Disconnect

Range Overview


Receptacle to Overmolded with Cable



Receptacle

Overmolded with Cable


In Line



Overmolded with Cable


Overmolded with Cable

Receptacle to Field Installable



Receptacle

Field Installable



Field Installable

Field Installable

Overmolded with Cable

Specification

Identifications	C Size (Middle Size: 13/16"-28 UNS)
Description	Receptacle Overmolded with Cable Field Installable
Current Rating / Data	20A
Material	Contacts: Copper Alloy, Tin & Gold Plated Connector Body (Housing) : Nylon+GF, UL Recognized
Waterproof Rating	IP67
Temperature Range	Receptacle: -40°C ~ +105°C Overmolded with Cable: -20°C~80°C Field Installable: -40°C~ +105°C
Contact Resistance	≤ 10mΩ
Insulation Resistance	≥ 100mΩ at DC500V
Durability	500 cycles
Breakdown Voltage	≥ AC 1600V / 1 minute
More to know	Salt Spray Corrosion Test: 12H Standard cable length: 01~99M

Ordering Information

1 2 3 4 5 6 7 8 9 10

Specification / Current Rating
(SCC) 20A

Number of Contacts
 03
 EX. **(03)** = 3 Contacts

Connector Body (Style)

> For Receptacle
(R) Rear Fastened

> For Overmolded with Cable
(M) With Strain Relief

> For Field installable
(F) Without Strain Relief

Connector (Housing) Gender

(M) Male Connector **(F)** Female Connector

Contact Gender

(S) Male
(P) Female

Assemble Style

> For Receptacle
(S) Solder Type

> For Overmolded with Cable
(S) Solder Type
 > For Field Installable
(C) Crimp Type

Mating Style

(Q) Push Lock (Sprind loaded nut)

Backshell

> For Receptacle
(C) Circular

> For Overmolded with Cable
(L) Straight
(R) Right Angle (Avaible soon)

> For Field Installable
(L) Straight

Waterproof Rating

(7) IP 67

More Information


> For Receptacle
 (001), (002).....
 Without Cable :
 Different Versions

> For Overmolded with Cable
 (□)+(■) : Cable Type + Cable Length
 EX. **(A01)** = UL2464 Cable + 1M

(□) : Cable Type (■) : Cable Length
(A) UL2464 Cable From 1M to 99M
(B) UL2586 Cable EX. **(01)** = 1M
(C) Power Cable(TC-ER)


Physical Dimension

Receptacle




* Maximum Panel Thickness: 4.2mm | Solder PIN: 12Awg ~ 14Awg

Overmolded with Cable



Field Installable



Cable OD Range : 4.0mm ~ 9.6mm
 Dimensions are shown in millimeters

Contact Configuration

	Middle Size					
	20A					
4 5	MM or FF			MF or FM		
3 Pin						
	R	C	F	R	C	F

R: Receptacle

C: Overmolded with Cable

F: Field Installable

20A (SCC)

1

Number of Contacts:

2

Ex.3 contacts (03)

Connector (Housing) Gender:

4

Male (M) or Female (F)

Contact Gender:

5

Male (S) or Female (P)

More to Choose:

6

• Solder (S)






* More available: 1. The plating to gold or tin
 2. Plated thickness




* Design and specification are subject to change without notice.

Find Our Standard Products




Receptacle and Mating Pair

• Male Connector • Push Lock (Sprind loaded nut)		Receptacle 	Overmolded with Cable 	Field Installable 
		** Selecting the cable length:01-99		
Current Rating (Code)	Contacts	Male Connector (M)	Female Connector (F)	Female Connector (F)
20A (SCC)	03	SCC- 03RMPS-QC7001	SCC- 03MFSS-QL70**	SCC- 03FFSC-QC7001

In-line

• Female Connector • Push Lock (Sprind loaded nut)		Overmolded with Cable 	Overmolded with Cable 	Field Installable 
		** Selecting the cable length:01-99		
Current Rating (Code)	Contacts	Female Connector (F)	Male Connector (M)	Male Connector (M)
20A (SCC)	03	SCC- 03MFSS-QL70**	SCC- 03MMPS-QL70**	SCC- 03FMPC-QC7001

In-line

• Female Connector • Push Lock (Sprind loaded nut)		Field Installable 	Field Installable 	Overmolded with Cable 
		** Selecting the cable length:01-99		
Current Rating (Code)	Contacts	Female Connector (F)	Male Connector (M)	Male Connector (M)
20A (SCC)	03	SCC- 03FFSC-QL7001	SCC- 03FMPC-QC7001	SCC- 03MMPS-QL70**


Accessories Index

• Cable	
T-Cable	21-1
Y-Cable	21-3
• Adaptor	
T-Adaptor	21-4
Y-Adaptor	21-6
I-Adaptor	21-7
• Cap	
Dust Cap	21-9
Waterproof Cap	21-11
Dummy	21-18
• Multi-port	
Multi-port	21-19
• Box	
Box	21-21
• Tool	
Wrench	21-22
Unlock Tool	21-22
• Joint	
Joint	21-23
• Patch Cable (Double-ended)	
Patch Cable (Double-ended).....	21-24

Accessories - Cable

➤ T-Cable > Circular > Standard Size: 5/8"-27 UNS

■ Customized – Upon Request



5 For connector 1
6 For connector 2


Choose Connector / Contacts Gender:
M: Male + Male
F: Female + Female
H: Male + Female
B: Female + Male

* Choose the cable length: 01-99 m /
PVC UL2464 Cable

Current Rating	Contacts 2	Mating Style	Connector 1 (Male Connector / Male Contacts)	Connector 1 (Female Connector / Female Contacts)	More options
			Connector 2 (Male Connector / Male Contacts)	Connector 2 (Female Connector / Female Contacts)	
10A	02,03,04	Screw Thread	BA-2200-MM0-TSA*	BA-2200-FF0-TSA*	BA-2200-560-TSA*
		2 point lock bayonet	BA-2200-MM0-TLA*	BA-2200-FF0-TLA*	BA-2200-560-TLA*
5A	02,03,04,05,06,07,08	Screw Thread	BA-2200-MM0-TSA*	BA-2200-FF0-TSA*	BA-2200-560-TSA*
		2 point lock bayonet	BA-2200-MM0-TLA*	BA-2200-FF0-TLA*	BA-2200-560-TLA*
2A	10, 12	Screw Thread	BA-2200-MM0-TSA*	BA-2200-FF0-TSA*	BA-2200-560-TSA*
		2 point lock bayonet	BA-2200-MM0-TLA*	BA-2200-FF0-TLA*	BA-2200-560-TLA*

➤ T-Cable > Circular > Other Size > Mix Size (10A+5A)

■ Customized – Upon Request




* Choose the cable length: 01-99 m /
PVC UL2464 Cable

Current Rating	Contacts	Mating Style	Connector 1 (Male Connector / Male Contacts)	Connector 1 (Female Connector / Female Contacts)	Connector 1 (Male Connector / Male Contacts)
			Connector 2 (Male Connector / Male Contacts)	Connector 2 (Female Connector / Female Contacts)	Connector 2 (Female Connector / Female Contacts)
5A	08	Screw Thread	GA-080800-MM0-TSA*	GA-080800-FF0-TSA*	GA-080800-MF0-TSA*

└ T-Cable > M Series Sensor > M12

Customized – Upon Request



Choose Connector / Contacts Gender:

6

For connector 1

7

For connector 2

A/B/D Code

M: Male + Male

F: Female + Female

I Style

K: Connector (Male) + Contact (Male+Female)

Z: Connector (Female) + Contact (Male+Female)


* Choose the cable length:01-99 m / PVC UL2464 Cable

Type		Current Rating	Contacts 2	Mating Style	Connector 1 (Male Connector / Male Contacts)	Connector 1 (Female Connector / Female Contacts)	More options
					Connector 2 (Male Connector / Male Contacts)	Connector 2 (Female Connector / Female Contacts)	
M12	A Code	4A	03,04,05	Screw Thread	SS-2200-MM0-TSA*	SS-2200-FF0-TSA*	SS-2200-670-TSA*
		2A	08		SS-080800-MM0-TSA*	SS-080800-FF0-TSA*	SS-080800-670-TSA*
	B Code	4A	04,05		SB-2200-MM0-TSA*	SB-2200-FF0-TSA*	SB-2200-670-TSA*
	D Code	4A	04,05		SD-2200-MM0-TSA*	SD-2200-FF0-TSA*	SD-2200-670-TSA*
	I Style	4A	05		SI-050500-KK0-TSA*	SI-050500-ZZ0-TSA*	SI-050500-670-TSA*
M12 (Plastic)	A Code	4A	03,04,05	Screw Thread	PS-2200-MM0-TSA*	PS-2200-FF0-TSA*	PS-2200-670-TSA*
		2A	08		PS-080800-MM0-TSA*	PS-080800-FF0-TSA*	PS-080800-670-TSA*
	B Code	4A	04,05		PB-2200-MM0-TSA*	PB-2200-FF0-TSA*	PB-2200-670-TSA*
	D Code	4A	04,05		PD-2200-MM0-TSA*	PD-2200-FF0-TSA*	PD-2200-670-TSA*
	I Style	4A	05		PI-050500-KK0-TSA*	PI-050500-ZZ0-TSA*	PI-050500-670-TSA*

* Design and specification are subject to change without notice.

Y-Cable > M Series Sensor > M12

Customized – Upon Request




* Choose the cable length:01-99 m / PU VW-1Cable


Type		Current Rating	Contacts ②	Mating Style	Connector (Male Connector / Male Contacts)	Connector (Female Connector / Female Contacts)
M12	A Code	4A	03,04,05	Screw Thread	SS- ② 0000-M00-YSB*	SS- ② 0000-F00-YSB*
		2A	08	Screw Thread	SS-080000-M00-YSB*	SS-080000-F00-YSB*
	B Code	4A	04,05	Screw Thread	SB- ② 0000-M00-YSB*	SB- ② 0000-F00-YSB*
	D Code	4A	04,05	Screw Thread	SD- ② 0000-M00-YSB*	SD- ② 0000-F00-YSB*
	I Style	4A	05	Screw Thread	SI-050000-K00-YSB*	SI-050000-Z00-YSB*

Accessories - Adaptor

└ T-Adaptor > Circular > Mini Size: 7/16"-28 UNS

Customized - Upon Request  5 For connector 1 6 For connector 2 7 For connector 3 Choose Connector / Contacts Gender: M: Male + Male F: Female + Female					
Current Rating	Contacts 2	Mating Style	Connector 1 (Male Connector / Male Contacts)	Connector 1 (Female Connector / Female Contacts)	More options
			Connector 2 (Male Connector / Male Contacts)	Connector 2 (Female Connector / Female Contacts)	
			Connector 3 (Male Connector / Male Contacts)	Connector 3 (Female Connector / Female Contacts)	
5A	02,03	Screw Thread	AA- 2 2 2 -MMM-TS001	AA- 2 2 2 -FFF-TS001	AA- 2 2 2 - 5 6 7 -TS001
		2 point lock bayonet	AA- 2 2 2 -MMM-TL001	AA- 2 2 2 -FFF-TL001	AA- 2 2 2 - 5 6 7 -TL001
2A	04,05,06	Screw Thread	AA- 2 2 2 -MMM-TS001	AA- 2 2 2 -FFF-TS001	AA- 2 2 2 - 5 6 7 -TS001
		2 point lock bayonet	AA- 2 2 2 -MMM-TL001	AA- 2 2 2 -FFF-TL001	AA- 2 2 2 - 5 6 7 -TL001

└ T-Adaptor > Circular > Standard Size: 5/8"-27 UNS

Customized - Upon Request  5 For connector 1 6 For connector 2 7 For connector 3 Choose Connector / Contacts Gender: M: Male + Male F: Female + Female H: Male + Female B: Female + Male					
Current Rating	Contacts 2	Mating Style	Connector 1 (Male Connector / Male Contacts)	Connector 1 (Female Connector / Female Contacts)	More options
			Connector 2 (Male Connector / Male Contacts)	Connector 2 (Female Connector / Female Contacts)	
			Connector 3 (Male Connector / Male Contacts)	Connector 3 (Female Connector / Female Contacts)	
5A	02,03,04,05,06,07,08	Screw Thread	BA- 2 2 2 -MMM-TS001	BA- 2 2 2 -FFF-TS001	BA- 2 2 2 - 5 6 7 -TS001
		2 point lock bayonet	BA- 2 2 2 -MMM-TL001	BA- 2 2 2 -FFF-TL001	BA- 2 2 2 - 5 6 7 -TL001
2A	10,12	Screw Thread	BA- 2 2 2 -MMM-TS001	BA- 2 2 2 -FFF-TS001	BA- 2 2 2 - 5 6 7 -TS001
		2 point lock bayonet	BA- 2 2 2 -MMM-TL001	BA- 2 2 2 -FFF-TL001	BA- 2 2 2 - 5 6 7 -TL001

* Design and specification are subject to change without notice.

└ T-Adaptor > M Series Sensor > M12

Customized – Upon Request

Choose Connector / Contacts Gender:

5

For connector 1

6

For connector 2

7

For connector 3

A/B/D Code

M: Male + Male

F: Female + Female

I Style

K: Connector (Male) + Contact (Male+Female)

Z: Connector (Female) + Contact (Male+Female)

Type		Current Rating	Contacts 2	Mating Style	Connector 1 (Male Connector / Male Contacts)	Connector 1 (Female Connector / Female Contacts)	More options
					Connector 2 (Male Connector / Male Contacts)	Connector 2 (Female Connector / Female Contacts)	
					Connector 3 (Male Connector / Male Contacts)	Connector 3 (Female Connector / Female Contacts)	
M 12	A Code	4A	03,04,05	Screw Thread	SS- 2 2 2 -MMM-TS001	SS- 2 2 2 -FFF-TS001	SS- 2 2 2 -5 6 7-TS001
		2A	08	Screw Thread	SS-080808-MMM-TS001	SS-080808-FFF-TS001	SS-080808-5 6 7-TS001
	B Code	4A	04,05	Screw Thread	SB- 2 2 2 -MMM-TS001	SB- 2 2 2 -FFF-TS001	SB- 2 2 2 -5 6 7-TS001
	D Code	4A	04,05	Screw Thread	SD- 2 2 2 -MMM-TS001	SD- 2 2 2 -FFF-TS001	SD- 2 2 2 -5 6 7-TS001
	I Style	4A	05	Screw Thread	SI-050505-KKK-TS001	SI-050505-ZZZ-TS001	SI-050505-5 6 7-TS001
M 12 (Plastic)	A Code	4A	03,04,05	Screw Thread	PS- 2 2 2 -MMM-TS001	PS- 2 2 2 -FFF-TS001	PS- 2 2 2 -5 6 7-TS001
		2A	08	Screw Thread	PS-080808-MMM-TS001	PS-080808-FFF-TS001	PS-080808-5 6 7-TS001
	B Code	4A	04,05	Screw Thread	PB- 2 2 2 -MMM-TS001	PB- 2 2 2 -FFF-TS001	PB- 2 2 2 -5 6 7-TS001
	D Code	4A	04,05	Screw Thread	PD- 2 2 2 -MMM-TS001	PD- 2 2 2 -FFF-TS001	PD- 2 2 2 -5 6 7-TS001
	I Style	4A	05	Screw Thread	PI-050505-KKK-TS001	PI-050505-ZZZ-TS001	PI-050505-5 6 7-TS001

Y-Adaptor > M Series Sensor > M12

Customized – Upon Request

Choose Connector / Contacts Gender:

5 For connector 1

6 For connector 2

7 For connector 3

A/B/D Code

M: Male + Male

F: Female + Female

I Style


K: Connector (Male) + Contact (Male+Female)

Z: Connector (Female) + Contact (Male+Female)


Type		Current Rating	Contacts 2	Mating Style	Connector 1 (Male Connector / Male Contacts)	Connector 1 (Female Connector / Female Contacts)	More options
					Connector 2 (Male Connector / Male Contacts)	Connector 2 (Female Connector / Female Contacts)	
					Connector 3 (Male Connector / Male Contacts)	Connector 3 (Female Connector / Female Contacts)	
M 12	A Code	4A	03,04,05	Screw Thread	SS-222-MMM-YS001	SS-222-FFF-YS001	SS-222-567-YS001
		2A	08	Screw Thread	SS-080808-MMM-YS001	SS-080808-FFF-YS001	SS-080808-567-YS001
	B Code	4A	04,05	Screw Thread	SB-222-MMM-YS001	SB-222-FFF-YS001	SB-222-567-YS001
	D Code	4A	04,05	Screw Thread	SD-222-MMM-YS001	SD-222-FFF-YS001	SD-222-567-YS001
	I Style	4A	05	Screw Thread	SI-050505-KKK-YS001	SI-050505-ZZZ-YS001	SI-050505-567-YS001
M 12 (Plastic)	A Code	4A	03,04,05	Screw Thread	PS-222-MMM-YS001	PS-222-FFF-YS001	PS-222-567-YS001
		2A	08	Screw Thread	PS-080808-MMM-YS001	PS-080808-FFF-YS001	PS-080808-567-YS001
	B Code	4A	04,05	Screw Thread	PB-222-MMM-YS001	PB-222-FFF-YS001	PB-222-567-YS001
	D Code	4A	04,05	Screw Thread	PD-222-MMM-YS001	PD-222-FFF-YS001	PD-222-567-YS001
	I Style	4A	05	Screw Thread	PI-050505-KKK-YS001	PI-050505-ZZZ-YS001	PI-050505-567-YS001

* Design and specification are subject to change without notice.


➤ I-Adaptor > Circular > Mini Size: 7/16"-28 UNS

Customized – Upon Request  6 For connector 1 7 For connector 2 Choose Connector / Contacts Gender: M: Male + Male F: Female + Female					
Current Rating	Contacts 3	Mating Style	Connector 1 (Male Connector / Male Contacts)	Connector 1 (Female Connector / Female Contacts)	More options
			Connector 2 (Male Connector / Male Contacts)	Connector 2 (Female Connector / Female Contacts)	
5A	02,03	Screw Thread	AA-00 3 3 -OMM-IS001	AA-00 3 3 -OFF-IS001	AA-00 3 3 -0 6 7 -IS001
		2 point lock bayonet	AA-00 3 3 -OMM-IL001	AA-00 3 3 -OFF-IL001	AA-00 3 3 -0 6 7 -IL001
2A	04,05,06	Screw Thread	AA-00 3 3 -OMM-IS001	AA-00 3 3 -OFF-IS001	AA-00 3 3 -0 6 7 -IS001
		2 point lock bayonet	AA-00 3 3 -OMM-IL001	AA-00 3 3 -OFF-IL001	AA-00 3 3 -0 6 7 -IL001

➤ I-Adaptor > Circular > Standard Size: 5/8"-27 UNS

Customized – Upon Request  6 For connector 1 7 For connector 2 Choose Connector / Contacts Gender: M: Male + Male F: Female + Female H: Male + Female B: Female + Male					
Current Rating	Contacts 3	Mating Style	Connector 1 (Male Connector / Male Contacts)	Connector 1 (Female Connector / Female Contacts)	More options
			Connector 2 (Male Connector / Male Contacts)	Connector 2 (Female Connector / Female Contacts)	
5A	02,03,04, 05,06,07, 08	Screw Thread	BA-00 3 3 -OMM-IS001	BA-00 3 3 -OFF-IS001	BA-00 3 3 -0 6 7 -IS001
		2 point lock bayonet	BA-00 3 3 -OMM-IL001	BA-00 3 3 -OFF-IL001	BA-00 3 3 -0 6 7 -IL001
2A	10, 12	Screw Thread	BA-00 3 3 -OMM-IS001	BA-00 3 3 -OFF-IS001	BA-00 3 3 -0 6 7 -IS001
		2 point lock bayonet	BA-00 3 3 -OMM-IL001	BA-00 3 3 -OFF-IL001	BA-00 3 3 -0 6 7 -IL001

└ I-Adaptor > Circular > Other Size > Mix Size (10A+5A)

Customized – Upon Request					
					
Current Rating	Contacts	Mating Style	Connector 1 (Male Connector / Male Contacts)	Connector 1 (Female Connector / Female Contacts)	Connector 1 (Female Connector / Female Contacts)
			Connector 2 (Male Connector / Male Contacts)	Connector 2 (Female Connector / Female Contacts)	Connector 1 (Male Connector / Male Contacts)
5A	08	3 point lock bayonet	GA-000808-0MM-IT001	GA-000808-OFF-IT001	GA-000808-0FM-IT001

└ I-Adaptor > M Series Sensor > M12

Customized – Upon Request

Choose Connector / Contacts Gender:

6

 For connector 1

7

 For connector 2

A/B/D Code

M: Male + Male

F: Female + Female

I Style

K: Connector (Male) + Contact (Male+Female)

Z: Connector (Female) + Contact (Male+Female)



* M12

Type		Current Rating	Contacts 3	Mating Style	Connector 1 (Male Connector / Male Contacts) Connector 2 (Male Connector / Male Contacts)	Connector 1 (Female Connector / Female Contacts) Connector 2 (Female Connector / Female Contacts)	More options
M12	A Code	4A	03,04,05	Screw Thread	SS-0033-0MM-IS001	SS-0033-OFF-IS001	SS-0033-067-IS001
		2A	08	Screw Thread	SS-000808-0MM-IS001	SS-000808-OFF-IS001	SS-000808-067-IS001
	B Code	4A	04,05	Screw Thread	SB-0033-0MM-IS001	SB-0033-OFF-IS001	SB-0033-067-IS001
	D Code	4A	04,05	Screw Thread	SD-0033-0MM-IS001	SD-0033-OFF-IS001	SD-0033-067-IS001
	I Style	4A	05	Screw Thread	SI-000505-0KK-IS001	SI-000505-0ZZ-IS001	SI-000505-0KZ-IS001 SI-000505-0ZK-IS001
M12 (Plastic)	A Code	4A	03,04,05	Screw Thread	PS-0033-0MM-IS001	PS-0033-OFF-IS001	PS-0033-067-IS001
		2A	08	Screw Thread	PS-000808-0MM-IS001	PS-000808-OFF-IS001	PS-000808-067-IS001
	B Code	4A	04,05	Screw Thread	PB-0033-0MM-IS001	PB-0033-OFF-IS001	PB-0033-067-IS001
	D Code	4A	04,05	Screw Thread	PD-0033-0MM-IS001	PD-0033-OFF-IS001	PD-0033-067-IS001
	I Style	4A	05	Screw Thread	PI-000505-0KK-IS001	PI-000505-0ZZ-IS001	PI-000505-0KZ-IS001 PI-000505-0ZK-IS001

* Design and specification are subject to change without notice.



Accessories - Cap

Dust Cap >Circular

Customized – Upon Request  * Mini Size Standard Size Middle Size Large Size * With Rubber Lead * Mix Size * With Rubber Lead			
Size	Mating Pair	Mating Pair (Gender)	P/N
Mini Size 7/16"-28 UNS	Receptacle	Male	CAP-DAAMDPC 1
Standard Size 5/8"-27 UNS	Receptacle	Male	CAP-DABMDPC 1 CAP-DABMDPC 2 CAP-DABMDPC 3
		Female	-
	Overmolded with Cable	Male	CAP-DABMDCC 1 CAP-DABMDCC 2
		Female	CAP-DABFDCC 1
Middle Size 13/16"-28 UNS	Receptacle	Male	CAP-DACMDPC 1 CAP-DACMDPC 2
	Overmolded with Cable	Female	CAP-DACFDCC 1
Large Size 1"-20 UNEF	Receptacle	Male	CAP-DADMDPC 1
Mix Size 12-5A	Receptacle	Male	CAP-DPLMDPC 1

▾ Dust Cap > D-SUB > Standard & High Density

■ Customized – Upon Request




*Choose rubber lead: Vertical type (1) / Horizontal type (2)

Type		Mating Pairs	Mating Pair (Gender)	P/N
Standard D-SUB	High Density D-SUB			
Standard (9 pins)	High Density (15 Pins)	Receptacle (With horizontal rubber lead)	Male	CAP-DD1MDPC2
		Receptacle and Overmolded with Cable (With horizontal / Vertical rubber lead)		CAP-DD1MDMA1
		Receptacle	Female	CAP-DD1FDPC1* CAP-DD1FDPC2*
		Receptacle and Overmolded with Cable		CAP-DD1FDMA1
Standard (15 pins)	High Density (26 Pins)	Receptacle and Overmolded with Cable	Male	CAP-DD2MDMA1
		Receptacle and Overmolded with Cable	Female	CAP-DD2FDMA1
Standard (25 pins)	High Density (44 Pins)	Receptacle and Overmolded with Cable	Male	CAP-DD3MDMA1
		Receptacle (With horizontal rubber lead)	Female	CAP-DD3FDPC1
		Receptacle and Overmolded with Cable		CAP-DD3FDMA1


* Design and specification are subject to change without notice.

Waterproof Cap > Circular


Customized – Upon Request



* Mini Size



* Standard Size



* Middle Size


Choose Connector / Contacts Gender:

- 6 More to choose: None(A) / With Chain(B) / With Rubber Lead(C) / With Fish Line(D)
- 7 * Mini Size: Choose 2 contacts(1) / 3 contacts(3) / 4~6 contacts(2) for male mating pair
- * Standard Size: Choose 12 contacts (2) for male mating pair
- * Middle Size: Choose plastic(1) or metal(2) items


Size	Mating Pair	Mating Style	Mating Pair (Gender)	P/N
Mini Size 7/16"-28 UNS	Receptacle	Screw Thread	Male	CAP-WAAMSP 6 1
		2 point lock bayonet	Male	CAP-WAAMLMP 6 7
			Female	CAP-WAAFLP 6 7
	Overmolded with Cable	Screw Thread	Male	CAP-WAAMSMA1
		2 point lock bayonet	Male	CAP-WAAMLMA 7
			Female	CAP-WAAFLMA 7
	Receptacle and Overmolded with Cable	Screw Thread	Male	CAP-WAAMSMA1
		2 point lock bayonet	Male	CAP-WAAMLMA 7
			Female	CAP-WAAFLMA 7
Standard Size 5/8"-27 UNS	Receptacle	Screw Thread	Male	CAP-WABMSP 6 1
		2 point lock bayonet	Female	CAP-WABFSP 6 1
			Male	CAP-WABMLP 6 7
	Overmolded with Cable	Screw Thread	Female	CAP-WABFLP 6 7
			Male	CAP-WABMSMA1
		2 point lock bayonet	Female	CAP-WABFSMA1
			Male	CAP-WABMLMA 7
	Receptacle and Overmolded with Cable	Screw Thread	Female	CAP-WABFLMA 7
			Male	CAP-WABMSMA1
		2 point lock bayonet	Female	CAP-WABFSMA1
			Male	CAP-WABMLMA 7
Middle Size 13/16"-28 UNS	Receptacle	Screw Thread	Male	CAP-WACMSP 6 7
		2 point lock bayonet	Male	CAP-WACMLP 6 1
			Female	CAP-WACFLP 6 1
	Overmolded with Cable	Screw Thread	Male	CAP-WACMSMA 7
		2 point lock bayonet	Male	CAP-WACMLMA1
			Female	CAP-WACFLMA1
	Receptacle and Overmolded with Cable	Screw Thread	Male	CAP-WACMSMA 7
		2 point lock bayonet	Male	CAP-WACMLMA1
			Female	CAP-WACFLMA1

Waterproof Cap > Circular

Customized – Upon Request



* Large Size



* Mix Size

6 More to choose: None(A) / With Chain(B) / With Rubber Lead(C) / With Fish Line(D)


7 * Large Size: Choose 18 contacts(2) for female mating pair

Size	Mating Pair	Mating Style	Mating Pair (Gender)	P/N
Large Size 1"-20 UNEF	Receptacle	Screw Thread	Male	CAP-WADMSP 6 1
		2 point lock bayonet	Male	CAP-WADMLP 6 7
			Female	CAP-WADFLP 6 7
	Overmolded with Cable	Screw Thread	-	-
		2 point lock bayonet	-	-
	Receptacle and Overmolded with Cable	Screw Thread	Male	CAP-WADMSMA1
		2 point lock bayonet	Male	CAP-WADMLMA 7
			Female	CAP-WADFLMA 7
Mix Size (Between Standard & Middle Size)	Receptacle	3 Points Lock	Male	CAP-WEBMLP 6 1
			Female	CAP-WEBFLP 6 1
	Receptacle and Overmolded with Cable	3 Points Lock	Male	CAP-WEBMLMA1
			Female	CAP-WEBFLMA1


* Design and specification are subject to change without notice.

Waterproof Cap > Power


Customized – Upon Request



* 8A (PWE) | 12A (PWF) | 16A (PWG)



* 20A (PWC) | 20A+2A (PWCU)




* 25A (PWH) | 30A (PWJ)

6 More to choose: None(A) / With Chain(B) /
With Rubber Lead(C) / With Fish Line(D)

Current Rating	Mating Pair	Mating Style	Mating Pair (Gender)	P/N
8A(PWE)	Receptacle	Screw Thread	Male	CAP-WTAMSP 6 1
	Receptacle and Overmolded with Cable		Female	CAP-WTAFSP 6 1
			Male	CAP-WTAMSMA1
			Female	CAP-WTAFSMA1
12A(PWF)	Receptacle	Screw Thread	Male	CAP-WTAMSP 6 1
	Receptacle and Overmolded with Cable		Female	CAP-WTAFSP 6 1
			Male	CAP-WTAMSMA1
			Female	CAP-WTAFSMA1
16A(PWG)	Receptacle	Screw Thread	Male	CAP-WTAMSP 6 1
	Receptacle and Overmolded with Cable		Female	CAP-WTAFSP 6 1
			Male	CAP-WTAMSMA1
			Female	CAP-WTAFSMA1
20A(PWC)	Receptacle	2 point lock bayonet	Male	CAP-WACMLP 6 1
	Receptacle and Overmolded with Cable			CAP-WACMLMA1
	Receptacle and Overmolded with Cable		Female	CAP-WACFLMA2
20A+2A(PWCU)	Receptacle	2 point lock bayonet	Male	CAP-WACMLP 6 1
	Receptacle and Overmolded with Cable			CAP-WACMLMA1
	Receptacle and Overmolded with Cable		Female	CAP-WACFLMA2
25A(PWH)	Receptacle and Overmolded with Cable	3 point lock bayonet	Female	CAP-WPWFTMD1
30A(PWJ)	Receptacle and Overmolded with Cable	3 point lock bayonet	Male	CAP-WPWMTMD1

Waterproof Cap > Sensor > M8

Customized – Upon Request




For Female

Size	Mating Pair	Mating Style	Mating Pair (Gender)	P/N
M8	Overmolded with Cable	Screw Thread	Female	CAP-WBBFSCC1
	Receptacle and Overmolded with Cable	Screw Thread	Male	CAP-WBBMSMA1
			Female	CAP-WBBFSMA1

Waterproof Cap > Sensor > M10.5

Customized – Upon Request




For male

Size	Mating Pair	Mating Style	Mating Pair (Gender)	P/N
M 10.5	Receptacle and Overmolded with Cable	Screw Thread	Male	CAP-WBCMSMA2

* Design and specification are subject to change without notice.

Waterproof Cap > Sensor > M12

Customized – Upon Request




* For Female

7 Choose plastic(1) or metal(2) items

Size	Size	Mating Pair	Mating Style	Mating Pair (Gender)	P/N
M12	A/B/D Code I Style	Receptacle	Screw Thread	Male	CAP-WBDPMSB1
		Receptacle and Overmolded with Cable	Screw Thread	Male	CAP-WBDMSMA 7
				Female	CAP-WBDFSMA 7
M12(Plastic)	A/B/D Code I Style	Receptacle and Overmolded with Cable	Screw Thread	Male	CAP-WBDMSMA 7
				Female	CAP-WBDFSMA 7

Waterproof Cap > Sensor > Heavy Duty Shielded Connectors


Customized – Upon Request



Size	Mating Pair	Mating Style	Mating Pair (Gender)	P/N
M22	Receptacle	Screw Thread	Male	CAP-WHBMSPD1




Waterproof Cap > Sensor > M23

Customized – Upon Request




Size	Mating Pair	Mating Style	Mating Pair (Gender)	P/N
M23	Receptacle and Overmolded with Cable	Screw Thread	Male	CAP-WBHMSMA1

Waterproof Cap > USB | IEEE 1394

    * USB Screw (Mating Pair: Male) * USB Lock * USB Screw (Mating Pair: Female) * IEEE 1394 6 More to choose: None(A) / With Chain(B) / With Rubber Lead(C) / With Fish Line(D)				
Type	Mating Pair	Mating Style	Mating Pair (Gender)	P/N
USB 2.0 Type A USB 2.0 Type B USB 3.0 Type A	Receptacle	Screw Thread	Male	CAP-WACMSP 6 1
		2 point lock bayonet	Male	CAP-WADMLP 6 1
	Receptacle and Overmolded with Cable	Screw Thread	Male	CAP-WACMSMA1
		2 point lock bayonet	Male	CAP-WADMLMA1
	Overmolded with Cable	Screw Thread	Female	CAP-WUSFSCC1
IEEE 1394	Receptacle	Screw Thread	Male	CAP-WACMSP 6 1
	Receptacle and Overmolded with Cable	Screw Thread	Male	CAP-WACMSMA1


Waterproof Cap > D-SUB | DVI

 7 Choose rubber lead: Vertical type (1) / Horizontal type (2)					
Type		Mating Pairs	Mating Style	Mating Pair (Gender)	P/N
Standard D-SUB	High Density D-SUB				
Standard (9 pins)	High Density (15 Pins)	Receptacle	Screw Thread	Male & Female	CAP-WD1CSPA1
Standard (15 pins)	High Density (26 Pins)	Receptacle	Screw Thread	Male & Female	CAP-WD2CSPA1
Standard (25 pins)	High Density (44 Pins)	Receptacle	Screw Thread	Male & Female	CAP-WD3CSPA1
DVI		Receptacle	Screw Thread	Male & Female	CAP-WDVCSPA1


* Design and specification are subject to change without notice.

Waterproof Cap > RJ


Customized – Upon Request




* RJ C 3 Point Lock



* RJ C Screw



* RJ D Screw




* RJ ODVA 3 Point Lock

6 More to choose: None(A) / With Chain(B)
/ With Rubber Lead(C) / With Fish Line(D)


7 Choose plastic (1) or metal (2) items

Size	Mating Pair	Mating Style	Mating Pair (Gender)	P/N
C Size	Receptacle	3 point lock bayonet	Male	CAP-WACMTMA1 CAP-WACMTP 6 1
		Screw Thread	Male	CAP-WACMSMA 7 CAP-WACMSP 6 7
D Size	Receptacle	Screw Thread	Male	CAP-WADMSMA1 CAP-WADMSP 6 1
ODVA	Receptacle	3 point lock bayonet	Male	CAP-WEOFTPC1

Waterproof Cap > HDMI




* D Size (Circular Type)




* Rectangle Type

Size	Mating Pair	Mating Style	Mating Pair (Gender)	P/N
D Size (Circular Type)	Receptacle	Screw Thread	Male	CAP-WADMSMA1
Rectangle Type	Receptacle	Latch Type	Female	CAP-WHDFLPA1

Waterproof Cap > Fiber Optic

Customized – Upon Request 7 				
Size	Mating Pair	Mating Style	Mating Pair (Gender)	P/N
Fiber Optic	Receptacle and Overmolded with Cable	3 point lock bayonet	Female	CAP-WBFTMA1

Dummy >Circular > Middle Size: 13/16"-28 UNS


Customized – Upon Request 			
Size	Mating Pair	Mating Style	P/N
13/16"-28 UNS	Receptacle (Female)	Screw Thread	CAP-CACFSBA1

* Design and specification are subject to change without notice.

Accessories - Multi-port

Multi-port > Circular > Mini Size: 7/16"-28 UNS

Customized - Upon Request




* Choose the cable length:01-99 m / Cable 22+24+B PVC

Current Rating	Contacts 2	Mating Style	Connector 1 (Male Connector / Male Contacts)	Connector 1 (Male Connector / Female Contacts)	More options
			Connector 2 (Male Connector / Male Contacts)	Connector 2 (Male Connector / Female Contacts)	
			Connector 3 (Male Connector / Male Contacts)	Connector 3 (Male Connector / Female Contacts)	
			Connector 4 (Male Connector / Male Contacts)	Connector 4 (Male Connector / Female Contacts)	
			Connector 5 (Male Connector / Male Contacts)	Connector 5 (Male Connector / Female Contacts)	
			Connector 6 (Male Connector / Male Contacts)	Connector 6 (Male Connector / Female Contacts)	
5A	02,03	Screw Thread	A-222222-MMMMMM-SA*	A-222222-HHHHHH-SA*	A-22222-78910111213-SA*
		2 point lock bayonet	A-222222-MMMMMM-LA* A-22222-MMMMMM-LA01	A-222222-HHHHHH-LA*	A-22222-78910111213-LA*
2A	04,05,06	Screw Thread	A-222222-MMMMMM-SA*	A-222222-HHHHHH-SA*	A-22222-78910111213-SA*
		2 point lock bayonet	A-222222-MMMMMM-LA*	A-222222-HHHHHH-LA*	A-22222-78910111213-LA*

Multi-port > Circular > Standard Size: 5/8"-27 UNS

Customized – Upon Request



- 6 For connector 1
- 7 For connector 2
- 8 For connector 3
- 9 For connector 4

Choose Connector / Contacts Gender:
M: Male + Male
F: Female + Female

* Choose the cable length:01-99 m /
Cable 22+24+B PVC


Current Rating	Contacts 2	Mating Style	Connector 1 (Male Connector / Male Contacts)	Connector 1 (Male Connector / Female Contacts)	More options
			Connector 2 (Male Connector / Male Contacts)	Connector 2 (Male Connector / Female Contacts)	
			Connector 3 (Male Connector / Male Contacts)	Connector 3 (Male Connector / Female Contacts)	
			Connector 4 (Male Connector / Male Contacts)	Connector 4 (Male Connector / Female Contacts)	
10A	02,03,04	Screw Thread	B-2222-MMMMMM-SA*	B-2222-HHHHHH-SA*	B-2222-6789-SA*
		2 point lock bayonet	B-2222-MMMMMM-LA*	B-2222-HHHHHH-LA*	B-2222-6789-LA*
5A	02,03,04,05,06,07,08	Screw Thread	B-2222-MMMMMM-SA*	B-2222-HHHHHH-SA* B-04040404-HHHH-SA*	B-2222-6789-SA*
		2 point lock bayonet	B-2222-MMMMMM-LA*	B-2222-HHHHHH-LA*	B-2222-6789-LA*
2A	10,12	Screw Thread	B-2222-MMMMMM-SA*	B-2222-HHHHHH-SA*	B-2222-6789-SA*
		2 point lock bayonet	B-2222-MMMMMM-LA*	B-2222-HHHHHH-LA*	B-2222-6789-LA*

* Design and specification are subject to change without notice.

Accessories - Box

Box > USB > 2.0 Type A, 2.0 Type B


Customized - Upon Request




Type	Ports	P/N
2.0 Type A	1	BOX-USA11
	2	BOX-USA22
	4	BOX-USA44
2.0 Type B	1	BOX-USB11
	2	BOX-USB22
	4	BOX-USB44

Accessories - Tool


└ **Wrench** > Circular > Standard Size:
5/8"-27 UNS




└ **Wrench** > Circular > Middle Size:
13/16"-28 UNS



└ **Wrench** > Circular > Large Size:
1"-20 UNEF





└ **Unlock Tool** > Cable Joiner >
8~10mm/10~12mm/12~16mm



Accessories - Joint

Joint > D-SUB > Standard & High Density

Customized – Upon Request



Type		Mating Style	P/N
Standard D-SUB	High Density D-SUB		
Standard (9 pins)	High Density (15 Pins)	Screw Thread	DJ1-00JNNA-SL7001
Standard (15 pins)	High Density (26 Pins)	Screw Thread	DJ2-00JNNA-SL7001
Standard (25 pins)	High Density (44 Pins)	Screw Thread	DJ3-00JNNA-SL7001

Accessories - Patch Cable (Double-ended)

Patch Cable (Double-ended) > RJ

Customized – Upon Request

End 2

Pin Header

End 1

Plug

End 1

Plug

End 2

Pin Header

Gold Plated 6u"

Pitch 2.54mm

Select cable length 10cm/20cm/30cm

End 1		End 2		P/ N
Type	Gender	Type	Gender	
RJ 45 Unshielded	Plug	RJ 45 Unshielded	Plug	UPG06-CHOP1-C10
			Pin Header	UPG06-UPG06-C10

* Design and specification are subject to change without notice.

Glossary

⌵ IP: IP65 • IP66 • IP67 • ALTW IP 68 (According to IEC 60950 standard.)

The IP Rating- Ingress Protection Rating, sometimes also interpreted as International Protection Rating, classifies and rates the degree of protection provided against the intrusion of solid objects (including body parts like hands and fingers), dust, accidental contact, and water in mechanical casings and with electrical enclosures.

The standard aims to provide users more detailed information than vague marketing terms such as waterproof.

IP65: No ingress of dust / Protected against low pressure jets of water.

IP66: No ingress of dust / Protected against powerful water jets.

IP67: No ingress of dust / Protected against harmful effects caused in 1M water within 30mins.

IP68: No ingress of dust / Protected against harmful effects caused in 1M water within 24hrs.

IP68 (Micro USB) : No ingress of dust / Protected against harmful effects caused in 1M water within 2hrs.

.....

⌵ Waterproof mated / unmated

Mated Waterproof:

Waterproof is only assured when mated & locked tightly to its counterpart.

Unmated Waterproof:

Standalone waterproof or waterproof is assured even without its counterpart. The water will not get through the inner portion of the exposed connector as it is entirely sealed.

.....

⌵ UV Resistance

Being resistant to ultra violet (UV) light or sunlight. UV light, or sunlight, will cause non-resistant materials and surfaces to fade or discolor.

.....

⌵ IEC

Founded in 1906, the IEC (International Electrotechnical Commission) is the world's leading organization for the preparation and publication of International Standards for all electrical, electronic and related technologies. These are known collectively as "electrotechnology".

IEC provides a platform to companies, industries and governments for meeting, discussing and developing the International Standards they require. All IEC International Standards are fully consensus-based and represent the needs of key stakeholders of every nation participating in IEC work. Every member country, no matter how large or small, has one vote and a say in what goes into an IEC International Standard.

.....

⌵ UL 1977

These requirements cover single and multipole connectors, intended for factory assembly to copper or copper alloy conductors or printed wiring boards, for use in data, signal, control and power applications within and between electrical equipment.

ODVA

Founded in 1995, ODVA is a global association whose members are comprised of the world's leading automation companies. ODVA's mission is to advance open, interoperable information and communication technologies in industrial automation. ODVA recognizes its media independent network protocol, the Common Industrial Protocol or "CIP" – and the network adaptations of CIP – EtherNet/IP, DeviceNet, CompoNet and ControlNet – as its core technology and the primary common interest of its membership. ODVA's vision is to contribute to the sustainability and prosperity of the global community by transforming the model for information and communication technology in the industrial ecosystem.

- ALTW ODVA connectors on P8-11

NMEA 2000

NMEA 2000 is a protocol used to create a network of electronic devices—chiefly marine instruments—on a boat. Various instruments that meet the NMEA 2000 standard are connected to one central cable, known as a backbone. The backbone powers each instrument and relays data among all of the instruments on the network. This allows one display unit to show many different types of information. It also allows the instruments to work together, since they share data. NMEA 2000 is meant to be "plug and play" to allow devices made by different manufacturers to talk and listen to each other.

- ALTW NMEA2000 connectors on P14-1

Industrial Automation New Products

ALTW offers these all new Product features to IA and keeps on working at its best to satisfy the industries continuously growing field of applications:

- * M8/M12 Improved Cable Assy. with Hex nuts, overall molded connector and UL approved cables (for UL / CSA by Q2 2014)
- * M8/M12 Ruggedized Distribution Boxes (for UL / CSA by Q4 2013)
- * M12 High-Speed 8Pin (Up to 10GB Ethernet Application)
- * M8 / M12 Field Installable in IDC Contacts (Pressed-In Conn.)

Amphenol LTW's X-Lok waterproof connector

"Click" when locking, for effort-saving and speed up. ALTW has X-Lok version for "3 Point Lock".

- ALTW X-Lok connectors on P20-1

Amphenol LTW's 3 Point Lock waterproof connector

To enhance the efficiency and improve the stability of Mating with Lock function, ALTW has the 3 Point Lock design to have better connector mating function.

ALTW provides Cable-to-Cable currently.

└ Amphenol LTW's RBL waterproof connector

Audible "Click" when locking; push both sides of the "Snap Lock" when unlocking. The creative design is effort-saving and speeds up the traditional connector locking nut function; furthermore, "Dual Snap Lock" is durable and protects from accidental loosening.

- ALTW RBL connectors on P19-1
-

└ Amphenol LTW waterproof connector : Mating with lock

"Secured connector mating" product locking mechanisms provides complete connector fastening for assured continuous transmission and reliable waterproof function.

- ALTW Power connector (PWII): P2-13 / P2-14
 - ALTW VTC I T-Junction PT: P15-10
 - ALTW VTC I SMC: P15-10
 - ALTW BMC: P15-13
 - Cable Joiner: P21-26
-

└ Amphenol LTW's Hybrid waterproof connector

A connector that contains contacts for more than one type of service. Note: Examples of hybrid connectors are those that have contacts for both optical fibers and twisted pairs, electric power and twisted pairs, or shielded and unshielded twisted pairs.

- ALTW Hybrid connectors
Circular series: P1-1
(5A+2A / 10A+2A / 10A+5A / 20A+2A / 20A+5A)
Power series: P2-1
(20A+2A)

Appendix

Standard Cable List

Product Series	Item No.	Jacket	Color	UL No.	Cable Spec.	Cable OD	Note
Circular	WCA0487UV01	PVC	Black	UL2464	26AWG*4C+Drain+AL.Mylar	4.8	Circular Mini Size / 2A / 4pin
Circular	WCA0486UV01	PVC	Black	UL2464	26AWG*5C+Drain+AL.Mylar	4.8	Circular Mini Size / 2A / 5pin
Circular	WCA0540UV01	PVC	Black	UL2464	26AWG*6C+Drain+AL.Mylar	5.0	Circular Mini Size / 2A / 6pin
Circular	WCA0072UV01	PVC	Black	UL2464	24AWG*2C+Drain+AL.Mylar	4.2	Circular Mini Size / 5A / 2pin Circular Standard Size / 5A / 2pin
Circular	WCA0549UV01	PVC	Black	UL2464	24AWG*3C+Drain+AL.Mylar	4.5	Circular Mini Size / 5A / 3pin Circular Standard Size / 5A / 3pin
Circular	WCA0219UV01	PVC	Black	UL2464	24AWG*4C+Drain+AL.Mylar	5.8	Circular Mini Size / 2A / 4pin Circular Standard Size / 5A / 4pin
Circular	WCA0217UV01	PVC	Black	UL2464	24AWG*6C+Drain+AL.Mylar	5.8	Circular Mini Size / 2A / 6pin Circular Standard Size / 5A / 6pin
Circular	WCA0543UV01	PVC	Black	UL2464	26AWG*10C+Drain+AL.Mylar	6.0	Circular Standard Size / 2A / 10pin
Circular	WCA0544UV01	PVC	Black	UL2464	26AWG*12C+Drain+AL.Mylar	6.0	Circular Standard Size / 2A / 12pin
Circular	WCA00010897	PVC	Black	UL1277,UL1581&UL83	18AWG*3C	8.5	Circular Standard Size / 5A / 3pin
Circular	WCA00010898	PVC	Black	UL1277,UL1581&UL83	18AWG*4C	9.2	Circular Standard Size / 5A / 4pin
Circular	WCA0551UV01	PVC	Black	UL2464	24AWG*5C+Drain+AL.Mylar	5.0	Circular Standard Size / 5A / 5pin
Circular	WCA0124UV01	PVC	Black	UL2464	20AWG*2C+Drain+AL.Mylar	5.8	Circular Standard Size / 10A / 2pin
Circular	WCA0489UV01	PVC	Black	UL2464	20AWG*3C+AL.Mylar	5.0	Circular Standard Size / 10A / 3pin
Circular	WCA0584UV01	PVC	Black	UL2464	26AWG*6C+24AWG*2C+Drain+AL.Mylar	5.5	Circular Standard Size / 5A+2A / 8pin
Circular	WCA0585UV01	PVC	Black	UL2464	24AWG*4C+20AWG*2C+Drain+AL.Mylar	6.0	Circular Standard Size / 10A+5A / 6pin
Circular	WCA0087UV01	PVC	Black	UL2464	24AWG*7C+Drain+AL/Mylar	5.8	Circular Standard Size / 5A / 7pin Circular Middle Size / 5A / 7pin
Circular	WCA0003UV01	PVC	Black	UL2464	24AWG*8C+Drain+AL/Mylar	5.5	Circular Standard Size / 5A / 8pin Circular Middle Size / 5A / 8pin
Circular	WCA0575UV01	PVC	Black	UL2464	20AWG*4C+Drain+AL.Mylar	5.5	Circular Standard Size / 10A / 4pin Circular Middle Size / 10A / 4pin
Circular	WCA0528UV01	PVC	Black	UL2464	24AWG*9C+Drain+AL.Mylar	6.0	Circular Middle Size / 5A / 9pin
Circular	WCA0556UV01	PVC	Black	UL2464	24AWG*10C+Drain+AL.Mylar	6.5	Circular Middle Size / 5A / 10pin
Circular	WCA0557UV01	PVC	Black	UL2464	24AWG*12C+Drain+AL.Mylar	7.0	Circular Middle Size / 5A / 12pin Circular Middle Size / 5A+2A / 12pin
Circular	WCA0558UV01	PVC	Black	UL2464	24AWG*14C+Drain+AL.Mylar	7.0	Circular Middle Size / 5A / 14pin Circular Middle Size / 5A+2A / 14pin
Circular	WCA0576UV01	PVC	Black	UL2464	20AWG*5C+Drain+AL.Mylar	6.0	Circular Middle Size / 10A / 5pin
Circular	WCA0577UV01	PVC	Black	UL2464	20AWG*6C+Drain+AL.Mylar	6.5	Circular Middle Size / 10A / 6pin
Circular	WCA00010710	PVC	Black	UL2464	(2P*24AWG+Drain+AL)+3C*16AWG+Filler+Pa per	12.0	Circular Middle Size / 10A+2A / 8Pin
Circular	WCA0042UV01	PVC	Black	UL2464	24AWG*6C+20AWG*2C+Drain+AL.Mylar	6.0	Circular Middle Size / 10A+5A / 8pin Circular Others / 10A+5A / 8pin
Circular	WCA0560UV01	PVC	Black	UL2464	24AWG*18C+Drain+AL.Mylar	8.0	Circular Middle Size / 2A / 18pin Circular Large Size / 5A / 18pin
Circular	WCA0264UV01	PVC	Black	UL2464	16AWG*2C+Talcum	5.8	Circular Middle Size / 20A / 2pin Circular Large Size / 20A / 2pin
Circular	WCA0579UV01	PVC	Black	UL2464	16AWG*3C+Drain+AL.Mylar	7.5	Circular Middle Size / 20A / 3pin Circular Large Size / 20A / 3pin
Circular	WCA00010045	PVC	Black	UL2464	26AWG*22C+Drain+AL.Mylar	7.5	Circular Large Size / 2A / 20~22pin
Circular	WCA0285UV01	PVC	Black	UL2464	16AWG*4C+AL.Mylar	7.5	Circular Large Size / 20A / 4pin
Circular	WCA0263UV01	PVC	Black	UL2464	16AWG*5C+Talcum	7.8	Circular Large Size / 20A / 5pin
Circular	WCA0582UV01	PVC	Black	UL2464	16AWG*6C+Filler+Drain+AL.Mylar	9.5	Circular Large Size / 20A / 6pin
Circular	WCA0583UV01	PVC	Black	UL2464	16AWG*7C+Drain+AL.Mylar	9.5	Circular Large Size / 20A / 7pin
Circular	WCA00010876	PVC	Black	UL2586	(24AWG*1P+A)*2C+16AWG*3C+EA	10.0	Circular Large Size / 20A+2A / 8pin
Circular	WCA00010635	PVC	Black	UL2464	(24AWG*4P+Drain+AL)+16AWG*3C+Filler+Pa per	11.0	Circular Large Size / 20A+5A / 12pin
Circular	WCA0449UV01	PVC	Black	UL2464	26AWG*31C+Drain+AL.Mylar	9.0	Circular Macro Size / 5A / 31pin
Circular	WCA0577UV01	PVC	Black	UL2464	20AWG*6C+Drain+AL.Mylar	6.5	Circular RBL / 5A / 6pin
Circular	WCA0485XX01	PVC	Black	UL2464	14AWG*3C+Talcum	7.0	Circular X-Lock / 20A / 3pin

* Design and specification are subject to change without notice.

Appendix

Standard Cable List

Product Series	Item No.	Jacket	Color	UL No.	Cable Spec.	Cable OD	Note
Power	WCA0576UV01	PVC	Black	UL2464	20AWG*5C+Drain+AL.Mylar	6.0	Power / 8A / 5pin
Power	WCA0577UV01	PVC	Black	UL2464	20AWG*6C+Drain+AL.Mylar	6.5	Power / 8A / 6pin
Power	WCA00010049	PVC	Black	UL2464	20AWG*7C+Drain+AL.Mylar	6.5	Power / 8A / 7pin
Power	WCA0264UV01	PVC	Black	UL2464	16AWG*2C+Talcum	5.8	Power / 12A / 2pin
Power	WCA0579UV01	PVC	Black	UL2464	16AWG*3C+Drain+AL.Mylar	7.5	Power / 12A / 3pin
Power	WCA0285UV01	PVC	Black	UL2464	16AWG*4C+AL.Mylar	7.5	Power / 12A / 4pin
Power	WCA0485XX01	PVC	Black	UL2464	14AWG*3C+Talcum	7.0	Power / 20A / 3pin
Power	WCA00010846	PVC	Black	UL1277,UL1581&UL83	14AWG*3C	9.7	Power / 20A / 3pin
Power	WCA0579UV01	PVC	Black	UL2464	16AWG*3C+Drain+AL.Mylar	7.5	Power / 20A+2A / 4pin
Power	WCA00010899	PVC	Black	UL1277,UL1581,UL83	14AWG*3C+16AWG*1C	10.3	Power / 20A+2A / 4pin
Power	WCA00010239	PVC	Black	-	SJT 10AWG*3C+Talc	15.6	Power / 25A / 3pin
Sensor	WCA0570UV01	PVC	Black	UL2464	22AWG*3C+Talcum	5.0	Sensor M8 / 5A / 3pin
Sensor	WCA00010063	PU	Black	NONUL	22AWG*3C+Talcum	4.5	Sensor M8 / 5A / 3pin
Sensor	WCA0571UV01	PVC	Black	UL2464	22AWG*4C+Talcum	5.0	Sensor M8 / 5A / 4pin
Sensor	WCA00010062	PU	Black	NONUL	22AWG*4C+Insulation	4.8	Sensor M8 / 5A / 4pin
Sensor	WCA0027UV01	PVC	Black	UL2464	24AWG*2C+Talcum	4.2	Sensor M10.5 / 2A / 2pin
Sensor	WCA0006UV01	PVC	Black	UL2464	24AWGx3C+Talcum	4.5	Sensor M10.5 / 2A / 3pin
Sensor	WCA0036UV01	PVC	Black	UL2464	24AWG*4C+Talcum	5.0	Sensor M10.5 / 2A / 4pin
Sensor	WCA0229UV01	PVC	Black	UL2464	24AWG*5C+Talcum	5.0	Sensor M10.5 / 2A / 5pin
Sensor	WCA0570UV01	PVC	Black	UL2464	22AWG*3C+Talcum	5.0	Sensor M12 / 5A / 3pin
Sensor	WCA00010063	PU	Black	NONUL	22AWG*3C+Talcum	4.5	Sensor M12 / 5A / 3pin
Sensor	WCA0571UV01	PVC	Black	UL2464	22AWG*4C+Talcum	5.0	Sensor M12 / 5A / 4pin
Sensor	WCA00010062	PU	Black	NONUL	22AWG*4C+Insulation	4.8	Sensor M12 / 5A / 4pin
Sensor	WCA0521UV01	PVC	Black	UL2464	22AWG*5C+Talcum	5.5	Sensor M12 / 5A / 5pin
Sensor	WCA00010061	PU	Black	NONUL	22AWG*5C+Filler+Talcum+Paper	5.0	Sensor M12 / 5A / 5pin
Sensor	WCA0203UV01	PVC	Black	UL2464	24AWG*8C+Talcum	5.5	Sensor M12 / 2A / 8pin
Sensor	WCA00010060	PU	Black	NONUL	24AWG*8C+Paper+Filler	6.0	Sensor M12 / 2A / 8pin
Sensor	WCA00010209	PVC	Black	UL2464	22AWG*3C+Drain+AL.Mylar	4.5	Sensor M12 Shielded / 5A / 3pin
Sensor	WCA00010139	PU	Black	NONUL	22AWG*3C+Drain+AL.Mylar	4.5	Sensor M12 Shielded / 5A / 3pin
Sensor	WCA0568UV01	PVC	Black	UL2464	22AWG*4C+Drain+AL.Mylar	5.5	Sensor M12 Shielded / 5A / 4pin
Sensor	WCA00010140	PU	Black	NONUL	22AWG*4C+Drain+AL.Mylar	4.5	Sensor M12 Shielded / 5A / 4pin
Sensor	WCA0569UV01	PVC	Black	UL2464	22AWG*5C+Drain+AL.Mylar	5.5	Sensor M12 Shielded / 5A / 5pin
Sensor	WCA00010141	PU	Black	NONUL	22AWG*5C+AL.Mylar+Drain	5.2	Sensor M12 Shielded / 5A / 5pin
Sensor	WCA0003UV01	PVC	Black	UL2464	24AWG*8C+Drain+AL/Mylar	5.5	Sensor M12 Shielded / 2A / 8pin
Sensor	WCA00010142	PU	Black	NONUL	24AWG*8C+Drain+AL.Mylar	5.5	Sensor M12 Shielded / 2A / 8pin
Sensor	WCA0352XX02	PU	Black	NONUL	22AWG*5C+Talcum	5.0	Sensor M12 Y Cable / 5A / 5pin
Sensor	WCA0251XX02	PU	Black	NONUL	24AWG*8C+Paper	5.2	Sensor M12 Y Cable / 2A / 8pin
USB	WCA0365UV01	PVC	Black	-	28AWG*1P+24AWG*2C+AL.Mylar+Drain+Braid (USB 2.0)	5.0	USB / 2.0
IEEE 1394	WCA00010037	PVC	Black	-	(28AWG*1P+AL+B)*2+22AWG*2C+Tran.Mylar+AL+B	6.5	IEEE 1394
D-SUB	WCA0528UV01	PVC	Black	UL2464	24AWG*9C+Drain+AL.Mylar	6.0	D-SUB Standard / 09pin
D-SUB	WCA0465UV01	PVC	Black	UL2464	24AWG*15C+Drain+AL.Mylar	7.0	D-SUB Standard / 15pin
D-SUB	WCA0284UV01	PVC	Black	UL2464	24AWG*25C+Drain+AL.Mylar	9.0	D-SUB Standard / 25pin
D-SUB	WCA00010114	PVC	Black	UL2464	24AWG*37C+Drain+AL/Mylar	8.5	D-SUB Standard / 37pin
D-SUB	WCA00010080	PVC	Black	UL2464	(24AWG*25C+Mylar)+24AWG*25C+Drain+AL.Mylar	12.0	D-SUB Standard / 50pin
D-SUB	WCA0545UV01	PVC	Black	UL2464	26AWG*15C+Drain+AL.Mylar	6.5	D-SUB High Density / 15pin
D-SUB	WCA0546UV01	PVC	Black	UL2464	26AWG*26C+Drain+AL.Mylar	8.0	D-SUB High Density / 26pin
D-SUB	WCA0547UV01	PVC	Black	UL2464	26AWG*44C+Drain+AL.Mylar	10.5	D-SUB High Density / 44pin
D-SUB	WCA00010115	PVC	Black	UL2464	(26AWG*31C+Mylar)+26AWG*31C+Drain+AL/Mylar	13.0	D-SUB High Density / 62pin
D-SUB	WCA00010081	PVC	Black	UL2464	((28AWG*28C+Mylar)+28AWG*22C+Mylar)+28AWG*28C+Drain+AL	13.0	D-SUB High Density / 78pin

Product Series	Item No.	Jacket	Color	UL No.	Cable Spec.	Cable OD	Note
DVI	WCA00010095	PVC	Black	UL20276	(28AWG*1P+Drain+AL+Mylar)*4C+(1P+3C)*28AWG+AL+Braid	7.3	DVI / 19pin
DVI	WCA00010096	PVC	Black	UL20276	[3COAX+(1P*28AWG+Drain+AL.Mylar+Mylar)*4+1P*28#+6C*28AWG]+AL.Mylar+Braid	8.5	DVI / 23pin
DVI	WCA00010097	PVC	Black	UL20276	(28AWG*1P+Drain+AL+Mylar)*7C+28AWG*1P+28AWG*3C+AL+Braid	8.5	DVI / 25pin
DVI	WCA00010098	PVC	Black	UL20276	[3COAX+(28AWG*1P+Drain+AL+Mylar)*7+28AWG*1P+28AWG*6C]+AL+Braid	10.0	DVI / 29pin
RJ	WCA0663UV01	PVC	Black	-	CAT.5E UTP 24AWG*4P	6.0	RJ / Cat.5E
RJ	WCA0664UV01	PVC	Black	-	CAT.5E FTP 24AWG*4P+Mylar+D+AL/Mylar	6.5	RJ / Cat.5E
RJ	WCA00010356	PVC	Black	-	CAT.5E FTP 24AWG*5P+Mylar+Drain+AL.Mylar	6.5	RJ / Cat.5E
HDMI	WCA00010264	PVC	Black	UL20276	(26AWG*1P+Drain+AL+Mylar)*4C+26AWG*1P+26AWG*5C+AL+Braid	8.5	HDMI / 19pin
NMEA	WCA00010257	PVC	Black	-	[(24AWG+1P+AL)+(22AWG+1P+AL)]+Drain+AL.Mylar+Braid	6.0	NMEA / 4A / 5pin
NMEA	WCA00010258	PVC	Black	-	[(22AWG+1P+AL)+(18AWG+1P+AL)]+Drain+AL.Mylar+Braid	7.0	NMEA / 4A / 5pin
NMEA	WCA00010437	PVC	Gray	-	[(24AWG+1P+AL)+(22AWG+1P+AL)]+Drain+Braid+Mylar	7.1	NMEA / 4A / 5pin
NMEA	WCA00010369	PVC	Black	-	STOOW 16AWG*4C	10.6	NMEA / 8A / 4pin
NMEA	WCA00010259	PVC	Black	UL20276	[(18AWG*1P+AL)+(16AWG*1P+AL)]+Drain+AL+Braid	10.0	NMEA / 8A / 5pin
NMEA	WCA00010436	PVC	Gray	-	[(18AWG+1P+AL)+(15AWG+1P+AL)]+Drain+Braid	12.2	NMEA / 8A / 5pin
Coaxial	WCA0033XX01	PVC	Black	-	20AWG,RG-58 / U1	5.0	Coaxial / 50Ω
Coaxial	WCA0009XX04	PVC	Black	-	RG-59U 1C+Braid	6.15	Coaxial / 75Ω
Coaxial	WCA0445XX01	PVC	Black	UL1185	26AWG*1C+Spiral	3.0	Coaxial / RCA
DC-JACK	WCA0072UV01	PVC	Black	UL2464	24AWG*2C+Drain+AL.Mylar	4.2	DC-JACK / 2pin,14pin
DC-JACK	WCA0549UV01	PVC	Black	UL2464	24AWG*3C+Drain+AL.Mylar	4.5	DC-JACK
KSZ Circular	WCA00010022	PVC	Black	UL2464	18AWGx2C+AL.Mylar	5.5	KSZ Circular / 10A / 2pin
KSZ Circular	WCA0242XX01	PVC	Black	UL2464	18AWG*3C+AL.Mylar	6.0	KSZ Circular / 10A / 3pin
KSZ Circular	WCA0416XX01	PVC	Black	UL2464	18AWG*4C+Drain+AL.Mylar	6.5	KSZ Circular / 10A / 4pin
Low Profile	WCA0542UV01	PVC	Black	UL2464	26AWG*8C+Drain+AL.Mylar	5.5	Low Profile / 1A / 8pin
Low Profile	WCA0543UV01	PVC	Black	UL2464	26AWG*10C+Drain+AL.Mylar	6.0	Low Profile / 1A / 10pin
Mini Din	WCA0487UV01	PVC	Black	UL2464	26AWG*4C+Drain+AL.Mylar	4.8	Mini Din / 4pin
Mini Din	WCA0486UV01	PVC	Black	UL2464	26AWG*5C+Drain+AL.Mylar	4.8	Mini Din / 5pin
Mini Din	WCA0540UV01	PVC	Black	UL2464	26AWG*6C+Drain+AL.Mylar	5.0	Mini Din / 6pin
Mini Din	WCA0541UV01	PVC	Black	UL2464	26AWG*7C+Drain+AL.Mylar	5.0	Mini Din / 7pin
Mini Din	WCA0542UV01	PVC	Black	UL2464	26AWG*8C+Drain+AL.Mylar	5.5	Mini Din / 8pin
Solar	WCA00010897	PVC	Black	UL1277,UL1581&UL83	18AWG*3C	8.5	Solar / 3pin
Solar	WCA00010898	PVC	Black	UL1277,UL1581&UL83	18AWG*4C	9.2	Solar / 4pin
Solar	WCA00010894	PVC	Black	UL1277,UL1581&UL83	12AWG*3C	11.0	Solar / 17A / 3pin
Solar	WCA00010895	PVC	Black	UL1277,UL1581&UL83	12AWG*4C	12.0	Solar / 17A / 4pin
Solar	WCA00010373	TPE-U	Black	-	12AWG*1C	6.5	Solar / 1Pin
Solar	WCA00010593	XLPO	Black	-	12AWG*1C	6.1	Solar / 1Pin
Solar	WCA00010750	XLPO	Black	-	12AWG*1C	6.3	Solar / 1Pin
Solar	WCA00010430	XLPO	Black	-	12AWG*1C	6.8	Solar / 1Pin

* Design and specification are subject to change without notice.

Maximum Wire Copper OD Size

Product Series	Categories	Sub-Categories	Solder Pin: Maximum Copper OD within allowed current rating (Unit: mm)	Screw Pin: Maximum Copper OD within allowed current rating (Unit: mm)
Circular Connectors	Mini (A) - Size	AD	1.00	-
Circular Connectors	Mini (A) - Size	AU	0.80	-
Circular Connectors	Standard (B) - Size	BB	1.30	-
Circular Connectors	Standard (B) - Size	BD	1.00	-
Circular Connectors	Standard (B) - Size	BB	1.30	-
Circular Connectors	Standard (B) - Size	BBD	1.00	-
Circular Connectors	Standard (B) - Size	BD	1.00	-
Circular Connectors	Standard (B) - Size	BDU	1.00	-
Circular Connectors	Standard (B) - Size	BU	0.80	-
Circular Connectors	Middle (C) - Size	CBU	1.3/0.8	-
Circular Connectors	Middle (C) - Size	CB	1.30	-
Circular Connectors	Middle (C) - Size	CC	1.70	2.00
Circular Connectors	Middle (C) - Size	CD	1.00	-
Circular Connectors	Middle (C) - Size	CU	0.80	-
Circular Connectors	Middle (C) - Size	CDU	1.0/0.8	-
Circular Connectors	Large (D) - Size	DCD	1.7/1.0	-
Circular Connectors	Large (D) - Size	DCU	1.7/0.8	-
Circular Connectors	Large (D) - Size	DC	1.70	2.00
Circular Connectors	Large (D) - Size	DD	1.00	-
Circular Connectors	Large (E) - Size	ED	1.00	-
M Series Sensor Connectors	M8	8P	0.80	-
M Series Sensor Connectors	M12	12,12B,12D,12B,SBP,SDP	1.00	1.10
M Series Sensor Connectors	M20	HB20,HC20,HD20,LB20,LC20,LD20	1.70	2.00
M Series Sensor Connectors	M23	LJ23	-	-
Power Connectors	20A+2A	PWCU	1.7/0.8	-
Power Connectors	30A	PWL	3.60	-
Power Connectors	30A	PWJ	-	2.60
Power Connectors	25A	PWH	2.60	-
Power Connectors	20A	PWC	1.70	-
Power Connectors	8A	PWE	1.20	1.10
Power Connectors	12A	PWF	1.60	1.60
Power Connectors	16A	PWG	2.00	2.00
NMEA 2000 Connectors	Micro	12,12P	1.00	-
D-SUB Connectors	Standard	SDB-09	1.00	-
D-SUB Connectors	Standard	SDB-15,SDB-25	1.00	-
D-SUB Connectors	Standard	SDB-15	1.00	-
D-SUB Connectors	High Density	HDB-15	1.00	-
D-SUB Connectors	High Density	HDB-26,HDB-44	1.00	-
D-SUB Connectors	High Density	HDB-26	1.00	-

Cable Max. OD for Field Installable

Product Series	Categories	Sub-Categories	Cable OD
Circular Connectors	Mini (A) - Size	AD,AU	4.5~6.5
Circular Connectors	Standard (B) - Size	BB,BD	3.5~6.5
Circular Connectors	Standard (B) - Size	BB,BBD,BD,BDU,BU	4.5~6.5
Circular Connectors	Middle (C) - Size	CBU	7.6~9.6
Circular Connectors	Middle (C) - Size	CB,CC,CD,CU,CDU	4.0~9.6
Circular Connectors	Large (D) - Size	DCD	10.0~12.4
Circular Connectors	Large (D) - Size	DCU	9.5~10.8
Circular Connectors	Large (D) - Size	DC,DD	9.5~10.8
Circular Connectors	Large (E) - Size	None	None
Circular Connectors	Other - Size	PLD	4.5~6.5
M Series Sensor Connectors	M8	8P	4.5~6.5
M Series Sensor Connectors	M12	12, 12B, 12D, 12B,SBP,SDP	4.5~6.5
M Series Sensor Connectors	M20	HB20,HC20,HD20,LB20,LC20,LD20	5.5~12.5
M Series Sensor Connectors	M23	LJ23	8.5~17.5
Power Connectors	20A+2A	PWCU	4.0~9.6 , 10~19
Power Connectors	30A	PWL	10~19
Power Connectors	30A	PWJ	9.0~12.0 , 13~16
Power Connectors	25A	PWH	9.0~12.0 , 13~16
Power Connectors	20A	PWC	4.0~9.6
Power Connectors	8A	PWE	5.5~10.8
Power Connectors	12A	PWF	5.5~10.8
Power Connectors	16A	PWG	6.0~12.5
USB Connectors	Mini USB 2.0 B Type	NUB	3.5~5.5
USB Connectors	USB 2.0 A Type	UA	5.0~10.8
USB Connectors	USB 2.0 B Type	UB	5.0~10.8
NMEA 2000 Connectors	Micro	12, 12P	4.5~6.5
NMEA 2000 Connectors	Mini	MN	8.0~11.0
NMEA 2000 Connectors	Micro	UMC	4.5~7.5
NMEA 2000 Connectors	Mini	UMN	8~12.2
D-SUB Connectors	Standard	SDB-09	3.5~7.0
D-SUB Connectors	Standard	SDB-15,SDB-25	6.0~10.0
D-SUB Connectors	Standard	SDB-15	6.0~8.0
D-SUB Connectors	High Density	HDB-15	3.5~7.0
D-SUB Connectors	High Density	HDB-26,HDB-44	6.0~10.0
D-SUB Connectors	High Density	HDB-26	6.0~8.0
IEEE 1394 Connectors	IEEE 1394B	13-	6.0~10.0
Fiber Optic Connectors	LC Type	FB-	2.5~2.8 , 4.5~6.8
Fiber Optic Connectors	SC Type	FB-	2.0~2.4
Cable Joiner	6~10mm	CX	6~10
Cable Joiner	8~10mm	CX	8~10
Cable Joiner	10~12mm	CX	10~12
Cable Joiner	12~16mm	CX	12~16
RJ Connector	-	RCP,RDP,ROP	4.5~6.5

* Design and specification are subject to change without notice.

Quick Search (Circular Connector)

└ In-line

Size	Mating Style	Connector (Housing) Gender / Contact Gender	Overmolded with Cable / Field Installable	To	Mating Pair	Page
Mini Size (A) 7/16"-28 UNS	2 Points Lock	MM	Overmolded with Cable	To	Overmolded with Cable & Field Installable	1-14
		FF	Overmolded with Cable	To	Overmolded with Cable & Field Installable	1-14
Standard Size (B) 5/8"-27 UNS	2 Points Lock	MM	Overmolded with Cable	To	Overmolded with Cable & Field Installable	1-16
			Field Installable	To	Overmolded with Cable & Field Installable	1-16
		FF	Overmolded with Cable	To	Overmolded with Cable & Field Installable	1-17
			Field Installable	To	Overmolded with Cable & Field Installable	1-17
		FM	Overmolded with Cable	To	Overmolded with Cable & Field Installable	1-18
Middle Size (C) 13/16"-28 UNS	2 Points Lock	MM	Overmolded with Cable	To	Overmolded with Cable & Field Installable	1-22
			Field Installable	To	Overmolded with Cable & Field Installable	1-22
		FF	Overmolded with Cable	To	Overmolded with Cable & Field Installable	1-22
			Field Installable	To	Overmolded with Cable & Field Installable	1-23
		MF	Overmolded with Cable	To	Overmolded with Cable & Field Installable	1-23
		FM	Overmolded with Cable	To	Overmolded with Cable & Field Installable	1-23
Large Size (D) 1"-20UNEF	2 Points Lock	MM	Overmolded with Cable	To	Overmolded with Cable & Field Installable	1-29
		FF	Overmolded with Cable	To	Overmolded with Cable & Field Installable	1-29
		MF	Overmolded with Cable	To	Overmolded with Cable & Field Installable	1-29
		FM	Overmolded with Cable	To	Overmolded with Cable & Field Installable	1-30
		MD*	Overmolded with Cable	To	Overmolded with Cable & Field Installable	1-30
			Field Installable	To	Overmolded with Cable & Field Installable	1-30
		ME*	Overmolded with Cable	To	Overmolded with Cable & Field Installable	1-31
			Field Installable	To	Overmolded with Cable & Field Installable	1-31

* (E) Male (Power) + Female (Signal) | (D) Female (Power) + Male (Signal)

└ Receptacle and Maing Pair

Size	Mating Style	Connector (Housing) Gender / Contact Gender	Receptacle / Receptacle with Overmolded Cable	To	Mating Pair	Page
Mini Size (A) 7/16"-28 UNS	Screw Thread / 2 Points Lock	MM	Receptacle	To	Overmolded with Cable & Field Installable	1-15
			Receptacle with Overmolded Cable	To	Overmolded with Cable & Field Installable	1-15
			Receptacle	To	Overmolded with Cable & Field Installable	1-19
Standard Size (B) 5/8"-27 UNS	Screw Thread / 2 Points Lock	MM	Receptacle with Overmolded Cable	To	Overmolded with Cable & Field Installable	1-20
		MF	Receptacle	To	Overmolded with Cable & Field Installable	1-21
			Receptacle	To	Overmolded with Cable & Field Installable	1-24
Middle Size (C) 13/16"-28 UNS	Screw Thread / 2 Points Lock	MM	Receptacle with Overmolded Cable	To	Overmolded with Cable & Field Installable	1-25
			Receptacle	To	Overmolded with Cable & Field Installable	1-26
			Receptacle with Overmolded Cable	To	Overmolded with Cable & Field Installable	1-27
			Receptacle	To	Overmolded with Cable & Field Installable	1-28
	3 Points Lock	MD*	Receptacle	To	Overmolded with Cable & Field Installable	1-28
		ME	Receptacle	To	Overmolded with Cable & Field Installable	1-28
Large Size (D) 1"-20UNEF	Screw Thread / 2 Points Lock	MM	Receptacle	To	Overmolded with Cable & Field Installable	1-32
		MF	Receptacle	To	Overmolded with Cable & Field Installable	1-33
	2 Points Lock	MD*	Receptacle	To	Overmolded with Cable & Field Installable	1-34
		ME*	Receptacle	To	Overmolded with Cable & Field Installable	1-34
Micro Size (E) 1 3/16"-20 UNS	2 Points Lock	MF	Receptacle	To	Overmolded with Cable & Field Installable	1-34

* (E) Male (Power) + Female (Signal) | (D) Female (Power) + Male (Signal)

Amphenol LTW Technology Co., Ltd. (Headquarter)

9F., No.657-12, Zhongzheng Rd., Xinzhuang Dist., New Taipei City 242, Taiwan
Telephone: +886-2-29085626 Fax: +886-2-29029787
www.amphenolltw.com

Shulin plant, Taiwan

No.10, Shutan St., Shulin Dist., New Taipei City 238, Taiwan

Kunshan plant, China

No. 62 Da Tung Road, Peng Lang Street, Kunshan City ,
Jiangsu Province, China
Telephone: +86-512-5761-0501
Fax: : +86-512-5761-0515

For further information, please contact :

Sales & Marketing Department | Email : sales@ltw-tech.com



Scan to visit our website

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[BD-04BFMM-LL7C10](#) [BD-04BFMM-LL7C02](#) [BD-04BFMM-LL7C05](#) [BD-04BFMM-LL7C01](#) [PWC-03AFFM-LL7D10](#)
[PWF-02AMMM-SL7A05](#)