



SCALE 1.000

4-Ø 3.4

Ø 32

19

19

25.4 SQ.

Ø 3.2

Ø 2.5

5 REF.

21

2.5

SEE DETAIL A

Ø 20

Ø 17.5

M20XPI.0-6g

CUSTOMER OUTLINE DRAWING

ALL OTHER SHEETS ARE FOR INTERNAL USE ONLY

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN METRIC AND TOLERANCES ARE:
<0.5mm ± 0.05mm 0.5 - 6mm ± 0.1mm 6 - 30mm ± 0.2mm 30 - 120mm ± 0.3mm ANGLES ± 1°

NOTICE - These drawings, specifications, or other data (1) are, and remain the property of Amphenol corp. (2) must be returned upon request; and (3) are confidential and not to be disclosed to any person other than those to whom they are given by Amphenol Corp. the furnishing of these drawings, specifications, or other data by Amphenol Corp., or to any other person to anyone for any purpose is not to be regarded by implicatioin or otherwise in any manner licensing, granting rights to permitting such holder or any other sperson to manufacture, use or sell any product, process or design, patented or otherwsie, that may in any way be related to or disclosed by said drawings, specifications, or other data.

MATERIAL

REFERENCE
EAR # 6645

FINISH

DRAWN
STAR

ENGINEER
SUNDE

APPROVED
S.HSIEH

CAD FILE

DATE
18-Aug-16

DATE
18-Aug-16

DATE
18-Aug-16

TITLE
4.3-10 PANEL JACK
(IP 68)

SCALE: 3.0:1.0

DWG SIZE
B

SHEET
2 OF 2

REV
B

Amphenol RF
Danbury CT USA, Tainan, Taiwan, Shenzhen, China
www.amphenolrf.com

DRAWING NO. 43106551A1-005-ATS-50

ITEM NO. 886551AAQ01AB5F

PART NO. 431-129J-52S

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[431-129J-52S](#)