



REV.	DATE	DESCRIPTION
A	12/29/00	REVISE PLATING TO SILVER
B	12/06/06	UPDATE DRAWING FORMAT
C	09/20/07	MODIFY BODY TO HEX COUPLING NUT



RECOMMENDED CABLE
STRIPPING DIM'S

8					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007” .315 – 1.180 = ± 0.015” 1.180 – 4.724 = ± 0.020”	APPROVALS		DATE		Amphenol Connex										
7						DRAWN	G.R.S.	09/20/07												
6						CHECKED														
5						ISSUED				PART DESCRIPTION										
4						SHEET	1 OF 1				7/16 PLUG – .250” SEMI RIGID CABLE									
3	CONTACT PIN	BER. COPPER	SILVER	1	DO NOT SCALE DRAWING	PART NO.					272110									
2	INSULATOR	TEFLON	NATURAL	1		CAD FILE					DWG. NO.		272110.DWG	REV.	C	SIZE	A	SCALE	NA	
1	BODY	BRASS	NEXCOTE	1		C:/272/272110.DWG														
	DESCRIPTION	MATERIAL	FINISH	QTY																

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[272110](#)