


REV.	DATE	DESCRIPTION
A	06/01/99	MODIFY FERRULE
B	05/24/07	UPDATE DRAWING FORMAT



NOTE:

1. CRIMPED FERRULE HEX CRIMP SIZE .213".
2. CRIMPED CONTACT PIN HEX CRIMP SIZE .100"

RECOMMENDED
CABLE STRIPPING DIM'S

8					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007” .315 – 1.180 = ± 0.015” 1.180 – 4.724 = ± 0.020”	APPROVALS		DATE		Amphenol Connex					
7						DRAWN	G.R.S.	05/24/07							
6						CHECKED				PART DESCRIPTION N CRIMP PLUG (FOR 58 PLENUM, BELDEN 88240, BELDEN 89907)					
5						ISSUED									
4	FERRULE	COPPER	NEXCOTE	1		SHEET	1 OF 1					PART NO. 172161			
3	CONTACT PIN	BRASS	GOLD	1											
2	INSULATOR	TEFLON	NATURAL	1						DWG. NO. 172161.DWG					
1	BODY	BRASS	NEXCOTE	1											
DESCRIPTION		MATERIAL	FINISH	QTY	DO NOT SCALE DRAWING		C:/172/172161.DWG			REV.	B	SIZE	A	SCALE	NA

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[172161](#)