



SIGN	DATE	DESCRIPTION	APPROVER
△	2010.03.31	Add the 2p mark	Jacke
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!			




Material:

- Item a :Terminal housing:Thermoplastic (UL94 V-0)
- Item b :With flange screw: Steel Zinc plated, M2.5"+/-"

Electrical (Match with A0 series)

- Voltage rating: 300V
- Current rating: 10A
- Wire range: 0.5-1.0mm²/1.5-2.5mm²
- Withstanding Voltage: 1.6KV



KI xx 50 x 2 xxxx G

No. OF POLES

02 2 CONTACTS

03 3 CONTACTS

... ..

24 24 CONTACTS

Color

0 Black (RAL9005)

2 Red (RAL3001/D)

3 Orange(RAL2011/P)

4 Yellow(RAL1018/A)

5 Green(RAL6018/T)

6 Blue (RAL5015/A)

8 Grey(RAL7035/D)

G: Pb<40000ppm

0000: "@" Logo (Standard)

000A: "ANYTEK" Mark

Any special item by customer request. please contact sales department.

N = Number of poles

Dim A=Nx5.08

Dim B=(N-1)x5.08



Dim. Poles	Dim A	Dim B
2-6p	±0.20	±0.20
7-12p	±0.25	±0.25
13-16p	±0.30	±0.30
17-24p	±0.40	±0.35

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE	KI 5.08 SERIES (加高有耳)								
PART NO.	Klxx50x2xxxxG				DWG NO.	8KI0103			
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.				Tolerance	
		Jacke 2010.03.31	Jacke 2010.03.31					UNIT: mm	X. ±0.50
					SCALE: 2/1	X.X ±0.30			
				SHEET: 01/01	REV.: C	X.XX ±0.10			
						X° ±1°			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Amphenol:

<u>KI0250520000G</u>	<u>KI0350520000G</u>	<u>KI0450520000G</u>	<u>KI0550520000G</u>	<u>KI0650520000G</u>	<u>KI0750520000G</u>
<u>KI0850520000G</u>	<u>KI0950520000G</u>	<u>KI1050520000G</u>	<u>KI1150520000G</u>	<u>KI1250520000G</u>	<u>KI1350520000G</u>
<u>KI1450520000G</u>	<u>KI1550520000G</u>	<u>KI1650520000G</u>	<u>KI1750520000G</u>	<u>KI1850520000G</u>	<u>KI1950520000G</u>
<u>KI2050520000G</u>	<u>KI2150520000G</u>	<u>KI2250520000G</u>	<u>KI2350520000G</u>	<u>KI2450520000G</u>	