




REV.	DATE	ECR NO.	DESCRIPTION
A	12/29/00	—	REVISE PLATING TO SILVER
B	06/01/04	—	UPDATE DRAWING FORMAT
C	04/19/06	—	REVISE BODY PLATING TO NEXCOTE
D	12/17/06	—	REVISE BODY STYLE TO 32 HEX
E	12/28/08	100070	REVISE BODY FORMAT



RECOMMENDED CABLE
STRIPPING DIM'S

NOTES:

1. CRIMPED FERRULE HEX CRIMP SIZE .429"

				UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 - 8mm ± 0.20mm 8 - 30mm ± 0.40mm 30 - 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 - .315 = ± 0.007" .315 - 1.180 = ± 0.015" 1.180 - 4.724 = ± 0.020" DO NOT SCALE DRAWING	APPROVALS		DATE		Amphenol Connex									
8						DRAWN	GRS	12/28/08										
7						CHECKED												
6						ISSUED				PART DESCRIPTION 7/16 STRAIGHT PLUG (FOR LMR400, BELDEN 9913 CABLE)								
5						SHEET		1 OF 1										
4	FERRULE	COPPER	NEXCOTE		1	CAD FILE		C:/272/272107.DWG		DWG. NO.		272107.DWG	REV.	E	SIZE	A	SCALE	NA
3	CONTACT PIN	BRASS	SILVER		1					PART NO.		272107						
2	INSULATOR	PTFE	NATURAL		1													
1	BODY	BRASS	NEXCOTE	1														
	DESCRIPTION	MATERIAL	FINISH	QTY														

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[272107](#)