



REVISIONS				
SYM	ZONE	ECN, ERN NO.	DATE	APPRD.
A		PROPOSAL	05/11/09	LCHAN



MATERIALS:

HOUSING:

HIGH TEMPERATURE THERMOPLASTIC
FLAMMABILITY RATING UL94V-0

CONTACTS:

PHOSPHOR BRONZE
PLATING AS FOLLOW: REFER TO PART NUMBER FOR GOLD
THICKNESS ON MATING SURFACES.
50 u" [1.27 MICRONS] MIN. NICKEL UNDERPLATE.
100 u" [2.54 MICRONS] MIN. MATTE TIN OR GOLD FLASH ON
CONTACT TAILS.

SHIELD:

COPPER ALLOY.
PLATING: NICKEL OVER COPPER UNDERPLATE.

PART NO.: RJE15-188-1X10

GOLD PLATING

- 1 = 6 u INCH
- 2 = 15 u INCH
- 3 = 30 u INCH
- 4 = 50 u INCH

DRAWN Chigow	DATE 05/11/09	Amphenol Canada Corp.		
DESIGNED				
CHECKED PAULW	05/11/09	TITLE SURFACE MOUNT MODULAR JACK 8 POSITION, 8 CONTACTS, SHIELDED -RoHS COMPLIANT		
I. E. APPRD.				
Q. A. APPRD.		DWG. DRAWING NO. P-RJE15-188-1X10		
DWG. APPRD.				
ENG. REL. NO.		REF. REV. A		
DIMENSIONS ARE IN INCHES [mm]	CODE ID. NO. 03554			
SCALE	WT. -----	SURF. -----	SHEET 1 OF 1	

THIS DOCUMENT CONTAINS PROPRIETARY INFORMATION AND SUCH INFORMATION
MAY NOT BE DISCLOSED TO OTHERS FOR ANY PURPOSE OR USED FOR MANUFACTURING
PURPOSES WITHOUT WRITTEN PERMISSION FROM AMPHENOL CANADA CORP.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[RJE151881110](#) [RJE151881210](#) [RJE151881310](#)