





SECTION A-A

N = Number of poles
Dim A = N x 5.0 + 3.0
Dim B = N x 5.0 + 3.2
Dim C = N x 5.0 + 8.8
Dim D = N x 5.0 + 14.8
Dim E = (N - 1) x 5.0

	Dim A	Dim B	Dim C	Dim D	Dim E
2-6p	±0.20	±0.20	±0.20	±0.20	±0.20
7-12p	±0.25	±0.25	±0.25	±0.25	±0.25
13-18p	±0.30	±0.30	±0.30	±0.30	±0.30
19-24p	±0.40	±0.40	±0.40	±0.40	±0.40

SIGN	DATE	DESCRIPTION	APPROVER
⚠	2009.09.19	The description in drawing is revised	Jacke
⚠	2010.04.22	Add "cULus" Safety Approval	Runner
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!			

Material:

- Item a :Terminal body Thermoplastic (UL94 V-0)
- Item b :Terminal body Thermoplastic (UL94 V-0)
- Item c :Male contact pin: Brass Tin plated
- Item d :Spring clamp: Stainless steel

Electrical cULus

- Voltage rating: 300V
- Current rating: 8A
- Wire range:
- Solid wire(AWG): 12-28
- Stranded wire(AWG): 12-28
- Wire strip length: 8-9mm
- Withstanding Voltage: 1.6KV
- Operating temperature: -40°C to +115°C
- ⚠ ● Safety Approval: cULus

NB xx 7 0 x 1 xxxx G

- 02 2 poles
03 3 poles
...
24 24 poles
- 0 Black
5 Green (RAL6018/T)
6 Blue
8 Grey (RAL7035/D)
- RoHS
Pb<40,000ppm
0000 Standard @ Logo
000A Standard ANY Logo
Any special item by customer request, please contact sales department.

ANYTEK

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATSOEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

CUSTOMER COPY

TITLE		NB 5.0mm series W/F	
PART NO.	NBxx70x1xxxxG	DWG NO.	8NB0002
APPROVED	CHECKED	DESIGNED	DRAWN
		Runner	Jacke
		2010.04.22	2009.09.19
SHEET: 01/01		REV.: D	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Amphenol:

<u>NB0270810000G</u>	<u>NB0370810000G</u>	<u>NB0470810000G</u>	<u>NB0570810000G</u>	<u>NB0670810000G</u>	<u>NB0770810000G</u>
<u>NB0870810000G</u>	<u>NB0970810000G</u>	<u>NB1070810000G</u>	<u>NB1170810000G</u>	<u>NB1270810000G</u>	<u>NB1370810000G</u>
<u>NB1470810000G</u>	<u>NB1570810000G</u>	<u>NB1670810000G</u>	<u>NB1770810000G</u>	<u>NB1870810000G</u>	<u>NB1970810000G</u>
<u>NB2070810000G</u>	<u>NB2170810000G</u>	<u>NB2270810000G</u>	<u>NB2370810000G</u>	<u>NB2470810000G</u>	