




REV	ECN	APP'D
—	4577	



NOTES:

1. MATERIALS:
A) HOUSING — POLYETHERIMIDE, COLOR: BLACK
B) GROMMET — SILICONE ELASTOMER, COLOR: BLUE
2. FIVE PIN CONTACTS IN ACCORDANCE WITH M39029/1-101 ARE INCLUDED.
3. WIRE SPLICE ASSEMBLY SHALL MEET APPLICABLE REQUIREMENTS OF MIL-T-81714, CLASS D.
4. TOTAL WEIGHT — 4.5 grams MAX.
5. RESISTOR—18K Ω 1W—AND JUMPER AFFIXED TO INTERNAL CONTACTS VIA SOLDER JOINT PER MIL-S-45743.

DIMENSIONS ANSI Y14.5M UNITS: INCHES ACAD FILE	TOLERANCES .XX ±.01 .XXX ±.005 ANGLES ±2°	PROJECTION 	<div><i>SPECIFICATION DRAWING</i></div> <div>ENGR A. PATRIE 6/26/01</div>		<div></div> <div>TITLE WIRE SPLICE, ELECTRONIC RESISTOR, 18KΩ, 1W SIZE 20</div>	
ORIGINAL	THIS DOCUMENT CONTAINS PROPRIETARY INFORMATION WHICH IS THE CONFIDENTIAL PROPERTY OF PCD, INC. PEABODY, MA, USA		<div>CHKD</div> <div>APPD</div>		<div><div>SIZE A</div><div>DWG NO. TJSE20554</div></div> <div>CODE: 58982 SCALE: 2X SHEET 1 OF 1</div> <div>REV —</div>	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[TJSE20554](#)