

#### DIMENSION

Dim L	Nx5.0
Dim B	(N-1)x5.0

N=Number of contacts

Poles	B Tolerance	L Tolerance
4pole~6pole	±0.15	±0.15
7pole~12pole	±0.25	±0.25
13pole~18pole	±0.35	±0.35
19pole~24pole	±0.40	±0.40

SIGN	DATE	DESCRIPTION	APPROVER
△			
△			
△			
△			

#### Material:

- Item 1 Terminal housing:Thermoplastic (UL 94V-0)
- Item 2 Clamp: Brass ,Ni plated
- Item 3 Wire guard solder pin: Brass ,Tin plated
- Item 4 Terminal screw: Steel , Zinc plating"-slot type

#### Electrical

- Voltage rating: 300VAC
- Current rating: 10A
- Wire range:
- Solid wire(AWG): 12-24
- Stranded wire(AWG): 12-24
- Torque(Lb-In): 3.5
- Screw: M2.5
- Wire strip length: 6-7mm
- Withstanding Voltage: 1.6KV
- Operating temperature: -40°C to +115°C
- Soldering temperature: 250°C±10°C/5 Sec


YE xx 01 x 1 xxxx G

04 4 CONTACTS	0 Black	0000:"@Logo (Standard )	Pb < 40,000ppm (RoHS)
05 5 CONTACTS	5 Green	000A:"ANYTEK"Logo	
... ..	6 Blue	Any special item by customer request,	
24 24 CONTACTS	8 Grey	please contact sales department.	

# ANYTEK

## CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATSOEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE		YE-5.0mm Series 4P-24P ( Solid block )					
PART NO.		YExx01x1xxxxG		DWG NO.		8YE0007	
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.		Tolerance	
		Aaron 2009.10.07	Aaron 2009.10.07			UNIT: mm	X. ±0.50
				SHEET: 01/01		SCALE: NONE	X.X ±0.30
				REV.: B			X.XX ±0.10
							X° ±1°

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

## Amphenol:

<a href="#"><u>YE0401510000G</u></a>	<a href="#"><u>YE0501510000G</u></a>	<a href="#"><u>YE0601510000G</u></a>	<a href="#"><u>YE0701510000G</u></a>	<a href="#"><u>YE0801510000G</u></a>	<a href="#"><u>YE0901510000G</u></a>
<a href="#"><u>YE1001510000G</u></a>	<a href="#"><u>YE1101510000G</u></a>	<a href="#"><u>YE1201510000G</u></a>	<a href="#"><u>YE1301510000G</u></a>	<a href="#"><u>YE1401510000G</u></a>	<a href="#"><u>YE1501510000G</u></a>
<a href="#"><u>YE1601510000G</u></a>	<a href="#"><u>YE1701510000G</u></a>	<a href="#"><u>YE1801510000G</u></a>	<a href="#"><u>YE1901510000G</u></a>	<a href="#"><u>YE2001510000G</u></a>	<a href="#"><u>YE2101510000G</u></a>
<a href="#"><u>YE2201510000G</u></a>	<a href="#"><u>YE2301510000G</u></a>	<a href="#"><u>YE2401510000G</u></a>			