






Dimension A&B&C

DIM A	$N \times 11.0 \pm 0.2$
DIM B	$(N-1) \times 11.0$
DIM C	$(N+1) \times 11.1$

N=Number of contacts

Poles	A&B Tolerance
2P-8P	± 0.20
9P-14P	± 0.30
15P-20P	± 0.40
21P-24P	± 0.50
25P-30P	± 0.60

SIGN	DATE	DESCRIPTION	APPROVER
△	2/07'06	Part No. changed	Tony
△	10/23'06	Added demention 16.60 and 13.10	Steady
△	5/20'09	Voltage & Current changed from DC 24V,30A to 300V,20A	Eris
△	5/20'09	Temperature changed from -40°C-105°C to -40°C-115°C	Eris
△	5/20'09	Screw torque value changed from 10Kgf.cm to 11lb-In	Eris
△	5/20'09	Add approval "CULUS"	Eris
△	01/12'10	The Dimension is changed from : $N \times 11.0 \pm 0.6$ to $N \times 11.0 \pm 0.2$	Seamus
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!			

MATERIALS ELECTRICAL

- △ RATED VOLTAGE & CURRENT: 300 V, 20 A
- WITHSTAND VOLTAGE: AC 2000 V/Min
- INSULATION RESISTANCE: 1000 MΩ OR MORE AT DC 500 V
- △ OPERATING TEMPERATURE RANG: -40 °C ~ +115°C
- △ SCREW TORQUE VALUE: 11lb-In
- WIRE RANGE: 22-12 AWG
- 1) MOLDED PARTS: Thermoplastic (UL 94 V-0)
- 2) TERMINAL: BRASS, 1.2t, Tin PLATED
- 3) TERMINAL SCREWS: STEEL, Ni PLATED, M4

△ APPROVAL:

△ PART NO.:

YK 114 xx 3 x x 00G

NO. OF POLES
02: 2 POLES
03: 3 POLES
04: 4 POLES
:
30: 30 POLES

G: Pb<40000 ppm

MARK
0: "@" MARK
1: "ANY" MARK

TERMINAL & SCREW PLATED

0: TERMINAL & SCREW: G/F
1: TERMINAL: G/F, SCREW: Ni
2: TERMINAL: Sn, SCREW: G/F
3: TERMINAL: Sn, SCREW: Ni

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATSOEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE		YK-114 FINISHED PRODUCTS						
PART NO.		YK114xx3xx00G			DWG NO.		8YK0001-114	
APPROVED		CHECKED	DESIGNED	DRAWN	CUST NO.			
		Seamus 2010.01.12	Seamus 2010.01.12	Aaron 2009.12.14			Tolerance	
							X.	±0.50
					UNIT: mm		X.X	±0.30
					SCALE: NONE		X.XX	±0.10
SHEET: 01/01		REV.: F				X°	±1°	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Amphenol:

<u>YK1140233000G</u>	<u>YK1140333000G</u>	<u>YK1140433000G</u>	<u>YK1140533000G</u>	<u>YK1140633000G</u>	<u>YK1140733000G</u>
<u>YK1140833000G</u>	<u>YK1140933000G</u>	<u>YK1141033000G</u>	<u>YK1141133000G</u>	<u>YK1141233000G</u>	<u>YK1141333000G</u>
<u>YK1141433000G</u>	<u>YK1141533000G</u>	<u>YK1141633000G</u>	<u>YK1141733000G</u>	<u>YK1141833000G</u>	<u>YK1141933000G</u>
<u>YK1142033000G</u>	<u>YK1142133000G</u>	<u>YK1142233000G</u>	<u>YK1142333000G</u>	<u>YK1142433000G</u>	<u>YK1142533000G</u>
<u>YK1142633000G</u>	<u>YK1142733000G</u>	<u>YK1142833000G</u>	<u>YK1142933000G</u>	<u>YK1143033000G</u>	