

PRODUCT DATA DRAWING

REVISION HISTORY			
REV	DESCRIPTION	DATE	APPROVED
B	REV. DCN 32852	03/05	VMJ

MATERIALS:


- INSULATORS:PTFE PER ASTM D1710, TYPE 1,
GRADE 1, CLASS B.
- SLEEVE:STAINLESS STEEL PER AMS-5640,
ALLOY UNS S30300, TYPE 303, COND. A
- BODY &
CONTACT:BERYLLIUM COPPER PER ASTM B196,
ALLOY C17300, COND. TD04
- SHRINK TUBING: POLYOLEFIN PER SAE AMS-DTL-23053/5-105-0

FINISHES:


- BODIES &
CONTACT:GOLD PER ASTM B488, TYPE II,
GRADE C, CLASS 1.27 OVER NICKEL
PER AMS-QQ-N-290 CLASS 1, .00005" MIN.

ELECTRICAL:

- IMPEDANCE:50 OHMS
- FREQ. RANGE:DC TO 3 GHz
- INSUL. RES.:5,000 MEGOHMS MIN.
- D.W.V:1,000 VRMS MIN.
- VSWR:1.20 + .04 X F IN GHz
- INSERTION LOSS: .11 X SQUARE ROOT OF F(GHz)
- (MAX FREQ. CAN BE LIMITED BY CABLE)



REF. AS39029/103 &
MIL-DTL-38999 SERIES III

MATERIAL:	SEE ABOVE	DIMENSIONS ARE IN INCHES TOLERANCES: FRACTIONAL: $\pm 1/64$ ANGULAR: X° $\pm 1'0''$ X'X' $\pm 15'$ DECIMAL: .X $\pm .030$.XX $\pm .010$.XXX $\pm .005$ INTERPRET DIMENSIONS AND TOLERANCES PER ASME Y14.5M - 1994	UNLESS OTHERWISE SPECIFIED 1) ALL DIMENSIONS ARE AFTER PLATING. 2) BREAK CORNERS & EDGES .005 R. MAX. 3) CHAM. 1ST & LAST THREADS. 4) SURFACE ROUGHNESS 63 $\sqrt{\text{MIL-STD-10}}$. 5) DIA.'S ON COMMON CENTERS TO BE CONCENTRIC WITHIN .005 T.I.R. 6) REMOVE ALL BURRS		SV Microwave, Inc. 2400 Centrepark West Drive, Suite 100 West Palm Beach, FL 33409	
FINISH:	SEE ABOVE					
PROPRIETARY THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF SV MICROWAVE, INC. ANY REPRODUCTION IN PART OR AS A WHOLE WITHOUT THE WRITTEN PERMISSION OF SV MICROWAVE, INC IS PROHIBITED.						
		DRAWN: VMJ 11/30/04		TITLE: SIZE 12 SOCKET FOR T-FLEX 405 CABLE		
		CHECKED: JMC 11/30/04				
APPROVED: JMC 11/30/04						
THIRD ANGLE PROJECTION		E.M. SIMULATION: N/A		SIZE B	CAGE CODE 95077	DWG. NO. 8001-4104
				SCALE: 8:1		SHEET 1 OF 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[8001-4104](#)