





SIGN	DATE	DESCRIPTION	APPROVER
△	04/28'11	Add is cULus	Aaron
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!			



- Material:
- Item a Terminal(housing): Thermoplastic (UL94V-0)
 - Item b Terminal(cover): Thermoplastic (UL94V-0)
 - Item c Male contact pin : Copper Tin plated

- Electrical:
- Voltage rating: 300V
 - Current rating: 12A
 - Withstanding Voltage: 1.6KV
 - Operating temperature: -40°C to +115°C
 - Soldering temperature: 250°C±10°C/5 Sec
 - △ ● Safety Approval: 



KE xx 7 3 x 2 xxxx G

- No. OF POLES
- 04: 2x2 POLES
 - 06: 2x3 POLES
 - ...
 - 48: 2x24 POLES
- COLOR
- 0 Black (RAL9005)
 - 2 Red (RAL3001/D)
 - 3 Orange(RAL2011/P)
 - 4 Yellow(RAL1018/A)
 - 5 Green(RAL6018/T)
 - 6 Blue (RAL5015/A)
 - 8 Grey(RAL7035/D)
 - 9 White(RAL1102)
 - C Green(RAL6018/U)
- G: Pb<40000ppm
- 0000: "@" Logo (Standard)
- 000A: "ANYTEK" Mark
- Any special item by customer request, please contact sales department.

N = Number of poles
Dim L=Nx5.0+2.8
Dim P=(N-1)x5.0

Poles	Dim L	Dim P
2x2-2x6p	±0.15	±0.15
2x7-2x12p	±0.25	±0.25
2x13-2x18p	±0.35	±0.35
2x19-2x24p	±0.40	±0.40

ANYTEK				CUSTOMER COPY				
				ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD				
TITLE	KE 5.0mm With latch holder Series (Vertical) DIP type							
PART NO.	KExx73x2xxxxG			DWG NO.	8KE0106			
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.		Tolerance		
		Jacke 2010.03.30	Jacke 2009.08.26		UNIT: mm	X.	±0.50	
					SCALE: NONE	X.X	±0.30	
					SHEET: 01/01	REV.: B	X.XX	±0.10
							X°	±1°

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Amphenol:

<u>KE0473520000G</u>	<u>KE0673520000G</u>	<u>KE0873520000G</u>	<u>KE1073520000G</u>	<u>KE1273520000G</u>	<u>KE1473520000G</u>
<u>KE1673520000G</u>	<u>KE1873520000G</u>	<u>KE2073520000G</u>	<u>KE2273520000G</u>	<u>KE2473520000G</u>	<u>KE2673520000G</u>
<u>KE2873520000G</u>	<u>KE3073520000G</u>	<u>KE3273520000G</u>	<u>KE3473520000G</u>	<u>KE3673520000G</u>	<u>KE3873520000G</u>
<u>KE4073520000G</u>	<u>KE4273520000G</u>	<u>KE4473520000G</u>	<u>KE4673520000G</u>	<u>KE4873520000G</u>	