


D see data sheet cable

Technical specification :

Rated voltage: IEC 61076-2-104	60 V
Current rating: IEC 61076-2-104	3 A at 40°C
Insulation resistance: IEC 60512	>=100 MΩ
Pollution degree: IEC 60664-1	3/2
Degree of protection: IEC 60529	IP 67, in mated condition
Temperature range: IEC 60664-1	-30°C ... +80°C
Mating cycles: IEC 60512-9a	>=100

Materials:

Contact:	CuZn
Contact plating:	Nickel, gold plated
Contact carrier:	TPU GF, UL 94
Coupling screw:	GD-Zn, nickel plated
Moulding body:	TPU, UL 94, grey


Installation specification:

Recommended torque:	0,4 Nm
Conec installation tool:	Torque wrench: 36-000200 Insert across flats 9: 36-000210

Contact assignment:

1	— brown
3	— blue
4	— black

Part no:	Description:	Length L:	Cable:
42-10028	SAL - 8 - RSW3 - 2 / K1	2m	TPU, UL 20549, black, 3x0,25mm ² Cable: 781-K12300
42-10029	SAL - 8 - RSW3 - 3 / K1	3m	
42-10030	SAL - 8 - RSW3 - 5 / K1	5m	
42-10031	SAL - 8 - RSW3 - 10 / K1	10m	
42-xxxxx	SAL - 8 - RSW3 - ... / K1	x	

DO NOT ALTER CAD DRAWING BY HAND Directive 2002/95/EC RoHS compliant	Index: b 16.03.11 VF Ä3945 Coupling screw modified, spanner flats added, data sheet modified		 dim. in mm		title: Male connector M8x1 angled	
			date	name		
	tolerance of cable:	L <= 4m: L + 40mm L > 4m: L + 1%	drawn	04.10.07	Franz	dwg no:
			appd.	04.10.07	Mankopf	
	general tolerance:	0 ± 0,50mm 0,0 ± 0,25mm 0,00 ± 0,10mm				42K1A008
THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH		part no:				see table

dwg no:

42K1A008

part no:

see table

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[42-10030](#) [42-10031](#) [42-10028](#) [42-10029](#)