


D-Subminiature connectors




smaller version:
connector with metal bracket flush


•370 inch

Solder pin angled
with threaded insert
and metal bracket

Socket connector



Plug connector



Kat 1 i K2A

No. of pos.	A - 0,76	B - 0,25	C
9	31,19	16,46	25,00 ^{+0,12} _{-0,13}
15	39,52	24,79	33,30 ^{+0,15} _{-0,16}
25	53,42	38,50	47,04 ^{+0,13} _{-0,14}
37	69,70	54,96	63,50 ^{+0,13} _{-0,14}

Kat 1 i K3A

No. of pos.	A - 0,76	B - 0,25	C	D - 0,30
9	31,19	16,79	25,00 ^{+0,12} _{-0,13}	6,12
15	39,52	25,12	33,30 ^{+0,15} _{-0,16}	6,12
25	53,42	38,84	47,04 ^{+0,13} _{-0,14}	5,99
37	69,70	55,30	63,50 ^{+0,13} _{-0,14}	5,99


Part numbers

No. of Pos.	Socket connector tin-plated – solder pin angled	
	UNC 4-40	M 3
9	CDF 09 ABWMKUNSN 164 A 13339 X	CDF 09 ABWMKMSN 164 A 13389 X
15	CDF 15 ABWMKUNSN 164 A 13349 X	CDF 15 ABWMKMSN 164 A 13399 X
25	CDF 25 ABWMKUNSN 164 A 13359 X	CDF 25 ABWMKMSN 164 A 13409 X
37	CDF 37 ABWMKUNSN 164 A 13369 X	CDF 37 ABWMKMSN 164 A 13419 X

No. of Pos.	Plug connector tin-plated with ground indent – solder pin angled	
	UNC 4-40	M 3
9	CDS 09 AFBWMKUNSN 163 A 14859 X	CDS 09 AFBWMKMSN 163 A 14909 X
15	CDS 15 AFBWMKUNSN 163 A 14869 X	CDS 15 AFBWMKMSN 163 A 14919 X
25	CDS 25 AFBWMKUNSN 163 A 14879 X	CDS 25 AFBWMKMSN 163 A 14929 X
37	CDS 37 AFBWMKUNSN 163 A 14889 X	CDS 37 AFBWMKMSN 163 A 14939 X



Part Number




Order example

Plug connector Solder bucket 25 pos. without printing			
Quality class		Part Number	
3		CDS 25 L	161 A 10039 X
2		CDS 25 L	161 B 10039 X
1		CDS 25 L	161 C 10039 X


D-Subminiature connectors

Hole pattern for straight and angled solder pins D-Sub standard


9 pos




37 pos




15 pos



25 pos



50 pos



Kat 1 i U3A

Kat 1 i U4A

Technical Data	D-Sub Standard	D-Sub High Density
Initial contact resistance	≤ 10 mΩ	≤ 10 mΩ
Initial insulation resistance	Quality class 1 ≥ 5GΩ Quality class 2 ≥ 5GΩ Quality class 3 ≥ 5GΩ	Quality class 1 ≥ 5GΩ Quality class 2 ≥ 5GΩ Quality class 3 ≥ 5GΩ
Clearance distance	contact–contact ≥ 1.0 mm contact–ground ≥ 1.2 mm	≥ 0.6 mm
Creepage distance	contact–contact ≥ 1.0 mm contact–ground ≥ 1.2 mm	≥ 0.6 mm
Test voltage V. r. m. s./NM	1000 V	1000 V
Working voltage/Insulation group* * nach SEV 50 V – acc. to SEV 50 V	125 V ≈	60 V ≈
Working current 20° C	5 A max.	25 A max.
Operating temperature	- 55° C – + 125° C	- 55° C – + 125° C
Moulding material	Polyester GF UL 94 V-O	PA 6.6 GF 25 UL 94 V-O
Contact material	Copper alloy	Copper alloy
Contact finish	hard-gold-plated over nickel	hard-gold-plated over nickel
Shell	Sheet steel, zinc lined and yellow chromate Sheet steel, nickel underneath and tin-plated	Sheet steel, nickel underneath and tin-plated
Insertion and withdrawal froces	9-polig/way 30 N 15-polig/way 50 N 25-polig/way 83 N 37-polig/way 123 N 50-polig/way 167 N	15-polig/way 50 N 26-polig/way 84 N 44-polig/way 120 N 62-polig/way 170 N 78-polig/way 200 N
Quality classes	Quality class 1 Quality class 2 Quality class 3	500 mating cycles 200 mating cycles 50 mating cycles

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[164A13349X](#) [164A13339X](#) [164A13369X](#) [163A14879X](#) [163A14869X](#) [163A14859X](#) [163A14889X](#)