



RECEPTACLE, 3 PIN, AT SERIES, W/FLANGE, GASKET

AT04-3P-PM05

23

MOUNTING PLATE SIZE





NOTES: UNLESS OTHERWISE SPECIFIED

1. MATERIAL:

HOUSING: THERMOPLASTIC; COLOR: GRAY SEAL: SILICONE RUBBER

2. MODIFICATIONS: FLANGE

3. SPECIFICATIONS:

3.1 CURRENT RATING: 13 AMPS

3.2 OPERATING TEMPERATURE: -55°C TO +125°C

3.3 DIELECTRIC WITHSTANDING VOLTAGE: LESS THAN 2 MILLIAMPS CURRENT LEAKAGE @ 1500 VOLTS AC.

3.4 INSULATION RESISTANCE: 1000 MEGOHMS MIN @ 25°C.


3.5 MOISTURE RESISTANCE: IP67 (MATED CONDITION)

3.6 MATING CYCLE DURABILITY: 100 CYCLES

3.7 RoHS COMPLIANT

4. MATING PART: AT06-S* PLUG (* = MODIFICATIONS)

5. ALL DIMENSIONS ARE FOR REFERENCE USE ONLY.



/ 6		CONTACT	SIZE AND	REAR	SEAL	WIRE R	RANGE:
------------	--	---------	----------	------	------	--------	--------

CONTACT	MIN. INSUL	MAX. INSUL	TYPICAL		
SIZE	O.D.	O.D.	WIRE RANGE		
16	2.24 mm (.088 in)	14 - 20 AWG			

AT04-3P-PM05 SECRIPTION STEM JANTITY MATERIALS LIST

	PARIN	IOMBER					
QUANTITY		ı	MATERIALS				
UNLESS OTHERWISE SPECIFIED		SIGN	IATURE	s	DATE		
All dimensions a Tolerances are a PL DEC ±0.30	as follows: Fractions ±1/64 Angles ±1°	DRAWN:	ORION.LI	1	1FEB14		
2 PL DEC ±0.15 3 PL DEC ±0.08		CHECKED:					
3) Note reference		ENGINEER:					
MATERIAL SPECIFICA	TIONS:	APPROVAL:					
PROCESS SPECIFICATIONS:		CUSTOMER:					
		THIS DRAWING IS SUPPLIED FOR INFORMATION ONLY. DESIGN FEATURES,					
		SPECIFICATIONS AND PERFORMANCE DATA SHOWN HEREON ARE THE PROPERTY OF THE AMPHENOL CORPORATION. NO RIGHTS OF REPRODUCTION ARE IMPLIED. ALL DIMENSIONS ARE SUBJECT TO NORMAL			B	T	
NEXT ASS'Y:		MANUFACTURING VARIATIONS.			SCALE: N	$\overline{}$	

Amphenol

Sine Systems - www.amphenol-sine.com 44724 Morley Drive Clinton Township, MI 48036

RECEPTACLE, 3 PIN, AT SERIES, W/FLANGE, GASKET

AT04-3P-PM05 AT04-

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Amphenol:
AT04-3P-PM05