


SIGN	DATE	DESCRIPTION	APPROVER
△			
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!			



PCB Layout

Material:

- Item ② Terminal(housing): PA66 30% GF (UL94V-0)
- Item ⑤ Contact pin of short: copper Tin plated
- Item ⑦ Contact pin of long: copper Tin plated
- Item ⑩ Contact pin of best long: copper Tin plated

Electrical:

- Voltage rating: 160V
- Current rating: 5.5A
- Withstanding Voltage: 1.32 KV
- Operating temperature: -40°C to +115°C
- Soldering temperature: 250°C ±10°C/5 Sec
- APPROVAL:

K3 xx 1 3 x 1 xxxx G

No. OF POLES

06: 3x2 POLES

09: 3x3 POLES

...

...

72: 3x24 POLES

COLOR

- 0 Black (RAL9005)
- 3 Orange(RAL2011/P)
- 5 Green(RAL6018/T)
- 6 Blue (RAL5015/A)
- 8 Grey(RAL7035/D)

G: Pb<40000ppm

A000: "@ Logo (Standard)

△ A00A: "ANYTEK" Mark


Any special item by customer request. please contact sales department.


POLE		3x2	3x3	3x4	3x5	3x6	3x7	3x8	3x9	3x10	3x11	3x12
A		7.90	11.40	14.90	18.40	21.90	25.40	28.90	32.40	35.90	39.40	42.90
B		3.50	7.00	10.50	14.00	17.50	21.00	24.50	28.00	31.50	35.00	38.50
Tol.		±0.15					±0.20					
POLE	3x13	3x14	3x15	3x16	3x17	3x18	3x19	3x20	3x21	3x22	3x23	3x24
A	46.40	49.90	53.40	56.90	60.40	63.90	67.40	70.90	74.40	77.90	81.40	84.90
B	42.00	45.50	49.00	52.50	56.00	59.50	63.00	66.50	70.00	73.50	77.00	80.50
Tol.		±0.25					±0.30					

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE	K3 3.5mm With latch Series (90°-Right angle) DIP type										
PART NO.	K3xx13x10000G				DWG NO.	8K30009					
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.						Tolerance	
		Runner 2010.09.18	Runner 2010.06.28							UNIT: mm	
					SCALE: NONE		X.X	±0.30			
							X.XX	±0.10			
					SHEET: 01/01		X°	±1°			



SHEET: 01/01

REV.: A2

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Amphenol:

<u>K3061351A000G</u>	<u>K3091351A000G</u>	<u>K3121351A000G</u>	<u>K3151351A000G</u>	<u>K3181351A000G</u>	<u>K3211351A000G</u>
<u>K3241351A000G</u>	<u>K3271351A000G</u>	<u>K3301351A000G</u>	<u>K3331351A000G</u>	<u>K3361351A000G</u>	<u>K3391351A000G</u>
<u>K3421351A000G</u>	<u>K3451351A000G</u>	<u>K3481351A000G</u>	<u>K3511351A000G</u>	<u>K3541351A000G</u>	<u>K3571351A000G</u>
<u>K3601351A000G</u>	<u>K3631351A000G</u>	<u>K3661351A000G</u>	<u>K3691351A000G</u>	<u>K3721351A000G</u>	