





| SIGN                                           | DATE       | DESCRIPTION                           | APPROVER |
|------------------------------------------------|------------|---------------------------------------|----------|
| △                                              | 2009.09.19 | The description in drawing is revised | Jacke    |
| THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!! |            |                                       |          |



SECTION A-A

Material:

- Item a Terminal lever: Thermoplastic (UL94 V-0)
- Item b Terminal body: Thermoplastic (UL94 V-0)
- Item c Terminal cover: Thermoplastic (UL94 V-0)
- Item d Terminal pad: Thermoplastic (UL94 V-0)
- Item e Solder pin: Brass Tin plated
- Item f Spring clamp: Stainless steel

Electrical cULus

- Voltage rating: 300V
- Current rating: 10A
- Solid wire(AWG): 16-20
- Wire strip length: 7-8mm
- Withstanding Voltage: 1.6KV
- Operating temperature: -40°C to +115°C
- Soldering temperature: 250°C±10°C/5 Sec
- Safety Approval: cULus

NE xx 2 0 x 0 xxxx G

- 01 1 pole
- 02 2 poles
- 03 3 poles
- ... ..
- 16 16 poles

- 0 Black any special item by customer request, please contact sales department.
- 5 Green
- 6 Blue
- 8 Grey

N = Number of poles

Dim L=Nx7.5-1.0

Dim P=(N-1)x7.5

|        | Dim L | Dim P |
|--------|-------|-------|
| 1-6p   | ±0.20 | ±0.20 |
| 7-12p  | ±0.30 | ±0.25 |
| 13-16p | ±0.35 | ±0.30 |

△

**ANYTEK**

**CUSTOMER COPY**

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATSOEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

|          |                 |                     |                     |                                                                                       |                                                                                                       |
|----------|-----------------|---------------------|---------------------|---------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------------------------|
| TITLE    | NE 7.5mm series |                     |                     |                                                                                       |                                                                                                       |
| PART NO. | NExx20x0xxxxG   |                     |                     | DWG NO.                                                                               | 8NE0101                                                                                               |
| APPROVED | CHECKED         | DESIGNED            | DRAWN               | CUST NO.                                                                              |                                                                                                       |
|          |                 | Jacke<br>2009.09.19 | Jacke<br>2009.09.19 |  | <div>UNIT: mm</div> <div>SCALE: 4/1</div> <div>REV: C</div>                                           |
|          |                 |                     |                     |                                                                                       | <div>Tolerance</div> <div>X. ±0.50</div> <div>X.X ±0.30</div> <div>X.XX ±0.10</div> <div>X° ±1°</div> |

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

## Amphenol:

[NE0220800000G](#) [NE0320800000G](#) [NE0420800000G](#) [NE0520800000G](#) [NE0620800000G](#) [NE0720800000G](#)  
[NE0820800000G](#) [NE0920800000G](#) [NE1020800000G](#) [NE1120800000G](#) [NE1220800000G](#) [NE1320800000G](#)  
[NE1420800000G](#) [NE1520800000G](#) [NE1620800000G](#)