

1	2	3	4	5	6	7																																																																																																																																													
				<table><tr><td>SIGN</td><td>DATE</td><td>DESCRIPTION</td><td>APPROVER</td></tr><tr><td>△</td><td></td><td colspan="2"></td></tr><tr><td colspan="4">THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!</td></tr></table>			SIGN	DATE	DESCRIPTION	APPROVER	△				THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!																																																																																																																																				
SIGN	DATE	DESCRIPTION	APPROVER																																																																																																																																																
△																																																																																																																																																			
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!																																																																																																																																																			
E					Material: - Terminal body (metal housing): Brass(CuZn) - Terminal screw: Steel Plated Zinc "- " slot type. - Wire guard: Stainless steel - Surface of solder tail: Tin plated - Insulator(housing): Thermoplastic (UL94V-0)																																																																																																																																														
D					Electrical: UL - Voltage rating: 125V - Current rating: 10A - Wire range: - Solid wire(AWG): 16-26 - Stranded wire(AWG): 16-26 - Torque: 1.7Lb-In - Screw: M2 - Wire strip length: 5-6mm - Withstanding Voltage: 1.25 KV - Operating temperature: -40°C to +115°C - Soldering temperature: 250°C±10°C/5 Sec - Safety Approval:																																																																																																																																														
C					TE xx 0 1 x x xxxx G No. OF POLES ———— 04: 4 POLES ———— Color ———— 24: 24POLES ———— 0 Black (RAL9005) 2 Red (RAL3001/D) 3 Orange(RAL2011/P) 4 Yellow(RAL1018/A) 5 Green(RAL6018/T) 6 Blue (RAL5015/A) 8 Grey(RAL7035/D) DIM A ———— 3: 4.4mm 4: 3.8mm 5: 3.5mm G: Pb<40000ppm 0000: "@ " Logo (Standard) 000A: "ANYTEK" Mark Any special item by customer request. please contact sales department.																																																																																																																																														
B																																																																																																																																																			
A	<table><tr><td>POLE</td><td></td><td></td><td>4</td><td>5</td><td>6</td><td>7</td><td>8</td><td>9</td><td>10</td><td>11</td><td>12</td></tr><tr><td>A</td><td></td><td></td><td>14.00</td><td>17.50</td><td>21.00</td><td>24.50</td><td>28.00</td><td>31.50</td><td>35.00</td><td>38.50</td><td>42.00</td></tr><tr><td>B</td><td></td><td></td><td>10.50</td><td>14.00</td><td>17.50</td><td>21.00</td><td>24.50</td><td>28.00</td><td>31.50</td><td>35.00</td><td>38.50</td></tr><tr><td>Tol.</td><td colspan="5">±0.10</td><td colspan="6">±0.15</td></tr><tr><td>POLE</td><td>13</td><td>14</td><td>15</td><td>16</td><td>17</td><td>18</td><td>19</td><td>20</td><td>21</td><td>22</td><td>23</td><td>24</td></tr><tr><td>A</td><td>45.50</td><td>49.00</td><td>52.50</td><td>56.00</td><td>59.50</td><td>63.00</td><td>66.50</td><td>70.00</td><td>73.50</td><td>77.00</td><td>80.50</td><td>84.00</td></tr><tr><td>B</td><td>42.00</td><td>45.50</td><td>49.00</td><td>52.50</td><td>56.00</td><td>59.50</td><td>63.00</td><td>66.50</td><td>70.00</td><td>73.50</td><td>77.00</td><td>80.50</td></tr><tr><td>Tol.</td><td colspan="5">±0.20</td><td colspan="7">±0.30</td></tr></table>				POLE			4	5	6	7	8	9	10	11	12	A			14.00	17.50	21.00	24.50	28.00	31.50	35.00	38.50	42.00	B			10.50	14.00	17.50	21.00	24.50	28.00	31.50	35.00	38.50	Tol.	±0.10					±0.15						POLE	13	14	15	16	17	18	19	20	21	22	23	24	A	45.50	49.00	52.50	56.00	59.50	63.00	66.50	70.00	73.50	77.00	80.50	84.00	B	42.00	45.50	49.00	52.50	56.00	59.50	63.00	66.50	70.00	73.50	77.00	80.50	Tol.	±0.20					±0.30							<table><tr><td colspan="2">TITLE</td><td colspan="2">TE 3.5mm Solid block series "- " Screw</td></tr><tr><td>PART NO.</td><td colspan="2">TExx01xxxxxxG</td><td>DWG NO.</td><td colspan="2">8TE0103</td></tr><tr><td>APPROVED</td><td>CHECKED</td><td>DESIGNED</td><td>DRAWN</td><td>CUST NO.</td><td>Tolerance</td></tr><tr><td></td><td></td><td>Runner</td><td>Runner</td><td></td><td>X. ±0.50</td></tr><tr><td></td><td></td><td>2010.03.26</td><td>2010.03.26</td><td></td><td>X.X ±0.30</td></tr><tr><td></td><td></td><td></td><td></td><td></td><td>X.XX ±0.10</td></tr><tr><td></td><td></td><td></td><td></td><td></td><td>X° ±1°</td></tr></table>			TITLE		TE 3.5mm Solid block series "- " Screw		PART NO.	TExx01xxxxxxG		DWG NO.	8TE0103		APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.	Tolerance			Runner	Runner		X. ±0.50			2010.03.26	2010.03.26		X.X ±0.30						X.XX ±0.10						X° ±1°
POLE			4	5	6	7	8	9	10	11	12																																																																																																																																								
A			14.00	17.50	21.00	24.50	28.00	31.50	35.00	38.50	42.00																																																																																																																																								
B			10.50	14.00	17.50	21.00	24.50	28.00	31.50	35.00	38.50																																																																																																																																								
Tol.	±0.10					±0.15																																																																																																																																													
POLE	13	14	15	16	17	18	19	20	21	22	23	24																																																																																																																																							
A	45.50	49.00	52.50	56.00	59.50	63.00	66.50	70.00	73.50	77.00	80.50	84.00																																																																																																																																							
B	42.00	45.50	49.00	52.50	56.00	59.50	63.00	66.50	70.00	73.50	77.00	80.50																																																																																																																																							
Tol.	±0.20					±0.30																																																																																																																																													
TITLE		TE 3.5mm Solid block series "- " Screw																																																																																																																																																	
PART NO.	TExx01xxxxxxG		DWG NO.	8TE0103																																																																																																																																															
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.	Tolerance																																																																																																																																														
		Runner	Runner		X. ±0.50																																																																																																																																														
		2010.03.26	2010.03.26		X.X ±0.30																																																																																																																																														
					X.XX ±0.10																																																																																																																																														
					X° ±1°																																																																																																																																														
1	2	3	4	5	6	7																																																																																																																																													

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Amphenol:

<u>TE0401640000G</u>	<u>TE0501640000G</u>	<u>TE0601640000G</u>	<u>TE0701640000G</u>	<u>TE0801640000G</u>	<u>TE0901640000G</u>
<u>TE1001640000G</u>	<u>TE1101640000G</u>	<u>TE1201640000G</u>	<u>TE1301640000G</u>	<u>TE1401640000G</u>	<u>TE1501640000G</u>
<u>TE1601640000G</u>	<u>TE1701640000G</u>	<u>TE1801640000G</u>	<u>TE1901640000G</u>	<u>TE2001640000G</u>	<u>TE2101640000G</u>
<u>TE2201640000G</u>	<u>TE2301640000G</u>	<u>TE2401640000G</u>	<u>TE0401540000G</u>	<u>TE0501540000G</u>	