


NOTES: UNLESS OTHERWISE SPECIFIED

- 1. MATERIAL: HOUSING: THERMOPLASTIC; COLOR: BLACK SEAL: SILICONE RUBBER
- 2. MODIFICATIONS: REDUCED DIAMETER WIRE SEAL; END CAP
- 3. SPECIFICATIONS:
 - 3.1 CURRENT RATING: SEE NOTE 6
 - 3.2 OPERATING TEMPERATURE: -55°C TO +125°C
 - 3.3 DIELECTRIC WITHSTANDING VOLTAGE: LESS THAN 2 MILLIAMPS CURRENT LEAKAGE @ 1500 VOLTS AC. 3.4 INSULATION RESISTANCE: 1000 MEGOHMS MIN @ 25°C. 3.5 MOISTURE RESISTANCE: IP67 (MATED CONDITION) 3.6 MATING CYCLE DURABILITY: 100 CYCLES 3.7 RoHS COMPLIANT
- 4. MATING PART: AT1612-13SB* PLUG (* = MODIFICATIONS)
- 5. ALL DIMENSIONS ARE FOR REFERENCE USE ONLY.



6 CONTACT SIZE AND REAR SEAL WIRE RANGE:

CONTACT SIZE	MIN. INSUL O.D.	MAX. INSUL O.D.	TYPICAL WIRE RANGE	CURRENT RATING
16	1.35 mm (.053 in)	3.05 mm (.120 in)	14-20 AWG	13 AMPS
12	2.46 mm (.097 in)	4.01 mm (.158 in)	12-14 AWG	25 AMPS

	AT1612-13PB-RDG		
	PART NUMBER		
QUANTITY		M	
UNLESS OTHER	SIGNAT		
 All dimensions Tolerances are PL DEC +0.30 	drawn: D.F		
2 PL DEC ±0.30 3 PL DEC ±0.15 3 PL DEC ±0.08	Fractions ±1/64 Angles ±1°	CHECKED:	
3) Note reference	ENGINEER:		
MATERIAL SPECIFICA	APPROVAL:		
MATERIAL OF LOT 10	CUSTOMER:		
	THIS DRAWING IS		
PROCESS SPECIFICA	INFORMATION ONL SPECIFICATIONS A SHOWN HEREON A THE AMPHENOL CO OF REPRODUCTIO DIMENSIONS ARE S		
NEXT ASS'Y:	MANUFACTURING		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Amphenol:

AT1612-13PB-RD AT1612-13PB AT1612-13PB-RDG