


D-Subminiature High Density Connectors

The new High Density D-Subminiature range is part of Amphenol's I/O-Connector portfolio which provides customers access to a wide range of industry standard and application specific I/O interconnect solutions. Amphenol's I/O connector solutions complete your board and system designs by providing high-density and high-speed interfaces to enable interconnect technologies for networking, storage and memory and complementary products for power distribution. Our range of standardized I/O solutions enables full compliance to industry standards, such as Ethernet, SFF, Infiniband, USB, PCMCIA or HDMI. Amphenol also has the capability to provide customized I/O solutions optimized to address application specific requirements.

Through Amphenol's high-speed, power, assembly and mechanical packaging expertise, you gain the advantage of getting your signals out of the box at optimal cost and performance. Amphenol's I/O connectors – coupled with Amphenol's extensive range of backplane and board-to-board connectors and cable assembly products–enable complete link solutions for your equipment designs.

Amphenol's D-Subminiature connectors are part of an industry standard for applications requiring robust and reliable connectors. These D-Subminiature connectors are one of the most popular Input – Output interconnects, addressing a wide variety of applications in Telecommunications, Data, Consumer, Industrial, Military, Instrumentation and Medical markets. Since many years Amphenol offers a wide range of D-Subminiature connectors to meet all design requirements, and to address increasing needs for high density packaging, Amphenol developed the D-Subminiature High Density Range.



TARGET MARKETS



FEATURES

- High density D-Sub connectors can accommodate more number of contacts in the basic shell sizes
- Selected layouts are also available in Press-fit and Pin-in-Paste versions
- Pin-in-Paste connectors comes in Tape & Reel packaging
- Various PCB and Panel mounting accessory options available
- Hoods available in plastic, metalized and metallic form with locking screws
- Lead-free and RoHS compliant

BENEFITS

- Answer to the increasing need for higher density packaging
- Meets different termination needs
- Time saving as it can be automatically positioned on the board using pick and place processes
- Wide variety of choices for secure connection
- Supports cable connection; Prevents risks of pulling up and accidental un-mating
- Meets environmental, health, and safety requirements

TECHNICAL INFORMATION

MATERIAL

- Insulator: Glass filled thermoplastic (UL94V-0), Black
- Contact: Copper Alloy
- Shell: SPCC Steel

ELECTRICAL PERFORMANCE

- Current Rating: Rated current: 2.5A
- Rated Voltage: 250V
- Contact Resistance: 25mΩ max. Initial and 40mΩmax. after
- Insulation Resistance: 5000mΩ min. at 500VDC
- Dielectric Strength: 750VRMS
- Operating Temperature Range: 55°C to +105°C

MECHANICAL PERFORMANCE

- Mating/Un-mating Cycles: 200/500
- Insertion/Extraction Force per contact: 5N max. / 0.2N min.

TARGET MARKETS/APPLICATIONS



Asymmetric Digital Subscriber Line (ADSL)
Base Station Switching Transmission



Set-top Box



Desktop and Laptop Storage System Router and Server



Automotive Diagnostics Control Drives Energy Meter Gaming Machine Test Equipment Office Automation POS & Handheld terminal Power Supplies Parking Meter Printer and Copier Renewable Energy Robotics Surveillance Camera Avionics



Medical Instrument



Military Equipment

HIGH DENSITY D-SUBMINIATURE STRAIGHT

ORDERING INFORMATION

SERIES — **P** — **YY** — **4** — **X** — **LF** — **RoHS status**

RoHS compliant

Gender	
Pin	P
Socket	S


No Of Contacts	
15	
26	
44	

Mounting Options	
UNC 4-40 Screw locks with Board locks	V
UNC 4-40 Clinch nuts with Board locks	X
M3 Clinch nuts with Board locks	L


Durability	
200 mating cycles	4
500 mating cycles	6

Series	Part Number
Male straight	10090928
Female straight	10090929


PCB LAYOUT



P.C.B LAYOUT(FOR 15P)




P.C.B LAYOUT(FOR 44P)






P.C.B LAYOUT(FOR 26P)

► D-Subminiature High Density Connectors

DIMENSION FOR MOUNTING OPTION 'X/L'




Pos.	Part Number	A	B	C	D	E
15P	10090929-S15**LF	30.81	24.99	16.33	2.29	19.10
26P	10090929-S26**LF	39.24	33.32	24.66	2.29	27.75
44P	10090929-S44**LF	53.04	47.04	38.38	2.29	41.30




► D-Subminiature High Density Connectors

HIGH DENSITY D-SUBMINIATURE RIGHT ANGLE

ORDERING INFORMATION




DIMENSION FOR MOUNTING OPTION 'V'






Pos.	Part Number	A	B	C	D	E	F	H
15P	10090926-P15*VLF	30.81	24.99	16.92	2.29	8.19	7.68	5.9 +0.25 -0
26P	10090926-P26*VLF	39.24	33.32	25.25	2.29	8.01	7.02	5.9 +0.25 -0
44P	10090926-P44*VLF	53.04	47.04	38.96	2.29	8.02	7.01	5.9 +0.25 -0

▶ D-Subminiature High Density Connectors





PCB LAYOUT



► D-Subminiature High Density Connectors


HIGH DENSITY D-SUBMINIATURE RIGHT ANGLE FEMALE

UL RECOGNISED FILE E 118235 (R)




► D-Subminiature High Density Connectors

HIGH DENSITY D-SUBMINIATURE 3 ROWS (15/26/44 POS)



Size	Dimensions						
	A + 0.38	B + 0.12	C + 0.10	D + 0.25	E	F	G
15	30,81	24,99	16,96	16,21	7,68	8,19	2,285
26	39,14	33,32	25,18	24,54	7,02	8,01	2,285
44	53,03	47,04	39,12	38,25	7,01	8,02	2,285

PCB DRILLING DIMENSIONS




► D-Subminiature High Density Connectors

HIGH DENSITY D-SUBMINIATURE SOLDER BUCKET




ORDERING INFORMATION

SERIES	P	YY	4	A	LF																												
<table border="1"> <tr> <th colspan="2">Gender</th> </tr> <tr> <td>Pin</td> <td>P</td> </tr> <tr> <td>Socket</td> <td>S</td> </tr> </table>	Gender		Pin	P	Socket	S	<table border="1"> <tr> <th colspan="2">No Of Contacts</th> </tr> <tr> <td>15</td> <td></td> </tr> <tr> <td>26</td> <td></td> </tr> <tr> <td>44</td> <td></td> </tr> </table>	No Of Contacts		15		26		44		<table border="1"> <tr> <th colspan="2">Durability</th> </tr> <tr> <td>200 mating cycles</td> <td>4</td> </tr> <tr> <td>500 mating cycles</td> <td>6</td> </tr> </table>	Durability		200 mating cycles	4	500 mating cycles	6	<table border="1"> <tr> <th colspan="2">RoHS status</th> </tr> <tr> <td colspan="2">RoHS compliant</td> </tr> </table>	RoHS status		RoHS compliant		<table border="1"> <tr> <th colspan="2">Mounting Options</th> </tr> <tr> <td>Standard Hole</td> <td>A</td> </tr> </table>	Mounting Options		Standard Hole	A	
	Gender																																
Pin	P																																
Socket	S																																
No Of Contacts																																	
15																																	
26																																	
44																																	
Durability																																	
200 mating cycles	4																																
500 mating cycles	6																																
RoHS status																																	
RoHS compliant																																	
Mounting Options																																	
Standard Hole	A																																
<table border="1"> <tr> <th>Description</th> <th>Series</th> </tr> <tr> <td>Male Solder Bucket</td> <td>10090769</td> </tr> <tr> <td>Female Solder Bucket</td> <td>10090770</td> </tr> </table>		Description	Series	Male Solder Bucket	10090769	Female Solder Bucket	10090770																										
Description	Series																																
Male Solder Bucket	10090769																																
Female Solder Bucket	10090770																																

DIMENSION



Pos.	Part Number	A	B	C	D	E	H
15P	10090769-P15*ALF	30.81	24.99	16.92	19.10	2.29	5.9 +0.25 -0
26P	10090769-P26*ALF	39.24	33.32	25.25	27.75	2.29	5.9 +0.25 -0
44P	10090769-P44*ALF	53.04	47.04	38.96	41.30	2.29	5.9 +0.25 -0



ACCESSORIES (HOODS)

Plastic: Core Range PNs	Metalised: Core Range PNs	Metallic: Core Range PNs
86303637BLF	863093C09MLF	8655MH0901BLF
86303638BLF	863093C15MLF	8655MH1501BLF
86303639BLF	863093C25MLF	8655MH2501BLF

Part Description	Part Number
D-Sub High density straight 15 way solder pin	10090928-P154VLF
D-Sub High density straight 26 way solder pin	10090928-P264VLF
D-Sub High density straight 44 way solder pin	10090928-P444VLF
D-Sub High density straight 15 way solder socket	10090929-S154VLF
D-Sub High density straight 26 way solder socket	10090929-S264VLF
D-Sub High density straight 44 way solder socket	10090929-S444VLF
D-Sub High density straight 15 way solder pin	10090928-P154XLF
D-Sub High density straight 26 way solder pin	10090928-P264XLF
D-Sub High density straight 44 way solder pin	10090928-P444XLF
D-Sub High density straight 15 way solder socket	10090929-S154XLF
D-Sub High density straight 26 way solder socket	10090929-S264XLF
D-Sub High density straight 44 way solder socket	10090929-S444XLF
D-Sub High density right angle 15 way solder pin	10090926-P154VLF
D-Sub High density right angle 26 way solder pin	10090926-P264VLF
D-Sub High density right angle 44 way solder pin	10090926-P444VLF
D-Sub High density right angle 15 way solder socket	ICD15S13E4GV00LF
D-Sub High density right angle 26 way solder socket	ICD26S13E4GV00LF
D-Sub High density right angle 44 way solder socket	ICD44S13E4GV00LF
D-Sub High density right angle 15 way solder pin	10090926-P154XLF
D-Sub High density right angle 26 way solder pin	10090926-P264XLF
D-Sub High density right angle 44 way solder pin	10090926-P444XLF

▶ D-Subminiature High Density Connectors

PART NUMBER LIST

Part Description	Part Number
D-Sub High density right angle 15 way solder socket	ICD15S13E4GX00LF
D-Sub High density right angle 26 way solder socket	ICD26S13E4GX00LF
D-Sub High density right angle 44 way solder socket	ICD44S13E4GX00LF
D-Sub High density 15 way solder bucket pin	10090769-P154ALF
D-Sub High density 26 way solder bucket pin	10090769-P264ALF
D-Sub High density 44 way solder bucket pin	10090769-P444ALF
D-Sub High density 15 way solder bucket socket	10090770-S154ALF
D-Sub High density 26 way solder bucket socket	10090770-S264ALF
D-Sub High density 44 way solder bucket socket	10090770-S444ALF

ACPADSUBHDEN0324E44

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[10090769-P446ALF](#) [10090769-P784ALF](#) [10090770-S446ALF](#) [10090770-S626ALF](#) [10090770-S784ALF](#) [10090926-P264LLF](#) [10090926-P444LLF](#) [10090926-P626XLF](#) [10090926-P784XLF](#) [10090926-P786LLF](#) [10090926-P786VLF](#) [10090927-S624VLF](#) [10090927-S624XLF](#) [10090927-S626XLF](#) [10090927-S786XLF](#) [10090928-P266XLF](#) [10090928-P624VLF](#) [10090928-P626VLF](#) [10090928-P626XLF](#) [10090928-P786XLF](#) [10090929-S266LLF](#) [10090929-S444LLF](#) [10090929-S624VLF](#) [10090929-S624XLF](#) [10090929-S626VLF](#) [10090929-S626XLF](#) [10090929-S784VLF](#) [10090929-S784XLF](#) [10090930-P150ALF](#) [10090930-P260ALF](#) [10090930-P440ALF](#) [10090930-P620ALF](#) [10090931-S150ALF](#) [10090931-S260ALF](#) [10090931-S440ALF](#) [10090931-S620ALF](#) [10090932-P2448LF](#) [10090932-P2468LF](#) [10090932-P2469LF](#) [10090933-S2448LF](#) [10090933-S2449LF](#) [10090933-S2468LF](#) [10090933-S2469LF](#)