



| SIGN                                           | DATE | DESCRIPTION | APPROVER |
|------------------------------------------------|------|-------------|----------|
|                                                |      |             |          |
| THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!! |      |             |          |

Material:

- Item a :Terminal body Thermoplastic (UL94 V-0)
- Item b :Terminal body Thermoplastic (UL94 V-0)
- Item c :Male contact pin: Brass Tin plated
- Item d :Spring clamp: Stainless steel

Electrical

- Voltage rating: 300V
- Current rating: 8A
- Wire range:
- Solid wire(AWG): 12-28
- Stranded wire(AWG): 12-28
- Wire strip length: 8-9mm
- Withstanding Voltage: 1.6KV
- Operating temperature: -40°C to +105°C
- Safety Approval: 



SECTION A-A

NB xx 7 0 x 2 xxxx G

- RoHS  
Pb<40,000ppm
- 02 2 poles  
03 3 poles  
...  
24 24 poles
- 0 Black  
5 Green  
(RAL6018/T)  
6 Blue  
8 Grey  
(RAL7035/D)
- 0000 Standard @ Logo  
000A Standard ANY Logo  
Any special item by  
customer request,  
please contact sales  
department.

N = Number of poles

Dim A=Nx5.0+1.5

Dim B=Nx5.0+3.2

Dim C=(N-1)x5.0

|        | Dim A | Dim B | Dim C |
|--------|-------|-------|-------|
| 2-6p   | ±0.20 | ±0.20 | ±0.20 |
| 7-12p  | ±0.25 | ±0.25 | ±0.25 |
| 13-18p | ±0.30 | ±0.30 | ±0.30 |
| 19-24p | ±0.40 | ±0.40 | ±0.40 |

**ANYTEK**

**CUSTOMER COPY**

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATSOEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

|          |  |                             |                      |                      |                                                                                       |         |            |            |  |
|----------|--|-----------------------------|----------------------|----------------------|---------------------------------------------------------------------------------------|---------|------------|------------|--|
| TITLE    |  | NB 5.0mm series Hook holder |                      |                      |                                                                                       | DWG NO. |            | 8NB0005    |  |
| PART NO. |  | NBxx70x2xxxxG               |                      | DWG NO.              |                                                                                       | 8NB0005 |            |            |  |
| APPROVED |  | CHECKED                     | DESIGNED             | DRAWN                | CUST NO.                                                                              |         | Tolerance  |            |  |
|          |  |                             | Runner<br>2010.04.22 | Runner<br>2010.04.22 |  |         | UNIT: mm   | X. ±0.50   |  |
|          |  |                             |                      |                      | SHEET: 01/01                                                                          |         | SCALE: 2/1 | X.X ±0.30  |  |
|          |  |                             |                      |                      |                                                                                       |         | REV.: B    | X.XX ±0.10 |  |
|          |  |                             |                      |                      |                                                                                       |         |            | X° ±1°     |  |

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

## Amphenol:

|                                      |                                      |                                      |                                      |                                      |                                      |
|--------------------------------------|--------------------------------------|--------------------------------------|--------------------------------------|--------------------------------------|--------------------------------------|
| <a href="#"><u>NB0270820000G</u></a> | <a href="#"><u>NB0370820000G</u></a> | <a href="#"><u>NB0470820000G</u></a> | <a href="#"><u>NB0570820000G</u></a> | <a href="#"><u>NB0670820000G</u></a> | <a href="#"><u>NB0770820000G</u></a> |
| <a href="#"><u>NB0870820000G</u></a> | <a href="#"><u>NB0970820000G</u></a> | <a href="#"><u>NB1070820000G</u></a> | <a href="#"><u>NB1170820000G</u></a> | <a href="#"><u>NB1270820000G</u></a> | <a href="#"><u>NB1370820000G</u></a> |
| <a href="#"><u>NB1470820000G</u></a> | <a href="#"><u>NB1570820000G</u></a> | <a href="#"><u>NB1670820000G</u></a> | <a href="#"><u>NB1770820000G</u></a> | <a href="#"><u>NB1870820000G</u></a> | <a href="#"><u>NB1970820000G</u></a> |
| <a href="#"><u>NB2070820000G</u></a> | <a href="#"><u>NB2170820000G</u></a> | <a href="#"><u>NB2270820000G</u></a> | <a href="#"><u>NB2370820000G</u></a> | <a href="#"><u>NB2470820000G</u></a> |                                      |