


POLE		2	3	4	5	6	7	8
A		13.24	20.86	28.48	36.10	43.72	51.34	58.96
B		7.62	15.24	22.86	30.48	38.10	45.72	53.34
Tol.		±0.15			±0.20			
POLE	9	10	11	12	13	14	15	16
A	66.58	74.20	81.82	89.44	97.06	104.68	112.30	119.92
B	60.96	68.58	76.20	83.82	91.44	99.06	106.68	114.30
Tol.		±0.30			±0.40			

SIGN	DATE	DESCRIPTION	APPROVER
△	12/02'08	Flange screw changed from "-" to "+/-"	Tony
△	3/11'09	Dim.A & Dim.B Changed	Tony
△	2009.12.18	Add UL standard	Jacke
△	2010.03.23	Add the 2p mark	Jacke
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!			

Material:

- Item ③ Clamp: Steel Zinc plated
- Item ④ Terminal(Up body): Thermoplastic (UL94V-0)
- Item ⑤ Terminal(Down body): Thermoplastic (UL94V-0)
- Item ⑥ Female contact: PbBz(CuSn),Tin plated.
- Item ⑦ Terminal screw: Steel Zinc plating "- " slot type
- Item ⑧ Clampcage:Steel/steel Zinc plated
- Item ⑨ With flange screw: Steel Zinc plated, M2.5

Electrical: cULus

- Voltage rating: 300V
- Current rating: 20A
- Wire range:
- Solid wire(AWG): 12-22
- Stranded wire(AWG): 12-22
- Torque: 3.5 Lb.-In.
- Screw: M2.5
- Wire strip length: 8-9mm
- Withstanding Voltage: 1.6KV
- Operating temperature: -40°C to +115°C
- Safety Approval: 

VM xx 0 5 x 3 xxxx G

POLES

02: 02 pole

///

16: 16 pole


Color

- 0 Black (RAL9005)
2 Red (RAL3001/D)
3 Orange(RAL2011/P)
4 Yellow(RAL1018/A)
5 Green(RAL6018/T)
6 Blue (RAL5015/A)
8 Grey(RAL7035/D)

— G: Pb<40000ppm

— 0000: “@” Logo (Standard)
(Steel screw plating Cr³⁺)

000A: "ANYTEK" Mark
Any special item by
customer request.
please contact sales
department.

<h1>ANYTEK</h1>				<h2>CUSTOMER COPY</h2> <p>ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATSOEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD</p>			
TITLE		VM 7.62 mm W/ Flange Series					
PART NO.		VMxx05x3xxxxG		DWG NO.		8VM0501	
APPROVED		CHECKED	DESIGNED	DRAWN	CUST NO.		Tolerance
			Jacke 2010.03.23	Jacke 2009.12.18			X. ±0.50 X.X ±0.30 X.XX ±0.10 X° ±1°
					UNIT: mm SCALE: NONE SHEET: 01/01		REV.: F

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Amphenol:

<u>VM0205530000G</u>	<u>VM0305530000G</u>	<u>VM0405530000G</u>	<u>VM0505530000G</u>	<u>VM0605530000G</u>	<u>VM0705530000G</u>
<u>VM0805530000G</u>	<u>VM0905530000G</u>	<u>VM1005530000G</u>	<u>VM1105530000G</u>	<u>VM1205530000G</u>	<u>VM1305530000G</u>
<u>VM1405530000G</u>	<u>VM1505530000G</u>	<u>VM1605530000G</u>	<u>VM0305030000G</u>	<u>VM0505030000G</u>	<u>VM0205030000G</u>
<u>VM0405030000G</u>	<u>VM0505830000G</u>	<u>VM0405830000G</u>	<u>VM0805030000G</u>	<u>VM1305830000G</u>	<u>VM1005830000G</u>
<u>VM1305030000G</u>	<u>VM1205030000G</u>	<u>VM1205830000G</u>	<u>VM1405030000G</u>	<u>VM1405830000G</u>	<u>VM1505030000G</u>
<u>VM1505830000G</u>	<u>VM0905830000G</u>	<u>VM0805830000G</u>	<u>VM1105030000G</u>	<u>VM1605030000G</u>	<u>VM1605830000G</u>
<u>VM0205830000G</u>	<u>VM0305830000G</u>	<u>VM0705830000G</u>	<u>VM0605830000G</u>	<u>VM0905030000G</u>	<u>VM0705030000G</u>
<u>VM0605030000G</u>	<u>VM1005030000G</u>	<u>VM1105830000G</u>			