




P/N	A	B	DEUTSCH CROSS	  				REVISIONS																																																									
REV	ECO	DESCRIPTION						DATE	BY	APPR																																																							
A1	—	RELEASE						12APR19	SULLEN	TOMMY																																																							
ATSS-12-00	62.4mm	Ø11.3mm	JS-12-00																																																														
ATSS-16-00	62.1mm	Ø8.8mm	JS-16-00																																																														
NOTES: UNLESS OTHERWISE SPECIFIED																																																																	
1. MATERIAL: SHELL: SILICONE RUBBER, RED INTEGRATED CONTACT RETENTION SYSTEM																																																																	
2. SPECIFICATIONS: 2.1 OPERATING TEMPERATURE: -55C TO +125C 2.2 MOISTURE RESISTANCE: IP67 2.3 MATING CYCLE DURABILITY: 100 CYCLES 2.4 RoHS COMPLIANT																																																																	
3. ALL DIMENSIONS ARE FOR REFERENCE USE ONLY																																																																	
4. CONTACT SIZE AND WIRE RANGE:																																																																	
<table><tr><td>CONTACT SIZE</td><td>MIN. INSUL O.D</td><td>MAX. INSUL O.D</td><td>TYPICAL WIRE RANGE</td><td>CURRENT RATING</td></tr><tr><td>12</td><td>3.40mm (.134 in)</td><td>4.32mm (.170 in)</td><td>10-14AWG</td><td>25 AMPS</td></tr><tr><td>16</td><td>2.54mm (.100 in)</td><td>3.40mm (.134 in)</td><td>14-20AWG</td><td>13 AMPS</td></tr></table>										CONTACT SIZE	MIN. INSUL O.D	MAX. INSUL O.D	TYPICAL WIRE RANGE	CURRENT RATING	12	3.40mm (.134 in)	4.32mm (.170 in)	10-14AWG	25 AMPS	16	2.54mm (.100 in)	3.40mm (.134 in)	14-20AWG	13 AMPS																																									
CONTACT SIZE	MIN. INSUL O.D	MAX. INSUL O.D	TYPICAL WIRE RANGE	CURRENT RATING																																																													
12	3.40mm (.134 in)	4.32mm (.170 in)	10-14AWG	25 AMPS																																																													
16	2.54mm (.100 in)	3.40mm (.134 in)	14-20AWG	13 AMPS																																																													
<table><tr><td colspan="2">PART NUMBER</td><td colspan="3">DESCRIPTION</td><td>ITEM</td></tr><tr><td>QUANTITY</td><td colspan="5">MATERIALS LIST</td></tr><tr><td colspan="2" rowspan="4"> UNLESS OTHERWISE SPECIFIED 1) All dimensions are in metric (mm). 2) Tolerances are as follows: 1 PL DEC ±0.30 2 PL DEC ±0.15 3 PL DEC ±0.08 Fractions ±1/64 Angles ±1° 3) Note reference =  </td><td colspan="2">SIGNATURES</td><td>DATE</td><td rowspan="4">  Sine Systems - www.amphenol-sine.com 44724 Morley Drive Clinton Township, MI 48036 SPEEDSPlice, SIZE X, ENVIROMENTAL </td></tr><tr><td colspan="2">DRAWN: SULLEN,ZHANG</td><td>12APR19</td></tr><tr><td colspan="2">CHECKED: ORION,LI</td><td>12APR19</td></tr><tr><td colspan="2">ENGINEER:</td><td></td></tr><tr><td colspan="2">APPROVAL: TOMMY,XIE</td><td>12APR19</td><td colspan="2">CUSTOMER:</td></tr><tr><td colspan="2">MATERIAL SPECIFICATIONS:</td><td colspan="3">THIS DRAWING IS SUPPLIED FOR INFORMATION ONLY. DESIGN FEATURES, SPECIFICATIONS AND PERFORMANCE DATA SHOWN HEREON ARE THE PROPERTY OF THE AMPHENOL CORPORATION. NO RIGHTS OF REPRODUCTION ARE IMPLIED. ALL DIMENSIONS ARE SUBJECT TO NORMAL MANUFACTURING VARIATIONS.</td><td rowspan="3"><table><tr><td>SIZE</td><td>TYPE</td><td>DWG NO:</td><td>REVISION</td></tr><tr><td>B</td><td>C</td><td>ATSS-XX-00</td><td>A1</td></tr></table></td></tr><tr><td colspan="2">PROCESS SPECIFICATIONS:</td><td colspan="3">SCALE: NONE</td></tr><tr><td colspan="2">NEXT ASS'Y:</td><td colspan="3">SHEET 1 OF 1</td></tr></table>										PART NUMBER		DESCRIPTION			ITEM	QUANTITY	MATERIALS LIST					UNLESS OTHERWISE SPECIFIED 1) All dimensions are in metric (mm). 2) Tolerances are as follows: 1 PL DEC ±0.30 2 PL DEC ±0.15 3 PL DEC ±0.08 Fractions ±1/64 Angles ±1° 3) Note reference = 		SIGNATURES		DATE	 Sine Systems - www.amphenol-sine.com 44724 Morley Drive Clinton Township, MI 48036 SPEEDSPlice, SIZE X, ENVIROMENTAL	DRAWN: SULLEN,ZHANG		12APR19	CHECKED: ORION,LI		12APR19	ENGINEER:			APPROVAL: TOMMY,XIE		12APR19	CUSTOMER:		MATERIAL SPECIFICATIONS:		THIS DRAWING IS SUPPLIED FOR INFORMATION ONLY. DESIGN FEATURES, SPECIFICATIONS AND PERFORMANCE DATA SHOWN HEREON ARE THE PROPERTY OF THE AMPHENOL CORPORATION. NO RIGHTS OF REPRODUCTION ARE IMPLIED. ALL DIMENSIONS ARE SUBJECT TO NORMAL MANUFACTURING VARIATIONS.			<table><tr><td>SIZE</td><td>TYPE</td><td>DWG NO:</td><td>REVISION</td></tr><tr><td>B</td><td>C</td><td>ATSS-XX-00</td><td>A1</td></tr></table>	SIZE	TYPE	DWG NO:	REVISION	B	C	ATSS-XX-00	A1	PROCESS SPECIFICATIONS:		SCALE: NONE			NEXT ASS'Y:		SHEET 1 OF 1		
PART NUMBER		DESCRIPTION			ITEM																																																												
QUANTITY	MATERIALS LIST																																																																
UNLESS OTHERWISE SPECIFIED 1) All dimensions are in metric (mm). 2) Tolerances are as follows: 1 PL DEC ±0.30 2 PL DEC ±0.15 3 PL DEC ±0.08 Fractions ±1/64 Angles ±1° 3) Note reference = 		SIGNATURES		DATE	 Sine Systems - www.amphenol-sine.com 44724 Morley Drive Clinton Township, MI 48036 SPEEDSPlice, SIZE X, ENVIROMENTAL																																																												
		DRAWN: SULLEN,ZHANG		12APR19																																																													
		CHECKED: ORION,LI		12APR19																																																													
		ENGINEER:																																																															
APPROVAL: TOMMY,XIE		12APR19	CUSTOMER:																																																														
MATERIAL SPECIFICATIONS:		THIS DRAWING IS SUPPLIED FOR INFORMATION ONLY. DESIGN FEATURES, SPECIFICATIONS AND PERFORMANCE DATA SHOWN HEREON ARE THE PROPERTY OF THE AMPHENOL CORPORATION. NO RIGHTS OF REPRODUCTION ARE IMPLIED. ALL DIMENSIONS ARE SUBJECT TO NORMAL MANUFACTURING VARIATIONS.			<table><tr><td>SIZE</td><td>TYPE</td><td>DWG NO:</td><td>REVISION</td></tr><tr><td>B</td><td>C</td><td>ATSS-XX-00</td><td>A1</td></tr></table>	SIZE	TYPE	DWG NO:	REVISION	B	C	ATSS-XX-00	A1																																																				
SIZE	TYPE	DWG NO:	REVISION																																																														
B	C	ATSS-XX-00	A1																																																														
PROCESS SPECIFICATIONS:		SCALE: NONE																																																															
NEXT ASS'Y:		SHEET 1 OF 1																																																															

TITLE: SPEEDSPlice, SIZE 12,ENVIRONMENTAL

DWG NO: ATSS-12-00

REV: A1

SH: 1

DF: 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[ATSS-12-00](#)