




# DIMENSION

Dim A	NX3.50+1.40
Dim B	(N-1)X3.50

N=Number of contacts

Poles	Tolerance
1p-6p	±0.10
7p-12p	±0.20
13p-18p	±0.30
19p-24p	±0.40



SIGN	DATE	DESCRIPTION	APPROVER
△	04/05'13	change the structure & update the drawing	Da cheng
△	10/17'13	Add is cULus	Da cheng
△			
△			
△			
△			

THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!

## Material:

- Item 1 Terminal housing : Thermoplastic (UL 94V-0)
- Item 2 Spring clamp: Stainless steel
- Item 3 Solder pin : Brass ,Tin plated
- Item 4 Terminal cover : Thermoplastic (UL 94V-0)

## △ Electrical

cULus

- Voltage rating: 300VAC
- Current rating: 10A
- Wire range:
- Solid wire(AWG): 16-24
- Stranded wire(AWG): 16-24
- Wire strip length: 9-10mm
- Withstanding Voltage: 1.6KV
- Operating temperature: -40°C to +115°C
- Soldering temperature: 260°C±5°C/5 Sec

## △ Safety Approval:



- Critical dimension: △

NJ xx 21 x 0 xxxx G

No. of poles

- 01 1 CONTACTS
- 02 2 CONTACTS
- 03 3 CONTACTS
- ... ..
- 24 24 CONTACTS

△ Color

- 0 Black (RAL9005)
- 2 Red (RAL3001/D)
- 3 Orange(RAL2011/P)
- 4 Yellow(RAL1018/A)
- 5 Green(RAL6018/T)
- 6 Blue (RAL5015/A)
- 8 Grey(RAL7004/P)
- 9 White(RAL1102)
- C Multiple colors


△ RoHs compliant  
(lead<4%)  
In copper Alloy

0000:"@ "Logo (Standard )  
000A:"ANYTEK"Logo  
Any special item by  
customer request,  
please contact sales  
department.

# ANYTEK

## CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE	NJ- 3.5 Series 1P-24P Horizontal ( 180D wire inlet )						
PART NO.	NJxx21x0xxxxG			DWG NO.	8NJ0001		
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.			
		Dacheng 2013.10.21	Dacheng 2013.10.21		UNIT: mm	X. ±0.50	
					SCALE: NONE	X.X ±0.30	
					REV.: D	X.XX ±0.10	
				SHEET: 01/01		X° ±1°	

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

## Amphenol:

<a href="#"><u>NJ0221500000G</u></a>	<a href="#"><u>NJ0321500000G</u></a>	<a href="#"><u>NJ0421500000G</u></a>	<a href="#"><u>NJ0521500000G</u></a>	<a href="#"><u>NJ0621500000G</u></a>	<a href="#"><u>NJ0721500000G</u></a>
<a href="#"><u>NJ0821500000G</u></a>	<a href="#"><u>NJ0921500000G</u></a>	<a href="#"><u>NJ1021500000G</u></a>	<a href="#"><u>NJ1121500000G</u></a>	<a href="#"><u>NJ1221500000G</u></a>	<a href="#"><u>NJ1321500000G</u></a>
<a href="#"><u>NJ1421500000G</u></a>	<a href="#"><u>NJ1521500000G</u></a>	<a href="#"><u>NJ1621500000G</u></a>	<a href="#"><u>NJ1721500000G</u></a>	<a href="#"><u>NJ1821500000G</u></a>	<a href="#"><u>NJ1921500000G</u></a>
<a href="#"><u>NJ2021500000G</u></a>	<a href="#"><u>NJ2121500000G</u></a>	<a href="#"><u>NJ2221500000G</u></a>	<a href="#"><u>NJ2321500000G</u></a>	<a href="#"><u>NJ2421500000G</u></a>	<a href="#"><u>NJ0221800000G</u></a>
<a href="#"><u>NJ0221000000G</u></a>					