


SIGN	DATE	DESCRIPTION	APPROVER
△	04/07'10	Add the 2P mark	RUNNER
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!			



Dimension

DIM A	N×5.08+0.62
DIM B	(N-1)×5.08


N=Number of poles

POLES	TOL
2p-6p	±0.15
7p-12p	±0.25
13p-16p	±0.35
17p-24p	±0.40

Material

- Item a Terminal body:Thermoplastic (UL94V-0)
- Item b Terminal body:Thermoplastic (UL94V-0)
- Item c Terminal lever:Thermoplastic (UL94V-0)
- Item d Wire guard:Stainless Steel
- Item e Femlae contact:PhBz (CuSn) Tin plated


Electrical cULus


- Voltage rating:300V
- Current rating:10A
- Solid wire(AWG):12-26
- Stranded wire(AWG):12-26
- Wire strip length:9-10mm
- Withstanding Voltage:1.6KV
- Operating temperature:-40°C to +115°C
- Safety Approval: 

H4 xx 50 x B xxxx G

02	2 CONTACTS	0	Black	0000	Standard @ Logo	RoHS
03	3 CONTACTS	5	Green	000A	Standard ANY Logo	Pb<40,000ppm
...	...	6	Blue	Any special item by customer request, please contact sales department.		
24	24 CONTACTS	8	Grey			

SECTION A-A



ANYTEK				CUSTOMER COPY			
ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD							
TITLE		H4 5.08 Series hook on back side (Without flange)					
PART NO.		H4xx50xBxxxxG		DWG NO.		8H40202	
APPROVED		CHECKED	DESIGNED	DRAWN	CUST NO.		Tolerance
			Runner 2010.04.07	Tony 2009.03.12			X. ±0.50
					UNIT: mm		X.X ±0.30
					SCALE: NONE		X.XX ±0.10
					SHEET: 01/01		X* ±1*
					REV.: C		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Amphenol:

<u>H402505B0000G</u>	<u>H403505B0000G</u>	<u>H404505B0000G</u>	<u>H405505B0000G</u>	<u>H406505B0000G</u>	<u>H407505B0000G</u>
<u>H408505B0000G</u>	<u>H409505B0000G</u>	<u>H410505B0000G</u>	<u>H411505B0000G</u>	<u>H412505B0000G</u>	<u>H413505B0000G</u>
<u>H414505B0000G</u>	<u>H415505B0000G</u>	<u>H416505B0000G</u>	<u>H417505B0000G</u>	<u>H418505B0000G</u>	<u>H419505B0000G</u>
<u>H420505B0000G</u>	<u>H421505B0000G</u>	<u>H422505B0000G</u>	<u>H423505B0000G</u>	<u>H424505B0000G</u>	