




REV	SIGN	DATE	DESCRIPTION	APPROVER
B		2017.09.28	The first release	Zhihua
RoHS Compliant				
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!				



The color of lever is consistent with body's







Material

- item① Insulating body(middle): Thermoplastic ( UL94V-0 )
- item② Insulating lever: Thermoplastic ( UL94V-0 )
- item③ Spring clamp: Phosphor Bronze , Tin Plated
- item④ Insulating cover: Thermoplastic ( UL94V-0 )
- item⑤ Insulating body(side): Thermoplastic ( UL94V-0 )

Electrical

cUL<sub>5</sub>

- Voltage rating: 300V
- Current rating: 2A
- Wire range : 2×AWG 20~26 (Solid wire)
- Wire strip length: 5~6mm
- Withstanding Voltage: 1.6KV
- Operating temperature: -40°C to +115°C
- Safety Approval:  **UL**us
- Critical dimension: 







code of color:

Yellow	White	Black	Red
RAL1018/A	RAL1102	RAL9005	RAL3001A

# Amphenol **ANYTEK**

**CUSTOMER COPY**

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

PROPRIETOR: PROPERTY OF ANYTEK TECHNOLOGY CO., LTD										
TITLE		NU 3.5mm series								
PART NO.		NU0400C0001AG			DWG NO.		8NU0004			
APPROVED		CHECKED	DESIGNED	DRAWN	CUST NO.		Tolerance			
		 Zhihua 2017.09.28	 Zhihua 2017.09.28			UNIT: mm		X.	±0.50	
						SCALE: NONE		X.X	±0.30	
					SHEET: 01/01		REV: B		X°	±1°

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[NU0400C0001AG](#)