

MEG-Array®

PROVEN BGA CONNECTOR FOR RELIABILITY AND HIGH DATA RATES

Patented BGA design, offering industry leading self-leveling and self-centering. 1.27mm x 1.27mm array of discrete circuit contacts allows flexible ground distribution to optimize high speed signal integrity at speeds up to 32 Gbps.

- High density, high speed, dual-point contacts
- 32 Gbps performance documented for 4mm and 6mm stack heights
- 1.27mm x 1.27mm grid, 71 contacts per cm²
- Wide range of sizes and PCB stack heights
- Self-alignment and leveling for multiple connector use



TARGET MARKETS



FEATURES

- 22+ year old solder joint reliability per IPC-SM-785
- Telcordia GR-1217-CORE and NPS-25298-2
- Stack heights available from 4mm to 14mm
- Pin counts 40 to 528 positions
- Multiple in-process vision systems

BENEFITS

- Long term quality and reliability
- Verified performance through environmental stress and uncontrolled environments
- Fits a large range of customer applications
- Fits a large range of customer applications
- BGA and contact integrity

TECHNICAL INFORMATION

MATERIAL

- Housing: Liquid crystal polymer
- Contact: Copper alloy
- Solder sphere: Lead Free

ELECTRICAL PERFORMANCE

- Insulation resistance: 1000mΩ min.
- Dielectric withstanding voltage: 200 VAC max
- 2.0A < 30°C Δ T (single contact energized)

MECHANICAL PERFORMANCE

- Durability: 50, 100, or 200 cycles
- Contact Wipe: 0.80mm Nominal
- IPC-SM-785 Solder Joint Reliability: 22.1 year product end-of-life

ENVIRONMENTAL

- Telcordia GR-1217-CORE

APPROVALS AND CERTIFICATIONS

- UL File Numer: E66906

SPECIFICATIONS

- Product specification: GS-12-100
- Application specification: GS-20-033

PACKAGING

- Tape and Reel

TARGET MARKETS/APPLICATIONS



Automotive



Data



Telecommunication



Industrial & Instrumentation



Consumer



Medical

PART NUMBERS

		MATED HEIGHT							
SIZE	TYPE	4.0mm	5.5mm	6.0mm	8.0mm	10.0mm	11.5mm	12.0mm	14.0mm
81 POSITION (9X9)	Plug	55714 / 0mm							
	Receptacle	55715 / 4mm							
100 POSITION (10X10)	Plug	84512 / 0mm							
	Receptacle	84513 / 4mm							
200 POSITION (10X20)	Plug	84516 / 0mm		84516 / 0mm	84516 / 0mm	84530 / 6mm		84530 / 6mm	84530 / 6mm
	Receptacle	84517 / 4mm		55724 / 6mm	84535 / 8mm	84517 / 4mm		55724 / 6mm	84535 / 8mm
240 POSITION (8X30)	Plug	74213 / 0mm		74213 / 0mm					
	Receptacle	74217 / 4mm		55755 / 6mm					
300 POSITION (10X30)	Plug	84500 / 0mm	84500 / 0mm		84500 / 0mm	84578 / 6mm	84578 / 6mm		84578 / 6mm
	Receptacle	84501 / 4mm	84502 / 5.5mm		84553 / 8mm	84501 / 4mm	84502 / 5.5mm		84553 / 8mm
320 POSITION (10X32)	Plug	10123981 / 0mm							
	Receptacle	10123982 / 4mm							
400 POSITION (10X40)	Plug	84740 / 0mm		84740 / 0mm	84740 / 0mm	84520 / 6mm		84520 / 6mm	84520 / 6mm
	Receptacle	74221 / 4mm		74388 / 6mm	74390 / 8mm	74221 / 4mm		74388 / 6mm	74390 / 8mm
528 POSITION (12X44)	Plug			10022671 / 0mm					
	Receptacle			10026846 / 6mm					

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[FCI / Amphenol:](#)

[55714-102](#) [55715-101](#) [55724-101](#) [74213-102](#) [74221-201](#) [84502-001LF](#) [84520-202](#) [84530-102](#) [84530-202](#) [84553-001](#) [84553-001LF](#) [84553-201](#) [84578-102](#) [84578-202](#) [84501-101LF](#) [74213-102LF](#) [74217-101LF](#) [74213-002LF](#) [74217-001LF](#) [55755-201](#) [74213-202](#) [74390-201LF](#) [84740-202LF](#) [84517-201LF](#) [84501-201LF](#) [74390-001LF](#) [74388-101LF](#) [74221-001LF](#) [74217-101](#) [74217-201](#) [74388-201](#) [74390-201](#) [74390-001](#) [74217-001](#) [84502-001](#) [74213-002](#) [84512-002](#) [84512-202](#) [84513-201](#) [84516-002](#) [84516-202](#) [84517-001](#) [84520-002](#) [84530-002](#) [84535-001](#) [84578-002](#) [84740-202](#) [10026846-101LF](#) [55714-002LF](#) [55714-102LF](#) [55715-001LF](#) [55715-101LF](#) [55724-001LF](#) [55724-101LF](#) [55724-201LF](#) [55755-001LF](#) [55755-201LF](#) [84535-201LF](#) [84740-002](#) [84500-102](#) [10022671-102](#) [10022671-102LF](#) [10043343-202](#) [10043343-202LF](#) [10043857-202](#) [55714-202LF](#) [55755-101LF](#) [55714-202](#) [55755-101](#) [55715-201](#) [55715-201LF](#) [84502-201LF](#) [84535-101LF](#) [84553-101LF](#) [84517-101LF](#) [84513-101LF](#) [84502-101LF](#) [74390-101LF](#) [74221-101LF](#) [84740-102LF](#) [84520-102LF](#) [84500-102LF](#) [84512-102LF](#) [84516-102LF](#) [84740-002LF](#) [74388-001LF](#) [84501-001LF](#) [84500-202LF](#) [10026846-101](#) [55714-002](#) [55715-001](#) [55724-001](#) [55724-201](#) [55755-001](#) [74388-201LF](#) [74213-202LF](#) [74217-201LF](#) [74221-201LF](#) [84512-002LF](#) [84512-202LF](#)