



N = Number of poles
Dim A = N x 7.62
Dim B = (N - 1) x 7.62

	Dim A	Dim B
2-6p	±0.20	±0.20
7-12p	±0.30	±0.30
13-16p	±0.40	±0.40

SIGN	DATE	DESCRIPTION	APPROVER
△	10/6'06	Wire range changed from 10-24AWG to 10-30AWG	Steady
△	10/6'06	Torque changed from 3.5Lb-In to 4.5Lb-In	Steady
△	10/6'06	Added cULus logo	Steady
△	02/22'07	Body screw hole is changed	Marvin
△	2010.03.09	The material is changed from Brass to Copper	Jacke
△	2010.03.09	The design is changed	Jacke
△	2010.03.09	Add the 2p mark	Jacke
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!			

Material

- Item (a) Clamp : Brass(CuZn) Ni plated
- Item (b) Terminal screw: Steel Zinc plating"-slot type
- △ Item (c) Female contact : Copper Tin plated
- Item (d) Terminal (body): Thermoplastic (UL94 V-0)
- Item (e) Terminal (cover): Thermoplastic (UL94 V-0)

Electrical cULus

- Voltage rating: 300V
- Current rating: 20A
- Wire range:
 - △ Solid wire(AWG): 10-30
 - Stranded wire(AWG): 10-30
- △ Torque: 4.5(Lb-In)
- Screw: M3
- Wire strip length: 7-8mm
- Withstanding Voltage: 1.6KV
- Operating temperature: -40°C to +115°C
- △ Safety Approval: cULus

VB xx 01 x 0 xxxx G

02	2 CONTACTS	0	Black (RAL9005)	0000: "@" Logo	RoHS
03	3 CONTACTS	2	Red (RAL3001/D)	000A: "ANYTEK" Logo	Pb<40,000ppm
...	...	3	Orange(RAL2011/P)	Any special item by	
16	16 CONTACTS	4	Yellow(RAL1018/A)	customer request.	
		5	Green(RAL6018/T)	please contact sales	
		6	Blue (RAL5015/A)	department.	
		8	Grey(RAL7035/D)		

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE		VB-7.62 SERIES Without flange			
PART NO.	VBxx01x0xxxxG			DWG NO.	8VB0001
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.	
		Jacke 210.03.10	Jacke 210.03.10		Tolerance
					UNIT: mm
					SCALE: NONE
				SHEET: 01/01	REV.: F

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Amphenol:

[VB0201500000G](#) [VB0301500000G](#) [VB0401500000G](#) [VB0501500000G](#) [VB0601500000G](#) [VB0701500000G](#)
[VB0801500000G](#) [VB0901500000G](#) [VB1001500000G](#) [VB1101500000G](#) [VB1201500000G](#) [VB1301500000G](#)
[VB1401500000G](#) [VB1501500000G](#) [VB1601500000G](#)