

P.C.B. LAYOUT

Poles	02	03	04	05	06	07	08	09	10	11	12	13
Dim A	6.61	10.42	14.23	18.04	21.85	25.66	29.47	33.28	37.09	40.9	44.71	48.52
Dim B	3.81	7.62	11.43	15.24	19.05	22.86	26.67	30.48	34.29	38.1	41.91	45.72
Dim C	18.1	21.82	25.63	29.44	33.25	37.06	40.87	44.68	48.49	52.3	56.11	59.92
TOL	±0.1				±0.15				±0.2			
Poles	14	15	16	17	18	19	20	21	22	23	24	
Dim A	52.33	56.14	59.95	63.76	67.57	71.38	75.19	79.0	82.81	86.62	90.43	
Dim B	49.53	53.34	57.15	60.96	64.77	68.58	72.39	76.2	80.01	83.82	87.63	
Dim C	63.73	67.54	71.35	75.16	78.97	82.78	86.59	90.4	94.21	98.02	101.83	
TOL	±0.2				±0.25				±0.30			

SIGN	DATE	DESCRIPTION	APPROVER
△	7/23'08	With flange type is changed	Marvin
△	7/23'08	Operating temperature is changed	Marvin
△	2009.11.14	The design is changed from the round hole to hexagonal hole	Jacke
△	2010.01.12	Add cULus standard	Jacke
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!			

Materials

Item a Terminal body:Thermoplastic (UL94V-0)

Item b Female contact:PhBz(CuSn), Tin plated

Item c With Flange Nut :Brass M2.5

Electrical

● Voltage rating: 300V AC

● Current rating: 8A

● Withstanding Voltage: 1.6kv

△ ● Operating temperature: -40°C to +115°C

● Soldering temperature: 250°C±10°C/5 Sec

△ ● Safety Approval: 

V7 xx 3 2 x 1 xxxx G

No. OF POLES

02 2 CONTACTS

03 3 CONTACTS

... ..

24 24 CONTACTS

Color

0 Black (RAL9005)

2 Red (RAL3001/D)

3 Orange(RAL2011/P)

4 Yellow(RAL1018/A)

5 Green(RAL6018/T)

6 Blue (RAL5015/A)

8 Grey(RAL7035/D)

G: Pb<40000ppm

0000: "@ " Logo (Standard)


000A: "ANYTEK" Mark

Any special item by
customer request.
please contact sales
department.

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATSOEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE		V7 3.81 series Right angle With flange					
PART NO.	V7xx32x1xxxxG			DWG NO.	8V70103		
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.			Tolerance
		Jacke 2010.01.14	Jacke 2010.01.14		UNIT: mm	X.	±0.5
					SCALE: 4/1	X.X	±0.3
				SHEET: 01/01	REV.: E	X.XX	±0.1
						X°	±1°

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Amphenol:

<u>V70232510000G</u>	<u>V70332510000G</u>	<u>V70432510000G</u>	<u>V70532510000G</u>	<u>V70632510000G</u>	<u>V70732510000G</u>
<u>V70832510000G</u>	<u>V70932510000G</u>	<u>V71032510000G</u>	<u>V71132510000G</u>	<u>V71232510000G</u>	<u>V71332510000G</u>
<u>V71432510000G</u>	<u>V71532510000G</u>	<u>V71632510000G</u>	<u>V71732510000G</u>	<u>V71832510000G</u>	<u>V71932510000G</u>
<u>V72032510000G</u>	<u>V72132510000G</u>	<u>V72232510000G</u>	<u>V72332510000G</u>	<u>V72432510000G</u>	