



Poles	02	03	04	05	06	07	08	09	10	11	12
Dim L	20.32	30.48	40.64	50.80	60.96	71.12	81.28	91.44	101.60	111.76	121.92
Dim B	10.16	20.32	30.48	40.64	50.80	60.96	71.12	81.28	91.44	101.60	111.76
TOL	±0.20			±0.30			±0.40				

SIGN	DATE	DESCRIPTION	APPROVER
△			
△			

THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!

#### Material:

- Item 1 Terminal housing :Thermoplastic (UL 94V-0)
- Item 2 Clamp : Steel stamping , Zinc plated
- Item 3 Wire guard solder pin : Copper , Tin plated
- Item 4 Terminal screw: Steel Zinc plating"-slot type

Electrical cULus IEC

- Voltage rating : 300V 250V
- Current rating : 65A 57A
- Wire range :
- Solid wire (AWG) : 6-20 / 0.5-16mm<sup>2</sup>
- Stranded wire (AWG) : 6-20 / 0.5-16mm<sup>2</sup>
- Torque (LB-In.) : 19 Lb-In / 1.2 N.m
- Screw : M4.5
- Wire strip length : 10-11mm
- Withstanding voltage : 1.6KV / 6KV
- Operating temperature : -40°C+115°C
- Soldering temperature : 250°C+10°C/5 Sec
- Safety Approval : cULus

VP xx 6 5 x 8 xxxx G

		RoHS Pb<40,000ppm
No. of poles end stackable design	0 Black (RAL9005)	0000:"@ "Logo (Standard )
02 2 CONTACTS	2 Red (RAL3001/D)	000A:"ANYTEK" Logo
03 3 CONTACTS	3 Orange(RAL2011/P)	Any special item by customer request, please contact sales department.
...	4 Yellow(RAL1018/A)	
12 12 CONTACTS	5 Green(RAL6018/T)	
	6 Blue (RAL5015/A)	
	8 Grey(RAL7035/D)	

# ANYTEK

## CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE	VP 10.16 Series 2P~12P ( pitch=4.00 Double parallel tail )						
PART NO.	VPxx65x8xxxxG			DWG NO.	8VP0008		
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.	Tolerance		
		Aaron 2010.12.02	Aaron 2010.12.02			UNIT: mm	X. ±0.50
						SCALE: NONE	X.X ±0.30
						REV.: B	X.XX ±0.10
							X° ±1°

SHEET: 01/01

REV.: B

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[VP0265880000G](#) [VP0365880000G](#) [VP0465880000G](#) [VP0565880000G](#) [VP0665880000G](#) [VP0765880000G](#)  
[VP0865880000G](#) [VP0965880000G](#) [VP1065880000G](#) [VP1165880000G](#) [VP1265880000G](#)