


SIGN	DATE	DESCRIPTION	APPROVER
△	06/26'06	Voltage rating is changed from 250V to 300V	Marvin
△	06/26'06	Current rating is changed from 6A to 10A	Marvin
△	06/26'06	Withstanding Voltage is changed from 1.5KV to 1.6KV	Marvin
△	1/31'07	Soldering temperature changed from 245° to 250°	Tony
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!			

Material:

- Item ① Terminal(housing): Thermoplastic (UL94V-0)
- Item ② Contact pin: Brass

Electrical: cULus

- △ ● Voltage rating: 300V
- △ ● Current rating: 10A
- △ ● Withstanding Voltage: 1.6KV
- Operating temperature: -40°C to +115°C
- △ ● Soldering temperature: 250°C±10°C/5 Sec
- Safety Approval: 
- Part No.:



OP xx 4 2 x x xxxx G

02 2 CONTACTS
03 3 CONTACTS
...
24 24 CONTACTS

0000: Standard Pb < 40,000ppm
Any special item by (RoHS)
customer request.
please contact sales
department.

0 Tin
1 Gold plating 10u"
2 Gold flash

0 PA66
1 PA46

Poles	02	03	04	05	06	07	08	09	10	11	12	13
Dim C	7.62	11.43	15.24	19.05	22.86	26.67	30.48	34.29	38.1	41.91	45.72	49.53
Dim B	3.81	7.62	11.43	15.24	19.05	22.86	26.67	30.48	34.29	38.1	41.91	45.72
TOL	±0.10				±0.15				±0.20			
Poles	14	15	16	17	18	19	20	21	22	23	24	
Dim C	53.34	57.15	60.96	64.77	68.58	72.39	76.2	80.01	83.82	87.63	91.44	
Dim B	49.53	53.34	57.15	60.96	64.77	68.58	72.39	76.2	80.01	83.82	87.63	
TOL	±0.25				±0.30							

ANYTEK				CUSTOMER COPY			
ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD							
TITLE		OP-3.81mm series					
PART NO.		OPxx42xxxxxxG		DWG NO.		80P0201	
APPROVED		CHECKED	DESIGNED	DRAWN	CUST NO.		Tolerance
			Tony 2007.01.31	Tony 2007.01.31			X. ±0.50
					UNIT: mm		X.X ±0.30
					SCALE: NONE		X.XX ±0.10
					SHEET: 01/01		X° ±1°
					REV.: E		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Amphenol:

<u>OP0242000000G</u>	<u>OP0342000000G</u>	<u>OP0442000000G</u>	<u>OP0542000000G</u>	<u>OP0642000000G</u>	<u>OP0742000000G</u>
<u>OP0842000000G</u>	<u>OP0942000000G</u>	<u>OP1042000000G</u>	<u>OP1142000000G</u>	<u>OP1242000000G</u>	<u>OP1342000000G</u>
<u>OP1442000000G</u>	<u>OP1542000000G</u>	<u>OP1642000000G</u>	<u>OP1742000000G</u>	<u>OP1842000000G</u>	<u>OP1942000000G</u>
<u>OP2042000000G</u>	<u>OP2142000000G</u>	<u>OP2242000000G</u>	<u>OP2342000000G</u>	<u>OP2442000000G</u>	