


CONTACT POSITION	PIN ASSIGNMENT	WIRE COLOUR
1	BI_DA+	BLUE
2	BI_DA-	WHITE



THIS DOCUMENT CONTAINS PROPRIETARY INFORMATION AND SUCH INFORMATION MAY NOT BE DISCLOSED TO OTHERS FOR ANY PURPOSE OR USED FOR MANUFACTURING PURPOSES WITHOUT WRITTEN PERMISSION FROM AMPHENOL CANADA CORP.

REVISIONS			
REV	DESCRIPTION, ECN, EAR NO.	DATE	APP'D
A	PROPOSAL DRAWING (EAR 14832)	JUN03/20	M.P.
B	PRODUCT DRAWING (EAR 14903)	JUL13/21	M.P.

ORDERING CODE: **M S P E - C 2 L 0 - B X X 10**

MSPE SERIES  
CABLE ASSEMBLY  
IP20 RATING  
LATCH-LOCKING  
PLUG ON BOTH ENDS  
CABLE LENGTH (DIMENSION 'L')  
STANDARD

CABLE LENGTH ORDERING CODES	
20 TO 99	LENGTH IN CM
A0 TO A9	1 METER + 0 TO 9 DECIMETERS
B0 TO B9	2 METERS + 0 TO 9 DECIMETERS
C0 TO C9	3 METERS + 0 TO 9 DECIMETERS
D0 TO D9	4 METERS + 0 TO 9 DECIMETERS
E0 TO E9	5 METERS + 0 TO 9 DECIMETERS
F0 TO F9	6 METERS + 0 TO 9 DECIMETERS
G0 TO G9	7 METERS + 0 TO 9 DECIMETERS
H0 TO H9	8 METERS + 0 TO 9 DECIMETERS
J0 TO J9	9 METERS + 0 TO 9 DECIMETERS
K0 TO K9	10 METERS + 0 TO 9 METERS
L0 TO L9	20 METERS + 0 TO 9 METERS
M0 TO M9	30 METERS + 0 TO 9 DECAMETERS

CABLE LENGTH ORDERING CODE EXAMPLES:  
75cm = 75 6.3m = F3 25m = L5 80m = M5

#### NOTES:

- MATERIAL: RoHS COMPLIANT PER EU DIRECTIVE 2011/65/EU AND AMENDMENTS.
  - EMI SHIELD: STAINLESS STEEL, NICKEL PLATED
  - CONTACTS: COPPER ALLOY PLATED WITH NICKEL OVERALL, 0.76µm (30µ") GOLD ON THE MATING AREA & GOLD FLASH ON THE TAILS
  - HOUSING, CAP, & INSERTS: ENGINEERING THERMOPLASTIC, UL94V-0 FLAMMABILITY RATING, COLOUR: BLACK
  - GROMMET: SILICONE RUBBER, COLOUR: BLACK, UL94V-0 FLAMMABILITY RATING
  - CABLE: 24AWG TINNED COPPER CONDUCTOR, PP INSULATION, AL-MYLAR WRAPPING, TINNED COPPER BRAID, PUR JACKET
- DESIGNED IN ACCORDANCE WITH IEC 63171-6 STANDARD.
  - COMPATIBLE WITH 10BASE-T1, 100BASE-T1, & 1000BASE-T1
  - COMPATIBLE WITH POWER OVER DATA LINES (PoDL)
- ELECTRICAL CHARACTERISTICS:
  - CURRENT RATING: 4A
  - VOLTAGE RATING: 60VDC
- OPERATING TEMPERATURE: -40° TO +80°C

UNLESS SPECIFIED OTHERWISE	DRAWN	M. PAHULJE	JUN02/20
PRIMARY UNITS MILLIMETRES	CHECKED		
SECONDARY INCHES	M.E. APP'D		
REFERENCE IN PARENTHESES	Q.A. APP'D		
GENERAL TOLERANCES	DWG APPR.		
1 DECIMAL PLACE	ENG. REL. NO.	EAR 14832	
2 DECIMAL PLACES ±0.15	REF.		
3 DECIMAL PLACES	THIRD ANGLE PROJECTION		
ANGULAR DEGREES	DO NOT SCALE DRAWING		

<b>Amphenol Canada Corp.</b> Commercial Products			
MSPE SERIES, CABLE ASSEMBLY, IP20 PLUG BOTH ENDS, RoHS COMPLIANT			
DWG. NO.	P-MSPE-C2L0-BXX10		REV B
CODE ID NO. 03554	DWG SIZE: X	SCALE: 4:1	SHEET 1 OF 1

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

## Amphenol:

[MSPE2P241CG30BP](#) [MSPE2P241DG30BP](#) [MSPEC2L0BC010](#) [MSPEC2L0BD010](#) [MSPEC2L0BE010](#)  
[MSPEP2L0C30](#) [MSPEP2L0C60](#) [MSPEP2L0C70](#) [MSPEP2L0CA0](#) [MSPEC2L0BL010](#) [MSPEC2L0BM210](#)  
[MSPEC2L0BM810](#) [MSPE-C2L0-BA010](#) [MSPEC2L0B3010](#) [MSPEC2L0BK010](#) [MSPEC2L0B5010](#) [MSPEC2L0BB010](#)