







N= Number of Poles
Dimension Dim A, B

Dim A	$N \times 10.0 + 2.0$
Dim B	$(N-1) \times 10.0$



SIGN	DATE	DESCRIPTION	APPROVER
	11/13'12	Change the screw plating specification	Guoxue
	11/13'12	Change the dimensional tolerance	Guoxue
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!			

MATERIALS ELECTRICAL

RATED VOLTAGE & CURRENT:	300 V, 25 A
WITHSTAND VOLTAGE:	AC 2000 V/Min
INSULATION RESISTANCE:	1000 M Ω OR MORE AT DC 500 V
OPERATING TEMPERATURE RANG:	-40 °C ~ +115 °C
SCREW TORQUE VALUE:	8.8 Lb-In.
WIRE RANGE:	22 - 12 AWG
1) MOLDED PARTS:	THERMOPLASTIC, UL 94 V-0 BLACK
2) TERMINAL:	BRASS, 0.8t, Tin PLATED
3) TERMINAL SCREWS:	STEEL, M3.5

APPROVAL:
Critical dimension:

Part No.:

YK 615 xx 0 x x 00G

NO. OF POLES
02: 2 POLES
03: 3 POLES
04: 4 POLES
:
30: 30 POLES

RoHS compliant
(lead<4%)
In copper Alloy

MARK

0: "@ " MAK
1: "ANY" MAK

TERMINAL & SCREW PLATED

0: TERMINAL & SCREW: G/F
 1: TERMINAL: G/F, SCREW: ZINC
2: TERMINAL: SN, SCREW: G/F
 3: TERMINAL: SN, SCREW: ZINC

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE	YK-615 W/O Flange Series										
PART NO.	YK615xx0xx00G				DWG NO.	8YK0001-615					
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.						Tolerance	
		Guoxue 2012.12.01	Guoxue 2012.12.01							UNIT: mm	X. ±0.50
					SCALE: NONE	X.X ±0.30					
						X.XX ±0.10					
						X° ±1°					
SHEET: 01/01				REV.: C							

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Amphenol:

<u>YK6150203000G</u>	<u>YK6150303000G</u>	<u>YK6150403000G</u>	<u>YK6150503000G</u>	<u>YK6150603000G</u>	<u>YK6150703000G</u>
<u>YK6150803000G</u>	<u>YK6150903000G</u>	<u>YK6151003000G</u>	<u>YK6151103000G</u>	<u>YK6151203000G</u>	<u>YK6151303000G</u>
<u>YK6151403000G</u>	<u>YK6151503000G</u>	<u>YK6151603000G</u>	<u>YK6151703000G</u>	<u>YK6151803000G</u>	<u>YK6151903000G</u>
<u>YK6152003000G</u>	<u>YK6152103000G</u>	<u>YK6152203000G</u>	<u>YK6152303000G</u>	<u>YK6152403000G</u>	<u>YK6152503000G</u>
<u>YK6152603000G</u>	<u>YK6152703000G</u>	<u>YK6152803000G</u>	<u>YK6152903000G</u>	<u>YK6153003000G</u>	