


Copied of this document and giving it to others and the use or communication of the contents thereof, are forbidden without express authority. Offenders are liable to the payment of damages. All rights are reserved in the event of the grant of a patent or the registration of the utility model or design.

Weitergabe sowie Vervielfältigung dieser Unterlage, Verwertung und Mitteilung ihres Inhalts nicht gestattet, soweit nicht ausdrücklich zugestanden. Zuwiderhandlungen verpflichten zu Schadenersatz. Alle Rechte für den Fall der Patenterteilung oder Gebrauchsmuster-Eintragung vorbehalten.



© Assembly instruction see N 22 091 0024

Number of contacts	Standard	3	4	5	5	6	7	7	8	12	14
Contact arrangement	IEC 61076-2-106	03-a	04-a	05-a	05-b	06-a	07-a	07-b	08-a	12-a	14-a
Rated voltage	IEC 60664-1	150 V		100 V						32 V	
Rated impulse withstand voltage	IEC 60664-1	2500 V		1500 V						800 V	
Pollution degree	IEC 60664-1	3 ⁿ									
Installation category	IEC 60664-1	III									
Insulation group	IEC 60664-1	II									
Current rating	IEC 60512-5-3	10A/+40°C		7A/+40°C						3A/+40°C	
Insulation resistance	IEC 60512-3-1	>10 ¹⁰ Ohm ²⁾									
Contact resistance	IEC 60512-2-1	<5mOhm									
Climatic category	IEC 60668-1	40 / 100 / 21									
Temperatur range		-40°C...+100°C									
IP degree	↑EC 60529	IP 68									
Insertion and withdrawal force	IEC 60512-13-2	25N	30N	35N	35N	50N	55N	55N	60N	50N	50N
mechanical operation	IEC 60512-9-1	≥500									
material housing		Zinc die cast, nickel plated									
dielectric material		Thermoplast									
sealing material		Chloroprene									
contacts		silver or gold plated, please order contacts separately acc. to drawing M-N 02 015 00XX X (3-8pol) or M-N 02 010 0158 X (12-14pol)									
termination technique		crimp									
wire gauge		0,09-1,0mm²			0,09-0,75mm²	0,09-1,0mm²	0,09-0,75mm²			0,09-0,25mm²	
flamability		UL 94 V0									
locking system		metal screw coupling; tightening torque 0,5 - 0,7Nm									

¹⁾ under operating conditions >10⁸ Ohm
²⁾ designed according pollution degree 2, can be used under pollution degree 3 if the rules according IEC 60664-1 are fulfilled
All technical data have been measured in a laboratory environment and can be different during practical usage of the product. Any product information is for descriptive usage only and not legally binding; particularly the information does not constitute or provide any legal guaranties ("Beschaffungsgarantie" or "Haltbarkeitgarantie").
Do not connect or disconnect under load. Metal housing parts shall be securely incorporated to protected ground.

	14 (14-a)	C091 11D014 000 4 U
	12 (12-a)	C091 11D012 000 4 U
	8 (08-a)	C091 11D008 000 4 U
	7 (07-b)	C091 11D107 000 4 U
	7 (07-a)	C091 11D007 000 4 U
	6 (06-a)	C091 11D006 000 4 U
	5 (05-b)	C091 11D105 000 4 U
	5 (05-a)	C091 11D005 000 4 U
	4 (04-a)	C091 11D004 000 4 U
	3 (03-a)	C091 11D003 000 4 U
Contact arrangement View on mating side	Number of contacts (Contact arrangement acc. IEC 61076-2-106)	Part number

Gewicht (errechnet) / Calc WT : g				Zul. Abw./Tolerances :		Maßstab / Scale : 2:1		A3		
Prüfmaß / Testdimension						Material: Oberfläche:				
Teileindex Partindexnumber										
						female cable connector for cable diameters 4-6mm				
				DIN / ISO 13715						
				2013	Datum/Date					Name
				Gez.	24.06.					Carle
				Drawn						
				Gepr.						
				Checked						
				Amphenol-Tuchel Electronics GmbH			M C091 11DXXX 000 4 U		Blatt/ Sheet 1	
02	201300837	04.12.13	IM						1 Bl.	
01	201300382	02.07.13	Cm							
Index	Änderung/Description	Datum/Date	Name				Ers. f. / Replacement for :			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[C09111D0070004U](#)