


RECOMMENDED P.C.B. LAYOUT

N = Number of poles
Dim L=Nx5.0
Dim P=(N-1)x5.0

	Dim L	Dim P
2-6p	±0.20	±0.15
7-12p	±0.25	±0.20
13-18p	±0.30	±0.25
19-24p	±0.40	±0.30



SECTION H-H

SIGN	DATE	DESCRIPTION	APPROVER
△	01.11'06	Standard spec is changed.	xionghaitao
△	10/9'06	VDE wire range changed from 0.75-1.5mm ² to 0.75-4.0mm ²	Steady
△	10/9'06	Solid wire and Stranded wire changed from 12-18 to 12-20	Steady
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!			

Material

- Terminal body
- (metal housing): Brass Stamped
- Terminal screw: Steel Zinc plating "+/-" slot type
- Wire guard: Stainless steel
- Surface of solder tail: Tin plated
- Insulator (housing): Thermoplastic (UL94V-0)

- △ Electrical cULus/VDE
- Voltage rating: 300VAC/450VAC
 - Current rating: 10A/17.5A
 - △ ● Wire range: 0.75-4.0mm²
 - △ ● Solid wire(AWG): 12-20
 - △ ● Stranded wire(AWG): 12-20
 - Torque: 3.5Lb-In/0.4Nm
 - Screw: M3
 - Wire strip length: 6-7mm
 - Withstanding Voltage: 1.6KV/2.5KV
 - Operating temperature: -40°C to +115°C
 - Soldering temperature: 250°C±10°C/5 Sec
 - SAFETY APPROVAL DATA:




T4 xx 04 x x xxxx G

02	2 CONTACTS	0	Black	0	4.4mm	0000	@ logo	RoHS
03	3 CONTACTS	5	Green	1	3.0mm	0091	ANY logo	Pb<40,000ppm
...	...	6	Blue				Any special item by customer request, please contact sales department.	
24	24 CONTACTS	8	Grey					

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATSOEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

				PROPRIETOR: PROPERTY OF ARYTER TECHNOLOGY CO., LTD			
TITLE	T4-5.0mm 2P-30P						
PART NO.	T4xx04xxxxxxG			DWG NO.	8T40001		
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.			
		Steady 2006.10.09	Steady 2006.10.09		UNIT: mm	X. ±0.50	
					SCALE: NONE	X.X ±0.30	
				SHEET: 01/01	REV: D	X.XX ±0.10	
						X° ±1°	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Amphenol:

<u>T40204500000G</u>	<u>T40304500000G</u>	<u>T40404500000G</u>	<u>T40504500000G</u>	<u>T40604500000G</u>	<u>T40704500000G</u>
<u>T40804500000G</u>	<u>T40904500000G</u>	<u>T41004500000G</u>	<u>T41104500000G</u>	<u>T41204500000G</u>	<u>T41304500000G</u>
<u>T41404500000G</u>	<u>T41504500000G</u>	<u>T41604500000G</u>	<u>T41704500000G</u>	<u>T41804500000G</u>	<u>T41904500000G</u>
<u>T42004500000G</u>	<u>T42104500000G</u>	<u>T42204500000G</u>	<u>T42304500000G</u>	<u>T42404500000G</u>	