


DIMENSION		Poles	Tolerance
Dim L	NX5.08	2p-6p	±0.15
Dim A	(N-1)X5.08	7p-12p	±0.25
		13p-18p	±0.35
		19p-24p	±0.40

SIGN	DATE	DESCRIPTION	APPROVER
△	3/22'06	Hole size changed from 0.5mm to 1.3mm	Tony
△	01/12 07	Soldering temperature changed from 245° to 250°	Tason
△	01/12 07	Part NO is Changed	Tason
△	6/04'08	Operating temperature is Changed	Marvin
△	6/04'08	Body type is Changed	Marvin
△	11/09'10	Add is " VDE "	Aaron
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!			

Material:

- Item 1 Terminal housing:Thermoplastic (UL 94V-0)
- Item 2 Clamp: Brass Ni plated
- Item 3 Wire guard solder pin:Brass Tin plated
- Item 4 Terminal screw: Steel Zinc plating"- "slot type


- △ Electrical cULus VDE
- Voltage rating: 300VAC 450V
  - Current rating: 20A 24A
  - Wire range : 0.2-2.5mm<sup>2</sup>
  - Solid wire(AWG): 12-30
  - Stranded wire(AWG): 12-30
  - Torque(Lb-In): 3.5 0.5 N.m
  - Screw: M3
  - Wire strip length: 6-7mm
  - Withstanding Voltage: 1.6KV 2.5KV
  - △ ● Operating temperature: -40°C to +115°C
  - △ ● Soldering temperature: 250°C±10°C/5 Sec
  - Safety Approval:



△ VJ xx 21 x 2 xxxx G

RoHS Pb<40,000ppm

No. of poles end stackable design	0 Black (RAL9005)	0000:"@ "Logo (Standard )
02 2 CONTACTS	2 Red (RAL3001/D)	000A:"ANYTEK" Logo
03 3 CONTACTS	3 Orange(RAL2011/P)	Any special item by customer request,
...	4 Yellow(RAL1018/A)	please contact sales department.
...	5 Green(RAL6018/T)	
24 24 CONTACTS	6 Blue (RAL5015/A)	
	8 Grey(RAL7035/D)	

<b>ANYTEK</b>				<b>CUSTOMER COPY</b>			
				ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD			
TITLE	VJ-5.08 Series 2P-24P Horizontal ( 180D wire inlet )-----Without cover						
PART NO.	VJxx21x2xxxxG			DWG NO.	8VJ0103		
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.			Tolerance
		Aaron 2010.11.09	Marvin 2008.06.04			UNIT: mm	X. ±0.50
						SCALE: NONE	X.X ±0.30
				SHEET: 01/01		REV.: F	X.XX ±0.10
							X* ±1°

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

## Amphenol:

<a href="#"><u>VJ0221520000G</u></a>	<a href="#"><u>VJ0321520000G</u></a>	<a href="#"><u>VJ0421520000G</u></a>	<a href="#"><u>VJ0521520000G</u></a>	<a href="#"><u>VJ0621520000G</u></a>	<a href="#"><u>VJ0721520000G</u></a>
<a href="#"><u>VJ0821520000G</u></a>	<a href="#"><u>VJ0921520000G</u></a>	<a href="#"><u>VJ1021520000G</u></a>	<a href="#"><u>VJ1121520000G</u></a>	<a href="#"><u>VJ1221520000G</u></a>	<a href="#"><u>VJ1321520000G</u></a>
<a href="#"><u>VJ1421520000G</u></a>	<a href="#"><u>VJ1521520000G</u></a>	<a href="#"><u>VJ1621520000G</u></a>	<a href="#"><u>VJ1721520000G</u></a>	<a href="#"><u>VJ1821520000G</u></a>	<a href="#"><u>VJ1921520000G</u></a>
<a href="#"><u>VJ2021520000G</u></a>	<a href="#"><u>VJ2121520000G</u></a>	<a href="#"><u>VJ2221520000G</u></a>	<a href="#"><u>VJ2321520000G</u></a>	<a href="#"><u>VJ2421520000G</u></a>	<a href="#"><u>VJ0321020000G</u></a>