

SIGN	DATE	DESCRIPTION	APPROVER
△	12/22/09	Add UL standard	Jacke
△	10/20/11	The dimensions are added	Aaron
△	11/18'13	Update the drawing	Chen Bo
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!			


Material:

- Item ㉔ Male contact pin: Copper, Tin plated
- Item ㉕ Terminal(housing): Thermoplastic (UL94 V-0)

Electrical:

- Voltage rating: 300V
- Current rating: 10A
- Withstanding Voltage: 1.6 KV
- Operating temperature: -40°C to +115°C
- Soldering temperature: 260°C±5°C/5 Sec
- △ ● Safety Approval: 
- Critical dimension: ▽

PART NO.	VS xx 51 x 0 xxxx G	
No. OF POLES		G RoHS compliant (lead<4%)
02 2 CONTACTS		In copper Alloy
03 3 CONTACTS		0000: "@" Logo (Standard)
...		000A: "ANYTEK" Mark
24 24 CONTACTS		Any special item by customer request.
	Color	please contact sales department.
	0 Black (RAL9005)	
	2 Red (RAL3001/D)	
	3 Orange(RAL2011/P)	
	4 Yellow(RAL1018/A)	
	5 Green(RAL6018/T)	
	6 Blue (RAL5015/A)	
	8 Grey(RAL7035/D)	
	9 White(RAL1102)	
	C Green(RAL6018/U)	



Dimension

N= Number of poles

Dim L	N×5.08	Poles	Tolerance
Dim B	(N-1)×5.08	2p-5p	±0.15
Dim C	(N-1)×5.08	6p-10p	±0.25
		11p-15p	±0.30
		16p-24p	±0.40

ANYTEK				CUSTOMER COPY			
ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD							
TITLE		VS 5.08 Series Close Vertical					
PART NO.		VSxx51x0xxxxG		DWG NO.		8VS0001	
APPROVED		CHECKED	DESIGNED	DRAWN	CUST NO.		Tolerance
			Chen Bo 11/18`13	Chen Bo 11/18`13		UNIT: mm	X. ±0.50
						SCALE: NONE	X.X ±0.30
						REV.: D	X.XX ±0.10
						SHEET: 01/01	X° ±1°

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Amphenol:

<u>VS0251500000G</u>	<u>VS0351500000G</u>	<u>VS0451500000G</u>	<u>VS0551500000G</u>	<u>VS0651500000G</u>	<u>VS0751500000G</u>
<u>VS0851500000G</u>	<u>VS0951500000G</u>	<u>VS1051500000G</u>	<u>VS1151500000G</u>	<u>VS1251500000G</u>	<u>VS1351500000G</u>
<u>VS1451500000G</u>	<u>VS1551500000G</u>	<u>VS1651500000G</u>	<u>VS1751500000G</u>	<u>VS1851500000G</u>	<u>VS1951500000G</u>
<u>VS2051500000G</u>	<u>VS2151500000G</u>	<u>VS2251500000G</u>	<u>VS2351500000G</u>	<u>VS2451500000G</u>	