



Copying of this document and giving it to others and the use or communication of the contents thereof, are forbidden without express authority. Offenders are liable to the payment of damages. All rights are reserved in the event of the grant of a patent or the registration of the utility model or design.

Weitergabe sowie Vervielfältigung dieser Unterlage, Verwertung und Mitteilung ihres Inhalts nicht gestattet, soweit nicht ausdrücklich zugestanden. Zuwiderhandlungen verpflichten zu Schadenersatz. Alle Rechte für den Fall der Patenterteilung oder Gebrauchsmuster-Eintragung vorbehalten.



*for 12, 14 and 19 pol = 2,7



	Number of contacts	Standard	3	4	5	5	6	7	7	8	12	14	14	19	
	Contact arrangement	IEC 61076-2-106	03-a	04-a	05-a	05-b	06-a	07-a	07-b	08-a	12-a	14-a	14-b	19-a	
D	Contact arrangement	IEC 60130-9 ⁿ	yes		no	yes		no	yes		no				
	Rated voltage ²⁾	IEC 60664-1	300 V (100 V)		300 V (63 V)	100 V (32 V)	300 V (63 V)		100 V (32 V)		150 V (32 V)		60 V (32 V)		
	Rated voltage	UL 1977	250V								60V				
	Rated impulse withstand voltage ²⁾	IEC 60664-1	1500 V (1500 V)			1200 V (800 V)	1500 V (1500 V)		1200 V (800 V)						
	Pollution degree ²⁾	IEC 60664-1	1 (3 ³⁾)												
	Installation category	IEC 60664-1	I												
C	Insulation group	IEC 60664-1	II, 400 ≤ CTI < 600												
	Current rating	IEC 60512-5-2 UL 1977	10A/+40°C		7A/+40°C						3A/+40°C				
	Insulation resistance	IEC 60512-3-1	>10 ¹⁰ Ohm ⁴⁾												
	Contact resistance	IEC 60512-2-1	<5mOhm												
	Climatic category	IEC 60668-1	40 / 100 / 56												
	Temperatur range	IEC 60668-1	-40°C...+100°C / -40°F...+212°F												
	Salt spray resistance	DIN IEC 60068-2-11, test Ka	720h												
	IP degree	IEC 60529	IP 69K / IP 67 / IP 65 (in mated condition)												
	Insertion and withdrawal force	IEC 60512-13-2	25N	30N	35N	35N	50N	55N	55N	60N	50N	50N	50N	60N	
	B	mechanical operation	IEC 60512-9-1	Silver ≥500 mating cycles / Gold ≥1000 mating cycles											
housing material			brass and / or zinc die cast, nickel plated												
dielectric material			thermoplastic												
sealing material			Chloroprene												
contacts			silver or gold plated												
termination technique			solder												
wire gauge			≤0,5mm² / 20 AWG								≤0,35mm² / 22 AWG				
flamability			UL 94 V0												
locking system		IEC 60130-9 DIN EN 61076-2-106	metal screw coupling; tightening torque 0,7 - 1,5 Nm												

ⁿ Edition 2000-05
ⁿ values in brackets are according to DIN EN 61076-2-106
ⁿ designed acc. pollution degree 2, can be used under pollution degree 3 when the rules of IEC 60644-1 are fulfilled
ⁿ under operating conditions >10⁸ Ohm

Do not connect or disconnect under load. Metal housing parts shall be securely incorporated to protected ground.

Remark for gold plated contacts:
In order to avoid brittle inter-metallic connections, gold plated terminals have to be tin-plated in the solder area.

All technical data have been measured in a laboratory environment and can be different during practical usage of the product. Any product information is for descriptive usage only and not legally binding, particularly the information does not constitute or provide any legal guaranties ("Beschaffenheitsgarantie" or "Haltbarkeitsgarantie").

	19 (19-a)	Ag	C091 31C019 100 2 U	F
		Au	C091 31C019 200 2 U	
	14 (14-b)	Ag	C091 31C114 100 2 U	
		Au	C091 31C114 200 2 U	
	14 (14-a)	Ag	C091 31C014 100 2 U	E
		Au	C091 31C014 200 2 U	
	12 (12-a)	Ag	C091 31C012 100 2 U	
		Au	C091 31C012 200 2 U	
	8 (08-a)	Ag	C091 31C008 100 2 U	D
		Au	C091 31C008 200 2 U	
	7 (07-b)	Ag	C091 31C107 100 2 U	
		Au	C091 31C107 200 2 U	
	7 (07-a)	Ag	C091 31C007 100 2 U	D
		Au	C091 31C007 200 2 U	
	6 (6-a)	Ag	C091 31C006 100 2 U	
		Au	C091 31C006 200 2 U	
	5 (05-b)	Ag	C091 31C105 100 2 U	C
		Au	C091 31C105 200 2 U	
	5 (05-a)	Ag	C091 31C005 100 2 U	
		Au	C091 31C005 200 2 U	
	4 (04-a)	Ag	C091 31C004 100 2 U	
		Au	C091 31C004 200 2 U	
	3 (03-a)	Ag	C091 31C003 100 2 U	B
		Au	C091 31C003 200 2 U	
Contact arrangement View on mating side	Number of contacts (Contact arrangement acc DIN EN 61076-2-106)	contact plating	Part number	

Gewicht (errechnet) / Calc WT: 15,562 g				Zul. Abw./Tolerances:		Maßstab / Scale : 2:1		A3			
 Prüfmaß / Testdimension				ISO 2768-c		 DIN / ISO 13715		CUSTOMER DRAWING			
Teileindex / Partindexnumber:						Male receptacle rear mounting					
Bagatelle change: 23.02.2021 MCARLE											
				Gez.	10.06.2020						
				Drawn	MCARLE						
				Status	Released						
				Gepr.	11.01.2021						
				Checked	MBERTSCH						
				Amphenol Tuchel Industrial GmbH		M C091 31CXXX X00 2 U				Blatt/ Sheet 1	
02	202000083	26.10.2020	MCARL							1 Bl.	
Index	Änderung/ Description	Datum/ Date	Name			Ers. f. / Replacement for : M-C091 31CXXX X00 2 U Rev.01					

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[C091 31C007 100 2](#)