

SECTION A-A

Dimension L&B&C

DIM B	(N-1)×15.0
DIM C	(N-1)×15.0+34.0
DIM L	(N-1)×15.0+45.0

N=Number of poles

Poles	L&B Tolerance
1P-2P	±0.30
2P-4P	±0.50
5P-10P	±0.80

SIGN	DATE	DESCRIPTION	APPROVER
△			
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!			

Material:

- Item 1 Terminal housing :Thermoplastic (UL 94V-0)
- Item 2 Clamp : Steel Stamping , Zinc plated
- Item 3 Wire guard solder pin : Copper , Tin plated
- Item 4 Terminal screw: Zinc plating"-slot type
- Electrical
- Voltage rating: 600V
- Current rating: 127A
- Wire range:
- Solid wire(AWG): 1-20
- Stranded wire(AWG): 1-20
- Torque(Lb-In): 36.5
- Screw: M6
- Wire strip length: 19-20mm
- Withstanding Voltage: 2.2KV
- Operating temperature: -40° C to +115° C
- Soldering temperature: 260° C±5° C/5 Sec
- Safety Approval:
- Critical dimension:

K9 xx C1 x 31 xxx G

POLES

01 01 POLES  
02 02 POLES  
03 03 POLES  
.....  
10 10 POLES

COLOR

0 BLACK  
5 Green  
(RAL6018/T)  
6 Blue  
8 Grey  
(RAL7035/D)  
C Green  
(RAL6018/U)

000:"@Logo (Standard )


00A:"ANYTEK"Logo  
Any special item by  
customer request,  
please contact sales  
department.

G RoHS compliant  
(lead<4%)  
In copper Alloy

**ANYTEK**

**CUSTOMER COPY**

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE		K9 15.0 Series With flange ( Double-handed )				
PART NO.		K9xxC1x31xxxG		DWG NO.	8K90006	
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.		
		Guoxue 2013.03.06	Guoxue 2013.03.06		UNIT: mm	X. ±0.50
					SCALE: NONE	X.X ±0.30
					REV.: A1	X.XX ±0.10
					SHEET: 01/01	X* ±1*

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

## Amphenol:

<a href="#">K902C1031000G</a>	<a href="#">K902C1231000G</a>	<a href="#">K902C1331000G</a>	<a href="#">K902C1431000G</a>	<a href="#">K902C1531000G</a>	<a href="#">K902C1631000G</a>
<a href="#">K902C1831000G</a>	<a href="#">K902C1931000G</a>	<a href="#">K902C1C31000G</a>	<a href="#">K903C1031000G</a>	<a href="#">K903C1231000G</a>	<a href="#">K903C1331000G</a>
<a href="#">K903C1431000G</a>	<a href="#">K903C1531000G</a>	<a href="#">K903C1631000G</a>	<a href="#">K903C1831000G</a>	<a href="#">K903C1931000G</a>	<a href="#">K903C1C31000G</a>
<a href="#">K904C1031000G</a>	<a href="#">K904C1231000G</a>	<a href="#">K904C1331000G</a>	<a href="#">K904C1431000G</a>	<a href="#">K904C1531000G</a>	<a href="#">K904C1631000G</a>
<a href="#">K904C1831000G</a>	<a href="#">K904C1931000G</a>	<a href="#">K904C1C31000G</a>	<a href="#">K905C1031000G</a>	<a href="#">K905C1231000G</a>	<a href="#">K905C1331000G</a>
<a href="#">K905C1431000G</a>	<a href="#">K905C1531000G</a>	<a href="#">K905C1631000G</a>	<a href="#">K905C1831000G</a>	<a href="#">K905C1931000G</a>	<a href="#">K905C1C31000G</a>
<a href="#">K906C1031000G</a>	<a href="#">K906C1231000G</a>	<a href="#">K906C1331000G</a>	<a href="#">K906C1431000G</a>	<a href="#">K906C1531000G</a>	<a href="#">K906C1631000G</a>
<a href="#">K906C1831000G</a>	<a href="#">K906C1931000G</a>	<a href="#">K906C1C31000G</a>	<a href="#">K907C1031000G</a>	<a href="#">K907C1231000G</a>	<a href="#">K907C1331000G</a>
<a href="#">K907C1431000G</a>	<a href="#">K907C1531000G</a>	<a href="#">K907C1631000G</a>	<a href="#">K907C1831000G</a>	<a href="#">K907C1931000G</a>	<a href="#">K907C1C31000G</a>
<a href="#">K908C1031000G</a>	<a href="#">K908C1231000G</a>	<a href="#">K908C1331000G</a>	<a href="#">K908C1431000G</a>	<a href="#">K908C1531000G</a>	<a href="#">K908C1631000G</a>
<a href="#">K908C1831000G</a>	<a href="#">K908C1931000G</a>	<a href="#">K908C1C31000G</a>	<a href="#">K909C1031000G</a>	<a href="#">K909C1231000G</a>	<a href="#">K909C1331000G</a>
<a href="#">K909C1431000G</a>	<a href="#">K909C1531000G</a>	<a href="#">K909C1631000G</a>	<a href="#">K909C1831000G</a>	<a href="#">K909C1931000G</a>	<a href="#">K909C1C31000G</a>
<a href="#">K910C1031000G</a>	<a href="#">K910C1231000G</a>	<a href="#">K910C1331000G</a>	<a href="#">K910C1431000G</a>	<a href="#">K910C1531000G</a>	<a href="#">K910C1631000G</a>
<a href="#">K910C1831000G</a>	<a href="#">K910C1931000G</a>	<a href="#">K910C1C31000G</a>			