


P.C.B. LAYOUT



SIGN	DATE	DESCRIPTION	APPROVER
△			
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!			

### Material

- Item ① Terminal body(metal housing): Brass(CuZn),Tin plated
- Item ② Terminal screw: Steel Zinc plating "-" slot type
- Item ③ Wire guard :stainless steel
- Item ④ Insulator (housing): Thermoplastic (UL94V-0)

### Electrical UL / CSA

- Voltage rating: 125V/125V
- Current rating: 10A/10A
- Wire range:
- Solid wire(AWG): 16-26 / 16-26
- Stranded wire(AWG): 16-26 / 16-26
- Torque: 1.7Lb-In/4kgf.cm
- Screw: M2
- Wire strip length: 5-6mm
- Withstanding Voltage: 1.25KV/1.25KV
- Operating temperature: -40°C to +115°C
- Soldering temperature: 260°C±5°C/5 Sec
- Safety Approval:
- Critical dimension:

TF xx 0 1 x x xxxx G


POLES	COLOR	DIM A Length	G RoHS compliant (Lead <4%) In copper Alloy
02 02 POLES	0 BLACK	0 4.4mm	000 0 @ logo
03 03 POLES	5 GREEN(RAL6018/T)	1 3.8mm	000 A ANY logo
6 BLUE	6 BLUE	2 3.5mm	Any special item by customer request, please contact sales department.
... 8 Grey(RAL7035/D)	8 Grey(RAL7035/D)		
24 24 POLES	C GREEN(RAL6018/U)		

Poles Dim	02	03	04	05	06	07	08	09	10	11	12	13
Dim L	7.00	10.50	14.00	17.50	21.00	24.50	28.00	31.50	35.00	38.50	42.00	45.50
Dim B	3.50	7.00	10.50	14.00	17.50	21.00	24.50	28.00	31.50	35.00	38.50	42.00
TOL	±0.15				±0.20				±0.25			
Poles Dim	14	15	16	17	18	19	20	21	22	23	24	
Dim L	49.00	52.50	56.00	59.50	63.00	66.50	70.00	73.50	77.00	80.50	84.00	
Dim B	45.50	49.00	52.50	56.00	59.50	63.00	66.50	70.00	73.50	77.00	80.50	
TOL	±0.25		±0.35				±0.40					

# ANYTEK

## CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE	TF 3.5 series “-”						
PART NO.	TFxx01xxxxxxG			DWG NO.	8TF0101		
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.			Tolerance
		Guoxue 2012.11.09	Guoxue 2012.11.09		UNIT: mm		X. ±0.50
					SCALE: NONE		X.X ±0.30
					REV.: B		X.XX ±0.10
				SHEET: 01/01			X° ±1°

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

## Amphenol:

<a href="#"><u>TF0201610000G</u></a>	<a href="#"><u>TF0301610000G</u></a>	<a href="#"><u>TF0401610000G</u></a>	<a href="#"><u>TF0501610000G</u></a>	<a href="#"><u>TF0601610000G</u></a>	<a href="#"><u>TF0701610000G</u></a>
<a href="#"><u>TF0801610000G</u></a>	<a href="#"><u>TF0901610000G</u></a>	<a href="#"><u>TF1001610000G</u></a>	<a href="#"><u>TF1101610000G</u></a>	<a href="#"><u>TF1201610000G</u></a>	<a href="#"><u>TF1301610000G</u></a>
<a href="#"><u>TF1401610000G</u></a>	<a href="#"><u>TF1501610000G</u></a>	<a href="#"><u>TF1601610000G</u></a>	<a href="#"><u>TF1701610000G</u></a>	<a href="#"><u>TF1801610000G</u></a>	<a href="#"><u>TF1901610000G</u></a>
<a href="#"><u>TF2001610000G</u></a>	<a href="#"><u>TF2101610000G</u></a>	<a href="#"><u>TF2201610000G</u></a>	<a href="#"><u>TF2301610000G</u></a>	<a href="#"><u>TF2401610000G</u></a>	