





SIGN	DATE	DESCRIPTION	APPROVER
△			
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!			



SECTION A-A

N=Number of poles

Dimension

DIM A	N×5.08
DIM B	(N-1)×5.08

POLES	TOL
2p-6p	±0.15
7p-12p	±0.20
13p-16p	±0.30
17p-24p	±0.40

Material

- Item a Terminal body:Thermoplastic (UL94V-0)
- Item b Terminal body:Thermoplastic (UL94V-0)
- Item c Terminal lever:Thermoplastic (UL94V-0)
- Item d Wire guard:Stainless Steel
- Item e Female contact:PhBz (CuSn) Tin plated

Electrical cULus

- Voltage rating:300V
- Current rating:10A
- Solid wire(AWG):12-26
- Stranded wire(AWG):12-26
- Wire strip length:9-10mm
- Withstanding Voltage:1.6KV
- Operating temperature:-40°C to +115°C

HW xx 50 x 4 xxxx G

02 2 CONTACTS	0 Black	0000 Standard @ Logo	RoHS
03 3 CONTACTS	5 Green	000A Standard ANY Logo	Pb<40,000ppm
... ..	6 Blue	Any special item by customer request, please contact sales department.	
24 24 CONTACTS	8 Grey		

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE	HW 5.08 Series Contact in the Middle < W/o flange >						
PART NO.	HWxx50x4xxxx G			DWG NO.	8HW0301		
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.			Tolerance
		Runner 2010.04.06	Runner 2010.04.06		UNIT: mm		X. ±0.50
					SCALE: NONE		X.X ±0.30
							X.XX ±0.10
				SHEET: 01/01	REV.: B		X° ±1°

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Amphenol:

<u>HW0250540000G</u>	<u>HW0350540000G</u>	<u>HW0450540000G</u>	<u>HW0550540000G</u>	<u>HW0650540000G</u>	<u>HW0750540000G</u>
<u>HW0850540000G</u>	<u>HW0950540000G</u>	<u>HW1050540000G</u>	<u>HW1150540000G</u>	<u>HW1250540000G</u>	<u>HW1350540000G</u>
<u>HW1450540000G</u>	<u>HW1550540000G</u>	<u>HW1650540000G</u>	<u>HW1750540000G</u>	<u>HW1850540000G</u>	<u>HW1950540000G</u>
<u>HW2050540000G</u>	<u>HW2150540000G</u>	<u>HW2250540000G</u>	<u>HW2350540000G</u>	<u>HW2450540000G</u>	<u>HW1950040000G</u>
<u>HW2150840000G</u>	<u>HW2050040000G</u>	<u>HW2450040000G</u>	<u>HW0550040000G</u>	<u>HW0850840000G</u>	<u>HW2350040000G</u>
<u>HW2450840000G</u>	<u>HW2250040000G</u>	<u>HW1750040000G</u>	<u>HW2050840000G</u>	<u>HW1450040000G</u>	<u>HW1350040000G</u>
<u>HW2250840000G</u>	<u>HW1850840000G</u>	<u>HW1850040000G</u>	<u>HW1950840000G</u>	<u>HW1550040000G</u>	<u>HW1750840000G</u>
<u>HW2350840000G</u>	<u>HW1650840000G</u>	<u>HW1250840000G</u>	<u>HW2150040000G</u>	<u>HW1350840000G</u>	<u>HW1550840000G</u>
<u>HW1050840000G</u>	<u>HW1150040000G</u>	<u>HW1450840000G</u>	<u>HW1650040000G</u>	<u>HW1250040000G</u>	<u>HW0350840000G</u>
<u>HW0450840000G</u>	<u>HW0850040000G</u>	<u>HW0950040000G</u>	<u>HW0350040000G</u>	<u>HW0650040000G</u>	<u>HW0250840000G</u>
<u>HW0750840000G</u>	<u>HW1150840000G</u>	<u>HW0650840000G</u>	<u>HW1050040000G</u>	<u>HW0250040000G</u>	<u>HW0550840000G</u>
<u>HW0750040000G</u>	<u>HW0450040000G</u>	<u>HW0950840000G</u>			