



SIGN	DATE	DESCRIPTION	APPROVER
△			
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!			

Material:

- Item ① Insulator(housing): Thermoplastic (UL94V-0)
- Item ② Spring clamp: Stainless steel
- Item ③ Terminal Body(contact pin): Brass.
- Item ④ Insulator(Cover): Thermoplastic (UL94V-0)

Electrical:

- Voltage rating: 300V
- Current rating: 10A
- Wire range:
- Solid wire(AWG): 12-28
- Stranded wire(AWG): 12-28
- Wire strip length: 8-9mm
- Withstanding Voltage: 1.6KV
- Operating temperature: -40°C to +115°C
- Soldering temperature: 250°C±10°C/5 Sec
- Safety Approval: cULus



PCB Layout

H3 xx 0 0 x 0 xxx G

No. OF POLES
02: 2 POLES
:
24: 24 POLES

COLOR
0: BLACK
5: GREEN
6: BLUE
8: GREY


G: Pb<40000ppm
0000: Standard
Any special item by
customer request.
please contact sales
department.

POLE		2	3	4	5	6	7	8	9	10	11	12
A		11.50	16.50	21.50	26.50	31.50	36.50	41.50	46.50	51.50	56.50	61.50
B		5.00	10.00	15.00	20.00	25.00	30.00	35.00	40.00	45.00	50.00	55.00
Tol.		±0.15					±0.20					
POLE	13	14	15	16	17	18	19	20	21	22	23	24
A	66.50	71.50	76.50	81.50	86.50	91.50	96.50	101.50	106.50	111.50	116.50	121.50
B	60.00	65.00	70.00	75.00	80.00	85.00	90.00	95.00	100.00	105.00	110.00	115.00
Tol.		±0.25					±0.30					

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE		H3 5.0mm Series										
PART NO.		H3xx00x0xxxxG				DWG NO.		8H30001				
APPROVED		CHECKED	DESIGNED	DRAWN	CUST NO.						Tolerance	
			Tony 2008.05.29	Tony 2008.05.29			UNIT: mm		X.		±0.50	
							SCALE: NONE		X.X		±0.30	
					SHEET: 01/01		REV: B		X.XX		±0.10	
									X°		±1°	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Amphenol:

<u>H30200800000G</u>	<u>H30300800000G</u>	<u>H30400800000G</u>	<u>H30500800000G</u>	<u>H30600800000G</u>	<u>H30700800000G</u>
<u>H30800800000G</u>	<u>H30900800000G</u>	<u>H31000800000G</u>	<u>H31100800000G</u>	<u>H31200800000G</u>	<u>H31300800000G</u>
<u>H31400800000G</u>	<u>H31500800000G</u>	<u>H31600800000G</u>	<u>H31700800000G</u>	<u>H31800800000G</u>	<u>H31900800000G</u>
<u>H32000800000G</u>	<u>H32100800000G</u>	<u>H32200800000G</u>	<u>H32300800000G</u>	<u>H32400800000G</u>	<u>H30800500000G</u>