



SIGN	DATE	DESCRIPTION	APPROVER
△	03/18`11	Structure is changed	Runner
△	07/02`12	Rated current is changed from 15A to 10A	Runner
△	07/02`12	Add "cULus" Safety Approval logo	Runner
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!			

Material

● Item 1	Insulating body	Thermoplastic (UL94V-0)
● Item 2	Insulating cover	Thermoplastic (UL94V-0)
● Item 3	Wire guard	Stainless Steel
● Item 4	Contacts PIN	Brass Tin plated

Electrical

	cULus	IEC
● Rated voltage:	300V	400V
● Rated current:	10A	18A
● Wire range:		
● Solid wire:	28-16AWG	0.08-1.5mm ²
● Stranded wire:	28-16AWG	0.08-1.5mm ²
● Wire strip length:	8-9mm	
● withstanding voltage:	1.6kv	6kv
△ ● Safety Approval:		
● Critical dimension:		

Part No:



DS 240 xx 1 x xxx G

02 2 poles
03 3 poles
...
24 24 poles

Color
0 Black
5 Gree(RAL6018/T)
6 Blue
8 Grey(RAL7004/P)

RoHS compliant
(lead<4%)
In copper Alloy

0000:"@ "Logo (Standard)
000A:"ANYTEK"Logo
Any special item by
customer request,
please contact sales
department.



Dimension

DIM A	N×5.0+3.0
DIM B	N×5.0+15.1
DIM C	N×5.0+7.9


N=Number of poles

Poles	Tolerance
1P-6P	±0.20
5P-10P	±0.30
11P-15P	±0.40
15P-20P	±0.50
20P-24P	±0.60

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATSOEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE	DS 240 Series With Snap-IN Mounting Feet (With Cover)										
PART NO.	DS240xx1x000G				DWG NO.	8DS240-0002					
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.						Tolerance	
		Runner 2012.07.03	Tason 08/16`07		UNIT: mm				X.	±0.5	
					SCALE: NONE				X.X	±0.3	
				SHEET: 01/01	REV.: C				X.XX	±0.1	
									X°	±1°	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Amphenol:

<u>DS2400118000G</u>	<u>DS2400218000G</u>	<u>DS2400318000G</u>	<u>DS2400418000G</u>	<u>DS2400518000G</u>	<u>DS2400618000G</u>
<u>DS2400718000G</u>	<u>DS2400818000G</u>	<u>DS2400918000G</u>	<u>DS2401018000G</u>	<u>DS2401118000G</u>	<u>DS2401218000G</u>
<u>DS2401318000G</u>	<u>DS2401418000G</u>	<u>DS2401518000G</u>	<u>DS2401618000G</u>	<u>DS2401718000G</u>	<u>DS2401818000G</u>
<u>DS2401918000G</u>	<u>DS2402018000G</u>	<u>DS2402118000G</u>	<u>DS2402218000G</u>	<u>DS2402318000G</u>	<u>DS2402418000G</u>