


Copying of this document and giving it to others and the use or communication of the contents thereof, are forbidden without express authority. Offenders are liable to the payment of damages. All rights are reserved in the event of the grant of a patent or the registration of the utility model or design.

Weitergabe sowie Vervielfältigung dieser Unterlage, Verwertung und Mitteilung ihres Inhalts nicht gestattet, soweit nicht ausdrücklich zugestanden. Zuwiderhandlungen verpflichten zu Schadenersatz. Alle Rechte für den Fall der Patenterteilung oder Gebrauchsmuster-Eintragung vorbehalten.

INDUSTRIAL@AMPHENOL
TRUSTED GLOBALLY



D	Number of contacts	Standard	3	4	5	5	6	7	7	8	12	14	14	19	
	Contact arrangement	IEC 61076-2-106	03-a	04-a	05-a	05-b	06-a	07-a	07-b	08-a	12-a	14-a	14-b	19-a	
	Contact arrangement	IEC 60130-9 ^{b)}	yes		no	yes		no	yes		no				
	Rated voltage ²⁾	IEC 60664-1	300 V (100 V)		300 V (63 V)	100 V (32 V)	300 V (63 V)		100 V (32 V)		150 V (32 V)		60 V (32 V)		
	Rated voltage	UL 1977	250V									60V			
	Rated impulse withstand voltage ²⁾	IEC 60664-1	1500 V (1500 V)			1200 V (800 V)	1500 V (1500 V)		1200 V (800 V)						
	Pollution degree ²⁾	IEC 60664-1	1 (3 ³⁾)												
C	Installation category	IEC 60664-1	I												
	Insulation group	IEC 60664-1	II, 400 ≤ CTI < 600												
	Current rating	IEC 60512-5-2 UL 1977	10A/+40°C		7A/+40°C						3A/+40°C				
	Insulation resistance	IEC 60512-3-1	>10 ¹⁰ Ohm ⁴⁾												
	Contact resistance	IEC 60512-2-1	<5mOhm												
	Climatic category	IEC 60668-1	40 / 100 / 56												
	Temperatur range	IEC 60668-1	-40°C...+100°C / -40°F...+212°F												
	Salt spray resistance	DIN IEC 60068-2-11, test Ka	720h												
	IP degree	IEC 60529	IP 69K / IP 67 / IP 65 (in mated condition)												
	B	Insertion and withdrawal force	IEC 60512-13-2	25N	30N	35N	35N	50N	55N	55N	60N	50N	50N	50N	60N
mechanical operation		IEC 60512-9-1	Silver ≥500 mating cycles / Gold ≥1000 mating cycles												
housing material			brass and / or zinc die cast, nickel plated												
dielectric material			thermoplastic												
sealing material			Chloroprene												
contacts			silver or gold plated												
termination technique			solder												
wire gauge			≤0,5mm ² / 20 AWG									≤0,35mm ² / 22 AWG			
flamability			UL 94 V0												
locking system		IEC 60130-9 DIN EN 61076-2-106	metal screw coupling; tightening torque 0,7 - 1,5 Nm												

^a Edition 2000-05
^b values in brackets are according to DIN EN 61076-2-106
^c designed acc. pollution degree 2, can be used under pollution degree 3 when the rules of IEC 60644-1 are fulfilled
^d under operating conditions >10⁸ Ohm

Do not connect or disconnect under load. Metal housing parts shall be securely incorporated to protected ground.
Remark for gold plated contacts:
In order to avoid brittle inter-metallic connections, gold plated terminals have to be tin-plated in the solder area.
All technical data have been measured in a laboratory environment and can be different during practical usage of the product. Any product information is for descriptive usage only and not legally binding, particularly the information does not constitute or provide any legal guaranties ("Beschaffenheitsgarantie" or "Haltbarkeitsgarantie").

	19 (19-a)	C091 31F019 100 2 U	C091 31F019 200 2 U
	14 (14-b)	C091 31F114 100 2 U	C091 31F114 200 2 U
	14 (14-a)	C091 31F014 100 2 U	C091 31F014 200 2 U
	12 (12-a)	C091 31F012 100 2 U	C091 31F012 200 2 U
	8 (08-a)	C091 31F008 100 2 U	C091 31F008 200 2 U
	7 (07-b)	C091 31F107 100 2 U	C091 31F107 200 2 U
	7 (07-a)	C091 31F007 100 2 U	C091 31F007 200 2 U
	6 (06-a)	C091 31F006 100 2 U	C091 31F006 200 2 U
	5 (05-b)	C091 31F105 100 2 U	C091 31F105 200 2 U
	5 (05-a)	C091 31F005 100 2 U	C091 31F005 200 2 U
	4 (04-a)	C091 31F004 100 2 U	C091 31F004 200 2 U
	3 (03-a)	C091 31F003 100 2 U	C091 31F003 200 2 U
Contact arrangement View on mating side	Number of contacts (Contact arrangement acc. IEC 61076-2-106)	Part number-Ag	Part number-Au

Gewicht (errechnet) / Calc WT:				Zul. Abw./Tolerances:		Maßstab / Scale: 1:1		A3				
Prüfmaß / Testdimension				ISO 2768-c				CUSTOMER DRAWING				
Teileindex / Partindexnumber:												
Bagatelle change:												
				Gez.	20.08.2020	Female cable connector n/a for cable diameter 4-6mm						
				Drawn	MCARLE							
				Status	Released							
				Gepr.	02.03.2021							
				Checked	MBERTSCH							
				Amphenol Tuchel Industrial GmbH		M C091 31FXXX X00 2 U				Blatt/Sheet 1		
02	202100006	01.03.2021	MCARL							1 Bl.		
01	202000083	26.10.2020	MCARL									
Index	Änderung/Description		Datum/Date	Name			Ers. f. / Replacement for:					

FAI2021-000885
NXM-V01

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[C091 31F003 100 2](#)