



Copyright FCI.

DESCRIPTION	
FCI	10104319-001RLF 10104319-003RLF 10104319-009RLF

NOTES:
1.MATERIAL:BERYLLIUM COPPER ALLOY.
2.CONTACT PLATING:
CONTACT AREA:PLATING 1um Au over 1.0/3.0 um Ni UNDERPLATE.
or PLATING 0.05 to 0.15um Au over 1.0/3.0 um Ni UNDERPLATE.
△ or PLATING 1um GXT over 1.0/3.0 um Ni UNDERPLATE.
(1um GXT is 0.025~0.125um Au over 0.875um PdNi)
SOLDER AREA :PLATING 0.05 to 0.15um Au over 1.0/3.0um Ni UNDERPLATE.
3.PACKAGING: TAPE & REEL
4.PART NUMBER DESCRIPTION:
10104319-0 0 X X X
LF:LEAD FREE
R :TAPE AND REEL
CONTACT PLATING
1 :1um Au over Ni.
3 :0.05~0.15um Au over Ni.
△ 9 :1um GXT over Ni.

rev	ecn no	dr	date
A	DG09-0331	NZ	2009-11-09
B	DG11-0048	SM	2011-02-22
C	ELX-DG-011079-1	ANDY	2012-03-27
-	-	-	-
-	-	-	-

spec ref	*	dr	Louis Ng	2009/10/06	projection	mm	size	scale			
tolerance std	TOLERANCES UNLESS OTHERWISE SPECIFIED	eng	Andy Lu	2012/03/27			A4	16.000			
ASME Y14.5		chr	Young Ou	2012/03/28							
		appr	Pei-Ming Zheng	2012/03/28							
surface	linear				product family	-	ecn no	ELX-DG-011079-1			
ASME Y14.5	0.X								±0.3	rel level	Released
	0.XX								±0.15		
	0.XXX	±0.050	title	ANTENNA CONNECTOR	dwg no	10104319	rev				
	angular	0°						±2°	cat. no.	10076429	Product - Customer Drw
		www.fci.com									

PrintE File - REV C - 2009-06-09

PDS: Rev :C

STATUS:Released

Printed: Mar 28, 2012

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[FCI / Amphenol:](#)

[10104319003RL](#) [10104319009RL](#) [10104319001RL](#) [10104319-003RLF](#)