






spec ref		GS-12-588, GS-20-12		dr	Jim Swain		2010/03/23		projection		MM		size	A2		scale	4:1				
tolerance std		TOLERANCES UNLESS OTHERWISE SPECIFIED		eng	Matthew Cheong		2014/04/04						ecn no		ELX-S-17348-1						
chr	-			-																	
ASME Y14.5				Chen-Hong Tan		2014/04/08		product family											XCede		Released
surface 		linear		0.X		±0.2				title		RECEPT MODULE, RIGHT ANGLE 8-COLUMN, 6-PAIR		dwg no		10105010		rev		B	
		0.XX		±0.13																	
		0.XXX		±-																	
ASME Y14.5		angular		0°		±3°		www.fci.com		cat. no. SEE PART NUMBER TABLE		Product - Customer Drw		sheet 1 of 5							



1		2		3		4		5		6		7		8	
A	PART NUMBER	LEAD FREE	MODULE DESCRIPTION AND USAGE NOTES	TELCORDIA APPLICATION (NOTE 16)	MODULE TYPE	IMPEDANCE	COMPLIANT TAIL (EON)								
							SIZE	DRILL DIAMETER	LENGTH (DIM K)						
	10105010-101	NO	SEE NOTES 6 & 14	CO	HSD	100Ω	STD	0.57 (.0225")	2.0						
	10105010-101LF	YES													
	10105010-111	NO	SEE NOTES 6 & 15												
	10105010-111LF	YES													
	10105010-501	NO	SEE NOTES 6 & 14	UE	HSD	100Ω	STD	0.57 (.0225")	2.0						
	10105010-501LF	YES													
	10105010-511	NO	SEE NOTES 6 & 15												
	10105010-511LF	YES													
	10105010-102	NO	SEE NOTES 6 & 14	CO	HSD	100Ω	MICRO	0.45 (.0177")	1.5						
	10105010-102LF	YES													
	10105010-112	NO	SEE NOTES 6 & 15												
	10105010-112LF	YES													
	10105010-502	NO	SEE NOTES 6 & 14	UE	HSD	100Ω	MICRO	0.45 (.0177")	1.5						
	10105010-502LF	YES													
10105010-512	NO	SEE NOTES 6 & 15													
10105010-512LF	YES														
10105010-103	NO	SEE NOTES 6 & 14	CO	LC	100Ω	STD	0.57 (.0225")	2.0							
10105010-103LF	YES														
10105010-113	NO	SEE NOTES 6 & 15													
10105010-113LF	YES														
10105010-503	NO	SEE NOTES 6 & 14	UE	LC	100Ω	STD	0.57 (.0225")	2.0							
10105010-503LF	YES														
10105010-513	NO	SEE NOTES 6 & 15													
10105010-513LF	YES														
10105010-104	NO	SEE NOTES 6 & 14	CO	LC	100Ω	MICRO	0.45 (.0177")	1.5							
10105010-104LF	YES														
10105010-114	NO	SEE NOTES 6 & 15													
10105010-114LF	YES														
10105010-504	NO	SEE NOTES 6 & 14	UE	LC	100Ω	MICRO	0.45 (.0177")	1.5							
10105010-504LF	YES														
10105010-514	NO	SEE NOTES 6 & 15													
10105010-514LF	YES														

FCI

Copyright FCI.

spec ref		GS-12-588, GS-20-121		dr	Jim Swain	20100323	projection	MM	size	A2	scale	4:1		
tolerance std	TOLERANCES UNLESS OTHERWISE SPECIFIED			eng	Matthew Cheong	20140404			ecn no				ELX-S-17348-1	
ASME Y14.5				chr	-	rel level			Released					
				appr	Chen-Hong Tan	20140408			product family			XCede		
surface		linear	0.X	±0.2		title	RECEPT MODULE, RIGHT ANGLE 8-COLUMN, 6-PAIR			diag no	10105010		rev	B
			0.XX	±0.13										
			0.XXX	±-										
ASME Y14.5	angular	0°	±3°		www.fci.com	cat. no.	SEE PART NUMBER TABLE		Product - Customer Drw		sheet 3 of 5			

Pro/E File - REV C - 2009-06-09

1

2

3

4



5

PDS: Rev :B

STATUS:Released

Printed: Apr 09, 2014

1		2		3		4		5		6		7		8																																
PART NUMBER	LEAD FREE	MODULE DESCRIPTION AND USAGE NOTES	TELCORDIA APPLICATION (NOTE 16)	MODULE TYPE	IMPEDANCE	COMPLIANT TAIL (EON)																																								
						SIZE	DRILL DIAMETER	LENGTH (DIM K)																																						
10105010-105	NO	SEE NOTES 6 & 14	CO	HSD	85Ω	STD	0.57 (.0225")	2.0																																						
10105010-105LF	YES																																													
10105010-115	NO	SEE NOTES 6 & 15																																												
10105010-115LF	YES																																													
10105010-505	NO	SEE NOTES 6 & 14	UE												85Ω	STD	0.57 (.0225")	2.0																												
10105010-505LF	YES																																													
10105010-515	NO	SEE NOTES 6 & 15																																												
10105010-515LF	YES																																													
10105010-605LF 	YES	SEE NOTE 6, 14 & 17	CO																						85Ω	STD	0.57 (.0225")	2.0																		
10105010-615LF 	YES	SEE NOTE 6, 15 & 17																																												
10105010-106	NO	SEE NOTES 6 & 14	CO																																85Ω	MICRO	0.45 (.0177")	1.5								
10105010-106LF	YES																																													
10105010-116	NO	SEE NOTES 6 & 15																																												
10105010-116LF	YES																																													
10105010-506	NO	SEE NOTES 6 & 14	UE	85Ω	MICRO	0.45 (.0177")	1.5																																							
10105010-506LF	YES																																													
10105010-516	NO	SEE NOTES 6 & 15																																												
10105010-516LF	YES																																													
10105010-606LF 	YES	SEE NOTE 6, 14 & 17	CO											85Ω	MICRO	0.45 (.0177")	1.5																													
10105010-616LF 	YES	SEE NOTE 6, 15 & 17																																												
10105010-107	NO	SEE NOTES 6 & 14	CO																					LC	85Ω	STD	0.57 (.0225")	2.0																		
10105010-107LF	YES																																													
10105010-117	NO	SEE NOTES 6 & 15																																												
10105010-117LF	YES																																													
10105010-507	NO	SEE NOTES 6 & 14	UE																																LC	85Ω	STD	0.57 (.0225")	2.0							
10105010-507LF	YES																																													
10105010-517	NO	SEE NOTES 6 & 15																																												
10105010-517LF	YES																																													
10105010-108	NO	SEE NOTES 6 & 14	CO	LC	85Ω	MICRO	0.45 (.0177")	1.5																																						
10105010-108LF	YES																																													
10105010-118	NO	SEE NOTES 6 & 15																																												
10105010-118LF	YES																																													
10105010-508	NO	SEE NOTES 6 & 14	UE												LC	85Ω	MICRO	0.45 (.0177")	1.5																											
10105010-508LF	YES																																													
10105010-518	NO	SEE NOTES 6 & 15																																												
10105010-518LF	YES																																													

spec ref		GS-12-588, GS-20-121		dr	Jim Swain	2010/03/23	projection	MM		size	A2	scale	4:1		
tolerance std		TOLERANCES UNLESS OTHERWISE SPECIFIED		eng	Matthew Cheong	2014/04/04			ecn no	ELX-S-17348-1					
ASME Y14.5				chr	-	-				Released					
				appr	Chen-Hong Tan	2014/04/08				product family		XCede	rel level		
surface			linear	0.X	±0.2		title				8-COLUMN, 6-PAIR	dwg no	10105010	rev	B
				0.XX	±0.13										
				0.XXX	±-										
ASME Y14.5			angular	0°	±3°	www.fci.com	cat. no. SEE PART NUMBER TABLE		Product - Customer Drw		sheet 4 of 5				

1

2

3



4

5

PDS: Rev :B

STATUS:Released

Printed: Apr 09, 2014

spec ref	GS-12-588, GS-20-12			dr	Jim Swain		2010/03/23				size	A2		scale	4:1					
tolerance std	TOLERANCES UNLESS OTHERWISE SPECIFIED			eng	Matthew Cheong		2014/04/04				ecn no	ELX-S-17348-1								
ASME Y14.5				chr	-		-				rel level	Released								
				appr	Chen-Hong Tan		2014/04/08		product family			XCede								
surface		linear	0.X	±0.2			title	RECEIPT MODULE, RIGHT ANGLE 8-COLUMN, 6-PAIR					dwg no	10105010					rev	B
			0.XX	±0.13																
ASME Y14.5		angular	0°	±3°																

NOTES:

1. CONNECTOR MATERIALS:

HOUSING: THERMOPLASTIC, GRAY, UL 94V-0
WAFERS: THERMOPLASTIC, GRAY, UL 94V-0
CONTACTS: HIGH-PERFORMANCE COPPER ALLOY
ORGANIZER: STAINLESS STEEL

2. CONTACT PLATING:

SEPARABLE INTERFACE:
PERFORMANCE-BASED PLATING, QUALIFIED TO MEET THE REQUIREMENTS
OF FCI PRODUCT SPECIFICATION GS-12-588, INCLUDING THE TELCORDIA
GR-1217-CORE (NOVEMBER 1995) CENTRAL OFFICE TEST SEQUENCE.

PRESS-FIT TAILS:
TIN-LEAD ALLOY OVER NICKEL, OR
TIN OVER NICKEL (LEAD-FREE)
SEE "LEAD-FREE" COLUMN IN PART NUMBER TABLE

3. PRODUCT SPECIFICATION: GS-12-588

4. APPLICATION SPECIFICATION: GS-20-121

5. PRODUCT MARKING: APPLIED TO CUSTOM MONOBLOCK ASSEMBLY

6. XCede® MODULES ARE DESIGNED TO BE STACKED INTO A MONOBLOCK ASSEMBLY,
JOINED TOGETHER BY A COMMON STAMPED METAL ORGANIZER. INDIVIDUALLY
ASSEMBLED MODULES ARE OFFERED FOR PURPOSES OF SAMPLING AND INITIAL
DESIGN-IN EVALUATION AS IDENTIFIED IN THE PART NUMBER TABLE.

7. DRAWING IS INTENDED FOR LAYOUT PURPOSES ONLY.

8. STATED PAD SIZE MAY REQUIRE FILLETING. REFER TO FCI APPLCATION SPECIFICATION
FOR ROUTING GUIDELINES.

9. SEE PCB REQUIREMENTS TABLE AND FCI APPLICATION SPECIFICATION
FOR PCB HOLE SPECIFICATIONS AND ROUTING GUIDELINES.

10. LEAD-FREE PRODUCT MEETS THE EUROPEAN UNION DIRECTIVES AND OTHER
COUNTRY REGULATIONS AS DESCRIBED IN FCI SPECIFICATION GS-22-008.

11. REQUIREMENTS APPLY TO THE MAJORITY OF PCB FINISHES. SEE APPLICATION SPECIFICATION
GS-20-121 FOR ADDITIONAL DETAILS AND EXCEPTIONS FOR LEAD-FREE HASL AND IMMERSION
SILVER FINISHES.

12. PACKAGING MEETS FCI SPECIFICATION GS-14-920 FOR LEAD-FREE LABELING.

13. THE SPECIFIED KEEP-OUT AREA IS REQUIRED FOR CONNECTOR REPAIRABILITY.


14. INDIVIDUAL MODULE ASSEMBLIES INCLUDING ASSEMBLED METAL ORGANIZER. THESE MODULES
ARE TO BE USED FOR SAMPLING AND INITIAL EVALUATION ONLY. REF NOTE 6.

15. INDIVIDUAL MODULES TO BE SPECIFIED AND USED IN CUSTOM MONOBLOCK CONFIGURATIONS.
REFERENCE NOTE 6 AND FCI APPLICATION SPECIFICATION FOR ADDITIONAL CONFIGURATION
GUIDELINES AND INFORMATION.


16. CO = TECORDIA GR-1217-CORE CENTRAL OFFICE APPLICATIONS
UE = TELCORDIA GR-1217 UNCONTROLLED ENVIRONMENT APPLICATIONS

17. CUSTOMER SPECIAL PARTNO.

18. A SYMBOL WILL BE NEXT TO ANY DIMENSION, NOTES OR VIEW WHICH HAS BEEN MODIFIED
WITH THE CURRENT DRAWING REVISION.




SCALE 3:1
HSD VERSION SHOWN



SCALE 3:1
LC VERSION SHOWN



Copyright FCI.

spec ref	GS-12-588, GS-20-121			dr	Jim Swain		2010/03/23		projection		MM		size	A2		scale	4:1									
tolerance std	TOLERANCES UNLESS OTHERWISE SPECIFIED			eng	Matthew Cheong		2014/04/04						ecn no		ELX-S-17348-1											
ASME Y14.5				chr	-		-																			
appr				Chen-Hong Tan		2014/04/08		product family											XCede		rel level		Released			
surface		linear	0.X	±0.2				title	RECEPT MODULE, RIGHT ANGLE 8-COLUMN, 6-PAIR						dwg no	10105010				rev	B					
ASME Y14.5			0.XX	±0.13																						
			0.XXX	±-																						
	angular	0°	±3°		www.fci.com		cat. no. SEE PART NUMBER TABLE		Product - Customer Drw						sheet 5 of 5											

PDS: Rev :B

STATUS:Released

Printed: Apr 09, 2014

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[FCI / Amphenol:](#)

[10105010-107LF](#) [10105010-108LF](#) [10105010-105LF](#) [10105010-101LF](#) [10105010-104LF](#) [10105010-102LF](#)
[10105010-103LF](#) [10105010-106LF](#)