




CATALOGUE

NMEA 2000 Connector

Range Overview




About NMEA 2000


Amphenol LTW Technology expands its coverage targeting the marine industry that features the NMEA 2000 standard.

The NMEA 2000 standard contains the requirements of a serial data communications network to inter-connect marine electronic equipment on


vessels. It is multi-master and self-configuring, and there is no central network controller. Equipment designed to this standard will have the ability to share data, including commands and status with other compatible equipment over a status with other compatible equipment over a single channel.




> Items (Mini to Micro)




> Items for devices



> Items for power source



> More Selection



【Note】 Design and specification are subject to change without notice.

Specification

Identifications	Micro (AWG: 22 AWG, 24 AWG) Mini (AWG: 18 AWG, 15AWG)
Description	Micro: Bulkhead (With Wire / Double-ended / Right Angle) Cable (Drop Line / Double-ended Cordset / T-Cable) Field Installable Network Terminator (Single-ended / In-line) Adaptor (T-Adaptor / Elbow) Multi-port Waterproof Cap Mini: Bulkhead (Double-ended) Cable (Drop Line / Double-ended Cordset / T-Cable) Field Installable Network Terminator (Single-ended) Adaptor (T-Adaptor / Elbow) Power Tap Tee Waterproof Cap Mini to Micro: Adaptor (T-Adaptor / I-Adaptor)
Current Rating / Data	Micro: 4A Mini: 8A
Material	Contacts: Copper Alloy, Gold Plated Contacts Holder: PA
Waterproof Rating	IP67~68
Temperature Range	Receptacle: -40°C ~ 85°C Overmolded with Cable: -20°C ~ 80°C Field Installable: Nylon+GF: -40°C ~ 105°C PU: -20°C ~ 85°C * Higer working temperature upon request.

Contact Configuration

	Micro-C	Mini-C
	4A	8A
	FF or MM	FF or MM
4Pin		
5Pin		

4A 8A	Number of Contacts: e.g. 2 contacts (02)
Connector (Housing) Gender: Male(M) or Female(F)	Contact Gender: Male(M) or Female(F)

More to Choose:

- Solder (S)
- Solder Cup



- Screw In (B)



Cabling Information

Micro

NMEA Approved


(A): (24#*1P+AL) + (22#*1P+AL) + Drain + Mylar + Braid

(B): (16#*1P+AL) + (20#*1P+AL) + D + AL + Braid

Conforming

(A): (24#*1P+AL) + (22#*1P+AL) + Drain + AL + Braid

(B): (22#*1P+AL) + (18#*1P+AL) + Drain + AL + Braid




Mini

NMEA Approved

(C): (18#*1P+AL) + (15#*1P+AL) + Drain + Braid

Conforming


(C): (18#*1P+AL) + (16#*1P+AL) + Drain + AL+Braid







【Note】 Design and specification are subject to change without notice.

Find Our Standard Products













Micro > Bulkhead (Double-ended)

• 5 Contacts • Screw Thread • Unmated IP68			
Type	Connector	Part Number (Female Connector / Female Contacts)	
Certified NMEA 2000 (4A, 60V)		UMC-000505-0FM-BS001	
None-Certified NMEA 2000 (4A, 60V)		MC-000505-0FM-BS001	

Micro > Bulkhead (Straight) > PCB Type

• 5 Contacts • Screw Thread • For Device Side • PCB Pin (180°) • Unmated IP68		Metal  Plastic 		Metal  Plastic 	
Type	Connector	Part Number (Male Connector / Male Contacts)		Part Number (Female Connector / Female Contacts)	
Certified NMEA 2000 (4A, 60V)	Metal	HMC-05PMMP-SF8001		HMC-05PFFP-SF8001	
	Plastic	HPC-05PMMP-SF8001		HPC-05PFFP-SF8001	



Micro > Bulkhead (Straight) > Solder Type

• 5 Contacts • Screw Thread • For Device Side • Solder Pin (180°) • Unmated IP68		Certified Metal  Maximum Panel Thickness: 4.5mm  OD: 15.4 13.6		Certified Metal  Maximum Panel Thickness: 4.5mm  OD: 15.4 13.6	
		Plastic   OD: 15.4 13.6		Plastic   OD: 15.4 13.6	
		None-Certified  Male: 25.9 Female: 22.9 Male: 20.5 Female: 20.0  OD: 15.4 13.6 18 (Hexagon)		None-Certified  Male: 24.5 Female: 28.0 Male: 22.0 Female: 22.6  OD: 15.4 13.6 18 (Hexagon)	
		Unit: mm			
Connector		Part Number (Male Connector / Male Contacts)		Part Number (Female Connector / Female Contacts)	
Certified NMEA 2000 (4A, 60V)	Metal	HMC-05PMMS-SF8001		HMC-05PFFS-SF8001	
	Plastic	HPC-05PMMS-SF8001		HPC-05PFFS-SF8001	
None-Certified NMEA 2000 (4A, 60V)	Metal	MC-05PMMS-S 8 8001		MC-05PFFS-S 8 8001	



8 Front Fastened (F) or Rear Fastened (H)

【Note】 Design and specification are subject to change without notice.

Micro > Bulkhead (Right Angle)


• 5 Contacts • Screw Thread • For device side • Unmated IP68 / Mated IP67		* IP 68 (Unmated) Male (29.5) Female (29.0) Male (20.5) Female (20.0) 	* IP 67 (Mated) Male (24.8) Female (25.5) Male (16.2) Female (16.9)  Unit: mm
Type	Connector	Part Number (Male Connector / Male Contacts)	Part Number (Female Connector / Female Contacts)
None - Certified NMEA 2000 (4A, 60V)	Metal	12-05PMMR-SF7001	12-05PMMR-SF7001
		12-05PMMR-SF8001	12-05PMMR-SF8001
	Plastic	12P-05PMMR-SF8001	12P-05PMMR-SF8001

Micro > Cable > Drop Line

• 5 Contacts • Screw Thread • For Power Tap Connection • Mated IP68 • Current Rating - Connector: 4A - Cable: 3A			 Unit: mm
Type	Connector	Part Number (Male Connector / Male Contacts)	Part Number (Female Connector / Female Contacts)
Certified NMEA 2000 (3A, 60V)	Metal	HMC-05BMMM-SL8A <u>XX</u> *	HMC-05BFFM-SL8A <u>XX</u> *
		UMC-05BMMM-SL8A <u>XX</u> *	-
	Plastic	HPC-05BMMM-SL8A <u>XX</u> *	HPC-05BFFM-SL8A <u>XX</u> *
None - Certified NMEA 2000 (3A, 60V)	Metal	MC-05BMMM-SL8A <u>XX</u> *	MC-05BFFM-SL8A <u>XX</u> *
		MC-05BMMM-SL8B <u>XX</u> *	MC-05BFFM-SL8B <u>XX</u> *
	Plastic	MCP-05BMMM-SL8A <u>XX</u> *	MCP-05BFFM-SL8A <u>XX</u> *
		MCP-05BMMM-SL8B <u>XX</u> *	MCP-05BFFM-SL8B <u>XX</u> *


*XX: Cable length available in 1M (01), 2M (02), 5M (05), 10M (10).

Micro > Power Cable

• 5 Contacts • Screw Thread • For Powering NMEA 2000 Network System • Mated IP68 • Current Rating - Connector: 4A - Cable: 3A (With 3A Fuse)			
Unit: mm			
Type	Connector	Part Number (Male Connector / Male Contacts)	
Certified NMEA 2000 (3A, 60V)		HPC-05CMMM-SL8A <u>XX</u> *	

*XX: Cable length available in 1M (01), 2M (02), 5M (05), 10M (10).

Micro > Cable > Double-ended Cordset

• 5 contacts • Screw Thread • For Power Tap Connection • Mated IP68 • Current Rating - Connector: 4A - Cable: 3A		 *Available in 1, 2, 5, 10 M *Cable 22+24+B PVC					
Connector		End 1	End 2	End 1	End 2	End 1	End 2
		Male		Female		Male	Female
Type	Metal	-		-		HMC-000505-0MF-CS <u>XX</u> *	
						UMC-000505-0MF-CS <u>XX</u> *	
	Plastic	-		-		HPC-000505-0MF-CS <u>XX</u> *	
None - Certified NMEA 2000 (3A, 60V)	Metal	MC-000505-0MM-C <u>XX</u> *		MC-000505-0FF-C <u>XX</u> *		MC-000505-0MF-CS <u>XX</u> *	
	Plastic	PC-000505-0MM-C <u>XX</u> *		PC-000505-0FF-C <u>XX</u> *		PC-000505-0MF-CS <u>XX</u> *	

*XX: Cable length available in 1 (01), 2 (02), 5 (05), 10 (10)M.

【Note】 Design and specification are subject to change without notice.

Micro > Power Cable (Double Ends)

• 5 Contacts • Screw Thread • For Powering NMEA 2000 Network System • Mated IP68 • Current Rating - Connector: 4A - Cable: 3A			
Type	Connector	End 1	End 2
		Male	Female
Certified NMEA 2000 (3A, 60V)	Plastic	HPC-000505-0MF-DSAXX*	



*XX: Cable length available in 1 (01), 2 (02), 5 (05), 10 (10)M.

Micro > Field Installable (Right Angle)

• 5 contacts • Screw Thread • Screw-in Contacts • Mated IP67			
Type	Connector	Part Number (Male Connector / Male Contacts)	Part Number (Female Connector / Female Contacts)
Certified NMEA 2000 (4A, 60V)	Metal	HMC-05BMMB-SR7001 (Ø4.5 ~ Ø6.0mm; 14AWG Max.)	HMC-05BFFB-SR7001 (Ø4.5 ~ Ø6.0mm; 14AWG Max.)
	Plastic	HPC-05BMMB-SR7001 (Ø4.5 ~ Ø6.0mm; 14AWG Max.)	HPC-05BFFB-SR7001 (Ø4.5 ~ Ø6.0mm; 14AWG Max.)
None - Certified NMEA 2000 (4A, 60V)	Metal	12-05BMMB-SR7001 (Ø4.5 ~ Ø6.0mm; 18AWG Max.)	12-05BFFB-SR7001 (Ø4.5 ~ Ø6.0mm; 18AWG Max.)
	Plastic	12P-05BMMB-SR7001 (Ø4.5 ~ Ø6.0mm; 18AWG Max.)	12P-05BFFB-SR7001 (Ø4.5 ~ Ø6.0mm; 18AWG Max.)




Unit: mm

Micro > Field Installable (Straight)

• 5 contacts • Screw Thread • Screw-in Contacts • Mated IP67			
		Unit: mm	
Type	Connector	Part Number (Male Connector / Male Contacts)	Part Number (Female Connector / Female Contacts)
Certified NMEA 2000 (4A, 60V)	Metal	UMC-05BMMB-SL7001 (Ø4.5 ~ Ø7.5mm; 18AWG Max.)	UMC-05BFFB-SL7001 (Ø4.5 ~ Ø7.5mm; 18AWG Max.)
		HMC-05BMMB-SL7001 (Ø4.5 ~ Ø6.0mm; 14AWG Max.)	HMC-05BFFB-SL7001 (Ø4.5 ~ Ø6.0mm; 14AWG Max.)
	Plastic	HPC-05BMMB-SL7001 (Ø4.5 ~ Ø6.0mm; 14AWG Max.)	HPC-05BFFB-SL7001 (Ø4.5 ~ Ø6.0mm; 14AWG Max.)
None - Certified NMEA 2000 (4A, 60V)	Metal	12-05BMMB-SL7001 (Ø4.5 ~ Ø6.0mm; 18AWG Max.)	12-05BFFB-SL7001 (Ø4.5 ~ Ø6.0mm; 18AWG Max.)
	Plastic	12P-05BMMB-SL7001 (Ø4.5 ~ Ø6.0mm; 18AWG Max.)	12P-05BFFB-SL7001 (Ø4.5 ~ Ø6.0mm; 18AWG Max.)



【Note】 Design and specification are subject to change without notice.

Micro > Cable > T-Cable



• 5 contacts • Screw Thread • For Power Tap Connection • Mated IP68 • Current Rating - Connector: 4A - Cable: 3A								Unit: mm	
Type \ Connector		End 1	End 2	End 1	End 2	End 1	End 2		
		Male		Female		Male	Female		
Certified NMEA 2000 (3A, 60V)	Metal	-		-		UMC-050500-FM0-TSAXX*			
	Plastic	-		-		HMC-050500-FM0-TSAXX*			
None - Certified NMEA 2000 (3A, 60V)	Metal	MC-050500-MM0-TSBXX*		MC-050500-FF0-TSBXX*		MC-050500-FM0-TSBXX*			
	Plastic	PC-050500-MM0-TSBXX*		PC-050500-FF0-TSBXX*		PC-050500-FM0-TSBXX*			

*XX: Cable length available in 1 (01), 2 (02), 5 (05), 10 (10)M.



Micro > Network Terminator > Terminator

• 5 contacts • Screw Thread • With 120Ω Resistor • Mated IP68						Unit: mm	
Type \ Connector		Part Number (Male Connector / Male Contacts)		Part Number (Female Connector / Female Contacts)			
Certified NMEA 2000 (3A, 60V)	Metal	HMC-05BMMT-SL8001		HMC-05BFFT-SL8001			
	Plastic	HMCP-05BMMT-SL8001		HMCP-05BFFT-SL8001			

Micro > Network Terminator > Terminator


• 5 contacts • Screw Thread • With 120Ω Resistor • Mated IP68					
Unit: mm					
Connector		Part Number (Male Connector / Male Contacts)		Part Number (Female Connector / Female Contacts)	
Type					
Certified NMEA 2000 (3A, 60V)	Metal	UMC-05BMMT-SL8001		UMC-05BFFT-SL8001	
None - Certified NMEA 2000 (3A, 60V)	Metal	MC-05BMMT-SL8001		MC-05BFFT-SL8001	
	Plastic	MCP-05BMMT-SL8001		MCP-05BFFT-SL8001	

Micro > Network Terminator > Terminator (In-Line)

• 5 contacts • Screw Thread • With 120Ω Resistor • Mated IP68					
Unit: mm					
Connector		End 1	End 2	End 1	End 2
Type		Male	Female	Male	Female
Certified NMEA 2000 (4A, 60V)	Metal	HMC-000505-0MF-IS001		—	
	Plastic	HPC-000505-0MF-IS001		—	
None - Certified NMEA 2000 (4A, 60V)	Metal	—		MC-000505-0MF-IS001	


【Note】 Design and specification are subject to change without notice.

Micro > Adaptor > T-Adaptor

• 5 contacts • Screw Thread • Mated IP68			
Connector Type		End 1 (Female Connector / Female Contacts)	
		End 2 (Male Connector / Male Contacts)	
		End 3 (Female Connector / Female Contacts)	
Certified NMEA 2000 (4A, 60V)	Metal	HMC-050505-FMF-TS001	
		UMC-050505-FMF-TS001	
	Plastic	HPC-050505-FMF-TS001	


Unit: mm

Micro > Adaptor > Elbow (L-Adaptor)

• 5 contacts • Screw Thread • Mated IP68			
Connector Type		Part Number (Male Connector / Male Contacts)	Part Number (Female Connector / Female Contacts)
Certified NMEA 2000 (4A, 60V)	Metal	HMC-000505-0FM-ES001	
	Plastic	HPC-000505-0FM-ES001	
None - Certified NMEA 2000 (4A, 60V)	Metal	MC-000505-0FM-ES001	


Unit: mm

Micro > Multi-port T-Adaptor

• 5 contacts • Screw Thread • Mated IP68			
Connector Type		End 1 (Female Connector / Female Contacts)	End 1 (Female Connector / Female Contacts)
		End 2 (Female Connector / Female Contacts)	End 2 (Female Connector / Female Contacts)
		End 3 (Female Connector / Female Contacts)	End 3 (Female Connector / Female Contacts)
		End 4 (Male Connector / Male Contacts)	End 4 (Female Connector / Female Contacts)
		-	End 5 (Female Connector / Female Contacts)
		-	End 6 (Male Connector / Male Contacts)
Certified NMEA 2000 (4A, 60V)	Metal	E-555500-FFFM00-S001	E-555555-FFFFFM-S001
	Plastic	P-555500-FFFM00-S001	P-555555-FFFFFM-S001
None - Certified NMEA 2000 (4A, 60V)	Metal	S-555500-FFFM00-S001	S-555500-FFFM00-S001



【Note】 Design and specification are subject to change without notice.

Micro > Multi-port > Box


• Unmated IP68			
		Unit: mm	
Type	Part Number		
None - Certified NMEA 2000 (4A, 30V)	S-555500-FFFF00-SB <u>XX</u> *		
Certified NMEA 2000 (4A, 30V)	E-555500-FFFF00-SA <u>XX</u> *		

* XX: Cable length available from 01 ~ 99m


Micro > Waterproof Cap

		* Plastic  * Metal  Unit: mm		
Size	Mating Pair	Mating Style	Mating Gender	Part Number
Micro	Receptacle	Screw Thread	Male	CAP-WBDMSPB2
	Receptacle and Overmolded with Cable		Male	CAP-WBDMSMA1 (Plastic)
			Male	CAP-WBDMSMA2 (Metal)
			Female	CAP-WBDFSMA1 (Plastic)
			Female	CAP-WBDFSMA2 (Metal)

Mini > Bulkhead (Double-ended)

• Unmated IP68	
	
Unit: mm	
Connector Type	Connector 1 (Female Connector / Female Contacts)
	Connector 2 (Male Connector / Male Contacts)
None - Certified NMEA 2000 (8A, 600V)	MN-000505-0FM-BS001
Certified NMEA 2000 (8A, 600V)	UMN-000505-0FM-BS001


Mini > Cable > Drop Line

• Mated IP68		
		
Unit: mm		
Type	Part Number (Male Connector / Male Contacts)	Part Number (Female Connector / Female Contacts)
None - Certified NMEA 2000 (8A, 30V)	MN-05AMMM-SL8CXX*	MN-05AFFM-SL8CXX*
Certified NMEA 2000 (8A, 600V)	UMN-05AMMM-SL8CXX*	-

*XX: Cable length available in 1 (01), 2 (02), 5 (05), 10 (10)M.



【Note】 Design and specification are subject to change without notice.

Mini > Cable > Double-ended Cordset

• Mated IP68		 * Available in 1, 2, 5, 10 M	
Connector Type	Connector	Connector 1 (Male Connector / Male Contacts)	
		Connector 2 (Female Connector / Female Contacts)	
None - Certified NMEA 2000 (8A, 30V)		MN-000505-0MF-CSCXX*	
Certified NMEA 2000 (8A, 600V)		UMN-000505-0MF-CSCXX*	


*XX: Cable length available in 1 (01), 2 (02), 5 (05), 10 (10)M.

Mini > Field Installable

• Screw-in Contacts • Mated IP68		* Conforming to NMEA  * NMEA approved  Unit: mm	
Type	Part Number (Male Connector / Male Contacts)	Part Number (Female Connector / Female Contacts)	
None - Certified NMEA 2000 (8A, 600V)	MN-05BMMB-SL7001	MN-05BFFB-SL7001	
Certified NMEA 2000 (8A, 600V)	UMN-05BMMB-SL7001	UMN-05BFFB-SL7001	

* Recommended Cable Information:
- None-Certified: Ø8 ~ Ø11mm; 15AWG Max.
- Certified NMEA 2000: Ø8 ~ Ø12.2mm; 15AWG Max.



Mini > T-Cable

• Mated IP68			
Connector Type		Connector 1 (Female Connector / Female Contacts)	
		Connector 2 (Male Connector / Male Contacts)	
None - Certified NMEA 2000 (8A, 30V)		MN-050500-FM0-TSCXX*	

Unit: mm

*XX: Cable length available in 1 (01), 2 (02), 5 (05), 10 (10)M.


Mini > Network Terminator

• With 120Ω Resistor • Mated IP68		* Conforming to NMEA * Signal function LED		* NMEA approved	
					
Type		Part Number (Male Connector / Male Contacts)		Part Number (Female Connector / Female Contacts)	
None - Certified NMEA 2000 (8A, 250V)		MNL-05BMMT-SL8001		MNL-05BFFT-SL8001	
Certified NMEA 2000 (8A, 250V)		UMN-05AMMT-SL8001		UMN-05AFFT-SL8001	


Unit: mm

【Note】 Design and specification are subject to change without notice.



Mini > T-Adaptor

• Mated IP68				Unit: mm
Connector Type	Connector 1 (Female Connector / Female Contacts)			
	Connector 2 (Male Connector / Male Contacts)			
	Connector 3 (Female Connector / Female Contacts)			
None-Certified NMEA 2000 (8A, 300V)		MN-050505-FMF-TS001		
Certified NMEA 2000 (8A, 300V)		UMN-050505-FMF-TS001		


Mini > Adaptor > Elbow (L-Adaptor)

• Mated IP68			
Connector Type		Connector 1 (Female Connector / Female Contacts)	
		Connector 2 (Male Connector / Male Contacts)	
None-Certified NMEA 2000 (8A, 300V)		MN-000505-OFM-ES001	

Mini > Power Tap Tee


• With replaceable fuse • Mated IP68			Recommended Mating Pair MN-04AFFM-SL8DXX Male (57.8) Female (58.0)  *XX: Cable length available in 1(01), 2(02), 5(05), 10(10)M. Unit: mm
Connector Type	Connector 1 (Male Connector / Male Contacts)		
	Connector 2 (Female Connector / Female Contacts)		
	Connector 3 (Female Connector / Female Contacts)		
None-Certified NMEA 2000 (8A, 250V)	N-455000-MFF000-S001		
Certified NMEA 2000 (8A, 250V)	U-455000-MFF000-S001		

Mini > Waterproof Cap


• 5 Contacts • Screw Thread • Mated IP68		Male (25.2) Female (25.4)  Unit: mm		
Size	Mating Pair	Mating Style	Mating Gender	Part Number
Mini	Receptacle and Overmolded with Cable	Screw Thread	Female	CAP-WMNMSMA1
			Male	CAP-WMNFSA1

【Note】 Design and specification are subject to change without notice.

Mini to Micro > T-Adaptor

• Mated IP68	
	
Unit: mm	
Connector Type	Connector 1 (Female Connector / Female Contacts)
	Connector 2 (Male Connector / Male Contacts)
	Connector 3 (Female Connector / Female Contacts)
None- Certified NMEA 2000 (4A, 60V)	NC-050505-FMF-TS001
Certified NMEA 2000 (4A, 60V)	UNC-050505-FMF-TS001

Mini to Micro > I-Adaptor

• Mated IP68	
	
Unit: mm	
Type	Part Number
None- Certified NMEA 2000 (4A, 60V)	NC-000505-0MF-IS001

Blank lined paper for writing.



Scan to visit our website

Amphenol LTW Technology Co., Ltd.

5F-3, No.51, Sec.4, Zhongyang Rd., Tucheng Dist., New Taipei City 236, Taiwan
Telephone: +886-2-77416888 Fax: +886-2-77416999
www.amphenolltw.com

Kunshan Factory

No. 62, DaTong Road, Development Zone, Kunshan City, JiangSu Province, 215333 China
Telephone: +86-512-5761-0501
Fax: : +86-512-5761-0515

For further information, please contact :

Sales & Marketing Department | Email : sales@ltw-tech.com

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[MN-000505-0MF-CSC01](#) [MN-000505-0MF-CSC02](#) [MN-000505-0MF-CSC05](#) [MN-000505-0MF-CSC10](#)