





REVISIONS			
REV	ECN, ERN NO.	DATE	APPRD.
C	PRODUCT DRAWING (EAR 14658)	MAY04/18	K.L.




TERMINATION-MTG. OPTION 030
.120 [3.05] DIA. THROUGH
HOLES (2 PLACES),
SEE ORDERING CODE.




TERMINATION-MTG. OPTION 130
VERTICAL MOUNT,
#4-40 UNC THREADED
THROUGH STANDOFFS




TERMINATION-MTG. OPTION 132
VERTICAL MOUNT,
#4-40 UNC STANDOFFS
WITH BOARDLOCKS



TERMINATION-MTG. OPTION 230
VERTICAL MOUNT, #4-40 UNC
HEX JACK SOCKETS,
STANDOFFS



TERMINATION-MTG. OPTION 232
VERTICAL MOUNT, #4-40 UNC
HEX JACK SOCKETS,
STANDOFFS WITH BOARDLOCKS



ORDERING CODE:

PART NUMBER: 1 7 E H D - 0 1 5 S X X - X 3 X

SERIES

NUMBER OF CONTACTS
015


STYLE
S=SOCKET

TERMINATION-MOUNTING OPTIONS

030=VERTICAL MOUNT, ϕ .120 [3.05] THROUGH HOLE
130=VERTICAL MOUNT, #4-40 UNC STANDOFFS
132=VERTICAL MOUNT, #4-40 UNC STANDOFFS
WITH BOARDLOCKS
230=VERTICAL MOUNT, #4-40 UNC HEX JACK
SOCKETS, STANDOFFS
232=VERTICAL MOUNT, #4-40 UNC HEX JACK
SOCKETS, STANDOFFS WITH BOARDLOCKS

CONTACT PLATING OPTIONS

AA=ENGAGEMENT AREA 3μ " [0.08 MICRONS] GOLD FLASH
CH=ENGAGEMENT AREA 15μ " [0.38 MICRONS] GOLD
AM=ENGAGEMENT AREA 30μ " [0.76 MICRONS] GOLD



RECOMMENDED P.C.B. LAYOUT
(COMPONENT SIDE OF BOARD)

SPECIFICATIONS:

MATERIALS: ALL MATERIALS ARE RoHS COMPLIANT

SHELL: STEEL, NICKEL PLATED

INSERTS: HIGH TEMPERATURE RESISTANT NYLON, GLASS
REINFORCED, UL FLAMMABILITY RATING
94V-0, COLOUR: BLACK

CONTACTS: COPPER ALLOY, GOLD PLATING (SEE ORDERING CODE) OVER
50u" [1.27 MICRONS] NICKEL ON ENGAGEMENT AREA WITH
100u" [2.54 MICRONS] MIN. MATTE TIN ON CONTACT
TERMINALS.

BOARDLOCK: COPPER ALLOY, TIN PLATED

ELECTRICAL DATA:

CURRENT RATING: 3 AMP

CONTACT RESISTANCE: 15 MILLIOHMS MAX.

INSULATION RESISTANCE: 3000 MEGOHMS MIN.

DIELECTRIC
WITHSTANDING VOLTAGE: 1000 VAC rms

OPERATING TEMPERATURE: -55°C TO +105°C

DRAWN	E.CHEN	DATE	JUN27/06
DESIGNED			
CHECKED	K.LAMBIE	JUL26/06	
I. E. APPRD.			
Q. A. APPRD.			
DWG. APPRD.			
ENG. REL. NO.			
REF.	EAR 12956		
DIMENSIONS ARE IN	CODE ID. NO.		
INCHES	03554		

Amphenol Canada Corp.

TITLE 17EHD SERIES HIGH DENSITY D-SUB
CONNECTOR, 15 SIZE SOCKET, VERTICAL PCB
MOUNT CONTACTS, PLATING & MOUNTING
OPTIONS, RoHS COMPLIANT

DWG	DRAWING NO.	REV.
C	P-17EHD-015SXX-X3X	C
SCALE	2/1	WT. -----
SURF.	-----	SHEET 1 OF 1

THIS DOCUMENT CONTAINS PROPRIETARY INFORMATION AND SUCH INFORMATION
MAY NOT BE DISCLOSED TO OTHERS FOR ANY PURPOSE OR USED FOR MANUFACTURING
PURPOSES WITHOUT WRITTEN PERMISSION FROM AMPHENOL CANADA CORP.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

<u>17EHD015SAA030</u>	<u>17EHD015SAA130</u>	<u>17EHD015SAA132</u>	<u>17EHD015SAA230</u>	<u>17EHD015SAA232</u>
<u>17EHD015SAM030</u>	<u>17EHD015SAM130</u>	<u>17EHD015SAM132</u>	<u>17EHD015SAM230</u>	<u>17EHD015SAM232</u>